

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P761033

Luminaire Tested: LD6D15D010-EU6DR2015309027-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P761033  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D15D010-EU6DR2015309027-6LBDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1505.0 lumens  
Efficiency: N/A  
Efficacy: 95.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P761033

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P761033

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  |  | 100 | 99  | 97  |  | 98  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 95  |
| 4   | 105 | 99  | 96  | 93  | 103 | 98  | 95  | 92  | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 93  |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  |  | 92  | 89  | 87  |  | 91  |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 87  | 85  |  | 90  | 87  | 84  |  | 88  |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  |  | 87  | 84  | 82  |  | 86  |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  |  | 85  | 82  | 80  |  | 84  |
| 9   | 91  | 85  | 81  | 78  | 91  | 85  | 81  | 78  | 84  | 80  | 78  |  | 83  | 80  | 78  |  | 82  |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 79  | 76  | 82  | 78  | 76  |  | 81  | 78  | 76  |  | 81  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 935884 |
| 5°  | 844346 |
| 10° | 473896 |
| 15° | 240890 |
| 20° | 101995 |
| 25° | 47077  |
| 30° | 24930  |
| 35° | 13432  |
| 40° | 7174   |
| 45° | 4249   |
| 50° | 2465   |
| 55° | 1314   |
| 60° | 830    |
| 65° | 595    |
| 70° | 256    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4249 cd/sqm

TEST NUMBER: P761033

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 609.9  | 40.5      |
| 10°-20°   | 600.5  | 39.9      |
| 20°-30°   | 196.2  | 13.0      |
| 30°-40°   | 66.8   | 4.4       |
| 40°-50°   | 22.5   | 1.5       |
| 50°-60°   | 6.8    | 0.4       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1406.6 | 93.5      |
| 0°-40°    | 1473.4 | 97.9      |
| 0°-60°    | 1502.6 | 99.8      |
| 0°-90°    | 1505.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1505.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8566 |      |
| 5°  | 7698 | 610  |
| 15° | 2130 | 601  |
| 25° | 390  | 196  |
| 35° | 101  | 67   |
| 45° | 28   | 22   |
| 55° | 7    | 7    |
| 65° | 2    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P761033

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 8565.6 |
| 0.5°  | 8565.6 |
| 1°    | 8554.9 |
| 1.5°  | 8533.6 |
| 2°    | 8494.7 |
| 2.5°  | 8442.8 |
| 3°    | 8369.6 |
| 3.5°  | 8267.4 |
| 4°    | 8115.6 |
| 4.5°  | 7931.0 |
| 5°    | 7698.4 |
| 5.5°  | 7392.5 |
| 6°    | 7079.0 |
| 6.5°  | 6719.8 |
| 7°    | 6368.2 |
| 7.5°  | 5956.3 |
| 8°    | 5588.6 |
| 8.5°  | 5218.7 |
| 9°    | 4877.0 |
| 9.5°  | 4563.5 |
| 10°   | 4271.4 |
| 12.5° | 3067.0 |
| 15°   | 2129.6 |
| 17.5° | 1391.2 |
| 20°   | 877.2  |
| 22.5° | 568.2  |
| 25°   | 390.5  |
| 27.5° | 274.6  |
| 30°   | 197.6  |
| 32.5° | 141.9  |
| 35°   | 100.7  |
| 37.5° | 70.2   |
| 40°   | 50.3   |
| 42.5° | 36.6   |
| 45°   | 27.5   |
| 47.5° | 21.4   |
| 50°   | 14.5   |
| 52.5° | 9.2    |
| 55°   | 6.9    |
| 57.5° | 5.3    |
| 60°   | 3.8    |
| 62.5° | 3.1    |
| 65°   | 2.3    |



TEST NUMBER: P761033

CATALOG NUMBER: LD6D15D010-EU6DR2015309027-6LBDP1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







|       |     |
|-------|-----|
| 67.5° | 1.5 |
| 70°   | 0.8 |



(END OF REPORT)