

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760921

Luminaire Tested: LD6D15D010-EU6DR1015209040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR1015209040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1578.7 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760921

CATALOG NUMBER: LD6D15D010-EU6DR1015209040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P760921

CATALOG NUMBER: LD6D15D010-EU6DR1015209040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100			
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98	98	98	98			
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97	97	97	97			
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95	95	95	95			
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94	94	94	94			
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93	93	93	93			
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91	91	91	91			
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90	90	90	90			
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89	89	89	89			
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88	88	88	88			
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87	87	87	87			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3755860
5°	1781019
10°	365257
15°	100276
20°	40416
25°	21652
30°	12806
35°	8336
40°	5577
45°	3616
50°	1989
55°	1486
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3616 cd/sqm



TEST NUMBER: P760921

CATALOG NUMBER: LD6D15D010-EU6DR1015209040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1122.6	71.1
10°-20°	303.8	19.2
20°-30°	87.0	5.5
30°-40°	39.7	2.5
40°-50°	18.2	1.2
50°-60°	6.1	0.4
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1513.3	95.9
0°-40°	1553.1	98.4
0°-60°	1577.3	99.9
0°-90°	1578.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1578.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	34375	
5°	16239	###
15°	886	304
25°	180	87
35°	62	40
45°	23	18
55°	8	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P760921

CATALOG NUMBER: LD6D15D010-EU6DR1015209040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	34375.2
0.5°	34078.4
1°	33316.8
1.5°	31848.4
2°	30204.2
2.5°	28032.8
3°	25619.3
3.5°	23283.9
4°	20764.9
4.5°	18445.1
5°	16238.6
5.5°	14239.0
6°	12333.2
6.5°	10657.8
7°	9080.0
7.5°	7732.7
8°	6537.6
8.5°	5491.0
9°	4584.9
9.5°	3893.7
10°	3292.2
12.5°	1570.0
15°	886.5
17.5°	538.9
20°	347.6
22.5°	242.1
25°	179.6
27.5°	132.8
30°	101.5
32.5°	78.1
35°	62.5
37.5°	46.9
40°	39.1
42.5°	31.2
45°	23.4
47.5°	15.6
50°	11.7
52.5°	7.8
55°	7.8
57.5°	3.9
60°	3.9
62.5°	3.9
65°	0.0



TEST NUMBER: P760921

CATALOG NUMBER: LD6D15D010-EU6DR1015209040-6LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







67.5°	0.0
70°	0.0



(END OF REPORT)