

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192174

Luminaire Tested: **LDA6A40927D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192174
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40927D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3848.6 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	32333	32333	32333
5°	85235	29452	10136
10°	172219	22929	6162
15°	317113	17185	8888
20°	491635	13745	14806
25°	577231	12194	18799
30°	625900	12261	14566
35°	659969	7301	7837
40°	676925	3113	3392
45°	634174	1225	1163
50°	443423	537	273
55°	155588	535	0
60°	31379	614	0
65°	1946	726	0
70°	385	1010	0
75°	0	1334	0
80°	0	1989	253
85°	0	4466	503



TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	2.0
10°-20°	422.0	11.0
20°-30°	997.4	25.9
30°-40°	1215.1	31.6
40°-50°	903.8	23.5
50°-60°	218.8	5.7
60°-70°	8.1	0.2
70°-80°	3.9	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.0	38.8
0°-40°	2710.1	70.4
0°-60°	3832.8	99.6
0°-90°	3848.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3848.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	590	590	590	590	590	
5°	1549	1158	535	250	184	194
15°	5588	2422	303	139	157	1684
25°	9543	3037	202	293	311	4382
35°	9862	2218	109	119	117	6142
45°	8180	845	16	17	15	6008
55°	1628	18	6	4	0	1842
65°	15	4	6	4	0	50
75°	0	4	6	5	0	0
85°	0	4	7	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8
2.5°	1028.6	1011.2	1009.6	992.3	985.9	983.5	959.0	950.4	917.9	911.6	865.7
5°	1548.9	1521.9	1516.5	1476.9	1447.7	1407.3	1385.9	1349.6	1272.9	1232.6	1158.3
7.5°	2203.5	2167.9	2160.0	2098.3	2037.5	1984.5	1940.2	1855.6	1714.9	1618.4	1466.6
10°	3093.8	2994.2	2957.8	2827.3	2701.6	2602.8	2551.4	2365.5	2153.7	2024.0	1812.1
12.5°	4224.4	4058.3	3990.3	3788.7	3567.4	3405.2	3305.7	3013.9	2669.2	2420.9	2118.2
15°	5587.5	5394.5	5272.8	5018.9	4616.5	4385.7	4209.4	3742.1	3239.2	2863.6	2421.7
17.5°	7071.4	6920.4	6738.6	6340.9	5692.6	5415.1	5094.8	4482.2	3792.6	3270.1	2692.9
20°	8427.3	8174.4	8037.6	7594.8	6843.7	6477.7	6083.2	5165.2	4282.1	3601.3	2900.9
22.5°	9161.9	8916.8	8834.6	8450.3	7761.7	7354.5	6852.4	5766.9	4657.7	3828.2	3011.6
25°	9543.0	9319.2	9324.8	8977.7	8356.3	7973.6	7462.9	6221.6	4913.8	3947.7	3036.9
27.5°	9841.1	9565.9	9517.6	9258.3	8705.7	8314.3	7821.8	6469.0	5007.9	3935.0	2968.0
30°	9887.7	9662.4	9697.2	9336.6	8832.2	8425.0	7912.7	6455.6	4911.4	3776.1	2789.4
32.5°	9856.1	9632.3	9712.2	9320.9	8777.6	8331.0	7760.9	6193.1	4628.3	3482.0	2526.8
35°	9861.6	9604.7	9545.3	9214.1	8567.4	8043.1	7355.3	5713.9	4210.2	3099.3	2217.7
37.5°	9743.9	9397.5	9407.8	8971.3	8160.9	7465.9	6687.2	5075.1	3715.2	2690.5	1907.0
40°	9459.2	9199.9	9117.6	8469.3	7387.7	6573.4	5822.2	4380.9	3142.8	2263.6	1542.5
42.5°	9053.6	8741.3	8500.2	7601.9	6291.9	5544.7	4895.6	3657.5	2601.9	1855.6	1197.8
45°	8180.0	7842.3	7375.0	6297.5	5188.1	4539.9	3998.3	2968.9	2104.7	1434.2	845.2
47.5°	6710.9	6393.9	5913.2	5007.9	4142.2	3602.1	3180.0	2325.2	1538.6	904.5	419.1
50°	5199.3	4958.1	4591.2	3805.3	3081.9	2576.6	2200.3	1460.3	785.1	412.7	175.5
52.5°	3388.7	3217.9	2891.3	2293.6	1741.8	1365.5	1110.0	621.4	370.0	173.9	51.4
55°	1627.9	1539.4	1302.9	944.8	683.9	561.4	474.4	301.2	139.9	41.9	18.2
57.5°	649.1	630.2	561.4	423.0	324.1	275.2	213.5	83.0	27.7	17.4	11.1
60°	286.2	277.5	232.5	154.2	83.0	47.4	34.8	20.6	13.5	10.3	7.1
62.5°	41.1	38.0	32.4	25.3	20.6	17.4	15.0	11.1	7.1	5.6	4.7
65°	15.0	15.0	13.5	11.1	9.5	8.7	7.9	5.6	3.9	3.9	3.9
67.5°	6.3	6.3	6.3	4.7	4.7	3.9	3.2	3.2	3.2	3.2	3.9
70°	2.4	2.4	2.4	1.5	1.5	1.5	2.4	2.4	2.4	3.2	3.9
72.5°	0.0	0.8	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.9
75°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	2.4	3.2	3.9
77.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
80°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
82.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.9	3.9
85°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.2	3.9
87.5°	0.0	0.0	0.8	0.8	1.5	1.5	1.5	2.4	3.2	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8
2.5°	827.0	815.9	778.8	741.6	736.1	720.3	687.9	649.9	600.9	570.1	539.2
5°	1061.8	1006.5	944.0	872.1	849.9	818.3	750.3	677.6	596.1	535.2	478.3
7.5°	1336.2	1212.8	1095.0	979.6	936.1	887.1	783.5	679.1	567.7	479.2	408.0
10°	1593.1	1403.4	1220.7	1057.1	992.3	925.8	786.7	652.3	513.9	411.9	339.2
12.5°	1849.3	1577.3	1327.5	1113.2	1025.5	940.1	769.2	604.0	447.5	350.3	291.7
15°	2050.9	1734.7	1405.0	1141.6	1032.6	928.2	726.6	537.6	382.7	302.8	250.6
17.5°	2190.9	1824.8	1434.2	1129.8	1004.9	887.1	659.4	460.1	330.5	265.6	215.1
20°	2287.3	1853.3	1413.6	1080.8	945.6	815.9	574.8	390.6	293.3	235.6	185.1
22.5°	2314.2	1825.6	1355.2	1007.3	868.1	734.5	487.1	344.7	266.4	211.9	179.5
25°	2288.1	1755.2	1267.4	919.5	773.3	633.3	413.5	317.0	245.9	201.6	208.7
27.5°	2193.2	1631.1	1145.6	806.5	656.2	524.2	363.7	283.8	216.6	212.7	221.4
30°	2036.7	1453.2	1000.9	661.7	518.7	418.3	305.2	223.7	189.8	193.7	199.3
32.5°	1811.3	1234.9	815.1	490.2	380.3	314.7	218.2	154.9	150.2	153.4	157.4
35°	1526.8	1004.9	610.4	338.4	269.6	216.6	128.1	109.9	107.5	109.1	110.7
37.5°	1238.9	776.4	415.1	227.7	163.7	109.9	76.7	71.9	70.4	71.2	71.9
40°	961.4	540.0	260.9	109.1	64.1	54.5	47.4	45.1	43.5	43.5	44.2
42.5°	702.1	320.2	129.6	42.7	34.8	32.4	28.5	26.8	25.3	26.1	26.8
45°	393.0	142.3	44.2	23.8	21.4	19.8	17.4	16.6	15.8	15.8	15.8
47.5°	167.6	49.8	21.4	15.0	13.5	12.7	11.1	10.3	9.5	9.5	9.5
50°	55.3	19.8	13.5	10.3	8.7	7.9	7.1	6.3	6.3	6.3	7.1
52.5°	19.8	12.7	8.7	7.1	6.3	6.3	5.6	5.6	5.6	5.6	5.6
55°	11.8	8.7	6.3	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
57.5°	7.9	5.6	5.6	4.7	4.7	4.7	4.7	4.7	4.7	5.6	5.6
60°	5.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	5.6	5.6
62.5°	4.7	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6
65°	3.9	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6
67.5°	3.9	3.9	4.7	4.7	4.7	4.7	5.6	5.6	5.6	5.6	6.3
70°	3.9	3.9	4.7	4.7	4.7	5.6	5.6	5.6	5.6	6.3	6.3
72.5°	3.9	4.7	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3
75°	3.9	4.7	4.7	5.6	5.6	5.6	5.6	6.3	6.3	6.3	6.3
77.5°	3.9	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3	6.3
80°	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3	6.3	7.1
82.5°	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3	6.3	7.1
85°	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3	7.1	7.1
87.5°	4.7	4.7	5.6	5.6	5.6	6.3	6.3	6.3	6.3	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8
2.5°	507.6	483.9	450.7	439.6	416.6	400.1	381.8	361.3	357.4	336.8	334.4
5°	423.0	385.0	347.1	332.9	313.1	296.5	278.3	258.5	249.9	230.1	218.2
7.5°	348.6	312.3	278.3	264.1	245.1	223.7	202.4	181.9	169.9	151.0	141.5
10°	292.6	256.1	219.8	205.5	188.1	164.5	141.5	120.1	112.2	107.5	108.3
12.5°	244.3	207.9	171.6	155.7	137.5	118.6	117.8	116.2	119.4	118.6	119.4
15°	204.8	166.0	131.3	126.5	126.5	129.6	132.8	133.6	139.2	139.2	140.7
17.5°	168.4	141.5	143.1	143.1	146.3	151.8	158.1	161.3	169.9	170.8	173.9
20°	156.6	162.8	169.9	171.6	177.1	185.8	194.5	200.8	211.9	215.1	221.4
22.5°	185.8	196.9	207.9	211.1	218.2	230.8	246.7	252.2	265.6	265.6	274.3
25°	219.0	235.6	246.7	250.6	258.5	269.6	279.9	283.1	292.6	289.4	292.6
27.5°	232.5	244.3	251.4	255.4	257.0	266.4	271.2	269.6	275.9	271.2	271.2
30°	206.4	215.1	219.0	221.4	221.4	228.5	228.5	226.1	230.1	226.1	223.7
32.5°	162.1	168.4	171.6	171.6	170.8	175.5	173.9	170.8	172.4	169.9	164.5
35°	113.1	117.8	120.1	119.4	118.6	122.5	120.1	117.8	118.6	117.1	113.1
37.5°	74.3	75.1	76.7	78.3	77.5	80.6	79.1	77.5	78.3	76.7	74.3
40°	45.1	46.6	48.2	48.2	48.2	49.1	49.1	48.2	49.8	48.2	46.6
42.5°	26.8	28.5	28.5	28.5	29.2	29.2	30.0	28.5	30.0	28.5	27.7
45°	16.6	16.6	16.6	17.4	16.6	17.4	17.4	16.6	17.4	16.6	15.8
47.5°	10.3	10.3	10.3	10.3	10.3	10.3	10.3	9.5	10.3	9.5	8.7
50°	6.3	7.1	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7
52.5°	5.6	5.6	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.2	3.2
55°	5.6	5.6	5.6	4.7	4.7	4.7	4.7	3.9	3.9	3.2	2.4
57.5°	5.6	5.6	4.7	4.7	4.7	4.7	3.9	3.9	3.2	2.4	2.4
60°	5.6	5.6	5.6	4.7	4.7	4.7	3.9	3.9	3.2	2.4	2.4
62.5°	5.6	5.6	5.6	4.7	4.7	4.7	4.7	3.9	3.2	2.4	2.4
65°	5.6	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.9	3.2	2.4
67.5°	6.3	5.6	5.6	5.6	5.6	5.6	4.7	3.9	3.9	3.2	2.4
70°	6.3	6.3	5.6	5.6	5.6	5.6	4.7	4.7	3.9	3.2	2.4
72.5°	6.3	6.3	6.3	6.3	5.6	5.6	5.6	4.7	3.9	3.2	3.2
75°	6.3	6.3	6.3	6.3	6.3	5.6	5.6	4.7	4.7	3.9	3.2
77.5°	7.1	6.3	6.3	6.3	6.3	6.3	5.6	4.7	4.7	3.9	3.2
80°	7.1	7.1	6.3	6.3	6.3	6.3	5.6	4.7	4.7	3.9	3.2
82.5°	7.1	7.1	6.3	6.3	6.3	6.3	5.6	5.6	4.7	3.9	3.2
85°	7.1	7.1	6.3	6.3	6.3	6.3	5.6	4.7	4.7	3.9	3.2
87.5°	7.1	7.1	6.3	6.3	6.3	6.3	5.6	4.7	4.7	3.9	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192174

CATALOG NUMBER: LDA6A40927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	589.8	589.8	589.8	589.8	589.8	589.8	589.8	589.8
2.5°	320.2	318.6	313.1	314.7	310.8	302.0	302.8	299.7
5°	210.3	205.5	200.1	200.1	194.5	186.6	186.6	184.2
7.5°	128.1	121.0	115.4	114.6	109.1	105.1	105.1	104.4
10°	108.3	109.1	109.1	109.9	109.1	109.1	109.9	110.7
12.5°	121.8	124.2	124.2	124.9	124.2	125.7	125.7	127.2
15°	145.5	149.5	150.2	151.8	151.0	153.4	154.9	156.6
17.5°	182.6	187.4	189.0	193.7	192.9	195.2	196.9	200.1
20°	230.1	237.2	239.6	245.9	245.1	247.5	251.4	253.8
22.5°	283.1	291.7	292.6	298.1	297.3	299.7	301.2	302.0
25°	297.3	302.8	302.0	305.2	305.2	305.9	305.9	310.8
27.5°	272.0	275.9	275.9	275.9	276.7	277.5	277.5	281.4
30°	223.7	225.3	226.1	223.7	225.3	226.1	226.1	230.1
32.5°	166.0	166.9	167.6	164.5	166.9	166.9	166.9	169.9
35°	114.6	114.6	115.4	113.1	114.6	115.4	114.6	117.1
37.5°	75.1	75.1	75.1	75.1	75.1	75.1	74.3	76.7
40°	46.6	47.4	46.6	46.6	45.9	45.9	45.9	47.4
42.5°	27.7	27.7	26.8	26.8	26.8	26.8	27.7	27.7
45°	15.8	15.8	15.0	15.0	14.2	15.0	15.0	15.0
47.5°	8.7	7.9	7.9	7.9	7.1	7.1	7.1	7.9
50°	3.9	3.9	3.9	3.2	3.2	3.2	2.4	3.2
52.5°	2.4	1.5	1.5	1.5	0.8	0.8	0.0	0.8
55°	1.5	1.5	0.8	0.8	0.0	0.0	0.0	0.0
57.5°	1.5	0.8	0.8	0.8	0.0	0.0	0.0	0.0
60°	1.5	0.8	0.8	0.8	0.0	0.0	0.0	0.0
62.5°	1.5	0.8	0.8	0.8	0.0	0.0	0.0	0.0
65°	1.5	0.8	0.8	0.8	0.0	0.0	0.0	0.0
67.5°	1.5	1.5	0.8	0.8	0.8	0.0	0.0	0.0
70°	2.4	1.5	1.5	0.8	0.8	0.0	0.0	0.0
72.5°	2.4	1.5	1.5	1.5	0.8	0.8	0.0	0.0
75°	2.4	1.5	1.5	1.5	0.8	0.8	0.0	0.0
77.5°	2.4	2.4	1.5	1.5	0.8	0.8	0.8	0.8
80°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
82.5°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
85°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
87.5°	2.4	2.4	1.5	1.5	1.5	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)