

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192186

Luminaire Tested: **LDA6A40930D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26670)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3724.6 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.6 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83		
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	75		
4	92	84	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67		
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	61		
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55		
7	76	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49		
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	43	51	46	42	41		
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65346	65346	65346
5°	125759	62602	23448
10°	208018	54942	8433
15°	307107	44331	13445
20°	445927	28230	22758
25°	640591	24661	27594
30°	725542	21358	20079
35°	725607	11089	10306
40°	586062	4136	4315
45°	438852	1427	1558
50°	287291	571	503
55°	33757	478	76
60°	1020	548	0
65°	208	649	0
70°	128	801	0
75°	0	1250	0
80°	0	1863	253
85°	0	3711	503

TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.0	3.3
10°-20°	498.3	13.4
20°-30°	1093.4	29.4
30°-40°	1213.8	32.6
40°-50°	702.7	18.9
50°-60°	83.5	2.2
60°-70°	3.2	0.1
70°-80°	3.5	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1714.7	46.0
0°-40°	2928.5	78.6
0°-60°	3714.6	99.7
0°-90°	3724.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3724.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1192	1192	1192	1192	1192	
5°	2285	1848	1138	651	426	263
15°	5411	3130	781	212	237	1625
25°	10590	3635	408	454	456	4783
35°	10842	2651	166	163	154	6537
45°	5661	624	18	22	20	4424
55°	353	5	5	3	1	777
65°	2	3	5	3	0	3
75°	0	3	6	3	0	0
85°	0	3	6	3	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0
2.5°	1733.6	1699.4	1665.0	1662.6	1634.1	1596.4	1622.3	1567.1	1583.9	1542.0	1516.1
5°	2285.3	2247.7	2197.5	2183.2	2134.6	2078.5	2099.5	2002.4	1992.3	1912.0	1847.5
7.5°	2961.8	2918.2	2839.6	2801.8	2721.5	2637.7	2647.8	2492.1	2445.3	2313.0	2194.9
10°	3736.9	3705.9	3593.0	3515.1	3388.7	3266.5	3245.5	3015.3	2913.2	2705.5	2519.7
12.5°	4606.7	4560.6	4404.1	4286.1	4113.6	3958.8	3912.7	3582.9	3399.6	3099.0	2835.3
15°	5411.2	5380.2	5245.4	5067.9	4849.4	4649.4	4570.7	4185.6	3895.9	3496.7	3130.0
17.5°	6442.5	6357.1	6114.4	5766.1	5453.8	5254.6	5159.1	4677.0	4322.1	3834.8	3366.9
20°	7643.8	7528.3	7156.5	6674.4	6156.2	5806.3	5596.1	5077.1	4637.7	4071.7	3521.0
22.5°	9382.5	9147.2	8441.5	7577.7	6856.9	6389.7	6089.3	5334.9	4867.9	4219.9	3606.3
25°	10590.5	10383.7	9739.1	8603.2	7447.8	6910.5	6487.7	5548.5	5018.5	4307.8	3634.7
27.5°	11355.6	11245.9	10504.3	9369.1	7905.0	7205.9	6728.0	5683.2	5075.5	4305.3	3577.0
30°	11461.8	11468.5	10780.5	9574.1	7941.0	7213.5	6676.0	5625.4	4957.4	4142.9	3387.0
32.5°	11415.9	11324.6	10475.8	9185.7	7542.5	6903.8	6393.1	5381.8	4672.8	3816.4	3057.1
35°	10842.4	10639.0	9741.6	8318.5	6962.3	6354.6	5878.3	4991.8	4219.9	3383.6	2651.2
37.5°	9791.0	9468.7	8466.6	7254.4	6250.8	5715.0	5355.1	4492.9	3751.2	2933.3	2247.7
40°	8189.5	7843.0	7136.5	6290.2	5499.0	5131.6	4785.8	3945.4	3223.0	2472.8	1857.6
42.5°	6775.7	6585.6	6058.3	5410.3	4883.8	4505.4	4175.6	3375.3	2717.3	2025.0	1316.0
45°	5660.6	5531.7	5199.4	4723.9	4201.5	3856.6	3556.1	2739.9	1985.7	1285.8	624.5
47.5°	4874.6	4731.4	4354.7	3854.2	3240.5	2865.5	2527.3	1708.5	1084.0	497.3	145.7
50°	3368.6	3199.5	2798.5	2316.3	1791.4	1509.4	1273.3	690.7	284.6	86.2	16.8
52.5°	1524.4	1407.2	1156.0	886.5	585.9	435.3	283.8	119.7	30.1	12.5	9.3
55°	353.2	309.7	235.3	144.8	72.0	47.7	31.8	12.5	9.3	6.7	5.0
57.5°	22.6	20.1	17.6	14.2	11.7	10.1	9.3	6.7	5.0	4.2	3.4
60°	9.3	9.3	8.3	6.7	5.9	5.0	5.0	3.4	3.4	3.4	3.4
62.5°	4.2	4.2	4.2	3.4	2.5	2.5	2.5	2.5	2.5	2.5	3.4
65°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.5	2.5	3.4
67.5°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	1.6	2.5	2.5	3.4
70°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	1.6	2.5	3.4	3.4
72.5°	0.0	0.8	0.8	0.8	1.6	1.6	1.6	1.6	2.5	3.4	3.4
75°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
77.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	1.6	2.5	3.4	3.4
80°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
82.5°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
85°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
87.5°	0.0	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0
2.5°	1477.5	1441.5	1403.8	1365.4	1347.8	1319.3	1274.1	1242.3	1213.8	1176.2	1128.5
5°	1769.6	1689.3	1604.7	1526.0	1487.6	1437.4	1349.4	1278.2	1212.2	1137.6	1064.0
7.5°	2061.0	1922.0	1788.0	1660.0	1598.1	1526.0	1390.5	1280.8	1177.0	1074.0	973.5
10°	2319.7	2118.8	1927.0	1748.8	1665.0	1568.7	1391.3	1244.8	1114.2	987.0	865.6
12.5°	2560.8	2288.7	2038.4	1807.4	1697.7	1582.2	1367.0	1192.9	1036.4	888.2	746.7
15°	2773.4	2430.2	2117.1	1835.0	1706.9	1568.7	1322.7	1123.4	948.4	781.1	599.4
17.5°	2924.9	2511.4	2145.5	1819.1	1675.1	1521.9	1250.7	1037.2	848.0	642.1	425.3
20°	3005.3	2536.5	2127.1	1768.8	1614.0	1448.2	1166.1	946.0	729.1	483.9	347.4
22.5°	3033.8	2521.4	2076.1	1697.7	1534.5	1366.2	1079.9	850.5	592.7	410.2	355.8
25°	3020.3	2476.2	2009.9	1614.0	1450.7	1281.6	996.2	728.3	479.7	407.7	379.2
27.5°	2930.8	2374.9	1886.1	1488.4	1324.3	1156.9	850.5	537.4	424.4	382.6	390.1
30°	2733.2	2169.0	1674.3	1283.3	1128.5	951.8	578.4	395.1	333.2	337.4	337.4
32.5°	2415.1	1860.9	1378.7	1019.6	819.5	593.5	329.8	247.8	251.9	251.1	247.8
35°	2025.0	1520.2	1058.1	626.2	401.8	272.9	166.5	161.6	166.5	165.7	163.3
37.5°	1666.7	1165.3	655.5	251.1	161.6	118.0	98.8	98.8	100.5	100.5	99.6
40°	1257.4	684.8	229.4	82.9	57.8	55.2	56.1	56.1	56.9	57.8	58.6
42.5°	704.0	226.0	60.3	32.6	32.6	31.0	31.0	31.0	32.6	32.6	33.5
45°	190.0	48.6	20.1	19.2	18.4	17.6	17.6	17.6	18.4	18.4	19.2
47.5°	28.5	14.2	11.7	10.9	10.9	10.1	10.1	10.1	10.9	10.9	10.9
50°	10.9	8.3	7.5	6.7	6.7	6.7	5.9	5.9	6.7	6.7	6.7
52.5°	6.7	5.9	5.0	4.2	5.0	4.2	4.2	4.2	5.0	5.0	5.0
55°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.0	5.0
57.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.0	5.0
60°	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.0
62.5°	3.4	4.2	4.2	4.2	4.2	4.2	4.2	4.2	5.0	5.0	5.0
65°	3.4	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0
67.5°	3.4	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
70°	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
72.5°	4.2	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.9
75°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9
77.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9
80°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9
82.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.0	5.9	5.9	5.9	5.9
85°	4.2	4.2	5.0	5.0	5.0	5.0	5.0	5.9	5.9	5.9	5.9
87.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.0	5.0	5.9	5.9	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0
2.5°	1094.9	1075.7	1040.5	1016.2	1006.3	986.1	948.4	944.2	899.1	875.6	851.3
5°	1001.2	953.5	894.0	856.4	834.6	791.9	733.3	706.5	651.3	615.3	562.6
7.5°	886.5	812.9	731.6	684.0	648.8	576.8	473.0	411.1	329.0	281.2	247.0
10°	755.1	657.1	534.1	455.4	397.6	313.1	248.6	228.6	206.8	189.2	172.4
12.5°	601.1	436.2	317.2	271.3	249.5	224.4	197.6	174.2	169.9	171.6	177.4
15°	409.3	291.3	251.1	232.7	217.7	193.4	199.3	205.9	211.8	216.0	223.5
17.5°	308.1	269.5	230.2	231.0	236.9	242.8	251.9	262.0	270.4	276.2	286.3
20°	303.9	279.6	284.6	294.7	301.4	309.7	325.7	334.8	345.7	353.2	364.2
22.5°	330.6	352.4	359.1	366.6	376.7	386.0	402.6	415.2	423.6	431.1	438.6
25°	392.6	409.3	415.2	421.0	427.7	434.5	445.3	456.2	453.8	456.2	457.0
27.5°	396.8	409.3	411.9	415.2	415.2	421.0	421.0	427.7	416.9	415.2	411.9
30°	341.5	345.7	348.2	348.2	344.9	349.0	344.9	350.0	337.4	333.2	329.0
32.5°	251.9	257.8	255.3	254.5	251.9	256.1	251.1	256.1	245.2	242.8	238.6
35°	161.6	170.8	166.5	169.1	167.5	171.6	168.3	171.6	163.3	162.4	159.9
37.5°	101.3	104.6	103.0	103.8	103.8	106.4	104.6	106.4	103.0	103.0	100.5
40°	59.5	61.1	61.1	61.9	62.7	63.6	62.7	64.5	62.7	63.6	61.1
42.5°	34.4	35.2	35.2	36.0	36.8	36.8	36.8	38.5	36.8	37.6	36.0
45°	19.2	20.9	20.1	20.9	20.9	21.8	21.8	21.8	21.8	21.8	20.9
47.5°	11.7	12.5	12.5	12.5	12.5	12.5	13.4	13.4	12.5	12.5	12.5
50°	7.5	7.5	7.5	7.5	8.3	8.3	8.3	7.5	7.5	7.5	6.7
52.5°	5.0	5.0	5.0	5.0	5.9	5.0	5.0	5.0	4.2	4.2	4.2
55°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	4.2	3.4	2.5	2.5
57.5°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5	2.5
60°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5	2.5
62.5°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	3.4	3.4	2.5	2.5
65°	5.0	5.0	5.0	5.0	5.0	4.2	4.2	4.2	3.4	2.5	2.5
67.5°	5.0	5.9	5.0	5.0	5.0	5.0	4.2	4.2	3.4	2.5	2.5
70°	5.0	5.9	5.0	5.0	5.0	5.0	4.2	4.2	3.4	2.5	2.5
72.5°	5.9	5.9	5.9	5.0	5.0	5.0	5.0	4.2	3.4	2.5	2.5
75°	5.9	5.9	5.9	5.0	5.0	5.0	5.0	4.2	3.4	2.5	2.5
77.5°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
80°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
82.5°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
85°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
87.5°	5.9	5.9	5.9	5.9	5.9	5.0	5.0	4.2	3.4	3.4	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192186

CATALOG NUMBER: LDA6A40930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0	1192.0
2.5°	857.2	848.9	843.0	829.6	822.0	813.7	801.1	795.3
5°	544.2	519.0	503.1	479.7	443.7	452.0	432.8	426.1
7.5°	234.4	223.5	220.1	215.1	206.8	202.5	201.7	200.1
10°	160.7	151.5	150.7	151.5	152.3	151.5	151.5	151.5
12.5°	180.8	181.7	183.3	185.9	186.7	186.7	185.9	185.9
15°	227.6	229.4	231.9	235.3	236.9	236.9	236.9	236.9
17.5°	292.1	294.7	298.8	302.2	305.5	305.5	305.5	306.3
20°	375.9	375.9	380.9	385.0	387.6	388.4	389.3	390.1
22.5°	450.4	451.2	454.6	457.9	460.4	459.6	457.9	457.9
25°	464.6	462.1	462.9	462.9	462.1	457.9	457.9	456.2
27.5°	414.4	411.1	411.1	408.5	407.7	406.0	402.6	401.0
30°	329.0	327.3	326.5	323.9	328.1	322.3	319.0	317.2
32.5°	236.9	237.7	236.9	234.4	238.6	232.7	231.0	228.6
35°	159.0	159.9	159.0	157.4	157.4	157.4	155.7	154.0
37.5°	100.5	99.6	100.5	100.5	102.1	99.6	99.6	97.9
40°	61.1	61.1	61.9	61.9	62.7	61.1	60.3	60.3
42.5°	36.0	36.0	36.8	36.8	37.6	36.0	36.0	36.0
45°	20.9	20.9	20.9	20.9	21.8	20.9	20.1	20.1
47.5°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	10.9
50°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9
52.5°	4.2	3.4	3.4	3.4	3.4	2.5	2.5	2.5
55°	1.6	1.6	1.6	1.6	1.6	0.8	0.8	0.8
57.5°	1.6	1.6	1.6	0.8	0.8	0.8	0.0	0.0
60°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
62.5°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
65°	1.6	1.6	0.8	0.8	0.8	0.0	0.0	0.0
67.5°	1.6	1.6	1.6	0.8	0.8	0.0	0.0	0.0
70°	1.6	1.6	1.6	0.8	0.8	0.8	0.0	0.0
72.5°	1.6	1.6	1.6	0.8	0.8	0.8	0.0	0.0
75°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
77.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.8	0.0
80°	2.5	1.6	1.6	1.6	0.8	0.8	0.8	0.8
82.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.8	0.8
85°	2.5	1.6	1.6	1.6	0.8	0.8	0.8	0.8
87.5°	2.5	1.6	1.6	1.6	0.8	0.8	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)