

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192199

Luminaire Tested: **LDA6A40930D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40930D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3966.6 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	101	99			99	97	96			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	89	83	79		86	81	77			84	80	76			81
4	92	82	75	70	90	81	75	70		79	73	69			77	72	68			75
5	85	75	68	63	83	74	67	62		72	66	62			70	65	61			69
6	80	69	61	56	78	68	61	56		66	60	55			65	59	55			63
7	74	63	55	50	73	62	55	50		61	54	50			59	54	50			58
8	69	58	50	45	68	57	50	45		56	50	45			55	49	45			54
9	65	53	46	41	64	53	46	41		52	45	41			51	45	41			50
10	61	49	42	37	60	49	42	37		48	42	37			47	41	37			46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	50160	50160	50160
5°	128483	46252	16955
10°	270937	36906	4798
15°	390734	26181	3995
20°	441009	17385	5618
25°	478824	17523	40454
30°	532576	11552	14148
35°	538055	6552	5434
40°	541629	2691	2462
45°	537195	1690	1427
50°	421658	1143	998
55°	126896	793	478
60°	26796	735	373
65°	3048	869	324
70°	801	1074	545
75°	169	1419	720
80°	0	2368	1073
85°	0	4214	2139

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.6	2.9
10°-20°	553.0	13.9
20°-30°	1042.6	26.3
30°-40°	1156.5	29.2
40°-50°	881.3	22.2
50°-60°	196.7	5.0
60°-70°	10.8	0.3
70°-80°	4.9	0.1
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1712.3	43.2
0°-40°	2868.7	72.3
0°-60°	3946.7	99.5
0°-90°	3966.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3966.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	915	915	915	915	915	
5°	2335	1730	840	404	308	302
15°	6885	3769	461	82	70	1920
25°	7916	4407	290	484	669	3684
35°	8040	2742	98	86	81	5036
45°	6929	807	22	23	18	5160
55°	1328	35	8	8	5	1639
65°	24	6	7	6	2	55
75°	1	3	7	6	3	1
85°	0	3	7	5	3	0
90°	0	0	0	0	0	

TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0
2.5°	1570.5	1542.8	1539.5	1530.3	1458.4	1457.4	1456.6	1419.0	1384.6	1367.0	1292.5
5°	2334.8	2314.7	2289.6	2257.7	2138.9	2122.2	2108.0	2051.8	1931.3	1861.0	1729.5
7.5°	3449.1	3438.2	3311.7	3295.0	3076.5	3023.0	2970.2	2826.2	2593.5	2442.8	2210.1
10°	4867.2	4815.2	4719.0	4588.4	4303.8	4202.5	4104.5	3809.8	3413.1	3097.5	2701.5
12.5°	6148.8	6082.7	5965.5	5813.2	5454.9	5316.7	5161.8	4800.2	4315.5	3802.3	3242.3
15°	6884.7	6873.8	6738.2	6676.2	6387.4	6246.8	6118.7	5702.7	5097.4	4493.8	3768.9
17.5°	7320.0	7320.8	7221.2	7184.4	6915.7	6781.8	6673.8	6370.7	5736.9	5004.4	4168.1
20°	7559.5	7583.7	7490.7	7433.0	7245.5	7126.6	7026.2	6713.9	6162.2	5349.3	4394.2
22.5°	7737.7	7749.4	7636.4	7588.8	7378.6	7263.9	7200.3	6901.4	6362.3	5533.6	4462.8
25°	7916.1	7910.2	7783.0	7687.5	7480.8	7369.4	7291.6	7032.9	6446.0	5576.3	4406.8
27.5°	8104.4	8131.2	7895.1	7742.8	7557.8	7427.2	7340.1	7073.1	6440.1	5464.9	4203.3
30°	8413.4	8196.5	7960.4	7750.3	7537.6	7399.5	7299.9	6960.0	6278.6	5169.4	3816.5
32.5°	8283.5	8130.4	7898.5	7682.5	7454.8	7302.4	7181.0	6777.6	5939.6	4683.0	3297.5
35°	8039.9	7998.9	7769.5	7593.7	7335.1	7171.0	7029.5	6496.2	5413.8	4097.8	2741.6
37.5°	7820.6	7777.9	7641.4	7459.8	7166.0	6994.4	6734.9	6049.2	4729.9	3365.3	2156.5
40°	7568.6	7558.6	7406.3	7238.0	6884.7	6568.2	6299.5	5260.7	3915.4	2646.2	1677.7
42.5°	7289.8	7284.0	7160.1	6911.5	6392.4	5999.9	5550.2	4370.8	3010.4	2008.3	1246.6
45°	6929.1	6894.7	6681.3	6318.8	5573.7	5006.2	4473.7	3339.4	2207.5	1434.9	807.0
47.5°	6303.7	6243.5	5932.0	5311.7	4418.5	3838.3	3348.6	2296.3	1377.1	811.2	400.2
50°	4944.1	4784.3	4340.6	3688.4	2772.6	2268.6	1883.6	1139.4	611.1	402.6	256.1
52.5°	3053.9	2881.4	2462.0	1969.8	1265.0	980.3	808.6	549.2	338.2	231.9	98.8
55°	1327.7	1246.6	1028.9	818.7	585.2	465.5	401.8	277.9	175.8	84.6	35.2
57.5°	518.1	502.3	437.8	369.2	277.1	226.0	200.1	125.6	48.6	30.1	20.1
60°	244.4	228.6	196.7	163.3	102.1	73.7	56.9	35.2	24.3	18.4	13.4
62.5°	67.0	57.8	46.9	40.2	31.0	27.7	24.3	19.2	15.0	11.7	9.3
65°	23.5	23.5	20.9	19.2	15.9	14.2	13.4	10.9	9.3	7.5	5.9
67.5°	10.9	10.9	10.1	9.3	7.5	7.5	6.7	5.9	5.0	4.2	4.2
70°	5.0	4.2	4.2	4.2	4.2	3.4	3.4	3.4	3.4	3.4	3.4
72.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	2.5	3.4	3.4	3.4
75°	0.8	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	3.4
77.5°	0.0	0.8	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	3.4
80°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	3.4
82.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
85°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	3.4	3.4	3.4
87.5°	0.0	0.0	0.8	0.8	1.6	1.6	1.6	2.5	2.5	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0
2.5°	1260.7	1229.0	1187.1	1117.6	1086.6	1079.9	1023.0	971.1	925.1	891.6	838.8
5°	1644.1	1552.1	1439.8	1305.1	1254.1	1218.1	1109.2	1005.4	916.7	840.5	760.1
7.5°	2024.2	1841.7	1673.5	1476.8	1381.3	1309.3	1147.7	1000.4	866.5	762.7	656.3
10°	2390.0	2130.5	1845.9	1587.3	1459.2	1350.3	1138.5	951.8	784.4	663.0	550.9
12.5°	2737.4	2364.9	1986.6	1642.5	1489.3	1352.8	1093.3	874.0	693.9	563.4	446.2
15°	3082.3	2534.9	2068.6	1654.2	1469.2	1305.1	1011.3	770.2	592.7	461.3	358.3
17.5°	3297.5	2629.5	2069.4	1602.3	1393.9	1214.7	899.1	662.2	489.8	371.7	281.2
20°	3403.8	2617.8	1990.7	1482.6	1265.8	1084.9	766.8	551.7	395.9	298.0	221.9
22.5°	3372.8	2514.0	1852.7	1324.3	1123.4	951.8	653.0	462.9	341.5	258.7	200.9
25°	3227.2	2345.7	1689.4	1175.4	982.8	820.4	573.5	426.1	336.6	289.7	249.5
27.5°	2975.2	2124.6	1489.3	1018.8	845.5	715.8	519.9	413.5	348.2	312.3	315.6
30°	2603.5	1831.7	1230.6	809.6	662.2	556.7	390.1	287.9	212.6	182.5	182.5
32.5°	2187.5	1497.7	951.0	598.6	478.9	404.4	274.6	196.7	157.4	143.2	136.5
35°	1797.3	1172.0	705.7	433.7	345.7	287.9	180.0	110.5	101.3	97.9	96.3
37.5°	1413.9	879.8	511.5	314.8	240.3	190.8	92.1	71.2	61.9	57.8	54.4
40°	1059.8	617.8	354.1	192.6	133.1	87.8	53.6	43.5	38.5	37.6	36.0
42.5°	741.7	414.4	219.3	84.6	61.9	49.4	36.8	31.0	28.5	27.7	26.7
45°	434.5	258.7	89.6	46.9	38.5	34.4	26.7	23.5	21.8	21.8	20.9
47.5°	272.9	104.6	47.7	30.1	25.9	24.3	20.1	17.6	16.8	16.8	16.8
50°	112.2	46.1	28.5	20.9	18.4	17.6	15.0	13.4	13.4	13.4	13.4
52.5°	41.0	25.9	19.2	15.0	13.4	12.5	10.9	10.1	10.1	10.9	10.1
55°	23.5	17.6	13.4	10.9	9.3	9.3	8.3	8.3	8.3	8.3	8.3
57.5°	15.0	11.7	9.3	7.5	6.7	6.7	6.7	6.7	6.7	7.5	6.7
60°	10.1	8.3	6.7	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7
62.5°	7.5	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7
65°	5.9	5.0	5.9	5.9	5.9	5.9	5.9	6.7	6.7	6.7	7.5
67.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5
70°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5
72.5°	4.2	4.2	5.0	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5
75°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	5.9	6.7	6.7	7.5
77.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7	7.5
80°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5	7.5
82.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	7.5	7.5
85°	4.2	5.0	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7	7.5
87.5°	4.2	4.2	5.0	5.0	5.0	5.9	5.9	6.7	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0
2.5°	802.8	766.0	735.8	720.0	702.4	672.2	643.7	617.8	606.9	571.7	578.4
5°	697.3	634.6	584.3	561.8	535.7	493.9	457.0	422.0	403.6	373.4	362.5
7.5°	580.2	506.5	446.2	420.2	397.7	358.3	323.9	291.3	267.9	236.9	224.4
10°	464.7	394.3	339.1	316.4	291.3	252.0	217.7	189.2	169.9	146.5	134.8
12.5°	367.5	304.7	248.6	226.0	205.1	172.4	145.7	119.7	98.8	86.2	82.9
15°	286.3	226.0	180.0	161.6	144.0	112.2	92.1	85.4	82.1	78.7	77.9
17.5°	215.1	166.5	125.6	107.2	97.1	88.8	85.4	82.1	80.3	77.9	78.7
20°	165.7	118.9	102.1	99.6	97.9	93.7	92.9	92.1	91.2	92.1	93.7
22.5°	157.4	148.1	153.2	156.6	164.1	164.9	178.3	189.2	199.3	226.8	240.3
25°	265.4	281.2	306.4	322.3	344.1	366.6	408.5	445.3	483.9	519.1	550.0
27.5°	332.4	339.9	339.9	348.2	339.1	337.4	332.4	328.1	345.7	339.9	358.3
30°	184.1	192.6	206.8	214.3	223.5	230.2	227.7	219.3	224.4	217.7	224.4
32.5°	131.5	131.5	134.8	135.6	137.3	138.2	139.0	139.8	140.6	136.5	139.0
35°	93.7	90.4	88.8	88.8	87.8	86.2	85.4	85.4	86.2	82.1	83.7
37.5°	52.8	51.0	51.0	51.0	51.0	51.0	51.9	52.8	52.8	52.8	54.4
40°	35.2	35.2	35.2	36.0	36.0	36.0	36.8	36.8	37.6	37.6	38.5
42.5°	26.7	25.9	26.7	26.7	26.7	27.7	27.7	28.5	28.5	28.5	29.3
45°	20.9	20.9	20.9	20.9	21.8	21.8	21.8	21.8	22.6	21.8	22.6
47.5°	16.8	16.8	16.8	17.6	17.6	16.8	17.6	17.6	17.6	17.6	17.6
50°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	14.2	13.4	14.2
52.5°	10.9	10.1	10.1	10.1	10.1	9.3	9.3	10.1	10.1	9.3	9.3
55°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
57.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9
60°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9	5.9	5.0
62.5°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9	5.0	5.0
65°	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0	5.0
67.5°	7.5	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.0	5.0
70°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0
72.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9
75°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9
77.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9	5.0
80°	7.5	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.9	5.0
82.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0	5.0
85°	6.7	6.7	6.7	6.7	6.7	5.9	5.9	5.9	5.0	5.0	5.0
87.5°	6.7	6.7	6.7	5.9	5.9	5.9	5.9	5.0	5.0	4.2	4.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192199

CATALOG NUMBER: LDA6A40930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	915.0	915.0	915.0	915.0	915.0	915.0	915.0	915.0
2.5°	543.3	531.6	541.6	529.0	524.9	515.7	511.5	515.7
5°	342.3	329.8	332.4	323.9	310.6	310.6	306.4	308.1
7.5°	206.8	194.2	195.0	187.5	177.4	175.8	171.6	173.3
10°	119.7	106.4	106.4	97.9	89.6	88.8	86.2	86.2
12.5°	79.5	77.9	76.2	75.3	73.7	73.7	73.7	72.0
15°	74.5	73.7	72.8	72.8	71.2	71.2	72.0	70.4
17.5°	76.2	75.3	74.5	74.5	74.5	74.5	75.3	73.7
20°	91.2	92.1	92.1	94.6	96.3	97.1	99.6	96.3
22.5°	239.4	247.0	252.8	283.8	310.6	300.6	319.0	287.9
25°	572.6	593.5	611.1	614.4	631.2	654.7	669.7	668.8
27.5°	358.3	359.1	369.2	369.2	365.8	379.3	388.4	386.8
30°	221.0	220.1	223.5	215.1	214.3	220.1	223.5	223.5
32.5°	136.5	135.6	138.2	136.5	132.3	139.0	137.3	137.3
35°	82.1	82.9	81.2	81.2	77.9	81.2	80.3	81.2
37.5°	53.6	52.8	51.9	51.9	50.2	51.0	50.2	48.6
40°	37.6	37.6	36.8	36.8	36.0	35.2	35.2	34.4
42.5°	28.5	28.5	27.7	27.7	26.7	25.9	25.9	25.1
45°	21.8	20.9	20.1	20.1	20.1	19.2	19.2	18.4
47.5°	16.8	16.8	16.8	15.9	15.9	15.0	15.0	14.2
50°	13.4	13.4	13.4	13.4	12.5	12.5	12.5	11.7
52.5°	9.3	9.3	8.3	8.3	7.5	7.5	7.5	6.7
55°	6.7	6.7	6.7	5.9	5.9	5.9	5.0	5.0
57.5°	5.9	5.9	5.0	5.0	5.0	4.2	4.2	4.2
60°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
62.5°	4.2	4.2	4.2	3.4	3.4	3.4	3.4	2.5
65°	4.2	4.2	3.4	3.4	3.4	2.5	2.5	2.5
67.5°	4.2	4.2	4.2	3.4	3.4	3.4	3.4	2.5
70°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
72.5°	5.0	4.2	4.2	4.2	4.2	3.4	3.4	3.4
75°	5.0	5.0	4.2	4.2	4.2	4.2	4.2	3.4
77.5°	5.0	4.2	4.2	4.2	4.2	4.2	3.4	3.4
80°	5.0	4.2	4.2	4.2	4.2	3.4	3.4	3.4
82.5°	5.0	4.2	4.2	4.2	3.4	3.4	3.4	3.4
85°	4.2	4.2	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	3.4	3.4	2.5	2.5	2.5	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)