

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192216

Luminaire Tested: **LDA6A40935D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40935D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4130.0 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	101	99		99	97	96		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	86	84
3	98	90	84	79	96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	82	75	70	90	81	75	70		79	73	69		77	72	68		75	71	67
5	85	75	68	63	83	74	67	62		72	66	62		70	65	61		69	64	60
6	80	69	61	56	78	68	61	56		66	60	55		65	59	55		63	58	54
7	74	63	55	50	73	62	55	50		61	54	50		59	54	50		58	53	49
8	69	58	50	45	68	57	50	45		56	50	45		55	49	45		54	48	45
9	65	53	46	41	64	53	46	41		52	45	41		51	45	41		50	44	41
10	61	49	42	37	60	49	42	37		48	42	37		47	41	37		46	41	37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	52233	52233	52233
5°	133782	48156	17648
10°	282103	38426	4999
15°	406841	27259	4154
20°	459182	18108	5846
25°	498555	18243	42123
30°	554522	12027	14730
35°	560233	6819	5662
40°	563957	2805	2555
45°	559329	1752	1481
50°	439039	1194	1040
55°	132124	832	497
60°	27903	767	384
65°	3165	908	337
70°	833	1122	561
75°	169	1483	741
80°	0	2462	1105
85°	0	4403	2201



TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	2.9
10°-20°	575.8	13.9
20°-30°	1085.6	26.3
30°-40°	1204.1	29.2
40°-50°	917.7	22.2
50°-60°	204.8	5.0
60°-70°	11.2	0.3
70°-80°	5.1	0.1
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1782.8	43.2
0°-40°	2987.0	72.3
0°-60°	4109.4	99.5
0°-90°	4130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4130.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	953	953	953	953	953	
5°	2431	1801	875	420	321	315
15°	7168	3924	480	85	73	1999
25°	8242	4588	302	504	696	3836
35°	8371	2855	102	90	85	5244
45°	7215	840	23	24	19	5373
55°	1382	37	9	8	5	1707
65°	24	6	7	6	3	57
75°	1	4	7	6	4	1
85°	0	4	7	5	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8
2.5°	1635.2	1606.5	1603.0	1593.4	1518.4	1517.5	1516.7	1477.5	1441.7	1423.4	1345.8
5°	2431.1	2410.1	2384.0	2350.8	2227.1	2209.6	2194.8	2136.5	2010.9	1937.7	1800.8
7.5°	3591.2	3579.9	3448.2	3430.8	3203.3	3147.6	3092.6	2942.7	2700.4	2543.5	2301.2
10°	5067.8	5013.8	4913.5	4777.5	4481.1	4375.7	4273.7	3966.9	3553.7	3225.1	2812.8
12.5°	6402.3	6333.4	6211.4	6052.7	5679.6	5535.8	5374.6	4998.0	4493.4	3959.1	3375.9
15°	7168.5	7157.1	7015.9	6951.4	6650.7	6504.2	6370.9	5937.6	5307.5	4679.0	3924.2
17.5°	7621.7	7622.6	7518.8	7480.5	7200.8	7061.3	6948.8	6633.2	5973.4	5210.8	4340.0
20°	7871.0	7896.2	7799.5	7739.4	7544.1	7420.4	7315.8	6990.6	6416.2	5569.9	4575.3
22.5°	8056.6	8068.9	7951.2	7901.5	7682.7	7563.3	7497.0	7185.8	6624.6	5761.6	4646.7
25°	8242.3	8236.2	8103.7	8004.4	7789.1	7673.1	7592.1	7322.8	6711.7	5806.1	4588.3
27.5°	8438.5	8466.3	8220.5	8061.9	7869.3	7733.3	7642.7	7364.6	6705.6	5690.1	4376.5
30°	8760.1	8534.3	8288.5	8069.8	7848.3	7704.5	7600.8	7246.9	6537.4	5382.5	3973.9
32.5°	8625.0	8465.5	8224.0	7999.1	7762.0	7603.4	7477.1	7056.8	6184.3	4876.0	3433.4
35°	8371.3	8328.6	8089.7	7906.7	7637.4	7466.6	7319.3	6764.0	5637.0	4266.8	2854.7
37.5°	8142.9	8098.5	7956.4	7767.2	7461.3	7282.6	7012.4	6298.5	4924.8	3504.0	2245.4
40°	7880.6	7870.1	7711.5	7536.3	7168.5	6839.0	6559.2	5477.4	4076.8	2755.3	1746.8
42.5°	7590.3	7584.2	7455.2	7196.3	6656.0	6247.2	5779.0	4550.9	3134.5	2091.1	1297.9
45°	7214.6	7178.9	6956.6	6579.2	5803.4	5212.4	4658.1	3477.0	2298.6	1494.1	840.2
47.5°	6563.5	6500.7	6176.5	5530.6	4600.6	3996.5	3486.6	2391.0	1433.9	844.6	416.6
50°	5147.9	4981.5	4519.5	3840.5	2886.9	2362.2	1961.2	1186.3	636.3	419.3	266.7
52.5°	3179.7	3000.2	2563.6	2051.0	1317.0	1020.7	842.0	571.8	352.1	241.4	102.9
55°	1382.4	1297.9	1071.3	852.5	609.3	484.6	418.4	289.4	183.0	88.1	36.6
57.5°	539.5	523.0	455.9	384.4	288.5	235.4	208.3	130.7	50.5	31.4	20.9
60°	254.5	237.9	204.8	169.9	106.4	76.7	59.3	36.6	25.3	19.1	14.0
62.5°	69.7	60.2	48.9	41.9	32.3	28.8	25.3	20.1	15.7	12.2	9.6
65°	24.4	24.4	21.8	20.1	16.6	14.8	14.0	11.3	9.6	7.8	6.1
67.5°	11.3	11.3	10.5	9.6	7.8	7.8	7.0	6.1	5.2	4.3	4.3
70°	5.2	4.3	4.3	4.3	4.3	3.5	3.5	3.5	3.5	3.5	3.5
72.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.6	3.5	3.5	3.5
75°	0.8	0.8	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	3.5
77.5°	0.0	0.8	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	3.5
80°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	3.5
82.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
85°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	3.5	3.5	3.5
87.5°	0.0	0.0	0.8	0.8	1.7	1.7	1.7	2.6	2.6	3.5	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8
2.5°	1312.7	1279.6	1236.0	1163.6	1131.4	1124.4	1065.2	1011.1	963.2	928.3	873.3
5°	1711.9	1616.1	1499.2	1358.9	1305.7	1268.3	1154.9	1046.9	954.4	875.1	791.5
7.5°	2107.7	1917.7	1742.5	1537.6	1438.2	1363.3	1195.0	1041.6	902.2	794.0	683.4
10°	2488.6	2218.3	1922.0	1652.7	1519.3	1406.0	1185.4	991.0	816.8	690.3	573.6
12.5°	2850.3	2462.5	2068.5	1710.2	1550.6	1408.6	1138.3	910.0	722.6	586.7	464.6
15°	3209.4	2639.4	2153.8	1722.4	1529.7	1358.9	1053.0	802.0	617.1	480.3	373.1
17.5°	3433.4	2737.8	2154.7	1668.3	1451.3	1264.8	936.2	689.5	509.9	387.0	292.9
20°	3544.1	2725.7	2072.8	1543.7	1317.9	1129.7	798.5	574.4	412.3	310.4	230.9
22.5°	3511.9	2617.6	1929.0	1378.9	1169.7	991.0	679.9	482.0	355.6	269.3	209.2
25°	3360.2	2442.4	1759.0	1223.8	1023.3	854.2	597.0	443.7	350.4	301.6	259.7
27.5°	3097.9	2212.3	1550.6	1060.8	880.3	745.3	541.3	430.6	362.6	325.2	328.7
30°	2710.9	1907.2	1281.3	842.9	689.5	579.7	406.2	299.9	221.4	190.0	190.0
32.5°	2277.6	1559.4	990.2	623.3	498.6	421.0	285.9	204.8	163.9	149.1	142.1
35°	1871.5	1220.3	734.8	451.5	360.0	299.9	187.4	115.1	105.4	101.9	100.2
37.5°	1472.2	916.1	532.5	327.7	250.2	198.7	95.9	74.1	64.5	60.2	56.7
40°	1103.5	643.2	368.7	200.5	138.6	91.6	55.8	45.4	40.1	39.2	37.4
42.5°	772.3	431.4	228.4	88.1	64.5	51.4	38.4	32.3	29.6	28.8	27.9
45°	452.4	269.3	93.3	48.9	40.1	35.7	27.9	24.4	22.6	22.6	21.8
47.5°	284.1	108.9	49.7	31.4	27.1	25.3	20.9	18.3	17.4	17.4	17.4
50°	116.8	47.9	29.6	21.8	19.1	18.3	15.7	14.0	14.0	14.0	14.0
52.5°	42.7	27.1	20.1	15.7	14.0	13.1	11.3	10.5	10.5	11.3	10.5
55°	24.4	18.3	14.0	11.3	9.6	9.6	8.7	8.7	8.7	8.7	8.7
57.5°	15.7	12.2	9.6	7.8	7.0	7.0	7.0	7.0	7.0	7.8	7.0
60°	10.5	8.7	7.0	6.1	6.1	6.1	6.1	6.1	7.0	7.0	7.0
62.5°	7.8	6.1	6.1	6.1	6.1	6.1	6.1	6.1	7.0	7.0	7.0
65°	6.1	5.2	6.1	6.1	6.1	6.1	6.1	7.0	7.0	7.0	7.8
67.5°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8
70°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8
72.5°	4.3	4.3	5.2	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8
75°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	6.1	7.0	7.0	7.8
77.5°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0	7.8
80°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8	7.8
82.5°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.8	7.8
85°	4.3	5.2	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0	7.8
87.5°	4.3	4.3	5.2	5.2	5.2	6.1	6.1	7.0	7.0	7.0	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8
2.5°	835.9	797.5	766.2	749.6	731.3	699.9	670.3	643.2	631.9	595.3	602.3
5°	726.0	660.7	608.4	584.9	557.9	514.2	476.0	439.3	420.1	388.7	377.4
7.5°	604.0	527.3	464.6	437.6	414.0	373.1	337.3	303.4	279.0	246.7	233.6
10°	483.8	410.5	353.0	329.5	303.4	262.4	226.6	197.0	176.9	152.6	140.3
12.5°	382.7	317.2	258.9	235.4	213.6	179.6	151.6	124.7	102.9	89.8	86.3
15°	298.1	235.4	187.4	168.2	149.9	116.8	95.9	88.9	85.4	82.0	81.1
17.5°	224.0	173.4	130.7	111.6	101.1	92.4	88.9	85.4	83.6	81.1	82.0
20°	172.6	123.8	106.4	103.7	101.9	97.6	96.8	95.9	95.0	95.9	97.6
22.5°	163.9	154.3	159.5	163.0	170.9	171.7	185.7	197.0	207.5	236.2	250.2
25°	276.3	292.9	319.0	335.6	358.3	381.7	425.4	463.7	503.8	540.5	572.7
27.5°	346.0	353.9	353.9	362.6	353.0	351.3	346.0	341.7	360.0	353.9	373.1
30°	191.7	200.5	215.3	223.1	232.7	239.7	237.1	228.4	233.6	226.6	233.6
32.5°	136.8	136.8	140.3	141.2	143.0	143.8	144.7	145.6	146.5	142.1	144.7
35°	97.6	94.1	92.4	92.4	91.6	89.8	88.9	88.9	89.8	85.4	87.1
37.5°	54.9	53.2	53.2	53.2	53.2	53.2	54.0	54.9	54.9	54.9	56.7
40°	36.6	36.6	36.6	37.4	37.4	37.4	38.4	38.4	39.2	39.2	40.1
42.5°	27.9	27.1	27.9	27.9	27.9	28.8	28.8	29.6	29.6	29.6	30.6
45°	21.8	21.8	21.8	21.8	22.6	22.6	22.6	22.6	23.6	22.6	23.6
47.5°	17.4	17.4	17.4	18.3	18.3	17.4	18.3	18.3	18.3	18.3	18.3
50°	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8	14.0	14.8
52.5°	11.3	10.5	10.5	10.5	10.5	9.6	9.6	10.5	10.5	9.6	9.6
55°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
57.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1
60°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1	6.1	5.2
62.5°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1	5.2	5.2
65°	7.8	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2	5.2
67.5°	7.8	7.8	7.0	7.0	7.0	7.0	7.0	6.1	6.1	5.2	5.2
70°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2
72.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1
75°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1
77.5°	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1	5.2
80°	7.8	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	6.1	5.2
82.5°	7.0	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2	5.2
85°	7.0	7.0	7.0	7.0	7.0	6.1	6.1	6.1	5.2	5.2	5.2
87.5°	7.0	7.0	7.0	6.1	6.1	6.1	6.1	5.2	5.2	4.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192216

CATALOG NUMBER: LDA6A40935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	952.8	952.8	952.8	952.8	952.8	952.8	952.8	952.8
2.5°	565.7	553.5	563.9	550.9	546.5	537.0	532.5	537.0
5°	356.5	343.5	346.0	337.3	323.4	323.4	319.0	320.7
7.5°	215.3	202.2	203.1	195.2	184.8	183.0	178.7	180.4
10°	124.7	110.7	110.7	101.9	93.3	92.4	89.8	89.8
12.5°	82.8	81.1	79.3	78.5	76.7	76.7	76.7	75.0
15°	77.6	76.7	75.8	75.8	74.1	74.1	75.0	73.2
17.5°	79.3	78.5	77.6	77.6	77.6	77.6	78.5	76.7
20°	95.0	95.9	95.9	98.5	100.2	101.1	103.7	100.2
22.5°	249.2	257.2	263.2	295.5	323.4	312.9	332.1	299.9
25°	596.2	618.0	636.3	639.8	657.2	681.6	697.3	696.4
27.5°	373.1	373.9	384.4	384.4	380.9	394.8	404.5	402.7
30°	230.1	229.3	232.7	224.0	223.1	229.3	232.7	232.7
32.5°	142.1	141.2	143.8	142.1	137.7	144.7	143.0	143.0
35°	85.4	86.3	84.6	84.6	81.1	84.6	83.6	84.6
37.5°	55.8	54.9	54.0	54.0	52.3	53.2	52.3	50.5
40°	39.2	39.2	38.4	38.4	37.4	36.6	36.6	35.7
42.5°	29.6	29.6	28.8	28.8	27.9	27.1	27.1	26.1
45°	22.6	21.8	20.9	20.9	20.9	20.1	20.1	19.1
47.5°	17.4	17.4	17.4	16.6	16.6	15.7	15.7	14.8
50°	14.0	14.0	14.0	14.0	13.1	13.1	13.1	12.2
52.5°	9.6	9.6	8.7	8.7	7.8	7.8	7.8	7.0
55°	7.0	7.0	7.0	6.1	6.1	6.1	5.2	5.2
57.5°	6.1	6.1	5.2	5.2	5.2	4.3	4.3	4.3
60°	5.2	4.3	4.3	4.3	3.5	3.5	3.5	3.5
62.5°	4.3	4.3	4.3	3.5	3.5	3.5	3.5	2.6
65°	4.3	4.3	3.5	3.5	3.5	2.6	2.6	2.6
67.5°	4.3	4.3	4.3	3.5	3.5	3.5	3.5	2.6
70°	5.2	4.3	4.3	4.3	3.5	3.5	3.5	3.5
72.5°	5.2	4.3	4.3	4.3	4.3	3.5	3.5	3.5
75°	5.2	5.2	4.3	4.3	4.3	4.3	4.3	3.5
77.5°	5.2	4.3	4.3	4.3	4.3	4.3	3.5	3.5
80°	5.2	4.3	4.3	4.3	4.3	3.5	3.5	3.5
82.5°	5.2	4.3	4.3	4.3	3.5	3.5	3.5	3.5
85°	4.3	4.3	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	3.5	3.5	2.6	2.6	2.6	1.7	1.7	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)