

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192220

Luminaire Tested: **LDA6A40940D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26670)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40940D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4027.9 lumens
Efficiency: N/A
Efficacy: 80.9 lumens/watt
Spacing Criteria (0/90/45): 2.28 / 0.6 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	109	106	104	110	107	105	102		103	101	99			99	98	96			96
2	106	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	81	97	90	84	80		87	83	79			85	81	77			82
4	92	83	77	72	91	82	76	71		80	75	71			78	73	70			76
5	86	76	69	64	85	75	69	64		74	68	63			72	67	63			70
6	81	70	63	58	79	69	62	58		68	62	57			66	61	57			65
7	76	64	57	52	74	64	57	52		62	56	52			61	55	51			60
8	71	59	52	47	69	59	52	47		57	51	47			56	51	47			55
9	66	55	48	43	65	54	47	43		53	47	43			52	47	43			51
10	62	51	44	39	61	50	44	39		49	43	39			48	43	39			48

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	70669	70669	70669
5°	136000	67703	25352
10°	224951	59418	9124
15°	332102	47934	14535
20°	482219	30528	24613
25°	692732	26669	29844
30°	784608	23098	21719
35°	784673	11993	11143
40°	633773	4466	4666
45°	474576	1551	1682
50°	310676	614	546
55°	36520	526	86
60°	1096	603	0
65°	246	713	0
70°	144	882	0
75°	0	1356	0
80°	0	2020	284
85°	0	4026	566



TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	3.3
10°-20°	538.9	13.4
20°-30°	1182.4	29.4
30°-40°	1312.6	32.6
40°-50°	759.9	18.9
50°-60°	90.3	2.2
60°-70°	3.5	0.1
70°-80°	3.8	0.1
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1854.3	46.0
0°-40°	3166.9	78.6
0°-60°	4017.0	99.7
0°-90°	4027.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4027.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1289	1289	1289	1289	1289	
5°	2471	1998	1230	704	461	284
15°	5852	3385	845	229	256	1757
25°	11452	3931	441	491	493	5172
35°	11725	2867	179	176	166	7069
45°	6121	675	20	24	22	4784
55°	382	6	6	4	1	840
65°	2	4	6	4	0	3
75°	0	4	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1
2.5°	1874.8	1837.7	1800.6	1797.8	1767.1	1726.3	1754.4	1694.6	1712.8	1667.5	1639.4
5°	2471.4	2430.7	2376.4	2360.9	2308.5	2247.8	2270.4	2165.4	2154.6	2067.6	1997.9
7.5°	3202.8	3155.8	3070.7	3029.9	2943.1	2852.5	2863.3	2694.9	2644.3	2501.2	2373.6
10°	4041.1	4007.6	3885.4	3801.2	3664.5	3532.4	3509.7	3260.8	3150.3	2925.8	2724.9
12.5°	4981.7	4931.9	4762.6	4634.9	4448.5	4281.0	4231.2	3874.5	3676.3	3351.3	3066.2
15°	5851.6	5818.1	5672.3	5480.5	5244.2	5027.9	4942.7	4526.3	4213.1	3781.3	3384.8
17.5°	6966.9	6874.6	6612.0	6235.4	5897.8	5682.3	5579.1	5057.7	4673.9	4147.0	3641.0
20°	8265.9	8141.1	7739.1	7217.7	6657.3	6279.0	6051.7	5490.5	5015.1	4403.2	3807.6
22.5°	10146.2	9891.9	9128.7	8194.5	7415.0	6909.8	6584.9	5769.2	5264.2	4563.4	3899.9
25°	11452.5	11228.9	10531.8	9303.4	8054.1	7472.9	7015.8	6000.1	5427.1	4658.5	3930.7
27.5°	12280.0	12161.4	11359.3	10131.8	8548.4	7792.6	7275.6	6145.8	5488.6	4655.8	3868.2
30°	12394.9	12402.2	11658.0	10353.6	8587.3	7800.7	7219.5	6083.4	5361.0	4480.2	3662.7
32.5°	12345.1	12246.4	11328.5	9933.4	8156.4	7465.7	6913.5	5820.0	5053.2	4127.1	3306.1
35°	11725.0	11505.1	10534.6	8995.6	7529.1	6871.9	6356.7	5398.1	4563.4	3659.1	2866.9
37.5°	10588.0	10239.5	9155.9	7845.0	6759.7	6180.2	5790.9	4858.6	4056.5	3172.0	2430.7
40°	8856.2	8481.5	7717.4	6802.1	5946.7	5549.3	5175.4	4266.5	3485.3	2674.2	2008.8
42.5°	7327.2	7121.7	6551.5	5850.7	5281.3	4872.1	4515.5	3650.1	2938.5	2189.9	1423.1
45°	6121.4	5982.0	5622.6	5108.4	4543.6	4170.6	3845.6	2962.9	2147.3	1390.5	675.3
47.5°	5271.4	5116.5	4709.2	4167.8	3504.3	3098.7	2733.0	1847.6	1172.3	537.7	157.5
50°	3642.8	3460.0	3026.3	2504.8	1937.3	1632.2	1376.9	746.8	307.8	93.2	18.1
52.5°	1648.5	1521.7	1250.2	958.6	633.7	470.7	306.9	129.4	32.6	13.6	10.0
55°	382.1	334.9	254.4	156.6	77.9	51.6	34.4	13.6	10.0	7.2	5.5
57.5°	24.5	21.7	19.0	15.4	12.7	10.9	10.0	7.2	5.5	4.5	3.6
60°	10.0	10.0	9.1	7.2	6.4	5.5	5.5	3.6	3.6	3.6	3.6
62.5°	4.5	4.5	4.5	3.6	2.7	2.7	2.7	2.7	2.7	2.7	3.6
65°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.7	2.7	3.6
67.5°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	1.9	2.7	2.7	3.6
70°	0.9	0.9	0.9	0.9	1.9	1.9	1.9	1.9	2.7	3.6	3.6
72.5°	0.0	0.9	0.9	0.9	1.9	1.9	1.9	1.9	2.7	3.6	3.6
75°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6
77.5°	0.0	0.0	0.9	0.9	1.9	1.9	1.9	1.9	2.7	3.6	3.6
80°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6
82.5°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6
85°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6
87.5°	0.0	0.0	0.9	0.9	0.9	1.9	1.9	1.9	2.7	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1
2.5°	1597.7	1558.9	1518.1	1476.5	1457.4	1426.7	1377.8	1343.5	1312.6	1271.9	1220.3
5°	1913.8	1826.8	1735.4	1650.3	1608.6	1554.3	1459.3	1382.3	1310.8	1230.3	1150.6
7.5°	2228.7	2078.4	1933.6	1795.1	1728.2	1650.3	1503.6	1385.0	1272.8	1161.5	1052.9
10°	2508.5	2291.2	2083.9	1891.1	1800.6	1696.5	1504.5	1346.1	1204.9	1067.4	936.0
12.5°	2769.2	2475.0	2204.4	1954.5	1835.9	1711.0	1478.3	1290.0	1120.7	960.5	807.5
15°	2999.1	2628.0	2289.4	1984.3	1845.9	1696.5	1430.3	1214.9	1025.7	844.6	648.2
17.5°	3163.0	2715.8	2320.2	1967.1	1811.4	1645.8	1352.5	1121.7	917.1	694.4	459.9
20°	3249.9	2743.0	2300.2	1912.8	1745.4	1566.1	1261.1	1022.9	788.5	523.3	375.7
22.5°	3280.7	2726.6	2245.1	1835.9	1659.4	1477.4	1167.8	919.7	641.0	443.6	384.7
25°	3266.2	2677.8	2173.5	1745.4	1568.8	1385.9	1077.2	787.6	518.8	440.9	410.1
27.5°	3169.4	2568.2	2039.6	1609.6	1432.1	1251.1	919.7	581.2	459.0	413.7	421.9
30°	2955.7	2345.5	1810.6	1387.8	1220.3	1029.3	625.5	427.3	360.3	364.9	364.9
32.5°	2611.7	2012.4	1491.0	1102.6	886.2	641.8	356.6	268.0	272.5	271.6	268.0
35°	2189.9	1643.9	1144.3	677.2	434.5	295.1	180.1	174.7	180.1	179.2	176.5
37.5°	1802.3	1260.1	708.9	271.6	174.7	127.7	106.8	106.8	108.6	108.6	107.7
40°	1359.7	740.5	248.0	89.6	62.4	59.8	60.7	60.7	61.5	62.4	63.4
42.5°	761.3	244.4	65.2	35.3	35.3	33.5	33.5	33.5	35.3	35.3	36.2
45°	205.5	52.5	21.7	20.8	20.0	19.0	19.0	19.0	20.0	20.0	20.8
47.5°	30.8	15.4	12.7	11.7	11.7	10.9	10.9	10.9	11.7	11.7	11.7
50°	11.7	9.1	8.1	7.2	7.2	7.2	6.4	6.4	7.2	7.2	7.2
52.5°	7.2	6.4	5.5	4.5	5.5	4.5	4.5	4.5	5.5	5.5	5.5
55°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.5	5.5
57.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.5	5.5
60°	3.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.5	5.5	5.5
62.5°	3.6	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.5	5.5	5.5
65°	3.6	4.5	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
67.5°	3.6	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
70°	4.5	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
72.5°	4.5	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.4
75°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.4	6.4
77.5°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4
80°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4
82.5°	4.5	4.5	5.5	5.5	5.5	6.4	5.5	6.4	6.4	6.4	6.4
85°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	6.4	6.4	6.4	6.4
87.5°	4.5	4.5	5.5	5.5	5.5	6.4	5.5	5.5	6.4	6.4	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1
2.5°	1184.1	1163.2	1125.3	1099.0	1088.1	1066.4	1025.7	1021.2	972.2	946.9	920.7
5°	1082.7	1031.1	966.9	926.1	902.6	856.4	793.0	764.0	704.3	665.3	608.4
7.5°	958.6	879.0	791.2	739.6	701.6	623.7	511.5	444.5	355.8	304.2	267.0
10°	816.6	710.6	577.6	492.4	430.0	338.5	268.9	247.1	223.6	204.6	186.5
12.5°	650.0	471.6	343.1	293.3	269.7	242.6	213.7	188.2	183.7	185.6	192.0
15°	442.6	315.0	271.6	251.6	235.4	209.1	215.4	222.7	229.0	233.5	241.7
17.5°	333.1	291.5	248.9	249.9	256.1	262.5	272.5	283.3	292.4	298.7	309.6
20°	328.6	302.3	307.8	318.7	325.9	334.9	352.1	362.1	373.9	382.1	393.8
22.5°	357.6	381.1	388.3	396.6	407.4	417.3	435.4	449.0	458.1	466.2	474.3
25°	424.5	442.6	449.0	455.4	462.6	469.8	481.6	493.4	490.7	493.4	494.3
27.5°	429.1	442.6	445.4	449.0	449.0	455.4	455.4	462.6	450.9	449.0	445.4
30°	369.4	373.9	376.6	376.6	373.0	377.5	373.0	378.5	364.9	360.3	355.8
32.5°	272.5	278.8	276.1	275.2	272.5	277.0	271.6	277.0	265.2	262.5	258.0
35°	174.7	184.6	180.1	182.9	181.0	185.6	182.0	185.6	176.5	175.6	172.9
37.5°	109.6	113.2	111.3	112.2	112.2	115.0	113.2	115.0	111.3	111.3	108.6
40°	64.3	66.0	66.0	67.0	67.9	68.8	67.9	69.7	67.9	68.8	66.0
42.5°	37.1	38.1	38.1	38.9	39.8	39.8	39.8	41.7	39.8	40.7	38.9
45°	20.8	22.6	21.7	22.6	22.6	23.6	23.6	23.6	23.6	23.6	22.6
47.5°	12.7	13.6	13.6	13.6	13.6	13.6	14.5	14.5	13.6	13.6	13.6
50°	8.1	8.1	8.1	8.1	9.1	9.1	9.1	8.1	8.1	8.1	7.2
52.5°	5.5	5.5	5.5	5.5	6.4	5.5	5.5	5.5	4.5	4.5	4.5
55°	5.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5	3.6	2.7	2.7
57.5°	5.5	5.5	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7	2.7
60°	5.5	5.5	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7	2.7
62.5°	5.5	5.5	5.5	5.5	5.5	4.5	4.5	3.6	3.6	2.7	2.7
65°	5.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5	3.6	2.7	2.7
67.5°	5.5	6.4	5.5	5.5	5.5	5.5	4.5	4.5	3.6	2.7	2.7
70°	5.5	6.4	5.5	5.5	5.5	5.5	4.5	4.5	3.6	2.7	2.7
72.5°	6.4	6.4	6.4	5.5	5.5	5.5	5.5	4.5	3.6	2.7	2.7
75°	6.4	6.4	6.4	5.5	5.5	5.5	5.5	4.5	3.6	2.7	2.7
77.5°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	3.6	3.6	2.7
80°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	3.6	3.6	2.7
82.5°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	3.6	3.6	2.7
85°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	3.6	3.6	2.7
87.5°	6.4	6.4	6.4	6.4	6.4	5.5	5.5	4.5	3.6	3.6	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192220

CATALOG NUMBER: LDA6A40940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1	1289.1
2.5°	926.9	917.9	911.6	897.1	889.0	879.9	866.4	860.0
5°	588.4	561.2	544.1	518.8	479.8	488.8	468.0	460.7
7.5°	253.5	241.7	238.0	232.7	223.6	219.1	218.2	216.3
10°	173.8	163.9	162.9	163.9	164.8	163.9	163.9	163.9
12.5°	195.6	196.5	198.2	201.0	201.8	201.8	201.0	201.0
15°	246.3	248.0	250.8	254.4	256.1	256.1	256.1	256.1
17.5°	315.9	318.7	323.2	326.8	330.4	330.4	330.4	331.3
20°	406.4	406.4	411.9	416.4	419.2	420.0	420.9	421.9
22.5°	487.1	487.9	491.6	495.2	497.9	497.0	495.2	495.2
25°	502.4	499.7	500.7	500.7	499.7	495.2	495.2	493.4
27.5°	448.1	444.5	444.5	441.8	440.9	439.0	435.4	433.6
30°	355.8	354.0	353.0	350.4	354.9	348.5	344.9	343.1
32.5°	256.1	257.1	256.1	253.5	258.0	251.6	249.9	247.1
35°	172.0	172.9	172.0	170.1	170.1	170.1	168.4	166.5
37.5°	108.6	107.7	108.6	108.6	110.5	107.7	107.7	106.0
40°	66.0	66.0	67.0	67.0	67.9	66.0	65.2	65.2
42.5°	38.9	38.9	39.8	39.8	40.7	38.9	38.9	38.9
45°	22.6	22.6	22.6	22.6	23.6	22.6	21.7	21.7
47.5°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	11.7
50°	7.2	7.2	7.2	7.2	7.2	6.4	6.4	6.4
52.5°	4.5	3.6	3.6	3.6	3.6	2.7	2.7	2.7
55°	1.9	1.9	1.9	1.9	1.9	0.9	0.9	0.9
57.5°	1.9	1.9	1.9	0.9	0.9	0.9	0.0	0.0
60°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
65°	1.9	1.9	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	1.9	1.9	1.9	0.9	0.9	0.0	0.0	0.0
70°	1.9	1.9	1.9	0.9	0.9	0.9	0.0	0.0
72.5°	1.9	1.9	1.9	0.9	0.9	0.9	0.0	0.0
75°	2.7	1.9	1.9	1.9	0.9	0.9	0.0	0.0
77.5°	2.7	1.9	1.9	1.9	0.9	0.9	0.9	0.0
80°	2.7	1.9	1.9	1.9	0.9	0.9	0.9	0.9
82.5°	2.7	1.9	1.9	1.9	0.9	0.9	0.9	0.9
85°	2.7	1.9	1.9	1.9	0.9	0.9	0.9	0.9
87.5°	2.7	1.9	1.9	1.9	0.9	0.9	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)