

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192230

Luminaire Tested: **LDA6A40940D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26668)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40940D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3307.2 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 2.16 / 1.11 / 1.51
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62		
5	83	72	65	59	81	71	64	59	69	63	58	67	62	57	66	61	57	55		
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49		
7	72	60	52	47	70	59	52	46	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39		
9	63	50	43	38	61	50	43	38	49	42	37	48	42	37	47	41	37	35		
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54601	54601	54601
5°	86798	53813	34779
10°	129184	51714	23491
15°	183560	49228	17679
20°	240284	47015	18062
25°	286111	47537	31218
30°	317296	45855	29397
35°	323694	39083	21630
40°	309401	30128	16001
45°	269834	21692	12071
50°	205716	15761	8025
55°	114835	11335	4674
60°	52814	7839	1886
65°	24905	4229	830
70°	12182	2036	882
75°	5761	1356	953
80°	2873	1421	1137
85°	1698	2264	1195



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	3.1
10°-20°	375.7	11.4
20°-30°	751.5	22.7
30°-40°	922.8	27.9
40°-50°	739.2	22.4
50°-60°	325.2	9.8
60°-70°	73.3	2.2
70°-80°	13.3	0.4
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1229.9	37.2
0°-40°	2152.7	65.1
0°-60°	3217.2	97.3
0°-90°	3307.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3307.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	996	996	996	996	996	
5°	1577	1357	978	724	632	174
15°	3234	2181	867	404	312	943
25°	4730	2695	786	489	516	2176
35°	4837	2428	584	352	323	2995
45°	3480	1604	280	171	156	2646
55°	1202	594	119	68	49	1142
65°	192	121	33	11	6	220
75°	27	15	6	6	4	34
85°	3	3	4	4	2	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0
2.5°	1270.3	1237.7	1264.0	1241.4	1234.1	1231.4	1220.5	1213.3	1210.5	1185.2	1165.3
5°	1577.3	1539.2	1566.4	1532.9	1515.8	1506.7	1487.7	1464.1	1445.1	1397.0	1357.2
7.5°	1936.7	1896.0	1921.4	1873.3	1840.7	1824.5	1793.7	1748.4	1705.9	1628.9	1561.8
10°	2320.7	2287.2	2308.9	2241.9	2191.2	2165.0	2119.6	2061.7	1974.8	1862.5	1763.8
12.5°	2768.0	2719.9	2737.1	2647.5	2575.1	2538.0	2473.7	2383.1	2260.0	2106.9	1972.1
15°	3234.3	3189.0	3199.8	3085.7	2985.2	2933.6	2850.4	2721.8	2558.7	2358.7	2181.2
17.5°	3712.3	3650.8	3648.9	3513.1	3379.1	3313.9	3209.8	3040.5	2849.4	2586.8	2367.7
20°	4118.8	4065.4	4050.9	3909.7	3726.8	3650.8	3524.9	3314.8	3080.3	2776.1	2518.9
22.5°	4467.4	4405.9	4379.6	4213.9	4006.6	3917.8	3773.9	3519.4	3258.6	2914.7	2624.9
25°	4730.1	4679.4	4641.3	4454.8	4223.0	4123.4	3965.9	3690.6	3388.2	3011.5	2694.6
27.5°	4938.3	4870.4	4822.3	4618.7	4357.9	4252.9	4083.5	3784.7	3454.3	3050.4	2715.4
30°	5012.5	4944.7	4889.4	4672.1	4396.0	4281.0	4103.5	3786.6	3436.2	3021.4	2670.1
32.5°	4977.3	4906.6	4844.2	4616.8	4330.7	4210.3	4029.2	3707.8	3341.0	2924.5	2569.6
35°	4836.8	4780.8	4710.1	4481.0	4198.6	4067.3	3887.1	3557.5	3193.5	2773.4	2428.4
37.5°	4638.6	4551.7	4486.5	4261.9	3988.5	3854.5	3681.5	3364.6	2996.1	2592.3	2258.2
40°	4323.5	4235.7	4170.5	3954.0	3706.0	3571.1	3411.7	3109.3	2753.5	2377.7	2059.0
42.5°	3930.5	3849.0	3785.6	3584.6	3365.5	3234.3	3093.9	2814.2	2483.6	2139.5	1840.7
45°	3480.5	3401.7	3347.4	3172.7	2978.0	2862.1	2735.4	2488.2	2185.7	1873.3	1603.5
47.5°	2992.5	2911.9	2865.7	2709.1	2544.3	2439.3	2330.6	2116.9	1846.2	1578.2	1343.7
50°	2412.1	2334.3	2292.6	2161.3	2044.5	1947.6	1868.8	1697.7	1475.8	1264.9	1073.8
52.5°	1766.6	1705.9	1675.1	1584.5	1514.8	1442.4	1391.7	1272.2	1110.0	960.7	816.7
55°	1201.5	1151.7	1137.2	1081.1	1043.1	1004.1	967.9	898.2	788.7	689.9	594.0
57.5°	751.6	746.1	756.1	706.3	689.0	672.8	644.7	605.8	537.0	475.4	417.4
60°	481.7	476.3	471.8	453.6	445.5	433.7	420.1	397.5	354.9	318.7	280.7
62.5°	305.1	301.5	306.0	295.1	284.3	284.3	269.8	257.2	230.9	209.1	182.0
65°	192.0	191.0	193.8	186.5	181.0	178.4	171.2	163.9	147.6	134.0	121.3
67.5°	121.3	120.5	122.2	120.5	114.1	112.2	107.7	103.2	92.4	84.2	75.2
70°	76.0	75.2	76.0	74.3	70.7	68.8	66.1	62.4	58.8	49.8	45.3
72.5°	46.2	45.3	46.2	45.3	42.6	42.6	38.9	37.1	34.4	29.0	25.3
75°	27.2	27.2	27.2	26.2	24.5	24.5	22.6	21.7	20.0	17.2	15.4
77.5°	15.4	15.4	15.4	15.4	14.5	14.5	13.6	12.7	11.7	10.0	10.0
80°	9.1	9.1	9.1	9.1	8.1	9.1	8.1	8.1	7.2	6.4	6.4
82.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
87.5°	0.0	0.0	0.0	0.9	0.9	0.9	0.9	1.9	1.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0
2.5°	1149.0	1120.0	1114.6	1083.8	1078.4	1061.2	1052.1	1035.8	1003.3	986.0	965.2
5°	1309.3	1264.0	1237.7	1182.5	1165.3	1136.4	1106.4	1066.6	1015.0	977.9	939.0
7.5°	1484.9	1410.7	1355.5	1273.9	1244.1	1201.5	1149.0	1086.5	1014.1	958.8	903.6
10°	1661.5	1545.6	1460.5	1351.0	1307.5	1251.3	1175.3	1091.0	1000.5	929.0	860.2
12.5°	1823.5	1678.7	1561.8	1422.5	1364.5	1295.7	1196.0	1091.0	983.3	898.2	817.6
15°	2000.2	1809.0	1657.0	1486.7	1415.3	1333.7	1211.5	1087.4	964.3	867.4	778.7
17.5°	2144.1	1916.8	1730.3	1532.0	1446.9	1353.6	1213.3	1072.9	939.8	833.9	741.6
20°	2250.0	1998.3	1780.1	1558.2	1462.3	1360.8	1206.0	1054.0	914.5	805.9	711.6
22.5°	2327.0	2047.2	1805.4	1567.3	1463.2	1357.2	1193.4	1037.6	897.3	791.4	701.8
25°	2373.2	2071.7	1813.6	1563.7	1456.0	1345.5	1178.9	1023.1	886.4	785.9	703.5
27.5°	2377.7	2061.7	1791.9	1536.5	1426.1	1315.6	1149.0	995.0	862.9	770.5	691.8
30°	2326.0	2005.5	1734.9	1476.8	1365.4	1256.7	1092.9	941.7	815.8	724.4	652.8
32.5°	2226.5	1906.9	1638.9	1386.2	1276.7	1170.7	1011.4	869.2	746.1	661.9	591.3
35°	2094.3	1781.9	1514.8	1277.6	1170.7	1070.2	915.4	775.9	663.7	584.0	519.7
37.5°	1937.6	1636.1	1386.2	1157.2	1054.0	960.7	811.3	684.5	576.8	503.4	444.6
40°	1759.2	1471.3	1236.9	1019.5	927.1	836.6	700.8	584.9	484.4	421.0	371.3
42.5°	1566.4	1296.5	1080.2	878.3	794.0	711.6	588.5	483.5	396.6	345.0	306.0
45°	1354.6	1111.9	917.2	740.6	660.1	592.2	476.3	389.4	323.2	279.8	252.6
47.5°	1128.2	917.2	747.8	595.8	525.1	467.2	372.2	307.0	259.8	230.0	207.4
50°	900.9	725.2	584.0	452.7	399.3	350.4	287.9	243.6	207.4	184.8	170.2
52.5°	688.2	546.0	434.6	332.3	296.1	262.6	221.8	192.0	164.8	148.5	137.6
55°	498.9	393.9	309.6	243.6	219.1	200.1	170.2	148.5	131.3	118.6	109.6
57.5°	347.7	272.5	216.4	177.4	162.9	149.4	128.6	114.1	102.4	93.3	86.0
60°	235.5	184.8	151.2	128.6	119.5	110.5	96.9	86.9	77.9	71.5	64.3
62.5°	154.8	126.7	107.7	94.1	86.0	79.7	71.5	63.4	56.2	50.7	44.3
65°	100.5	83.3	74.3	63.4	59.8	55.2	48.0	43.4	37.1	32.6	28.1
67.5°	63.4	54.3	48.0	41.7	38.9	35.3	31.7	27.2	23.6	20.0	17.2
70°	38.1	33.5	29.0	25.3	23.6	21.7	19.0	16.3	13.6	12.7	10.9
72.5°	22.6	20.0	17.2	15.4	14.5	13.6	11.7	10.0	9.1	8.1	7.2
75°	13.6	12.7	10.9	9.1	9.1	8.1	8.1	7.2	6.4	6.4	5.5
77.5°	9.1	8.1	7.2	6.4	6.4	6.4	5.5	5.5	5.5	5.5	5.5
80°	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	4.5	4.5
85°	2.7	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6
87.5°	2.7	2.7	2.7	2.7	3.6	3.6	3.6	3.6	3.6	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0
2.5°	956.2	929.0	918.1	901.8	885.5	884.7	865.6	855.7	848.4	835.7	823.0
5°	912.6	871.1	845.7	824.0	803.1	788.7	760.6	741.6	724.4	706.3	682.7
7.5°	861.9	808.5	772.3	745.2	720.7	698.1	663.7	638.3	616.6	599.4	570.4
10°	807.6	746.1	700.8	670.9	645.6	613.0	579.5	551.4	527.9	508.9	480.8
12.5°	756.9	689.0	638.3	607.5	581.3	546.0	511.6	482.6	457.2	439.1	413.8
15°	709.9	638.3	584.0	553.2	526.1	490.8	456.3	427.4	403.9	384.8	362.2
17.5°	668.2	593.0	539.6	511.6	483.5	450.9	416.5	389.4	365.8	348.6	330.5
20°	640.1	568.7	517.0	490.8	466.3	435.5	408.4	386.6	363.9	350.4	339.6
22.5°	635.6	572.3	527.9	506.1	487.1	464.4	448.2	437.3	422.0	415.6	415.6
25°	644.7	590.4	555.1	537.8	522.5	509.8	501.6	494.4	488.9	489.9	489.9
27.5°	639.2	590.4	561.4	545.1	531.5	523.4	515.2	510.6	505.3	508.0	508.0
30°	603.9	556.8	532.4	515.2	502.5	495.3	483.5	478.0	471.8	472.7	469.9
32.5°	545.1	500.8	477.2	460.8	447.3	440.1	427.4	421.0	412.9	412.9	407.5
35°	476.3	434.6	412.9	398.4	385.8	378.5	366.7	360.3	352.2	347.7	345.0
37.5°	403.9	367.6	347.7	336.8	326.9	319.6	308.7	304.2	296.1	292.5	288.9
40°	336.8	310.6	291.5	282.5	274.3	268.0	258.1	254.4	247.2	244.5	240.8
42.5°	278.9	258.9	243.6	236.3	227.2	223.6	216.4	212.7	206.5	203.7	200.1
45°	232.7	216.4	203.7	197.4	192.0	187.4	180.2	177.4	171.2	168.4	166.6
47.5°	192.0	179.3	169.3	163.9	161.2	155.7	149.4	146.7	142.2	139.5	136.7
50°	157.6	147.6	139.5	134.9	133.1	127.7	122.2	120.5	115.9	114.1	111.4
52.5°	128.6	120.5	113.2	109.6	106.0	102.4	97.8	96.0	91.4	88.8	85.1
55°	103.2	95.0	88.8	86.0	84.2	78.8	74.3	71.5	67.9	63.4	60.7
57.5°	79.7	72.4	67.0	63.4	62.4	57.1	53.4	48.9	44.3	41.7	38.9
60°	58.8	52.6	47.1	43.4	42.6	37.1	32.6	29.8	26.2	24.5	23.6
62.5°	38.9	34.4	29.8	28.1	26.2	22.6	20.0	18.1	16.3	15.4	14.5
65°	24.5	20.8	18.1	17.2	15.4	13.6	12.7	11.7	10.9	10.0	9.1
67.5°	14.5	12.7	10.9	10.9	10.0	9.1	9.1	8.1	7.2	7.2	7.2
70°	9.1	8.1	7.2	7.2	7.2	7.2	7.2	6.4	6.4	6.4	6.4
72.5°	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	6.4	5.5	5.5
75°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
77.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
80°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
82.5°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	3.6	3.6	3.6
85°	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	3.6	2.7
87.5°	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7	2.7	2.7	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192230

CATALOG NUMBER: LDA6A40940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	996.0	996.0	996.0	996.0	996.0	996.0	996.0	996.0
2.5°	813.1	797.7	795.9	792.3	788.7	793.2	790.4	783.2
5°	674.5	655.6	651.9	646.5	641.1	642.8	638.3	632.0
7.5°	558.7	538.7	535.1	528.7	523.4	522.5	517.9	511.6
10°	464.4	449.1	445.5	439.1	432.8	431.9	426.5	422.0
12.5°	397.5	383.0	379.4	373.0	367.6	365.8	361.3	357.7
15°	347.7	334.1	330.5	325.1	318.7	318.7	315.1	311.5
17.5°	316.9	305.1	300.6	296.1	290.6	289.8	287.9	285.3
20°	329.6	318.7	316.9	311.5	312.4	312.4	310.6	309.6
22.5°	411.1	407.5	414.7	409.3	419.2	422.9	424.6	424.6
25°	493.5	494.4	501.6	498.9	508.0	515.2	518.9	516.1
27.5°	508.0	508.9	511.6	510.6	517.9	522.5	525.1	518.9
30°	466.3	465.4	464.4	463.6	468.2	469.9	470.8	464.4
32.5°	402.0	399.3	400.2	395.6	397.5	397.5	401.1	392.0
35°	337.7	334.1	334.1	329.6	329.6	329.6	332.3	323.2
37.5°	283.4	279.8	278.9	274.3	273.4	271.7	274.3	266.2
40°	236.3	232.7	233.6	228.2	229.1	228.2	228.2	223.6
42.5°	195.6	192.9	192.0	190.1	191.0	191.0	193.8	190.1
45°	162.1	159.3	158.4	157.6	158.4	158.4	159.3	155.7
47.5°	134.9	131.3	130.3	128.6	128.6	125.8	125.8	122.2
50°	108.6	103.2	102.4	99.6	98.7	96.9	96.9	94.1
52.5°	82.4	77.9	76.0	74.3	73.3	71.5	71.5	69.7
55°	57.9	53.4	52.6	51.6	50.7	49.8	50.7	48.9
57.5°	36.2	34.4	33.5	32.6	31.7	30.8	30.8	29.8
60°	21.7	20.0	20.0	19.0	18.1	17.2	17.2	17.2
62.5°	13.6	12.7	12.7	11.7	11.7	10.9	10.9	10.9
65°	9.1	8.1	8.1	7.2	7.2	6.4	6.4	6.4
67.5°	6.4	6.4	6.4	6.4	5.5	5.5	5.5	5.5
70°	6.4	5.5	5.5	5.5	5.5	5.5	5.5	5.5
72.5°	5.5	5.5	5.5	5.5	4.5	4.5	4.5	4.5
75°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
77.5°	4.5	4.5	4.5	4.5	3.6	3.6	3.6	3.6
80°	4.5	3.6	3.6	3.6	3.6	3.6	3.6	3.6
82.5°	3.6	3.6	3.6	3.6	3.6	2.7	2.7	2.7
85°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	1.9
87.5°	1.9	1.9	1.9	1.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)