

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192244

Luminaire Tested: **LDA6A40950D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26674)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4260.5 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 2.68 / 0.47 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91		
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	67	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	59	54	77	66	59	54	65	58	53	63	57	53	61	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	36801	36801	36801
5°	96984	33579	10830
10°	193656	25734	4303
15°	352556	18059	4699
20°	542115	12963	29659
25°	635777	19362	24546
30°	692227	12154	7147
35°	728558	5039	2965
40°	747064	2218	1682
45°	693491	1458	1240
50°	486432	1126	571
55°	177905	803	354
60°	37574	822	219
65°	3178	973	259
70°	1074	1202	449
75°	191	1589	784
80°	284	2368	1168
85°	0	4717	1258



TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	2.0
10°-20°	464.4	10.9
20°-30°	1122.5	26.3
30°-40°	1319.6	31.0
40°-50°	996.8	23.4
50°-60°	250.1	5.9
60°-70°	12.1	0.3
70°-80°	5.8	0.1
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1671.4	39.2
0°-40°	2991.0	70.2
0°-60°	4237.9	99.5
0°-90°	4260.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4260.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	671	671	671	671	671	
5°	1762	1280	610	259	197	220
15°	6212	2694	318	86	83	1880
25°	10511	3353	320	444	406	4835
35°	10886	2470	75	54	44	6779
45°	8945	971	19	20	16	6591
55°	1861	27	8	8	4	2059
65°	24	7	8	7	2	66
75°	1	5	8	7	4	2
85°	0	5	8	6	2	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3
2.5°	1171.2	1152.4	1139.2	1116.5	1105.3	1110.1	1086.5	1054.6	1045.1	1016.9	967.8
5°	1762.4	1742.7	1711.6	1663.6	1627.8	1622.2	1576.0	1498.8	1450.0	1377.4	1279.5
7.5°	2488.4	2471.5	2419.7	2348.0	2287.8	2265.2	2197.4	2061.9	1953.6	1808.7	1640.1
10°	3478.9	3413.0	3315.9	3171.0	3032.5	2968.6	2849.0	2625.0	2448.8	2250.1	2021.4
12.5°	4720.7	4603.9	4446.7	4229.3	3991.0	3871.5	3681.3	3338.5	3030.7	2689.9	2356.6
15°	6212.0	6094.3	5866.5	5529.4	5146.2	4954.1	4673.7	4133.2	3674.6	3174.7	2694.5
17.5°	7971.7	7779.5	7476.5	6987.8	6394.6	6093.4	5696.1	4947.5	4264.0	3611.6	2990.2
20°	9292.6	9152.2	8865.1	8353.9	7646.8	7259.0	6725.2	5694.1	4812.0	3960.9	3214.3
22.5°	10103.2	9977.1	9713.4	9286.0	8636.4	8206.1	7604.5	6349.4	5237.5	4202.8	3326.3
25°	10510.9	10420.5	10236.9	9864.1	9296.4	8864.1	8255.9	6834.4	5525.6	4333.8	3352.6
27.5°	10869.6	10718.0	10419.6	10165.4	9662.5	9222.8	8646.8	7075.4	5626.4	4318.7	3285.9
30°	10935.5	10848.9	10613.5	10250.1	9782.1	9337.7	8730.5	7040.5	5512.5	4143.6	3104.1
32.5°	10878.9	10803.6	10625.7	10229.3	9705.9	9215.3	8548.8	6754.4	5178.3	3818.8	2797.2
35°	10886.5	10766.9	10455.3	10116.4	9463.1	8886.8	8104.4	6230.8	4710.4	3397.0	2470.4
37.5°	10742.5	10545.7	10288.7	9851.8	8969.6	8255.1	7360.6	5555.8	4147.3	2966.6	2089.2
40°	10439.3	10289.6	9947.9	9276.6	8128.8	7230.7	6404.1	4781.0	3532.5	2496.8	1703.2
42.5°	9944.2	9765.3	9287.9	8275.7	6911.5	6128.2	5384.4	3988.2	2928.0	2042.0	1336.9
45°	8945.1	8672.1	8047.8	6840.9	5677.3	5012.6	4406.2	3252.0	2373.5	1597.6	970.6
47.5°	7349.4	7116.8	6456.8	5449.4	4533.3	4019.2	3502.4	2564.5	1766.2	1027.1	499.0
50°	5703.6	5520.0	5016.3	4132.2	3367.7	2868.7	2462.0	1637.3	941.4	472.7	224.1
52.5°	3752.8	3637.0	3204.9	2579.7	1933.8	1578.0	1281.3	710.8	438.8	210.0	77.3
55°	1861.4	1712.6	1506.4	1116.5	807.9	653.4	554.5	350.3	181.7	60.2	27.2
57.5°	758.8	725.9	653.4	504.6	387.9	327.7	261.8	109.2	40.5	24.5	17.0
60°	342.7	327.7	284.3	199.7	108.3	66.9	47.1	30.2	20.8	15.1	11.3
62.5°	60.2	55.5	49.0	37.6	30.2	26.3	22.6	17.0	13.2	10.4	8.4
65°	24.5	24.5	22.6	19.8	16.0	15.1	13.2	10.4	8.4	7.5	6.7
67.5°	13.2	12.2	12.2	10.4	9.5	8.4	7.5	6.7	6.7	5.7	5.7
70°	6.7	6.7	6.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
72.5°	3.7	3.7	3.7	3.7	3.7	3.7	2.8	2.8	2.8	3.7	3.7
75°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
77.5°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
80°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	4.7
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	4.7
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	4.7
87.5°	0.0	0.0	0.9	0.9	0.9	2.0	2.0	2.8	2.8	3.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3
2.5°	966.0	917.1	879.4	843.5	835.1	805.9	778.6	731.5	689.2	649.6	604.4
5°	1241.9	1145.8	1065.8	987.7	962.2	913.2	847.3	762.5	683.5	610.2	532.9
7.5°	1542.1	1379.4	1237.2	1105.3	1059.2	989.5	883.2	762.5	648.8	543.3	449.1
10°	1836.8	1593.9	1379.4	1189.1	1119.5	1029.1	883.2	729.7	584.7	462.3	369.1
12.5°	2121.2	1787.9	1498.0	1246.5	1155.2	1042.2	859.6	672.3	503.7	383.2	305.0
15°	2343.3	1951.7	1581.7	1269.1	1155.2	1024.4	805.0	592.2	421.8	318.2	248.6
17.5°	2510.0	2048.7	1610.0	1247.5	1115.7	968.9	722.2	498.1	347.4	263.6	196.8
20°	2607.1	2073.2	1580.8	1184.5	1040.4	884.9	619.5	410.5	294.7	222.2	159.1
22.5°	2629.6	2039.3	1513.0	1103.4	954.7	797.5	529.2	367.1	284.3	226.9	198.6
25°	2604.2	1970.5	1423.6	1021.6	873.7	718.4	496.2	395.4	340.8	320.1	342.7
27.5°	2503.4	1842.6	1313.4	930.2	781.4	636.5	470.7	398.3	342.7	333.2	323.0
30°	2323.7	1649.4	1144.0	760.8	603.5	483.0	334.3	237.3	189.3	192.0	190.2
32.5°	2042.0	1369.0	895.3	532.0	415.2	326.8	221.2	140.3	131.8	131.8	129.9
35°	1732.3	1111.9	673.1	373.8	289.0	229.7	131.8	102.6	86.6	75.3	67.8
37.5°	1417.0	865.3	464.2	252.4	183.6	117.7	63.1	51.8	46.1	43.4	42.3
40°	1096.9	609.1	296.5	138.4	81.0	51.8	40.5	34.8	32.0	31.0	31.0
42.5°	811.6	392.6	160.1	54.6	43.4	35.8	29.2	25.5	24.5	24.5	23.5
45°	488.6	196.8	60.2	33.9	28.3	25.5	21.6	19.8	18.8	18.8	19.8
47.5°	226.0	73.4	33.0	22.6	20.8	18.8	17.0	16.0	16.0	16.0	17.0
50°	82.0	32.0	20.8	16.0	15.1	14.1	13.2	12.2	12.2	13.2	13.2
52.5°	31.0	19.8	15.1	12.2	11.3	11.3	10.4	10.4	10.4	10.4	10.4
55°	18.8	14.1	11.3	9.5	9.5	8.4	8.4	8.4	8.4	8.4	8.4
57.5°	12.2	10.4	8.4	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
60°	9.5	7.5	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5
62.5°	7.5	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5
65°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
67.5°	5.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5
70°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5
72.5°	4.7	5.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5
75°	4.7	5.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5
77.5°	4.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
80°	4.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
82.5°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4	8.4
85°	4.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5	8.4
87.5°	4.7	5.7	5.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3
2.5°	579.9	541.3	514.1	489.5	480.2	458.5	435.0	407.7	385.0	383.2	364.4
5°	481.1	427.4	388.9	364.4	352.0	329.5	302.2	284.3	258.9	251.4	232.5
7.5°	388.9	338.9	303.2	280.6	266.4	239.1	208.1	188.2	167.5	151.6	130.8
10°	316.4	268.3	229.7	207.2	193.0	163.8	131.8	109.2	90.4	86.6	84.8
12.5°	254.2	205.3	166.7	142.2	127.1	99.8	91.3	87.5	84.8	82.0	82.0
15°	197.7	147.9	106.4	96.9	94.1	91.3	89.4	87.5	85.7	84.8	85.7
17.5°	144.0	104.5	99.8	98.8	96.9	96.9	98.8	99.8	101.6	103.6	106.4
20°	127.1	128.0	138.4	145.9	143.1	157.2	176.9	193.0	231.6	255.1	287.1
22.5°	227.9	261.8	309.7	338.9	355.0	402.1	453.9	532.0	571.5	628.0	678.8
25°	389.7	429.3	470.7	482.0	490.5	495.2	488.6	452.8	444.4	428.4	423.7
27.5°	291.8	273.0	279.7	282.5	279.7	275.9	264.6	244.8	240.0	232.5	234.4
30°	172.2	166.7	174.2	173.2	173.2	173.2	169.4	153.4	145.9	137.5	131.8
32.5°	127.1	116.7	108.3	100.8	97.9	93.2	90.4	83.7	81.0	77.3	77.3
35°	63.1	60.2	60.2	58.4	57.4	58.4	58.4	55.5	53.7	52.7	52.7
37.5°	41.4	41.4	42.3	41.4	41.4	41.4	41.4	40.5	39.6	38.6	38.6
40°	31.0	31.0	32.0	32.0	31.0	31.0	31.0	30.2	30.2	30.2	30.2
42.5°	24.5	24.5	24.5	24.5	23.5	24.5	24.5	24.5	23.5	23.5	22.6
45°	20.8	19.8	19.8	19.8	19.8	19.8	20.8	19.8	19.8	18.8	18.8
47.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	16.0	16.0
50°	13.2	13.2	13.2	13.2	13.2	12.2	12.2	11.3	11.3	10.4	10.4
52.5°	10.4	10.4	9.5	9.5	9.5	9.5	9.5	9.5	8.4	8.4	8.4
55°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	7.5	6.7	6.7
57.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7
60°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	5.7	5.7	5.7
62.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7
65°	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7	5.7
67.5°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
70°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
72.5°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
75°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
77.5°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
80°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
82.5°	8.4	8.4	8.4	8.4	8.4	7.5	7.5	7.5	6.7	6.7	5.7
85°	8.4	8.4	7.5	7.5	7.5	7.5	7.5	6.7	5.7	5.7	4.7
87.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	4.7	4.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192244

CATALOG NUMBER: LDA6A40950D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	671.3	671.3	671.3	671.3	671.3	671.3	671.3	671.3
2.5°	360.7	347.4	344.6	348.3	333.2	333.2	333.2	339.9
5°	225.0	211.8	208.1	209.0	196.8	188.2	193.0	196.8
7.5°	122.4	108.3	103.6	103.6	91.3	86.6	87.5	89.4
10°	82.0	80.0	80.0	79.0	77.3	76.2	77.3	77.3
12.5°	79.0	78.1	78.1	77.3	77.3	76.2	76.2	77.3
15°	82.8	82.8	82.8	82.0	82.0	81.0	82.8	82.8
17.5°	105.5	107.3	111.1	112.9	116.7	112.9	119.6	118.7
20°	309.7	340.8	398.3	420.0	482.0	451.9	516.9	508.4
22.5°	701.4	724.0	733.5	738.2	739.0	769.2	773.9	784.3
25°	414.2	408.6	403.8	403.8	387.0	406.7	403.0	405.8
27.5°	221.2	219.4	214.8	216.5	208.1	214.8	216.5	216.5
30°	125.2	121.5	117.7	117.7	110.2	114.0	112.9	112.9
32.5°	72.5	70.6	68.6	67.8	65.9	65.9	64.9	64.9
35°	49.8	49.0	48.0	47.1	45.1	44.3	44.3	44.3
37.5°	36.7	35.8	34.8	34.8	33.9	32.0	32.0	32.0
40°	28.3	27.2	26.3	26.3	25.5	23.5	23.5	23.5
42.5°	21.6	20.8	19.8	18.8	18.8	17.9	17.0	17.0
45°	17.9	17.9	17.0	17.0	16.0	16.0	16.0	16.0
47.5°	15.1	15.1	14.1	14.1	14.1	13.2	13.2	12.2
50°	9.5	8.4	8.4	7.5	7.5	6.7	6.7	6.7
52.5°	7.5	6.7	6.7	5.7	5.7	4.7	4.7	4.7
55°	5.7	5.7	4.7	4.7	4.7	3.7	3.7	3.7
57.5°	4.7	4.7	3.7	3.7	3.7	2.8	2.8	2.8
60°	4.7	3.7	3.7	2.8	2.8	2.8	2.0	2.0
62.5°	4.7	3.7	3.7	2.8	2.8	2.0	2.0	2.0
65°	4.7	3.7	3.7	2.8	2.8	2.8	2.8	2.0
67.5°	4.7	4.7	3.7	3.7	3.7	2.8	2.8	2.8
70°	5.7	4.7	4.7	3.7	3.7	3.7	3.7	2.8
72.5°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
75°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
77.5°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
80°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
82.5°	4.7	4.7	4.7	3.7	3.7	3.7	3.7	3.7
85°	3.7	3.7	3.7	2.8	2.8	2.8	2.8	2.0
87.5°	2.8	2.8	2.0	2.0	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)