

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192250

Luminaire Tested: **LDA6A40950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A40950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4461.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56415	56415	56415
5°	144502	52019	19068
10°	304704	41510	5394
15°	439441	29444	4484
20°	495981	19555	6318
25°	538513	19701	45505
30°	598959	12996	15914
35°	605132	7375	6110
40°	609156	3027	2762
45°	604156	1899	1613
50°	474236	1288	1126
55°	142714	908	545
60°	30151	822	406
65°	3412	973	363
70°	914	1202	593
75°	191	1589	784
80°	0	2652	1168
85°	0	4717	2327



TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	2.9
10°-20°	621.9	13.9
20°-30°	1172.6	26.3
30°-40°	1300.6	29.2
40°-50°	991.2	22.2
50°-60°	221.2	5.0
60°-70°	12.1	0.3
70°-80°	5.6	0.1
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1925.7	43.2
0°-40°	3226.3	72.3
0°-60°	4438.7	99.5
0°-90°	4461.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4461.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1029	1029	1029	1029	1029	
5°	2626	1945	945	454	346	340
15°	7743	4239	519	92	79	2159
25°	8903	4956	326	544	752	4144
35°	9042	3084	110	97	91	5664
45°	7793	908	24	26	21	5803
55°	1493	40	10	8	6	1843
65°	26	7	8	7	3	62
75°	1	4	8	7	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1
2.5°	1766.2	1735.1	1731.4	1721.0	1640.2	1639.1	1638.2	1595.9	1557.2	1537.4	1453.7
5°	2625.9	2603.2	2574.9	2539.3	2405.5	2386.7	2370.8	2307.7	2172.0	2093.0	1945.1
7.5°	3879.0	3866.8	3724.6	3705.7	3460.1	3399.8	3340.4	3178.6	2916.8	2747.3	2485.5
10°	5473.8	5415.6	5307.3	5160.4	4840.3	4726.4	4616.1	4284.8	3838.5	3483.6	3038.2
12.5°	6915.4	6841.0	6709.2	6537.9	6134.9	5979.5	5805.3	5398.5	4853.5	4276.3	3646.3
15°	7742.9	7730.6	7578.1	7508.5	7183.7	7025.5	6881.5	6413.5	5732.8	5054.0	4238.6
17.5°	8232.5	8233.5	8121.4	8080.0	7777.7	7627.2	7505.7	7164.9	6452.2	5628.4	4687.8
20°	8501.8	8529.0	8424.5	8359.6	8148.7	8015.1	7902.0	7550.8	6930.5	6016.2	4942.0
22.5°	8702.3	8715.4	8588.3	8534.8	8298.5	8169.4	8097.9	7761.8	7155.4	6223.3	5019.1
25°	8902.9	8896.3	8753.1	8645.8	8413.2	8288.1	8200.5	7909.5	7249.5	6271.3	4956.1
27.5°	9114.7	9144.7	8879.3	8707.9	8499.9	8353.0	8255.1	7954.8	7243.0	6146.2	4727.2
30°	9462.1	9218.2	8952.7	8716.4	8477.4	8322.0	8210.0	7827.7	7061.3	5813.7	4292.4
32.5°	9316.1	9143.9	8883.1	8640.1	8384.2	8212.8	8076.2	7622.4	6680.0	5266.8	3708.5
35°	9042.2	8996.1	8738.1	8540.4	8249.4	8064.9	7905.8	7306.1	6088.7	4608.7	3083.5
37.5°	8795.5	8747.5	8594.0	8389.7	8059.2	7866.2	7574.3	6803.4	5319.5	3784.9	2425.3
40°	8512.2	8500.9	8329.5	8140.2	7742.9	7387.0	7084.8	5916.4	4403.4	2976.1	1886.8
42.5°	8198.6	8192.0	8052.7	7773.1	7189.3	6747.7	6242.1	4915.7	3385.7	2258.6	1401.9
45°	7792.8	7754.2	7514.1	7106.4	6268.5	5630.1	5031.4	3755.6	2482.8	1613.8	907.6
47.5°	7089.5	7021.7	6671.5	5973.8	4969.2	4316.7	3766.0	2582.5	1548.8	912.4	450.1
50°	5560.6	5380.6	4881.8	4148.2	3118.2	2551.4	2118.4	1281.5	687.2	452.8	288.1
52.5°	3434.6	3240.6	2768.9	2215.4	1422.6	1102.5	909.5	617.7	380.3	260.8	111.1
55°	1493.2	1401.9	1157.1	920.8	658.1	523.4	451.9	312.6	197.7	95.1	39.6
57.5°	582.8	564.8	492.4	415.2	311.7	254.2	225.0	141.2	54.6	33.9	22.6
60°	275.0	257.1	221.2	183.6	114.9	82.8	64.0	39.6	27.2	20.8	15.1
62.5°	75.3	64.9	52.7	45.1	34.8	31.0	27.2	21.6	17.0	13.2	10.4
65°	26.3	26.3	23.5	21.6	17.9	16.0	15.1	12.2	10.4	8.4	6.7
67.5°	12.2	12.2	11.3	10.4	8.4	8.4	7.5	6.7	5.7	4.7	4.7
70°	5.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7	3.7	3.7
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.8	3.7	3.7	3.7
75°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	3.7
77.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	3.7
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	3.7
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	3.7	3.7	3.7
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.8	2.8	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1
2.5°	1417.9	1382.2	1335.0	1256.9	1222.1	1214.6	1150.4	1092.2	1040.4	1002.8	943.4
5°	1849.1	1745.5	1619.4	1467.8	1410.3	1369.9	1247.5	1130.7	1031.0	945.3	854.9
7.5°	2276.6	2071.3	1882.1	1660.8	1553.4	1472.5	1290.8	1125.2	974.5	857.7	738.2
10°	2688.0	2396.1	2076.0	1785.2	1641.0	1518.6	1280.4	1070.5	882.1	745.7	619.5
12.5°	3078.7	2659.7	2234.2	1847.2	1674.9	1521.5	1229.6	983.0	780.5	633.7	501.9
15°	3466.6	2850.8	2326.5	1860.5	1652.4	1467.8	1137.3	866.1	666.6	518.8	403.0
17.5°	3708.5	2957.2	2327.4	1802.0	1567.6	1366.1	1011.2	744.7	550.8	418.0	316.4
20°	3828.1	2944.0	2238.9	1667.4	1423.6	1220.1	862.4	620.5	445.3	335.2	249.5
22.5°	3793.3	2827.3	2083.6	1489.4	1263.5	1070.5	734.3	520.7	384.2	290.9	226.0
25°	3629.5	2638.1	1899.9	1321.8	1105.3	922.7	644.9	479.1	378.5	325.7	280.6
27.5°	3346.1	2389.6	1674.9	1145.8	951.0	805.0	584.7	465.1	391.7	351.2	355.0
30°	2928.1	2060.0	1384.0	910.4	744.7	626.1	438.8	323.9	239.1	205.3	205.3
32.5°	2460.1	1684.4	1069.5	673.1	538.5	454.8	308.9	221.2	176.9	161.0	153.4
35°	2021.4	1318.1	793.7	487.8	388.9	323.9	202.4	124.3	114.0	110.2	108.3
37.5°	1590.2	989.5	575.2	354.0	270.2	214.8	103.6	80.0	69.7	64.9	61.2
40°	1191.9	694.8	398.3	216.5	149.7	98.8	60.2	49.0	43.4	42.3	40.5
42.5°	834.2	466.0	246.7	95.1	69.7	55.5	41.4	34.8	32.0	31.0	30.2
45°	488.6	290.9	100.8	52.7	43.4	38.6	30.2	26.3	24.5	24.5	23.5
47.5°	306.9	117.7	53.7	33.9	29.2	27.2	22.6	19.8	18.8	18.8	18.8
50°	126.2	51.8	32.0	23.5	20.8	19.8	17.0	15.1	15.1	15.1	15.1
52.5°	46.1	29.2	21.6	17.0	15.1	14.1	12.2	11.3	11.3	12.2	11.3
55°	26.3	19.8	15.1	12.2	10.4	10.4	9.5	9.5	9.5	9.5	9.5
57.5°	17.0	13.2	10.4	8.4	7.5	7.5	7.5	7.5	7.5	8.4	7.5
60°	11.3	9.5	7.5	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5
62.5°	8.4	6.7	6.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5
65°	6.7	5.7	6.7	6.7	6.7	6.7	6.7	7.5	7.5	7.5	8.4
67.5°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4
70°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4
72.5°	4.7	4.7	5.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4
75°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	6.7	7.5	7.5	8.4
77.5°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5	8.4
80°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4	8.4
82.5°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	8.4	8.4
85°	4.7	5.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5	8.4
87.5°	4.7	4.7	5.7	5.7	5.7	6.7	6.7	7.5	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1
2.5°	902.9	861.4	827.6	809.6	790.0	756.1	724.0	694.8	682.6	643.0	650.5
5°	784.3	713.6	657.2	631.7	602.6	555.5	514.1	474.4	453.9	420.0	407.7
7.5°	652.5	569.6	501.9	472.7	447.2	403.0	364.4	327.7	301.3	266.4	252.4
10°	522.5	443.5	381.3	355.9	327.7	283.4	244.8	212.8	191.2	164.7	151.6
12.5°	413.3	342.7	279.7	254.2	230.7	194.0	163.8	134.6	111.1	96.9	93.2
15°	322.0	254.2	202.4	181.8	161.9	126.2	103.6	96.1	92.2	88.5	87.5
17.5°	242.0	187.3	141.2	120.4	109.2	99.8	96.1	92.2	90.4	87.5	88.5
20°	186.5	133.7	114.9	112.0	110.2	105.5	104.5	103.6	102.6	103.6	105.5
22.5°	176.9	166.7	172.2	176.1	184.5	185.5	200.6	212.8	224.1	255.1	270.2
25°	298.5	316.4	344.6	362.4	387.0	412.5	459.5	500.9	544.2	583.6	618.6
27.5°	373.8	382.2	382.2	391.7	381.3	379.5	373.8	369.1	388.9	382.2	403.0
30°	207.2	216.5	232.5	241.1	251.4	258.9	256.2	246.7	252.4	244.8	252.4
32.5°	147.9	147.9	151.6	152.6	154.3	155.4	156.3	157.2	158.1	153.4	156.3
35°	105.5	101.6	99.8	99.8	98.8	96.9	96.1	96.1	96.9	92.2	94.1
37.5°	59.3	57.4	57.4	57.4	57.4	57.4	58.4	59.3	59.3	59.3	61.2
40°	39.6	39.6	39.6	40.5	40.5	40.5	41.4	41.4	42.3	42.3	43.4
42.5°	30.2	29.2	30.2	30.2	30.2	31.0	31.0	32.0	32.0	32.0	33.0
45°	23.5	23.5	23.5	23.5	24.5	24.5	24.5	24.5	25.5	24.5	25.5
47.5°	18.8	18.8	18.8	19.8	19.8	18.8	19.8	19.8	19.8	19.8	19.8
50°	15.1	15.1	15.1	15.1	15.1	15.1	15.1	15.1	16.0	15.1	16.0
52.5°	12.2	11.3	11.3	11.3	11.3	10.4	10.4	11.3	11.3	10.4	10.4
55°	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
57.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7
60°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7	6.7	5.7
62.5°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7	5.7	5.7
65°	8.4	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7	5.7
67.5°	8.4	8.4	7.5	7.5	7.5	7.5	7.5	6.7	6.7	5.7	5.7
70°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7
72.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7
75°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7
77.5°	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7	5.7
80°	8.4	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	6.7	5.7
82.5°	7.5	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7	5.7
85°	7.5	7.5	7.5	7.5	7.5	6.7	6.7	6.7	5.7	5.7	5.7
87.5°	7.5	7.5	7.5	6.7	6.7	6.7	6.7	5.7	5.7	4.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192250

CATALOG NUMBER: LDA6A40950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1	1029.1
2.5°	611.1	597.8	609.1	595.1	590.3	579.9	575.2	579.9
5°	385.0	370.9	373.8	364.4	349.3	349.3	344.6	346.5
7.5°	232.5	218.5	219.4	210.9	199.7	197.7	193.0	194.9
10°	134.6	119.6	119.6	110.2	100.8	99.8	96.9	96.9
12.5°	89.4	87.5	85.7	84.8	82.8	82.8	82.8	81.0
15°	83.7	82.8	82.0	82.0	80.0	80.0	81.0	79.0
17.5°	85.7	84.8	83.7	83.7	83.7	83.7	84.8	82.8
20°	102.6	103.6	103.6	106.4	108.3	109.2	112.0	108.3
22.5°	269.3	277.7	284.3	319.2	349.3	338.0	358.7	323.9
25°	644.1	667.6	687.2	691.1	709.9	736.2	753.2	752.3
27.5°	403.0	403.8	415.2	415.2	411.4	426.5	436.8	435.0
30°	248.6	247.6	251.4	242.0	241.1	247.6	251.4	251.4
32.5°	153.4	152.6	155.4	153.4	148.7	156.3	154.3	154.3
35°	92.2	93.2	91.3	91.3	87.5	91.3	90.4	91.3
37.5°	60.2	59.3	58.4	58.4	56.5	57.4	56.5	54.6
40°	42.3	42.3	41.4	41.4	40.5	39.6	39.6	38.6
42.5°	32.0	32.0	31.0	31.0	30.2	29.2	29.2	28.3
45°	24.5	23.5	22.6	22.6	22.6	21.6	21.6	20.8
47.5°	18.8	18.8	18.8	17.9	17.9	17.0	17.0	16.0
50°	15.1	15.1	15.1	15.1	14.1	14.1	14.1	13.2
52.5°	10.4	10.4	9.5	9.5	8.4	8.4	8.4	7.5
55°	7.5	7.5	7.5	6.7	6.7	6.7	5.7	5.7
57.5°	6.7	6.7	5.7	5.7	5.7	4.7	4.7	4.7
60°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
62.5°	4.7	4.7	4.7	3.7	3.7	3.7	3.7	2.8
65°	4.7	4.7	3.7	3.7	3.7	2.8	2.8	2.8
67.5°	4.7	4.7	4.7	3.7	3.7	3.7	3.7	2.8
70°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
72.5°	5.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7
75°	5.7	5.7	4.7	4.7	4.7	4.7	4.7	3.7
77.5°	5.7	4.7	4.7	4.7	4.7	4.7	3.7	3.7
80°	5.7	4.7	4.7	4.7	4.7	3.7	3.7	3.7
82.5°	5.7	4.7	4.7	4.7	3.7	3.7	3.7	3.7
85°	4.7	4.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	3.7	3.7	2.8	2.8	2.8	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)