

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192327

Luminaire Tested: **LDA6A45950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26671)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4907.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 2.69 / 0.5 / 1.42
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	89	102	97	92	88	94	90	86	91	87	85	88	85	83	81		
3	98	89	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72		
4	91	81	74	69	89	80	73	68	78	72	68	75	71	67	73	69	66	64		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	78	67	60	54	77	66	59	54	65	58	53	63	57	53	62	57	53	51		
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41		
9	63	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	38	37		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	41225	41225	41225
5°	108678	37552	12926
10°	219574	29236	7854
15°	404321	21918	11334
20°	626852	17531	18872
25°	735980	15545	23959
30°	798034	15629	18566
35°	841471	9316	9985
40°	863096	3965	4322
45°	808572	1566	1481
50°	565363	682	350
55°	198378	679	0
60°	40008	778	0
65°	2478	921	0
70°	481	1282	0
75°	0	1694	0
80°	0	2526	316
85°	0	5661	629

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	2.0
10°-20°	538.0	11.0
20°-30°	1271.8	25.9
30°-40°	1549.3	31.6
40°-50°	1152.4	23.5
50°-60°	279.0	5.7
60°-70°	10.3	0.2
70°-80°	5.0	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1906.2	38.8
0°-40°	3455.4	70.4
0°-60°	4886.9	99.6
0°-90°	4907.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4907.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	752	752	752	752	752	
5°	1975	1477	682	319	235	248
15°	7124	3088	386	177	200	2147
25°	12168	3872	257	373	396	5587
35°	12574	2828	139	151	149	7831
45°	10430	1078	20	22	19	7661
55°	2076	23	7	5	0	2348
65°	19	5	7	5	0	64
75°	0	5	8	6	0	0
85°	0	5	9	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0
2.5°	1311.4	1289.4	1287.3	1265.2	1257.0	1254.0	1222.8	1211.7	1170.3	1162.3	1103.8
5°	1974.9	1940.6	1933.5	1883.1	1845.8	1794.3	1767.2	1720.8	1623.0	1571.5	1476.8
7.5°	2809.5	2764.1	2754.0	2675.5	2597.8	2530.2	2473.7	2366.0	2186.5	2063.5	1869.9
10°	3944.5	3817.6	3771.2	3604.8	3444.6	3318.6	3253.1	3016.1	2746.0	2580.7	2310.6
12.5°	5386.1	5174.4	5087.7	4830.7	4548.3	4341.8	4214.7	3842.8	3403.2	3086.7	2700.7
15°	7124.1	6878.0	6722.9	6399.3	5886.2	5591.8	5366.9	4771.3	4130.0	3651.2	3087.7
17.5°	9016.3	8823.7	8591.9	8084.8	7258.1	6904.2	6496.0	5714.8	4835.8	4169.4	3433.5
20°	10745.1	10422.5	10248.1	9683.5	8725.9	8259.2	7756.1	6585.8	5459.8	4591.8	3698.7
22.5°	11681.6	11369.1	11264.2	10774.3	9896.2	9377.2	8737.0	7352.9	5938.5	4881.1	3839.8
25°	12167.5	11882.2	11889.3	11446.7	10654.4	10166.4	9515.2	7932.5	6265.2	5033.3	3872.0
27.5°	12547.5	12196.7	12135.1	11804.5	11099.9	10600.9	9972.9	8248.0	6385.1	5017.2	3784.2
30°	12607.0	12319.7	12364.0	11904.4	11261.1	10742.1	10088.7	8231.0	6262.2	4814.6	3556.5
32.5°	12566.6	12281.4	12383.2	11884.2	11191.6	10622.0	9895.3	7896.3	5901.3	4439.6	3221.8
35°	12573.7	12246.1	12170.5	11748.0	10923.5	10255.1	9378.2	7285.3	5368.0	3951.7	2827.7
37.5°	12423.4	11981.9	11995.2	11438.5	10405.3	9519.3	8526.2	6470.9	4736.9	3430.5	2431.5
40°	12060.7	11730.0	11625.1	10798.5	9419.4	8381.2	7423.5	5585.7	4007.1	2886.1	1966.7
42.5°	11543.5	11145.3	10837.8	9692.7	8022.2	7069.7	6242.1	4663.4	3317.6	2366.0	1527.2
45°	10429.5	9999.1	9403.4	8029.2	6614.9	5788.3	5097.8	3785.3	2683.5	1828.7	1077.6
47.5°	8556.5	8152.2	7539.4	6385.1	5281.3	4592.8	4054.4	2964.8	1961.6	1153.3	534.4
50°	6629.1	6321.6	5853.8	4851.9	3929.4	3285.3	2805.5	1861.9	1001.1	526.1	223.8
52.5°	4320.6	4102.8	3686.5	2924.5	2220.7	1741.0	1415.3	792.4	471.7	221.7	65.5
55°	2075.6	1962.7	1661.4	1204.7	871.9	715.7	604.9	384.1	178.5	53.4	23.1
57.5°	827.6	803.5	715.7	539.3	413.4	350.8	272.2	105.9	35.3	22.3	14.0
60°	364.9	353.8	296.4	196.6	105.9	60.4	44.3	26.2	17.2	13.1	9.0
62.5°	52.4	48.4	41.4	32.3	26.2	22.3	19.1	14.0	9.0	7.1	6.0
65°	19.1	19.1	17.2	14.0	12.2	11.1	10.1	7.1	5.0	5.0	5.0
67.5°	8.0	8.0	8.0	6.0	6.0	5.0	4.1	4.1	4.1	4.1	5.0
70°	3.0	3.0	3.0	2.1	2.1	2.1	3.0	3.0	3.0	4.1	5.0
72.5°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	5.0
75°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	5.0
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
80°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	5.0	5.0
85°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0
2.5°	1054.5	1040.3	992.9	945.6	938.5	918.3	877.0	828.7	766.2	726.9	687.4
5°	1353.9	1283.3	1203.7	1112.0	1083.7	1043.3	956.6	863.9	760.0	682.4	610.0
7.5°	1703.6	1546.4	1396.2	1249.0	1193.6	1131.0	999.0	865.9	723.7	610.9	520.1
10°	2031.3	1789.3	1556.5	1347.7	1265.2	1180.4	1003.0	831.7	655.3	525.2	432.5
12.5°	2357.9	2011.2	1692.5	1419.4	1307.5	1198.6	980.9	770.1	570.6	446.6	372.0
15°	2615.0	2211.7	1791.4	1455.7	1316.6	1183.5	926.3	685.5	488.0	386.2	319.6
17.5°	2793.3	2326.6	1828.7	1440.5	1281.2	1131.0	840.7	586.7	421.4	338.7	274.2
20°	2916.4	2362.9	1802.4	1378.0	1205.6	1040.3	732.9	498.1	374.0	300.5	236.0
22.5°	2950.6	2327.6	1727.8	1284.3	1106.9	936.4	621.0	439.5	339.8	270.2	228.8
25°	2917.4	2238.0	1615.8	1172.4	985.9	807.5	527.2	404.2	313.5	257.0	266.1
27.5°	2796.5	2079.7	1460.7	1028.2	836.7	668.3	463.7	361.9	276.2	271.2	282.3
30°	2596.8	1852.9	1276.2	843.8	661.3	533.3	389.1	285.3	241.9	246.9	254.1
32.5°	2309.5	1574.7	1039.3	625.0	484.8	401.2	278.2	197.6	191.5	195.5	200.5
35°	1946.6	1281.2	778.2	431.5	343.7	276.2	163.3	140.1	137.1	139.2	141.1
37.5°	1579.7	990.0	529.3	290.4	208.7	140.1	97.9	91.7	89.6	90.7	91.7
40°	1225.7	688.5	332.6	139.2	81.6	69.5	60.4	57.5	55.4	55.4	56.5
42.5°	895.2	408.3	165.3	54.4	44.3	41.4	36.3	34.2	32.3	33.2	34.2
45°	501.0	181.4	56.5	30.3	27.2	25.2	22.3	21.2	20.2	20.2	20.2
47.5°	213.7	63.4	27.2	19.1	17.2	16.1	14.0	13.1	12.2	12.2	12.2
50°	70.5	25.2	17.2	13.1	11.1	10.1	9.0	8.0	8.0	8.0	9.0
52.5°	25.2	16.1	11.1	9.0	8.0	8.0	7.1	7.1	7.1	7.1	7.1
55°	15.1	11.1	8.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
57.5°	10.1	7.1	7.1	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1
60°	7.1	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1
62.5°	6.0	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1
65°	5.0	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1
67.5°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0
70°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0
72.5°	5.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0
75°	5.0	6.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	8.0	8.0
77.5°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	8.0
80°	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	8.0	9.0
82.5°	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	8.0	9.0
85°	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	9.0	9.0
87.5°	6.0	6.0	7.1	7.1	7.1	8.0	8.0	8.0	8.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0
2.5°	647.1	616.9	574.6	560.6	531.2	510.0	486.9	460.6	455.6	429.4	426.4
5°	539.3	490.9	442.5	424.3	399.2	377.9	354.8	329.7	318.6	293.3	278.2
7.5°	444.5	398.2	354.8	336.8	312.4	285.3	258.0	231.8	216.7	192.5	180.4
10°	372.9	326.7	280.3	262.1	239.9	209.8	180.4	153.3	143.2	137.1	138.1
12.5°	311.6	265.2	218.8	198.6	175.3	151.2	150.2	148.2	152.3	151.2	152.3
15°	261.1	211.6	167.3	161.3	161.3	165.3	169.4	170.4	177.4	177.4	179.5
17.5°	214.8	180.4	182.4	182.4	186.5	193.5	201.6	205.6	216.7	217.8	221.7
20°	199.7	207.7	216.7	218.8	225.8	236.9	247.9	256.2	270.2	274.2	282.3
22.5°	236.9	251.1	265.2	269.2	278.2	294.3	314.5	321.6	338.7	338.7	349.8
25°	279.2	300.5	314.5	319.6	329.7	343.7	356.9	360.9	372.9	368.9	372.9
27.5°	296.4	311.6	320.6	325.6	327.6	339.8	345.8	343.7	351.8	345.8	345.8
30°	263.1	274.2	279.2	282.3	282.3	291.4	291.4	288.3	293.3	288.3	285.3
32.5°	206.6	214.8	218.8	218.8	217.8	223.8	221.7	217.8	219.8	216.7	209.8
35°	144.2	150.2	153.3	152.3	151.2	156.2	153.3	150.2	151.2	149.2	144.2
37.5°	94.7	95.8	97.9	99.7	98.8	102.9	100.8	98.8	99.7	97.9	94.7
40°	57.5	59.5	61.5	61.5	61.5	62.5	62.5	61.5	63.4	61.5	59.5
42.5°	34.2	36.3	36.3	36.3	37.3	37.3	38.3	36.3	38.3	36.3	35.3
45°	21.2	21.2	21.2	22.3	21.2	22.3	22.3	21.2	22.3	21.2	20.2
47.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	12.2	13.1	12.2	11.1
50°	8.0	9.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0
52.5°	7.1	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	4.1
55°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.0	5.0	4.1	3.0
57.5°	7.1	7.1	6.0	6.0	6.0	6.0	5.0	5.0	4.1	3.0	3.0
60°	7.1	7.1	7.1	6.0	6.0	6.0	5.0	5.0	4.1	3.0	3.0
62.5°	7.1	7.1	7.1	6.0	6.0	6.0	6.0	5.0	4.1	3.0	3.0
65°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	5.0	4.1	3.0
67.5°	8.0	7.1	7.1	7.1	7.1	7.1	6.0	5.0	5.0	4.1	3.0
70°	8.0	8.0	7.1	7.1	7.1	7.1	6.0	6.0	5.0	4.1	3.0
72.5°	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0	5.0	4.1	4.1
75°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0	5.0	4.1
77.5°	9.0	8.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0	4.1
80°	9.0	9.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0	4.1
82.5°	9.0	9.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	5.0	4.1
85°	9.0	9.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0	4.1
87.5°	9.0	9.0	8.0	8.0	8.0	8.0	7.1	6.0	6.0	5.0	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192327

CATALOG NUMBER: LDA6A45950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	752.0	752.0	752.0	752.0	752.0	752.0	752.0	752.0
2.5°	408.3	406.2	399.2	401.2	396.1	385.1	386.2	382.1
5°	268.1	262.1	255.1	255.1	247.9	237.8	237.8	234.9
7.5°	163.3	154.2	147.2	146.1	139.2	134.2	134.2	133.1
10°	138.1	139.2	139.2	140.1	139.2	139.2	140.1	141.1
12.5°	155.2	158.3	158.3	159.3	158.3	160.3	160.3	162.3
15°	185.4	190.4	191.5	193.5	192.5	195.5	197.6	199.7
17.5°	232.9	238.9	241.0	246.9	246.1	249.0	251.1	255.1
20°	293.3	302.3	305.4	313.5	312.4	315.5	320.6	323.5
22.5°	360.9	372.0	372.9	380.0	379.0	382.1	384.1	385.1
25°	379.0	386.2	385.1	389.1	389.1	390.1	390.1	396.1
27.5°	346.8	351.8	351.8	351.8	352.8	353.8	353.8	358.8
30°	285.3	287.2	288.3	285.3	287.2	288.3	288.3	293.3
32.5°	211.6	212.7	213.7	209.8	212.7	212.7	212.7	216.7
35°	146.1	146.1	147.2	144.2	146.1	147.2	146.1	149.2
37.5°	95.8	95.8	95.8	95.8	95.8	95.8	94.7	97.9
40°	59.5	60.4	59.5	59.5	58.4	58.4	58.4	60.4
42.5°	35.3	35.3	34.2	34.2	34.2	34.2	35.3	35.3
45°	20.2	20.2	19.1	19.1	18.1	19.1	19.1	19.1
47.5°	11.1	10.1	10.1	10.1	9.0	9.0	9.0	10.1
50°	5.0	5.0	5.0	4.1	4.1	4.1	3.0	4.1
52.5°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	1.0
55°	2.1	2.1	1.0	1.0	0.0	0.0	0.0	0.0
57.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
60°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.1	2.1	1.0	1.0	0.0	0.0	0.0
72.5°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.0	3.0	2.1	2.1	1.0	1.0	1.0	1.0
80°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
82.5°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
85°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
87.5°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)