

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192333

Luminaire Tested: **LDA6A45950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26672)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5118.7 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 2.54 / 0.51 / 1.33
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	101	99			99	97	96			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	89	83	79		86	81	77			84	80	76			81
4	92	82	75	70	90	81	75	70		79	73	69			77	72	68			75
5	85	75	68	62	83	74	67	62		72	66	62			70	65	61			69
6	80	69	61	56	78	68	61	56		66	60	55			64	59	55			63
7	74	63	55	50	73	62	55	50		61	54	50			59	54	49			58
8	69	58	50	45	68	57	50	45		56	49	45			55	49	45			54
9	65	53	46	41	64	53	46	41		52	45	41			51	45	41			50
10	61	49	42	37	60	49	42	37		48	41	37			47	41	37			46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	62988	62988	62988
5°	161077	58078	21192
10°	346186	46848	7799
15°	505003	34262	8922
20°	571851	24636	13762
25°	619923	19816	21340
30°	691701	16268	20547
35°	702070	10520	13692
40°	707246	5045	6927
45°	702825	2109	2892
50°	562711	947	947
55°	167812	679	96
60°	34252	778	0
65°	3269	921	0
70°	337	1282	0
75°	0	1694	0
80°	0	2841	316
85°	0	5661	629

TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	2.9
10°-20°	717.9	14.0
20°-30°	1319.4	25.8
30°-40°	1513.8	29.6
40°-50°	1145.3	22.4
50°-60°	253.8	5.0
60°-70°	10.7	0.2
70°-80°	4.7	0.1
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2185.7	42.7
0°-40°	3699.5	72.3
0°-60°	5098.6	99.6
0°-90°	5118.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5118.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1149	1149	1149	1149	1149	
5°	2927	2186	1055	516	385	387
15°	8898	4826	604	156	157	2480
25°	10249	5675	328	318	353	4782
35°	10491	3503	157	197	205	6571
45°	9066	991	27	35	37	6765
55°	1756	37	7	5	1	2174
65°	25	5	7	4	0	67
75°	0	4	8	5	0	0
85°	0	5	9	5	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0
2.5°	1946.4	1927.2	1932.2	1956.4	1856.6	1853.6	1807.3	1801.2	1754.8	1670.1	1627.8
5°	2927.1	2915.0	2893.8	2901.9	2787.9	2711.3	2630.7	2572.2	2453.4	2293.0	2186.3
7.5°	4491.3	4360.3	4296.9	4174.9	4029.8	3881.6	3732.5	3559.0	3309.1	3029.8	2804.0
10°	6219.0	6161.5	6031.5	5954.0	5632.3	5414.7	5182.8	4828.1	4370.4	3864.4	3443.1
12.5°	7912.3	7844.8	7648.4	7482.9	7054.5	6860.0	6558.8	6111.1	5530.5	4809.9	4143.6
15°	8898.1	8913.2	8690.4	8682.4	8313.6	8060.5	7799.5	7270.3	6533.5	5706.0	4826.0
17.5°	9475.6	9513.0	9292.3	9354.7	8986.7	8724.8	8530.3	8143.1	7360.0	6367.2	5353.2
20°	9802.3	9861.7	9626.9	9675.3	9360.7	9183.3	8985.8	8602.8	7911.3	6815.7	5652.5
22.5°	10051.2	10074.5	9813.3	9877.9	9534.2	9356.8	9216.7	8857.8	8175.4	7052.7	5746.3
25°	10248.8	10307.1	10009.0	10014.0	9672.2	9494.8	9339.6	9013.1	8288.4	7115.1	5674.8
27.5°	10533.0	10580.3	10141.9	10103.6	9773.0	9577.5	9409.1	9087.6	8283.3	6976.0	5404.6
30°	10927.2	10663.0	10214.5	10115.7	9743.8	9545.1	9364.8	8947.5	8097.8	6601.0	4913.8
32.5°	10814.2	10600.5	10158.1	10000.7	9631.9	9419.2	9212.5	8704.6	7667.4	6020.4	4244.3
35°	10490.7	10422.2	9957.5	9908.1	9461.5	9238.7	9031.2	8336.6	7007.2	5261.5	3502.6
37.5°	10217.5	10100.6	9801.3	9723.6	9255.0	9009.0	8678.4	7787.4	6134.3	4293.8	2797.0
40°	9882.9	9804.3	9515.0	9432.4	8890.0	8515.1	8111.0	6791.5	5080.1	3342.4	2160.1
42.5°	9527.0	9456.5	9183.3	9010.0	8287.3	7791.4	7163.5	5585.9	3910.8	2518.9	1618.8
45°	9065.5	8965.6	8624.0	8301.4	7265.3	6555.6	5849.1	4262.6	2862.5	1793.1	990.8
47.5°	8272.2	8113.9	7699.6	7051.6	5778.6	5097.1	4361.3	2890.8	1767.9	923.3	498.9
50°	6598.0	6321.8	5770.4	4999.4	3701.2	3048.0	2471.5	1469.6	759.0	475.8	293.3
52.5°	4066.1	3813.1	3343.3	2599.5	1706.5	1314.4	1035.2	684.3	418.3	269.2	108.8
55°	1755.8	1597.5	1372.8	1047.2	743.9	611.8	491.8	341.6	215.7	82.7	37.3
57.5°	663.3	615.9	558.4	458.6	342.7	286.2	240.9	151.2	52.4	31.3	21.2
60°	312.4	283.3	249.9	198.6	131.0	94.7	59.5	38.3	25.2	17.2	12.2
62.5°	85.7	64.5	53.4	43.3	33.2	29.2	25.2	19.1	14.0	9.0	7.1
65°	25.2	22.3	21.2	18.1	15.1	13.1	11.1	9.0	7.1	5.0	5.0
67.5°	9.0	9.0	8.0	7.1	6.0	5.0	5.0	4.1	4.1	4.1	4.1
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.0	3.0	4.1	4.1
72.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
75°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
80°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
85°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0
2.5°	1592.6	1534.1	1451.4	1409.1	1371.8	1361.8	1285.1	1235.7	1177.3	1116.9	1053.3
5°	2086.4	1937.3	1779.0	1646.0	1578.4	1539.1	1389.9	1278.2	1170.2	1055.4	957.5
7.5°	2576.3	2309.2	2078.3	1863.7	1745.7	1657.0	1443.4	1275.0	1111.8	962.5	830.5
10°	3050.0	2665.0	2297.2	2006.8	1844.5	1712.5	1436.3	1217.6	1013.0	841.6	703.6
12.5°	3529.8	2968.4	2479.5	2083.4	1889.9	1720.6	1388.0	1121.8	905.2	723.7	580.6
15°	3958.1	3204.2	2593.4	2101.5	1867.7	1668.2	1293.2	999.9	784.3	603.7	478.8
17.5°	4255.5	3331.3	2600.4	2035.1	1775.0	1560.3	1161.2	871.8	662.3	502.9	393.1
20°	4390.6	3327.2	2504.7	1897.0	1624.8	1401.0	1005.0	740.8	552.3	422.3	328.6
22.5°	4350.2	3200.2	2335.4	1701.4	1441.3	1217.6	859.9	624.9	474.8	362.9	288.3
25°	4148.7	2978.5	2136.8	1505.8	1243.7	1035.2	728.8	534.2	412.3	327.6	262.1
27.5°	3819.1	2676.0	1869.7	1277.1	1037.1	875.0	613.8	461.6	362.9	289.3	273.2
30°	3337.3	2309.2	1556.3	1030.1	837.6	692.5	497.8	371.9	290.3	257.0	258.0
32.5°	2806.1	1905.0	1223.6	787.2	631.0	534.2	367.8	260.0	212.7	210.6	211.6
35°	2277.0	1483.7	910.2	575.5	462.6	385.1	236.9	163.3	158.3	157.2	159.2
37.5°	1807.3	1103.6	656.1	402.2	306.4	234.8	128.0	110.9	106.9	108.8	109.8
40°	1349.6	774.2	443.5	237.8	149.1	107.8	77.7	71.6	69.5	70.5	70.5
42.5°	928.3	483.8	264.2	98.7	71.6	59.5	49.4	46.4	44.3	43.3	44.3
45°	499.9	301.4	102.9	50.4	42.3	38.3	31.3	29.2	28.2	27.2	27.2
47.5°	319.6	111.9	46.4	31.3	27.2	25.2	21.2	19.1	18.1	17.2	17.2
50°	119.9	43.3	28.2	20.2	17.2	16.1	13.1	12.2	11.1	11.1	11.1
52.5°	41.4	26.2	18.1	13.1	11.1	10.1	9.0	8.0	8.0	8.0	8.0
55°	23.1	16.1	11.1	8.0	8.0	7.1	7.1	7.1	7.1	7.1	7.1
57.5°	14.0	9.0	7.1	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1
60°	8.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1
62.5°	5.0	5.0	5.0	5.0	5.0	6.0	6.0	7.1	7.1	7.1	7.1
65°	5.0	5.0	5.0	5.0	5.0	6.0	6.0	7.1	7.1	7.1	7.1
67.5°	4.1	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	8.0	7.1
70°	5.0	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0
72.5°	5.0	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0
75°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0	8.0
77.5°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0	8.0
80°	5.0	5.0	6.0	7.1	7.1	7.1	7.1	8.0	8.0	9.0	9.0
82.5°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	9.0	9.0	9.0
85°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	9.0	9.0	9.0
87.5°	5.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	9.0	9.0	9.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0
2.5°	1019.0	960.6	913.2	914.3	875.0	844.7	806.3	785.2	768.0	739.8	713.6
5°	886.0	796.2	728.8	715.6	670.3	623.9	576.6	541.3	516.2	488.8	463.6
7.5°	741.8	639.0	561.5	543.3	505.0	461.6	418.3	383.0	352.8	323.5	293.3
10°	601.7	507.9	437.4	419.3	381.0	335.6	294.3	263.1	239.8	216.7	193.5
12.5°	486.8	404.2	337.7	314.5	283.3	247.9	214.7	184.4	159.2	149.1	146.1
15°	394.2	315.4	263.1	244.0	217.8	181.4	162.3	157.2	156.2	156.2	156.2
17.5°	318.6	257.0	209.6	189.5	176.4	174.3	174.3	174.3	175.3	177.4	181.4
20°	267.1	212.7	194.5	196.6	196.6	198.6	202.6	205.6	209.6	214.7	220.7
22.5°	236.9	225.8	223.8	229.7	230.8	236.9	244.9	251.0	258.0	266.0	271.1
25°	259.1	263.1	266.0	275.1	278.2	288.3	300.4	309.5	317.5	326.6	332.6
27.5°	282.3	289.3	295.3	304.4	306.4	319.6	329.7	335.6	341.6	345.7	349.8
30°	266.0	273.2	279.2	287.2	287.2	301.4	306.4	311.4	316.5	318.6	322.5
32.5°	218.8	225.8	231.8	237.8	238.9	249.0	255.0	257.0	261.0	262.1	265.0
35°	164.2	167.3	173.4	178.5	179.4	186.5	191.5	193.5	196.6	196.6	198.6
37.5°	112.9	114.9	119.9	123.0	125.0	130.0	133.1	135.0	137.1	138.1	139.0
40°	73.5	74.6	77.7	80.6	82.7	85.7	87.8	89.6	90.7	92.8	92.8
42.5°	45.3	46.4	48.4	50.4	50.4	53.4	54.4	56.5	57.5	58.4	58.4
45°	28.2	29.2	29.2	30.3	31.3	32.3	34.2	34.2	35.3	35.3	35.3
47.5°	17.2	18.1	17.2	18.1	18.1	19.1	20.2	20.2	20.2	20.2	20.2
50°	11.1	11.1	11.1	11.1	11.1	11.1	12.2	12.2	12.2	12.2	11.1
52.5°	8.0	8.0	7.1	8.0	7.1	7.1	7.1	7.1	7.1	7.1	6.0
55°	7.1	7.1	7.1	7.1	6.0	6.0	6.0	5.0	5.0	4.1	4.1
57.5°	7.1	7.1	6.0	6.0	6.0	5.0	5.0	5.0	4.1	4.1	3.0
60°	7.1	7.1	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0	3.0
62.5°	7.1	7.1	6.0	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0
65°	7.1	7.1	7.1	6.0	6.0	6.0	5.0	5.0	4.1	4.1	3.0
67.5°	7.1	7.1	7.1	7.1	6.0	6.0	6.0	5.0	4.1	4.1	3.0
70°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.0	5.0	4.1	3.0
72.5°	8.0	8.0	7.1	7.1	7.1	6.0	6.0	5.0	5.0	4.1	4.1
75°	8.0	8.0	7.1	7.1	7.1	6.0	6.0	5.0	5.0	4.1	4.1
77.5°	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0	5.0	5.0	4.1
80°	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0	5.0	5.0	4.1
82.5°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	5.0	5.0	4.1
85°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	5.0	5.0	4.1
87.5°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	5.0	5.0	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192333

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0
2.5°	689.4	676.3	675.3	664.2	642.1	653.2	639.0	628.9
5°	441.4	427.3	413.3	415.3	399.2	402.2	391.0	385.1
7.5°	280.2	265.0	261.0	261.0	242.9	242.9	235.9	231.8
10°	176.4	164.2	160.3	153.3	145.1	144.0	141.1	140.1
12.5°	143.2	143.2	140.1	141.1	141.1	141.1	140.1	140.1
15°	156.2	157.2	154.1	155.2	157.2	156.2	157.2	157.2
17.5°	180.4	185.4	181.4	183.5	187.5	186.5	187.5	188.6
20°	220.7	228.8	223.8	227.9	232.9	231.8	234.8	235.9
22.5°	275.1	285.2	280.2	284.2	292.3	290.3	294.3	296.3
25°	335.6	345.7	339.8	344.8	349.8	351.7	351.7	352.8
27.5°	349.8	355.8	351.7	356.8	358.8	360.8	358.8	359.8
30°	320.4	325.5	321.5	326.6	326.6	328.6	326.6	324.6
32.5°	264.2	268.1	263.1	269.2	268.1	269.2	270.1	271.1
35°	199.5	201.6	198.6	199.5	200.5	201.6	204.6	204.6
37.5°	139.0	142.2	139.0	140.1	140.1	142.2	144.0	144.0
40°	92.8	95.8	92.8	94.7	93.7	94.7	96.8	96.8
42.5°	58.4	60.4	58.4	59.5	59.5	59.5	60.4	61.5
45°	35.3	36.3	35.3	36.3	36.3	36.3	37.3	37.3
47.5°	20.2	21.2	20.2	20.2	21.2	20.2	21.2	21.2
50°	11.1	11.1	11.1	11.1	11.1	10.1	10.1	11.1
52.5°	6.0	6.0	5.0	5.0	5.0	5.0	5.0	5.0
55°	3.0	3.0	2.1	2.1	2.1	1.0	2.1	1.0
57.5°	2.1	2.1	1.0	1.0	1.0	1.0	0.0	0.0
60°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
62.5°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
65°	2.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
67.5°	3.0	2.1	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.1	2.1	1.0	1.0	0.0	0.0	0.0
72.5°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.0	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.0	3.0	2.1	2.1	1.0	1.0	1.0	0.0
80°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
82.5°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
85°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
87.5°	3.0	3.0	2.1	2.1	2.1	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)