

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192335

Luminaire Tested: **LDA6A45950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4776.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 53.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	60401	60401	60401
5°	154705	55690	20416
10°	326224	44438	5778
15°	470468	31521	4807
20°	531008	20932	6767
25°	576535	21098	48717
30°	641251	13914	17041
35°	647855	7890	6552
40°	652165	3242	2963
45°	646819	2031	1729
50°	507719	1373	1194
55°	152797	965	573
60°	32267	877	450
65°	3658	1038	389
70°	962	1282	657
75°	212	1694	868
80°	0	2841	1294
85°	0	5032	2579



TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	2.9
10°-20°	665.8	13.9
20°-30°	1255.4	26.3
30°-40°	1392.5	29.2
40°-50°	1061.2	22.2
50°-60°	236.8	5.0
60°-70°	12.9	0.3
70°-80°	5.9	0.1
80°-90°	5.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2061.7	43.2
0°-40°	3454.2	72.3
0°-60°	4752.1	99.5
0°-90°	4776.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4776.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1102	1102	1102	1102	1102	
5°	2811	2082	1012	486	371	364
15°	8290	4538	555	99	85	2311
25°	9532	5306	349	583	805	4436
35°	9681	3301	118	104	98	6064
45°	8343	972	26	27	22	6213
55°	1599	42	10	9	6	1974
65°	28	7	8	7	3	66
75°	1	4	8	7	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8
2.5°	1891.0	1857.6	1853.7	1842.6	1755.9	1754.9	1753.9	1708.5	1667.2	1646.0	1556.4
5°	2811.3	2787.0	2756.8	2718.6	2575.4	2555.2	2538.1	2470.5	2325.4	2240.8	2082.5
7.5°	4152.9	4139.8	3987.6	3967.4	3704.4	3639.9	3576.4	3403.0	3122.7	2941.3	2661.0
10°	5860.4	5798.0	5682.0	5524.8	5182.0	5060.1	4942.2	4587.3	4109.6	3729.5	3252.7
12.5°	7403.7	7324.1	7183.0	6999.5	6568.0	6401.7	6215.2	5779.8	5196.2	4578.3	3903.8
15°	8289.6	8276.5	8113.2	8038.7	7690.9	7521.6	7367.4	6866.4	6137.6	5410.8	4537.9
17.5°	8813.9	8814.8	8694.8	8650.5	8327.0	8165.7	8035.7	7670.7	6907.7	6025.8	5018.7
20°	9102.2	9131.3	9019.4	8949.9	8724.1	8581.0	8460.1	8084.0	7419.8	6441.0	5290.9
22.5°	9316.7	9330.9	9194.7	9137.4	8884.4	8746.3	8669.6	8309.9	7660.6	6662.8	5373.6
25°	9531.5	9524.4	9371.2	9256.3	9007.3	8873.3	8779.6	8468.1	7761.5	6714.1	5306.1
27.5°	9758.3	9790.5	9506.3	9322.9	9100.1	8942.9	8838.0	8516.5	7754.3	6580.2	5061.1
30°	10130.2	9869.2	9585.0	9331.9	9075.9	8909.6	8789.7	8380.4	7559.9	6224.3	4595.4
32.5°	9974.0	9789.6	9510.4	9250.3	8976.1	8792.7	8646.5	8160.7	7151.7	5638.7	3970.4
35°	9680.6	9631.3	9355.1	9143.5	8832.0	8634.4	8464.0	7821.9	6518.6	4934.2	3301.2
37.5°	9416.6	9365.2	9200.9	8982.1	8628.3	8421.7	8109.2	7283.7	5695.1	4052.0	2596.6
40°	9113.2	9101.1	8917.6	8715.0	8289.6	7908.7	7585.1	6334.1	4714.3	3186.1	2020.0
42.5°	8777.5	8770.4	8621.3	8321.9	7697.0	7224.2	6682.9	5262.7	3624.7	2418.1	1500.9
45°	8343.1	8301.8	8044.7	7608.2	6711.2	6027.7	5386.7	4020.8	2658.0	1727.6	971.8
47.5°	7590.1	7517.5	7142.6	6395.6	5320.1	4621.6	4032.0	2764.9	1658.2	976.8	481.8
50°	5953.2	5760.7	5226.4	4441.2	3338.4	2731.6	2267.9	1372.0	735.8	484.8	308.5
52.5°	3677.1	3469.4	2964.4	2371.8	1523.1	1180.3	973.6	661.2	407.2	279.2	118.9
55°	1598.7	1500.9	1238.8	985.8	704.6	560.5	483.8	334.7	211.6	101.8	42.3
57.5°	624.0	604.8	527.2	444.5	333.6	272.2	240.9	151.2	58.4	36.3	24.1
60°	294.3	275.2	236.9	196.6	123.0	88.6	68.5	42.3	29.2	22.3	16.1
62.5°	80.6	69.5	56.5	48.4	37.3	33.2	29.2	23.1	18.1	14.0	11.1
65°	28.2	28.2	25.2	23.1	19.1	17.2	16.1	13.1	11.1	9.0	7.1
67.5°	13.1	13.1	12.2	11.1	9.0	9.0	8.0	7.1	6.0	5.0	5.0
70°	6.0	5.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1	4.1	4.1
72.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.0	4.1	4.1	4.1
75°	1.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	4.1
77.5°	0.0	1.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	4.1
80°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	4.1
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
85°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	4.1	4.1	4.1
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.0	3.0	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8
2.5°	1518.1	1479.7	1429.3	1345.7	1308.3	1300.3	1231.8	1169.3	1113.8	1073.6	1009.9
5°	1979.6	1868.8	1733.8	1571.4	1510.0	1466.6	1335.6	1210.6	1103.8	1012.0	915.3
7.5°	2437.3	2217.6	2014.9	1778.1	1663.2	1576.5	1382.0	1204.6	1043.3	918.2	790.3
10°	2877.8	2565.3	2222.6	1911.2	1756.9	1625.8	1370.9	1146.1	944.4	798.3	663.3
12.5°	3296.2	2847.5	2392.0	1977.7	1793.2	1629.0	1316.3	1052.4	835.6	678.4	537.3
15°	3711.4	3052.2	2490.7	1991.8	1769.0	1571.4	1217.6	927.3	713.6	555.4	431.5
17.5°	3970.4	3166.1	2491.7	1929.3	1678.4	1462.7	1082.6	797.3	589.7	447.5	338.7
20°	4098.4	3151.9	2397.0	1785.2	1524.0	1306.3	923.3	664.4	476.8	358.8	267.1
22.5°	4061.1	3027.0	2230.7	1594.6	1352.7	1146.1	786.1	557.4	411.3	311.4	241.9
25°	3885.8	2824.3	2034.0	1415.2	1183.4	987.9	690.5	513.0	405.2	348.8	300.5
27.5°	3582.4	2558.3	1793.2	1226.7	1018.2	861.7	626.0	497.8	419.3	376.1	380.0
30°	3134.9	2205.5	1481.8	974.7	797.3	670.3	469.7	346.7	255.9	219.8	219.8
32.5°	2633.9	1803.3	1145.0	720.6	576.6	486.9	330.7	236.9	189.5	172.3	164.2
35°	2164.1	1411.2	849.8	522.2	416.3	346.7	216.7	133.1	122.0	117.9	116.0
37.5°	1702.5	1059.3	615.9	379.0	289.3	229.8	110.9	85.7	74.6	69.5	65.5
40°	1276.1	743.9	426.4	231.8	160.3	105.9	64.5	52.4	46.4	45.3	43.3
42.5°	893.0	498.9	264.2	101.8	74.6	59.5	44.3	37.3	34.2	33.2	32.3
45°	523.1	311.4	107.8	56.5	46.4	41.4	32.3	28.2	26.2	26.2	25.2
47.5°	328.6	125.9	57.5	36.3	31.3	29.2	24.1	21.2	20.2	20.2	20.2
50°	135.0	55.4	34.2	25.2	22.3	21.2	18.1	16.1	16.1	16.1	16.1
52.5°	49.4	31.3	23.1	18.1	16.1	15.1	13.1	12.2	12.2	13.1	12.2
55°	28.2	21.2	16.1	13.1	11.1	11.1	10.1	10.1	10.1	10.1	10.1
57.5°	18.1	14.0	11.1	9.0	8.0	8.0	8.0	8.0	8.0	9.0	8.0
60°	12.2	10.1	8.0	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0
62.5°	9.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0
65°	7.1	6.0	7.1	7.1	7.1	7.1	7.1	8.0	8.0	8.0	9.0
67.5°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0
70°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0
72.5°	5.0	5.0	6.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0
75°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	7.1	8.0	8.0	9.0
77.5°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0	9.0
80°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0	9.0
82.5°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	9.0	9.0
85°	5.0	6.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0	9.0
87.5°	5.0	5.0	6.0	6.0	6.0	7.1	7.1	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8
2.5°	966.7	922.3	886.1	866.8	845.7	809.4	775.2	743.9	730.7	688.5	696.5
5°	839.7	764.1	703.6	676.3	645.1	594.7	550.4	507.9	485.9	449.6	436.5
7.5°	698.6	609.8	537.3	506.1	478.8	431.5	390.1	350.8	322.5	285.3	270.2
10°	559.4	474.8	408.2	381.1	350.8	303.4	262.1	227.9	204.7	176.4	162.3
12.5°	442.4	366.9	299.4	272.2	246.9	207.7	175.3	144.0	118.9	103.8	99.7
15°	344.8	272.2	216.7	194.6	173.4	135.0	110.9	102.9	98.7	94.7	93.7
17.5°	259.1	200.5	151.2	129.0	116.9	106.9	102.9	98.7	96.8	93.7	94.7
20°	199.7	143.2	123.0	119.9	117.9	112.9	111.9	110.9	109.8	110.9	112.9
22.5°	189.5	178.5	184.4	188.6	197.6	198.6	214.8	227.9	239.9	273.2	289.3
25°	319.6	338.7	368.9	388.0	414.2	441.6	491.9	536.2	582.6	624.9	662.3
27.5°	400.2	409.2	409.2	419.3	408.2	406.2	400.2	395.2	416.3	409.2	431.5
30°	221.7	231.8	249.0	258.0	269.2	277.2	274.2	264.2	270.2	262.1	270.2
32.5°	158.3	158.3	162.3	163.3	165.3	166.3	167.3	168.4	169.3	164.2	167.3
35°	112.9	108.8	106.9	106.9	105.9	103.8	102.9	102.9	103.8	98.7	100.8
37.5°	63.4	61.5	61.5	61.5	61.5	61.5	62.5	63.4	63.4	63.4	65.5
40°	42.3	42.3	42.3	43.3	43.3	43.3	44.3	44.3	45.3	45.3	46.4
42.5°	32.3	31.3	32.3	32.3	32.3	33.2	33.2	34.2	34.2	34.2	35.3
45°	25.2	25.2	25.2	25.2	26.2	26.2	26.2	26.2	27.2	26.2	27.2
47.5°	20.2	20.2	20.2	21.2	21.2	20.2	21.2	21.2	21.2	21.2	21.2
50°	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	17.2	16.1	17.2
52.5°	13.1	12.2	12.2	12.2	12.2	11.1	11.1	12.2	12.2	11.1	11.1
55°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
57.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1
60°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1	7.1	6.0
62.5°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1	6.0	6.0
65°	9.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0	6.0
67.5°	9.0	9.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	6.0	6.0
70°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0
72.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1
75°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1
77.5°	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1	6.0
80°	9.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	7.1	6.0
82.5°	8.0	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0	6.0
85°	8.0	8.0	8.0	8.0	8.0	7.1	7.1	7.1	6.0	6.0	6.0
87.5°	8.0	8.0	8.0	7.1	7.1	7.1	7.1	6.0	6.0	5.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192335

CATALOG NUMBER: LDA6A45950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8	1101.8
2.5°	654.3	640.0	652.2	637.1	632.0	620.9	615.9	620.9
5°	412.3	397.1	400.2	390.1	374.0	374.0	368.9	371.0
7.5°	249.0	233.9	234.9	225.8	213.7	211.6	206.6	208.7
10°	144.0	128.0	128.0	117.9	107.8	106.9	103.8	103.8
12.5°	95.8	93.7	91.7	90.7	88.6	88.6	88.6	86.7
15°	89.6	88.6	87.8	87.8	85.7	85.7	86.7	84.7
17.5°	91.7	90.7	89.6	89.6	89.6	89.6	90.7	88.6
20°	109.8	110.9	110.9	113.9	116.0	116.9	119.9	116.0
22.5°	288.3	297.3	304.4	341.6	374.0	361.8	384.1	346.7
25°	689.5	714.7	735.8	740.0	760.0	788.2	806.3	805.4
27.5°	431.5	432.3	444.5	444.5	440.5	456.7	467.7	465.7
30°	266.0	265.2	269.2	259.1	258.0	265.2	269.2	269.2
32.5°	164.2	163.3	166.3	164.2	159.2	167.3	165.3	165.3
35°	98.7	99.7	97.9	97.9	93.7	97.9	96.8	97.9
37.5°	64.5	63.4	62.5	62.5	60.4	61.5	60.4	58.4
40°	45.3	45.3	44.3	44.3	43.3	42.3	42.3	41.4
42.5°	34.2	34.2	33.2	33.2	32.3	31.3	31.3	30.3
45°	26.2	25.2	24.1	24.1	24.1	23.1	23.1	22.3
47.5°	20.2	20.2	20.2	19.1	19.1	18.1	18.1	17.2
50°	16.1	16.1	16.1	16.1	15.1	15.1	15.1	14.0
52.5°	11.1	11.1	10.1	10.1	9.0	9.0	9.0	8.0
55°	8.0	8.0	8.0	7.1	7.1	7.1	6.0	6.0
57.5°	7.1	7.1	6.0	6.0	6.0	5.0	5.0	5.0
60°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
62.5°	5.0	5.0	5.0	4.1	4.1	4.1	4.1	3.0
65°	5.0	5.0	4.1	4.1	4.1	3.0	3.0	3.0
67.5°	5.0	5.0	5.0	4.1	4.1	4.1	4.1	3.0
70°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
72.5°	6.0	5.0	5.0	5.0	5.0	4.1	4.1	4.1
75°	6.0	6.0	5.0	5.0	5.0	5.0	5.0	4.1
77.5°	6.0	5.0	5.0	5.0	5.0	5.0	4.1	4.1
80°	6.0	5.0	5.0	5.0	5.0	4.1	4.1	4.1
82.5°	6.0	5.0	5.0	5.0	4.1	4.1	4.1	4.1
85°	5.0	5.0	4.1	4.1	4.1	4.1	4.1	4.1
87.5°	4.1	4.1	3.0	3.0	3.0	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)