

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192386

Luminaire Tested: **LDA6A50935D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192386
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26675)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A50935D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.3 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 2.52 / 0.5 / 1.32
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59		
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	49	42	37	60	49	42	37	48	42	37	47	41	37	46	41	37	35		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59595	59595	59595
5°	152641	54947	20141
10°	321877	43848	5706
15°	464202	31101	4745
20°	523926	20658	6668
25°	568847	20814	48063
30°	632711	13724	16806
35°	639222	7783	6458
40°	643470	3199	2913
45°	638198	2000	1690
50°	500947	1365	1194
55°	150762	956	573
60°	31840	877	439
65°	3606	1038	376
70°	962	1282	641
75°	191	1694	847
80°	0	2810	1263
85°	0	5032	2516



TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	2.9
10°-20°	657.0	13.9
20°-30°	1238.7	26.3
30°-40°	1373.9	29.2
40°-50°	1047.0	22.2
50°-60°	233.6	5.0
60°-70°	12.7	0.3
70°-80°	5.8	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.2	43.2
0°-40°	3408.1	72.3
0°-60°	4688.8	99.5
0°-90°	4712.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1087	1087	1087	1087	1087	
5°	2774	2055	998	479	366	359
15°	8179	4478	548	97	84	2281
25°	9404	5235	344	575	795	4377
35°	9552	3257	116	102	96	5983
45°	8232	959	26	27	22	6130
55°	1577	42	10	9	6	1947
65°	28	7	8	7	3	65
75°	1	4	8	7	4	2
85°	0	4	8	6	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1
2.5°	1865.7	1833.0	1829.0	1818.1	1732.5	1731.5	1730.5	1685.8	1645.0	1624.1	1535.6
5°	2773.8	2749.9	2720.1	2682.3	2541.1	2521.1	2504.2	2437.7	2294.4	2210.9	2054.7
7.5°	4097.6	4084.7	3934.4	3914.6	3655.0	3591.3	3528.7	3357.7	3081.1	2902.1	2625.6
10°	5782.3	5720.7	5606.3	5451.1	5113.0	4992.6	4876.3	4526.2	4054.7	3679.8	3209.4
12.5°	7305.0	7226.4	7087.1	6906.2	6480.5	6316.4	6132.4	5702.7	5126.9	4517.3	3851.9
15°	8179.2	8166.3	8005.1	7931.5	7588.4	7421.3	7269.2	6774.8	6055.8	5338.8	4477.5
17.5°	8696.3	8697.4	8578.9	8535.2	8216.0	8056.9	7928.6	7568.5	6815.7	5945.5	4951.9
20°	8980.8	9009.6	8899.3	8830.6	8607.8	8466.6	8347.3	7976.2	7320.8	6355.2	5220.3
22.5°	9192.6	9206.5	9072.3	9015.6	8765.9	8629.7	8554.1	8199.0	7558.6	6574.0	5301.9
25°	9404.4	9397.5	9246.3	9132.9	8887.3	8755.0	8662.5	8355.2	7658.0	6624.7	5235.3
27.5°	9628.3	9660.1	9379.5	9198.6	8978.8	8823.7	8720.3	8403.0	7651.1	6492.4	4993.6
30°	9995.3	9737.6	9457.1	9207.6	8954.9	8790.8	8672.5	8268.7	7459.1	6141.4	4534.2
32.5°	9841.0	9659.1	9383.5	9127.0	8856.4	8675.4	8531.3	8051.8	7056.3	5563.5	3917.5
35°	9551.6	9502.9	9230.4	9021.6	8714.3	8519.3	8351.2	7717.7	6431.7	4868.4	3257.2
37.5°	9291.0	9240.3	9078.2	8862.4	8513.3	8309.5	8001.1	7186.6	5619.2	3998.0	2562.0
40°	8991.7	8979.8	8798.8	8598.9	8179.2	7803.2	7484.0	6249.7	4651.6	3143.8	1993.1
42.5°	8660.5	8653.6	8506.4	8211.0	7594.4	7128.0	6593.8	5192.5	3576.4	2385.9	1480.9
45°	8231.9	8191.1	7937.5	7506.9	6621.7	5947.4	5314.8	3967.3	2622.7	1704.7	958.7
47.5°	7488.9	7417.3	7047.4	6310.4	5249.2	4560.0	3978.2	2728.1	1636.0	963.7	475.4
50°	5873.8	5683.9	5156.7	4382.0	3293.9	2695.2	2237.7	1353.5	726.1	478.4	304.3
52.5°	3628.1	3423.3	2925.0	2340.2	1502.7	1164.6	960.7	652.5	401.8	275.5	117.4
55°	1577.4	1480.9	1222.3	972.7	695.2	552.9	477.4	330.2	208.8	100.5	41.8
57.5°	615.6	596.7	520.2	438.6	329.2	268.5	237.7	149.2	57.6	35.8	23.8
60°	290.4	271.5	233.7	193.9	121.4	87.6	67.6	41.8	28.9	21.8	16.0
62.5°	79.6	68.7	55.8	47.8	36.9	32.9	28.9	22.9	18.0	14.0	10.9
65°	27.8	27.8	24.9	22.9	18.9	16.9	16.0	12.9	10.9	8.9	6.9
67.5°	12.9	12.9	12.0	10.9	8.9	8.9	8.0	6.9	6.0	4.9	4.9
70°	6.0	4.9	4.9	4.9	4.9	4.0	4.0	4.0	4.0	4.0	4.0
72.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.9	4.0	4.0	4.0
75°	0.9	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.0
77.5°	0.0	0.9	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.0
80°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.0
82.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
85°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	4.0	4.0	4.0
87.5°	0.0	0.0	0.9	0.9	2.0	2.0	2.0	2.9	2.9	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1
2.5°	1497.8	1460.0	1410.2	1327.7	1291.0	1283.0	1215.4	1153.6	1099.0	1059.2	996.5
5°	1953.3	1843.9	1710.6	1550.5	1489.8	1447.1	1317.7	1194.5	1089.0	998.5	903.1
7.5°	2404.8	2188.0	1988.2	1754.4	1641.0	1555.5	1363.5	1188.5	1029.4	906.0	779.7
10°	2839.5	2531.1	2193.0	1885.7	1733.5	1604.2	1352.6	1130.8	931.9	787.7	654.5
12.5°	3252.1	2809.6	2360.1	1951.3	1769.3	1607.2	1298.8	1038.3	824.5	669.4	530.1
15°	3661.9	3011.5	2457.5	1965.3	1745.4	1550.5	1201.4	915.0	704.1	548.0	425.7
17.5°	3917.5	3123.9	2458.5	1903.5	1655.9	1443.1	1068.2	786.7	581.8	441.6	334.2
20°	4043.8	3110.0	2365.0	1761.4	1503.8	1289.0	911.0	655.4	470.4	354.1	263.5
22.5°	4007.1	2986.6	2201.0	1573.4	1334.6	1130.8	775.7	550.0	405.8	307.3	238.7
25°	3834.0	2786.8	2007.1	1396.4	1167.6	974.7	681.2	506.2	399.8	344.1	296.4
27.5°	3534.7	2524.2	1769.3	1210.3	1004.5	850.4	617.6	491.3	413.7	371.0	375.0
30°	3093.1	2176.1	1462.0	961.7	786.7	661.4	463.5	342.1	252.6	216.8	216.8
32.5°	2598.7	1779.2	1129.8	711.2	568.9	480.4	326.2	233.7	187.0	170.1	162.1
35°	2135.3	1392.4	838.4	515.1	410.8	342.1	213.9	131.3	120.3	116.3	114.3
37.5°	1679.8	1045.3	607.6	373.9	285.4	226.8	109.4	84.5	73.6	68.7	64.7
40°	1259.0	733.9	420.7	228.8	158.1	104.5	63.6	51.8	45.8	44.7	42.7
42.5°	881.2	492.3	260.6	100.5	73.6	58.7	43.8	36.9	33.8	32.9	31.8
45°	516.2	307.3	106.5	55.8	45.8	40.7	31.8	27.8	25.8	25.8	24.9
47.5°	324.2	124.3	56.7	35.8	30.9	28.9	23.8	20.9	19.8	19.8	19.8
50°	133.2	54.7	33.8	24.9	21.8	20.9	18.0	16.0	16.0	16.0	16.0
52.5°	48.7	30.9	22.9	18.0	16.0	14.9	12.9	12.0	12.0	12.9	12.0
55°	27.8	20.9	16.0	12.9	10.9	10.9	10.0	10.0	10.0	10.0	10.0
57.5°	18.0	14.0	10.9	8.9	8.0	8.0	8.0	8.0	8.0	8.9	8.0
60°	12.0	10.0	8.0	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0
62.5°	8.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0
65°	6.9	6.0	6.9	6.9	6.9	6.9	6.9	8.0	8.0	8.0	8.9
67.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9
70°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9
72.5°	4.9	4.9	6.0	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9
75°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	6.9	8.0	8.0	8.9
77.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0	8.9
80°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9	8.9
82.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.9	8.9
85°	4.9	6.0	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0	8.9
87.5°	4.9	4.9	6.0	6.0	6.0	6.9	6.9	8.0	8.0	8.0	8.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1
2.5°	953.8	910.0	874.2	855.3	834.4	798.6	764.8	733.9	721.0	679.2	687.2
5°	828.4	753.9	694.1	667.4	636.5	586.7	543.1	501.3	479.3	443.5	430.6
7.5°	689.2	601.6	530.1	499.3	472.4	425.7	384.9	346.1	318.3	281.5	266.6
10°	552.0	468.4	402.8	375.9	346.1	299.4	258.6	224.8	201.9	174.1	160.1
12.5°	436.6	362.0	295.4	268.5	243.7	204.9	173.0	142.3	117.4	102.5	98.5
15°	340.1	268.5	213.9	191.9	171.0	133.2	109.4	101.4	97.4	93.5	92.5
17.5°	255.6	197.9	149.2	127.3	115.4	105.4	101.4	97.4	95.4	92.5	93.5
20°	197.0	141.2	121.4	118.3	116.3	111.4	110.4	109.4	108.5	109.4	111.4
22.5°	187.0	176.1	182.0	186.0	195.0	195.9	211.9	224.8	236.7	269.5	285.4
25°	315.3	334.2	364.0	382.9	408.8	435.6	485.3	529.1	574.9	616.7	653.4
27.5°	394.8	403.8	403.8	413.7	402.8	400.8	394.8	389.9	410.8	403.8	425.7
30°	218.8	228.8	245.7	254.6	265.5	273.5	270.5	260.6	266.6	258.6	266.6
32.5°	156.1	156.1	160.1	161.2	163.1	164.1	165.1	166.1	167.1	162.1	165.1
35°	111.4	107.4	105.4	105.4	104.5	102.5	101.4	101.4	102.5	97.4	99.4
37.5°	62.7	60.7	60.7	60.7	60.7	60.7	61.6	62.7	62.7	62.7	64.7
40°	41.8	41.8	41.8	42.7	42.7	42.7	43.8	43.8	44.7	44.7	45.8
42.5°	31.8	30.9	31.8	31.8	31.8	32.9	32.9	33.8	33.8	33.8	34.9
45°	24.9	24.9	24.9	24.9	25.8	25.8	25.8	25.8	26.9	25.8	26.9
47.5°	19.8	19.8	19.8	20.9	20.9	19.8	20.9	20.9	20.9	20.9	20.9
50°	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.0	16.9	16.0	16.9
52.5°	12.9	12.0	12.0	12.0	12.0	10.9	10.9	12.0	12.0	10.9	10.9
55°	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9	8.9
57.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9
60°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9	6.9	6.0
62.5°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9	6.0	6.0
65°	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0	6.0
67.5°	8.9	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.0	6.0
70°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0
72.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9
75°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9
77.5°	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9	6.0
80°	8.9	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.9	6.0
82.5°	8.0	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0	6.0
85°	8.0	8.0	8.0	8.0	8.0	6.9	6.9	6.9	6.0	6.0	6.0
87.5°	8.0	8.0	8.0	6.9	6.9	6.9	6.9	6.0	6.0	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192386

CATALOG NUMBER: LDA6A50935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1	1087.1
2.5°	645.4	631.6	643.4	628.5	623.6	612.7	607.6	612.7
5°	406.8	391.9	394.8	384.9	369.0	369.0	364.0	366.0
7.5°	245.7	230.8	231.7	222.8	210.8	208.8	203.9	205.9
10°	142.3	126.3	126.3	116.3	106.5	105.4	102.5	102.5
12.5°	94.5	92.5	90.5	89.6	87.6	87.6	87.6	85.6
15°	88.5	87.6	86.5	86.5	84.5	84.5	85.6	83.6
17.5°	90.5	89.6	88.5	88.5	88.5	88.5	89.6	87.6
20°	108.5	109.4	109.4	112.4	114.3	115.4	118.3	114.3
22.5°	284.4	293.4	300.4	337.2	369.0	357.0	378.9	342.1
25°	680.3	705.2	726.1	730.1	749.9	777.7	795.7	794.6
27.5°	425.7	426.6	438.6	438.6	434.6	450.5	461.5	459.5
30°	262.6	261.6	265.5	255.6	254.6	261.6	265.5	265.5
32.5°	162.1	161.2	164.1	162.1	157.2	165.1	163.1	163.1
35°	97.4	98.5	96.5	96.5	92.5	96.5	95.4	96.5
37.5°	63.6	62.7	61.6	61.6	59.6	60.7	59.6	57.6
40°	44.7	44.7	43.8	43.8	42.7	41.8	41.8	40.7
42.5°	33.8	33.8	32.9	32.9	31.8	30.9	30.9	29.8
45°	25.8	24.9	23.8	23.8	23.8	22.9	22.9	21.8
47.5°	19.8	19.8	19.8	18.9	18.9	18.0	18.0	16.9
50°	16.0	16.0	16.0	16.0	14.9	14.9	14.9	14.0
52.5°	10.9	10.9	10.0	10.0	8.9	8.9	8.9	8.0
55°	8.0	8.0	8.0	6.9	6.9	6.9	6.0	6.0
57.5°	6.9	6.9	6.0	6.0	6.0	4.9	4.9	4.9
60°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
62.5°	4.9	4.9	4.9	4.0	4.0	4.0	4.0	2.9
65°	4.9	4.9	4.0	4.0	4.0	2.9	2.9	2.9
67.5°	4.9	4.9	4.9	4.0	4.0	4.0	4.0	2.9
70°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
72.5°	6.0	4.9	4.9	4.9	4.9	4.0	4.0	4.0
75°	6.0	6.0	4.9	4.9	4.9	4.9	4.9	4.0
77.5°	6.0	4.9	4.9	4.9	4.9	4.9	4.0	4.0
80°	6.0	4.9	4.9	4.9	4.9	4.0	4.0	4.0
82.5°	6.0	4.9	4.9	4.9	4.0	4.0	4.0	4.0
85°	4.9	4.9	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	4.0	4.0	2.9	2.9	2.9	2.0	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)