

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192497

Luminaire Tested: **LDA6A55950D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A55950D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5561.2 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	54990	54990	54990
5°	141063	50027	15579
10°	274973	38448	7487
15°	493607	26113	10040
20°	732859	19823	16574
25°	833002	16332	25991
30°	902987	17864	24453
35°	951137	11564	15158
40°	971699	5145	7385
45°	877641	1969	2744
50°	577721	785	785
55°	158217	679	0
60°	31598	778	0
65°	2244	1051	0
70°	321	1298	0
75°	0	1949	0
80°	0	2904	316
85°	0	5787	629

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.9	2.2
10°-20°	652.8	11.7
20°-30°	1479.6	26.6
30°-40°	1776.0	31.9
40°-50°	1251.7	22.5
50°-60°	258.3	4.6
60°-70°	9.1	0.2
70°-80°	5.5	0.1
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2255.3	40.6
0°-40°	4031.3	72.5
0°-60°	5541.3	99.6
0°-90°	5561.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5561.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1003	1003	1003	1003	1003	
5°	2563	1868	909	378	283	315
15°	8697	3826	460	164	177	2581
25°	13772	4628	270	378	430	6355
35°	14212	3241	173	226	226	8835
45°	11320	1111	25	34	35	8326
55°	1655	22	7	5	0	2181
65°	17	5	8	5	0	51
75°	0	5	9	6	0	0
85°	0	6	9	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1
2.5°	1709.9	1658.3	1678.6	1618.9	1605.9	1594.6	1605.9	1541.1	1504.7	1458.2	1420.7
5°	2563.4	2501.7	2515.9	2411.8	2364.2	2331.8	2325.8	2192.2	2092.3	1981.9	1867.6
7.5°	3568.6	3509.9	3501.8	3340.1	3242.0	3186.4	3163.1	2971.9	2799.1	2602.8	2388.5
10°	4939.7	4806.3	4764.8	4530.2	4343.1	4224.8	4079.2	3773.7	3470.5	3174.2	2901.2
12.5°	6535.4	6462.7	6359.5	5945.8	5618.2	5450.4	5233.0	4755.7	4296.7	3807.2	3350.0
15°	8697.3	8438.5	8262.5	7664.8	7137.0	6878.2	6560.6	5830.7	5136.9	4517.0	3826.4
17.5°	10809.8	10674.2	10399.3	9623.6	8810.7	8402.1	7928.9	6936.9	5957.0	5075.2	4231.9
20°	12562.2	12434.8	12121.3	11390.2	10488.2	9885.5	9289.9	7928.9	6648.7	5520.1	4502.9
22.5°	13401.4	13320.5	13064.7	12438.8	11670.3	11096.9	10456.8	8773.1	7160.3	5811.4	4626.2
25°	13771.5	13734.1	13569.3	13075.8	12351.9	11865.5	11260.8	9370.8	7478.8	5946.8	4628.3
27.5°	14146.7	14153.8	13789.8	13399.4	12712.8	12245.6	11663.2	9635.7	7536.5	5871.0	4476.6
30°	14265.0	14190.2	14029.4	13469.2	12817.0	12320.5	11695.6	9513.4	7299.9	5559.5	4174.2
32.5°	14216.5	14187.2	14010.2	13417.7	12640.1	12092.9	11383.1	9028.0	6832.7	5114.7	3745.5
35°	14212.4	14157.8	13752.3	13243.7	12286.0	11610.6	10675.3	8243.2	6171.4	4528.2	3241.0
37.5°	13955.7	13820.0	13515.7	12830.2	11568.1	10711.7	9663.1	7284.7	5362.3	3869.8	2740.4
40°	13578.3	13396.3	12996.0	11958.4	10324.4	9337.4	8314.1	6195.6	4505.9	3220.7	2208.4
42.5°	12790.6	12515.7	11949.3	10522.5	8667.0	7777.1	6925.8	5092.4	3674.7	2624.0	1685.6
45°	11320.4	10944.2	10178.7	8612.4	7001.5	6275.5	5590.9	4097.4	2941.6	1946.5	1111.3
47.5°	9098.9	8749.9	8053.1	6855.9	5490.9	4877.1	4331.0	3047.8	1994.0	1127.6	530.9
50°	6774.0	6474.7	5930.7	4764.8	3685.8	3203.4	2736.3	1731.2	934.4	535.9	220.4
52.5°	4041.8	3893.1	3410.8	2642.2	1820.1	1568.3	1258.9	733.1	471.2	194.2	59.7
55°	1655.4	1527.9	1346.9	1080.9	791.9	671.4	574.4	361.9	146.6	40.5	22.2
57.5°	748.3	720.0	638.1	501.6	364.0	305.4	206.3	68.8	32.3	20.3	13.2
60°	288.2	259.9	222.5	120.4	51.6	43.5	35.4	23.3	16.2	11.1	8.1
62.5°	41.5	39.4	35.4	28.3	22.2	20.3	17.3	12.2	9.2	7.1	6.0
65°	17.3	17.3	15.2	12.2	10.1	9.2	8.1	6.0	5.1	5.1	5.1
67.5°	7.1	7.1	6.0	5.1	4.1	4.1	4.1	3.0	4.1	4.1	5.1
70°	2.0	2.0	2.0	2.0	2.0	2.0	3.0	3.0	4.1	4.1	5.1
72.5°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
75°	0.0	0.0	1.0	1.0	2.0	2.0	2.0	3.0	4.1	5.1	5.1
77.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	5.1
80°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	6.0
82.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	6.0
85°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	6.0
87.5°	0.0	0.0	1.0	1.0	2.0	2.0	3.0	3.0	4.1	5.1	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1
2.5°	1388.4	1323.6	1305.5	1248.8	1201.3	1178.0	1148.7	1083.0	1033.3	967.7	928.3
5°	1787.9	1665.5	1568.3	1450.1	1372.2	1321.7	1242.8	1122.5	1025.4	909.1	826.2
7.5°	2219.6	1996.1	1821.1	1626.0	1513.7	1425.7	1291.3	1118.4	975.8	821.1	692.7
10°	2636.2	2302.5	2027.5	1747.4	1599.7	1477.3	1292.3	1074.9	885.9	690.7	555.2
12.5°	3003.2	2572.4	2185.2	1825.2	1642.2	1489.5	1258.0	997.0	768.6	568.3	449.0
15°	3309.7	2781.8	2296.4	1854.5	1645.3	1463.3	1186.1	885.9	638.1	460.1	376.2
17.5°	3542.2	2892.0	2330.7	1819.2	1586.6	1388.4	1076.0	745.2	517.7	390.3	316.5
20°	3662.6	2913.2	2281.3	1723.1	1478.4	1275.0	931.3	604.7	438.9	339.8	264.9
22.5°	3677.6	2853.7	2163.0	1585.6	1341.8	1137.6	771.6	504.5	391.4	300.4	233.6
25°	3587.7	2724.2	1994.0	1429.8	1192.2	979.9	628.0	452.1	356.0	270.0	268.9
27.5°	3395.6	2501.7	1791.9	1248.8	1011.2	796.7	532.9	408.6	317.5	286.2	304.4
30°	3124.6	2216.6	1543.2	1020.3	789.8	612.8	449.0	336.8	279.0	282.2	297.3
32.5°	2757.6	1862.6	1250.8	747.2	565.2	461.0	336.8	229.5	231.5	232.5	245.8
35°	2296.4	1493.5	934.4	502.6	397.4	324.6	190.1	168.8	171.9	172.8	182.0
37.5°	1840.4	1147.7	620.9	334.7	249.8	170.9	118.4	113.3	115.3	114.3	124.4
40°	1409.6	799.9	372.1	165.9	96.1	79.9	72.9	69.8	70.8	71.9	77.8
42.5°	998.0	433.8	184.0	62.7	50.5	46.5	43.5	41.5	42.4	42.4	46.5
45°	506.6	205.3	62.7	34.3	31.3	28.3	26.2	25.4	25.4	25.4	27.2
47.5°	219.3	67.8	29.3	21.3	19.2	18.2	16.2	15.2	15.2	15.2	16.2
50°	68.8	27.2	18.2	14.1	12.2	11.1	10.1	10.1	10.1	9.2	10.1
52.5°	25.4	17.3	12.2	9.2	8.1	8.1	8.1	7.1	8.1	7.1	8.1
55°	15.2	11.1	8.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1
57.5°	10.1	8.1	7.1	7.1	6.0	6.0	7.1	7.1	7.1	7.1	7.1
60°	7.1	7.1	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	7.1
62.5°	6.0	6.0	6.0	6.0	6.0	6.0	7.1	7.1	7.1	7.1	8.1
65°	5.1	6.0	6.0	6.0	6.0	6.0	7.1	7.1	8.1	8.1	8.1
67.5°	5.1	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	8.1
70°	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	8.1	9.2
72.5°	6.0	6.0	7.1	7.1	7.1	7.1	8.1	8.1	9.2	9.2	9.2
75°	6.0	7.1	7.1	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2
77.5°	6.0	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2
80°	6.0	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2	10.1
82.5°	6.0	7.1	7.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2	10.1
85°	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	9.2	9.2	10.1
87.5°	7.1	7.1	8.1	8.1	8.1	8.1	9.2	9.2	10.1	9.2	10.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1
2.5°	875.7	817.0	776.6	761.4	732.2	685.7	658.2	633.0	585.5	575.3	549.1
5°	731.1	637.1	570.3	545.1	511.7	472.3	433.8	408.6	378.1	366.0	347.9
7.5°	576.4	482.4	424.7	404.6	381.3	348.9	314.4	289.2	257.9	241.7	226.5
10°	453.0	383.2	334.7	314.4	290.3	255.8	220.4	187.1	159.8	142.6	139.6
12.5°	368.1	310.3	258.9	237.6	209.4	174.9	149.7	148.6	146.6	145.6	147.7
15°	301.4	245.8	191.2	168.0	159.8	158.8	161.8	164.8	163.9	166.9	168.8
17.5°	247.7	188.0	175.9	176.9	177.9	181.0	186.1	194.2	195.2	200.2	204.3
20°	202.3	199.3	204.3	208.3	211.4	217.4	228.5	238.7	241.7	248.8	256.9
22.5°	229.5	238.7	249.8	254.9	258.9	270.0	282.2	298.4	304.4	313.6	324.6
25°	277.1	292.2	309.5	315.4	321.6	339.8	353.9	373.2	378.1	389.3	400.5
27.5°	316.5	332.7	350.9	359.0	364.0	382.2	394.4	406.5	406.5	412.6	420.7
30°	310.3	323.5	338.7	344.9	346.8	360.0	372.1	376.2	374.1	377.2	383.2
32.5°	257.9	267.9	280.1	285.2	287.1	296.3	306.4	306.4	305.4	305.4	309.5
35°	191.2	198.2	204.3	209.4	212.4	218.4	227.4	226.5	226.5	224.4	227.4
37.5°	128.4	132.4	139.6	141.5	142.6	146.6	153.7	153.7	151.7	152.7	154.8
40°	77.8	82.9	86.9	88.0	90.0	93.0	98.1	98.1	98.1	98.1	99.1
42.5°	46.5	49.5	52.6	52.6	53.6	57.6	59.7	59.7	59.7	59.7	60.7
45°	27.2	28.3	30.3	31.3	31.3	33.4	34.3	34.3	34.3	34.3	35.4
47.5°	16.2	17.3	17.3	18.2	18.2	19.2	20.3	20.3	19.2	19.2	19.2
50°	10.1	10.1	10.1	10.1	11.1	11.1	11.1	11.1	11.1	11.1	10.1
52.5°	8.1	8.1	8.1	8.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1
55°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	6.0	5.1	4.1	3.0
57.5°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	4.1	4.1	3.0
60°	7.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	4.1	4.1	3.0
62.5°	8.1	8.1	7.1	7.1	7.1	6.0	6.0	5.1	5.1	4.1	3.0
65°	8.1	8.1	7.1	7.1	7.1	7.1	6.0	6.0	5.1	4.1	3.0
67.5°	8.1	8.1	8.1	8.1	7.1	7.1	7.1	6.0	5.1	4.1	3.0
70°	9.2	9.2	8.1	8.1	8.1	7.1	7.1	6.0	5.1	5.1	4.1
72.5°	9.2	9.2	8.1	8.1	8.1	8.1	7.1	6.0	6.0	5.1	4.1
75°	9.2	9.2	9.2	9.2	8.1	8.1	7.1	7.1	6.0	5.1	4.1
77.5°	9.2	9.2	9.2	9.2	8.1	8.1	8.1	7.1	6.0	5.1	4.1
80°	9.2	9.2	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	4.1
82.5°	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1	6.0	5.1	5.1
85°	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1	6.0	6.0	5.1
87.5°	10.1	10.1	9.2	9.2	9.2	8.1	8.1	7.1	6.0	6.0	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192497

CATALOG NUMBER: LDA6A55950D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1	1003.1
2.5°	532.9	502.6	492.4	499.6	491.5	485.4	477.3	473.2
5°	333.7	311.4	304.4	306.4	299.3	293.3	285.2	283.1
7.5°	205.3	184.0	175.9	175.9	168.0	160.8	155.8	152.7
10°	137.5	133.4	134.5	135.5	134.5	135.5	132.4	134.5
12.5°	147.7	145.6	147.7	148.6	148.6	150.7	146.6	149.7
15°	171.9	169.8	172.8	174.9	174.9	177.9	173.9	176.9
17.5°	210.4	209.4	214.4	216.3	217.4	222.5	217.4	221.4
20°	265.9	264.9	272.0	275.0	274.0	284.1	277.1	284.1
22.5°	337.8	335.7	345.8	348.9	349.9	363.0	357.0	361.9
25°	409.4	411.5	416.6	421.6	422.7	433.8	424.7	429.7
27.5°	424.7	421.6	424.7	430.8	431.8	436.8	428.8	432.7
30°	384.3	379.2	380.2	387.3	389.3	391.4	384.3	386.3
32.5°	312.5	304.4	304.4	311.4	313.6	316.5	304.4	309.5
35°	230.6	223.4	223.4	228.5	229.5	231.5	222.5	226.5
37.5°	157.8	151.7	153.7	155.8	156.7	158.8	157.8	156.7
40°	101.1	97.0	100.2	100.2	101.1	102.1	102.1	103.2
42.5°	61.7	58.7	60.7	60.7	61.7	61.7	61.7	62.7
45°	35.4	34.3	34.3	35.4	35.4	35.4	34.3	35.4
47.5°	19.2	18.2	19.2	19.2	19.2	19.2	19.2	19.2
50°	10.1	9.2	9.2	9.2	9.2	9.2	9.2	9.2
52.5°	5.1	4.1	4.1	4.1	3.0	4.1	3.0	3.0
55°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
57.5°	2.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
60°	2.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.0	1.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.0	2.0	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.0	2.0	2.0	1.0	1.0	0.0	0.0	0.0
72.5°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
75°	3.0	2.0	2.0	2.0	1.0	1.0	0.0	0.0
77.5°	3.0	3.0	2.0	2.0	1.0	1.0	1.0	0.0
80°	4.1	3.0	2.0	2.0	2.0	1.0	1.0	1.0
82.5°	4.1	3.0	2.0	2.0	2.0	1.0	1.0	1.0
85°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
87.5°	4.1	3.0	3.0	2.0	2.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)