

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192509

Luminaire Tested: **LDA6A60927D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60927D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4590.3 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	71041	71041	71041
5°	137656	67703	22832
10°	233875	59245	10254
15°	360394	47253	16300
20°	521703	30756	28358
25°	765437	29675	36462
30°	890004	28118	27941
35°	900831	14890	14770
40°	745819	5618	6197
45°	563283	1907	2256
50°	385386	699	699
55°	53609	602	86
60°	1403	603	0
65°	350	817	0
70°	144	1010	0
75°	0	1334	0
80°	0	2305	284
85°	0	4592	0

TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	3.0
10°-20°	574.7	12.5
20°-30°	1311.0	28.6
30°-40°	1517.1	33.1
40°-50°	915.0	19.9
50°-60°	124.3	2.7
60°-70°	4.0	0.1
70°-80°	4.3	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2021.6	44.0
0°-40°	3538.8	77.1
0°-60°	4578.0	99.7
0°-90°	4590.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4590.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1296	1296	1296	1296	1296	
5°	2502	2048	1230	673	415	291
15°	6350	3569	833	256	287	1880
25°	12654	4230	491	590	603	5727
35°	13461	3225	222	227	221	8112
45°	7266	878	25	30	29	5681
55°	561	6	6	4	1	1099
65°	3	4	6	4	0	4
75°	0	4	6	4	0	0
85°	0	4	7	4	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9
2.5°	1874.0	1856.7	1864.0	1844.9	1796.5	1786.5	1785.7	1772.9	1731.8	1699.9	1661.6
5°	2501.5	2500.6	2505.1	2464.2	2379.4	2352.9	2340.1	2309.1	2209.8	2133.1	2048.3
7.5°	3284.9	3279.4	3273.9	3199.2	3066.0	3015.0	2982.1	2870.0	2733.1	2597.3	2445.9
10°	4201.4	4198.7	4177.7	4046.4	3833.0	3739.1	3675.2	3497.4	3277.6	3084.3	2827.1
12.5°	5265.7	5241.1	5203.7	5011.2	4718.5	4616.4	4475.9	4194.2	3856.8	3560.3	3201.1
15°	6350.1	6314.5	6247.9	6000.7	5637.8	5463.6	5289.4	4918.3	4460.5	4029.9	3569.4
17.5°	7410.6	7371.5	7215.5	6796.0	6441.2	6228.7	6035.5	5525.6	4987.6	4434.0	3850.3
20°	8942.7	8800.5	8528.8	7867.6	7208.2	6825.2	6599.0	6060.1	5394.2	4749.5	4050.0
22.5°	10989.2	10673.7	10094.6	9020.3	8078.3	7525.5	7155.3	6438.6	5687.1	4955.7	4173.1
25°	12654.5	12511.3	11852.9	10324.5	8854.3	8203.2	7688.0	6739.4	5900.4	5093.4	4229.7
27.5°	13727.9	13692.3	12939.9	11404.2	9488.2	8633.6	8058.2	6938.3	6003.5	5122.5	4202.4
30°	14059.9	14115.4	13393.2	11770.8	9671.4	8720.2	8090.9	6941.0	5924.2	4990.3	4027.3
32.5°	14035.2	14037.9	13152.4	11454.3	9373.2	8468.6	7817.4	6710.3	5631.4	4659.2	3694.3
35°	13460.7	13319.3	12317.9	10482.1	8679.3	7881.2	7275.7	6263.5	5148.9	4161.3	3224.7
37.5°	12199.5	12014.2	10847.0	9237.4	7857.6	7119.7	6631.0	5677.0	4574.4	3629.6	2739.6
40°	10421.9	10159.3	9196.3	8080.1	6958.3	6403.8	5993.4	5021.4	3959.7	3108.0	2284.5
42.5°	8642.7	8514.2	7877.6	6970.2	6202.3	5680.6	5252.0	4334.6	3368.9	2593.6	1709.0
45°	7265.6	7155.3	6727.6	6129.3	5376.1	4900.0	4486.9	3618.7	2617.4	1740.0	878.2
47.5°	6262.5	6173.2	5763.6	5135.3	4309.1	3788.3	3362.4	2372.9	1482.9	751.5	219.8
50°	4518.8	4427.6	4026.4	3298.5	2552.7	2116.7	1810.3	1059.7	420.4	152.3	22.8
52.5°	2215.1	2140.4	1867.7	1398.1	938.4	674.8	493.4	198.7	48.4	16.5	11.0
55°	560.9	515.2	429.5	269.9	132.2	79.3	51.1	18.3	11.8	9.1	6.3
57.5°	31.9	31.0	28.3	21.0	15.5	13.6	11.8	9.1	6.3	5.5	4.5
60°	12.8	11.8	11.0	9.1	7.3	6.3	6.3	4.5	3.7	3.7	3.7
62.5°	5.5	5.5	5.5	4.5	3.7	3.7	3.7	2.7	3.7	3.7	3.7
65°	2.7	2.7	2.7	1.8	1.8	1.8	2.7	2.7	2.7	3.7	3.7
67.5°	1.8	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	3.7
70°	0.9	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5
72.5°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5
75°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
77.5°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
80°	0.0	0.9	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
82.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
85°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	3.7	3.7	4.5
87.5°	0.0	0.0	0.9	0.9	1.8	1.8	1.8	2.7	2.7	3.7	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9
2.5°	1612.4	1579.5	1531.3	1499.3	1468.3	1439.1	1390.8	1363.3	1314.1	1268.5	1229.3
5°	1946.2	1864.0	1764.6	1679.8	1625.1	1571.3	1473.7	1401.7	1311.4	1230.3	1155.4
7.5°	2283.6	2138.6	1975.3	1835.8	1751.0	1668.0	1522.1	1405.4	1277.7	1161.9	1051.5
10°	2589.9	2372.1	2141.3	1941.5	1826.6	1719.0	1526.6	1371.6	1207.5	1064.3	925.6
12.5°	2874.5	2576.3	2275.3	2014.5	1872.3	1742.8	1507.5	1317.8	1122.7	953.0	791.6
15°	3128.1	2745.1	2372.9	2056.5	1889.6	1736.3	1462.8	1242.1	1022.3	832.6	628.3
17.5°	3320.5	2849.9	2415.8	2050.1	1858.6	1688.1	1386.2	1147.3	915.6	685.8	455.0
20°	3437.2	2894.6	2406.7	2000.9	1792.0	1611.4	1295.0	1044.2	787.1	527.2	401.3
22.5°	3486.5	2890.9	2363.8	1927.0	1709.9	1527.6	1207.5	943.9	652.1	476.9	418.6
25°	3494.6	2853.5	2303.6	1845.8	1628.7	1447.3	1119.0	829.8	566.4	490.6	468.8
27.5°	3431.7	2766.0	2190.5	1729.2	1514.8	1326.9	986.8	659.4	531.7	488.8	503.4
30°	3245.7	2566.3	1990.8	1523.9	1316.9	1129.0	704.9	517.0	441.4	444.2	447.8
32.5°	2918.4	2234.4	1669.8	1223.8	997.6	744.2	438.7	345.6	335.6	335.6	333.8
35°	2481.5	1828.5	1310.5	774.3	496.1	357.5	227.0	228.0	223.5	222.5	221.7
37.5°	2030.0	1442.8	829.8	320.1	215.2	149.5	134.0	135.9	134.0	136.8	135.0
40°	1600.5	891.0	302.8	102.1	75.7	73.0	74.8	76.6	76.6	78.5	78.5
42.5°	930.3	295.5	79.3	41.1	41.1	39.2	40.1	41.9	42.9	43.7	42.9
45°	276.4	61.1	25.6	22.8	22.8	21.9	21.9	22.8	23.8	24.6	24.6
47.5°	43.7	17.3	14.6	12.8	12.8	12.8	12.8	12.8	13.6	13.6	14.6
50°	13.6	11.0	9.1	8.2	8.2	7.3	7.3	8.2	8.2	8.2	9.1
52.5°	8.2	6.3	6.3	5.5	6.3	6.3	5.5	6.3	6.3	6.3	7.3
55°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3
57.5°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
60°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	6.3
62.5°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3
65°	4.5	4.5	5.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3
67.5°	4.5	5.5	5.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3
70°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
72.5°	4.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
75°	5.5	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.3
77.5°	5.5	5.5	6.3	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3
80°	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
82.5°	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
85°	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
87.5°	5.5	5.5	6.3	6.3	6.3	6.3	6.3	7.3	7.3	7.3	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9
2.5°	1195.5	1153.6	1133.6	1105.4	1085.3	1040.5	1022.3	991.3	965.7	923.8	926.6
5°	1091.6	1012.3	958.5	916.5	887.4	816.2	768.8	718.6	673.0	616.5	595.5
7.5°	947.6	850.0	767.8	717.7	680.3	585.5	480.6	398.5	336.6	291.8	274.5
10°	803.4	676.7	546.3	468.8	414.9	323.8	277.2	255.4	235.3	210.7	194.2
12.5°	635.6	455.0	336.6	305.5	283.7	253.6	223.5	199.7	204.2	205.2	211.5
15°	434.1	327.4	290.0	269.1	245.3	228.0	238.0	244.4	256.3	257.1	265.4
17.5°	352.9	307.3	277.2	276.4	278.2	288.2	303.7	312.0	327.4	331.1	342.9
20°	352.9	326.5	352.0	352.0	356.6	370.2	390.3	402.1	419.6	425.9	440.5
22.5°	402.1	420.4	452.3	456.0	457.8	472.4	497.9	509.8	529.8	533.5	549.0
25°	490.6	507.0	536.3	539.0	539.8	550.8	569.9	576.4	590.0	582.7	591.9
27.5°	518.9	526.2	544.5	546.3	541.7	546.3	553.6	553.6	558.1	543.5	546.3
30°	456.0	457.8	467.0	467.8	457.8	459.6	460.5	459.6	458.7	443.2	443.2
32.5°	338.4	338.4	350.2	347.4	336.6	339.2	339.2	339.2	338.4	325.6	323.8
35°	224.3	225.3	235.3	233.5	225.3	227.0	227.0	229.8	227.0	219.8	218.0
37.5°	136.8	137.7	142.2	143.2	140.5	141.4	142.2	141.4	143.2	139.5	137.7
40°	79.3	81.2	84.8	85.7	84.8	84.8	85.7	86.6	90.3	85.7	84.0
42.5°	46.5	47.4	49.2	49.2	49.2	49.2	50.2	51.1	52.0	51.1	50.2
45°	26.4	27.4	28.3	28.3	29.1	28.3	29.1	29.1	30.1	29.1	29.1
47.5°	15.5	15.5	16.5	16.5	17.3	16.5	17.3	17.3	17.3	16.5	16.5
50°	9.1	10.0	10.0	10.0	10.0	10.0	10.0	10.0	10.0	9.1	9.1
52.5°	7.3	7.3	7.3	7.3	7.3	6.3	6.3	6.3	6.3	5.5	5.5
55°	6.3	6.3	6.3	6.3	6.3	6.3	5.5	4.5	4.5	3.7	3.7
57.5°	5.5	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7	2.7
60°	6.3	6.3	6.3	6.3	5.5	5.5	5.5	4.5	3.7	2.7	2.7
62.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7	2.7
65°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7	2.7
67.5°	6.3	6.3	6.3	6.3	6.3	5.5	5.5	4.5	3.7	3.7	2.7
70°	6.3	7.3	7.3	6.3	6.3	6.3	5.5	4.5	4.5	3.7	2.7
72.5°	6.3	7.3	7.3	6.3	6.3	6.3	5.5	4.5	4.5	3.7	2.7
75°	7.3	7.3	7.3	7.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7
77.5°	7.3	7.3	7.3	7.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7
80°	7.3	7.3	7.3	7.3	7.3	6.3	6.3	5.5	4.5	3.7	3.7
82.5°	7.3	7.3	7.3	7.3	7.3	6.3	6.3	5.5	4.5	3.7	3.7
85°	7.3	7.3	7.3	7.3	7.3	6.3	6.3	5.5	4.5	3.7	2.7
87.5°	7.3	7.3	7.3	7.3	6.3	6.3	5.5	5.5	4.5	3.7	2.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192509

CATALOG NUMBER: LDA6A60927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9	1295.9
2.5°	892.8	871.9	862.7	877.4	870.1	848.1	852.6	839.0
5°	532.6	500.7	480.6	489.7	460.5	434.1	434.1	414.9
7.5°	257.1	247.1	241.6	243.5	237.1	228.8	224.3	224.3
10°	180.6	176.9	177.8	177.8	183.3	182.4	185.1	184.2
12.5°	214.3	216.2	217.0	220.7	225.3	225.3	228.0	226.2
15°	274.5	272.7	278.2	279.1	286.4	287.2	290.9	287.2
17.5°	349.2	352.9	358.4	357.5	372.0	373.0	373.0	372.0
20°	449.7	452.3	457.8	459.6	476.9	478.8	485.1	486.1
22.5°	559.1	559.1	561.8	565.4	581.9	582.7	585.5	585.5
25°	596.4	591.0	591.9	596.4	605.5	601.9	604.7	602.8
27.5°	548.1	539.8	538.1	544.5	550.8	540.8	544.5	544.5
30°	445.0	437.7	435.9	442.3	446.8	435.9	439.5	441.4
32.5°	325.6	321.0	320.1	324.6	328.3	319.1	322.8	325.6
35°	219.8	218.0	216.2	217.0	222.5	215.2	218.9	220.7
37.5°	139.5	135.9	136.8	138.7	142.2	137.7	141.4	141.4
40°	85.7	84.0	84.0	85.7	87.5	84.0	85.7	86.6
42.5°	50.2	50.2	50.2	51.1	52.0	50.2	50.2	51.1
45°	29.1	28.3	28.3	29.1	30.1	28.3	29.1	29.1
47.5°	16.5	15.5	15.5	16.5	16.5	15.5	16.5	16.5
50°	9.1	8.2	8.2	9.1	9.1	8.2	8.2	8.2
52.5°	4.5	4.5	4.5	4.5	4.5	4.5	3.7	3.7
55°	2.7	2.7	1.8	1.8	1.8	1.8	1.8	0.9
57.5°	1.8	1.8	0.9	0.9	0.9	0.9	0.0	0.0
60°	1.8	1.8	0.9	0.9	0.9	0.0	0.0	0.0
62.5°	1.8	1.8	0.9	0.9	0.9	0.0	0.0	0.0
65°	1.8	1.8	0.9	0.9	0.9	0.0	0.0	0.0
67.5°	1.8	1.8	0.9	0.9	0.9	0.0	0.0	0.0
70°	2.7	1.8	1.8	0.9	0.9	0.9	0.0	0.0
72.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
75°	2.7	1.8	1.8	1.8	0.9	0.9	0.0	0.0
77.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.0
80°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.9
82.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.9
85°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.0
87.5°	2.7	1.8	1.8	1.8	0.9	0.9	0.9	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)