

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192528

Luminaire Tested: **LDA6A60930D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60930D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4525.4 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	97	90	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		80	74	70			77	73	69			76
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			70
6	80	70	62	57	79	69	62	57		67	61	57			66	60	56			64
7	75	64	57	51	74	63	56	51		62	56	51			60	55	51			59
8	70	59	52	47	69	58	51	46		57	51	46			56	50	46			55
9	66	54	47	42	64	54	47	42		53	46	42			52	46	42			51
10	62	50	43	38	61	50	43	38		49	43	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	70625	70625	70625
5°	138080	67131	24488
10°	232411	57636	5433
15°	353935	43644	8916
20°	511447	35359	99467
25°	761161	57203	28744
30°	879167	19585	5684
35°	879443	4377	3065
40°	718804	2440	1882
45°	544312	1589	1209
50°	361489	1083	827
55°	58120	927	650
60°	3629	965	537
65°	1141	1258	636
70°	625	1410	785
75°	402	1652	1038
80°	316	2462	1547
85°	629	4906	1824

TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	3.0
10°-20°	575.0	12.7
20°-30°	1353.6	29.9
30°-40°	1426.1	31.5
40°-50°	889.2	19.6
50°-60°	127.8	2.8
60°-70°	8.1	0.2
70°-80°	6.4	0.1
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.0	45.6
0°-40°	3489.2	77.1
0°-60°	4506.2	99.6
0°-90°	4525.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4525.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1288	1288	1288	1288	1288	
5°	2509	2031	1220	633	445	291
15°	6236	3530	769	134	157	1857
25°	12584	4232	946	684	475	5662
35°	13141	3100	65	61	46	7927
45°	7021	858	20	22	16	5495
55°	608	16	10	11	7	1093
65°	9	7	10	8	5	13
75°	2	5	8	8	5	2
85°	1	5	8	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3
2.5°	1880.6	1867.9	1871.8	1842.6	1803.5	1821.2	1777.2	1778.1	1750.8	1681.5	1651.3
5°	2509.2	2507.2	2504.3	2450.5	2381.3	2389.1	2324.7	2300.3	2230.0	2108.0	2031.0
7.5°	3289.9	3290.9	3276.2	3145.5	3068.4	3063.5	2962.0	2888.7	2758.0	2565.7	2425.2
10°	4175.1	4202.4	4176.0	3975.0	3831.6	3833.5	3651.0	3510.5	3300.6	3020.6	2820.5
12.5°	5214.5	5218.4	5177.3	4912.9	4694.3	4677.7	4432.8	4164.3	3845.2	3479.3	3188.4
15°	6236.3	6263.6	6210.9	5885.0	5580.4	5534.6	5222.3	4867.9	4471.8	3930.1	3530.0
17.5°	7369.3	7326.4	7186.9	6720.3	6354.4	6287.0	5951.3	5487.7	4982.2	4327.4	3802.3
20°	8766.9	8781.5	8485.9	7789.0	7170.3	6907.7	6518.4	6010.8	5380.4	4619.1	3983.7
22.5°	10763.6	10684.7	10050.3	8923.1	7993.0	7642.6	7087.3	6387.5	5678.0	4840.6	4119.5
25°	12583.8	12375.9	11791.4	10240.6	8784.4	8351.1	7776.3	6708.6	5924.9	5004.7	4231.7
27.5°	13629.1	13536.4	12873.7	11309.2	9423.7	8813.8	8004.7	6944.8	6071.3	5085.6	4263.9
30°	13888.7	13905.2	13315.8	11663.5	9575.0	8878.1	8041.8	6937.9	5972.8	4941.2	4078.4
32.5°	13822.2	13732.6	12995.7	11272.1	9171.9	8537.5	7678.7	6627.7	5580.4	4510.8	3616.8
35°	13141.1	13009.3	12102.7	10254.3	8487.8	7871.0	7092.2	6119.2	5032.9	3962.3	3099.6
37.5°	11845.0	11692.8	10646.5	9032.4	7667.0	7144.8	6471.5	5553.1	4479.6	3451.0	2644.8
40°	10044.4	9855.1	8980.6	7861.2	6784.8	6419.8	5850.7	4907.1	3905.8	2966.9	2225.1
42.5°	8360.9	8270.2	7745.1	6784.8	6059.6	5707.3	5133.5	4255.1	3333.8	2472.1	1647.4
45°	7020.9	6960.5	6612.0	6002.1	5266.2	4936.3	4395.6	3538.7	2536.5	1664.9	857.9
47.5°	6145.5	5991.3	5650.8	5010.5	4192.6	3781.8	3266.5	2331.5	1430.7	737.8	263.5
50°	4238.6	4253.2	3868.6	3163.0	2467.2	2119.7	1750.8	1072.6	473.3	161.0	45.8
52.5°	2231.9	2067.1	1796.7	1341.9	934.0	712.5	520.2	214.7	85.9	32.2	24.4
55°	608.1	533.9	426.5	301.6	162.9	114.2	75.2	40.0	28.3	22.4	15.6
57.5°	59.6	56.7	51.7	41.9	36.1	33.1	30.2	24.4	19.5	13.6	9.7
60°	33.1	32.2	30.2	26.3	23.4	21.4	19.5	16.6	11.7	8.8	7.8
62.5°	18.5	17.5	16.6	14.6	12.7	11.7	11.7	9.7	7.8	6.8	6.8
65°	8.8	8.8	8.8	8.8	8.8	7.8	6.8	6.8	6.8	6.8	6.8
67.5°	6.8	6.8	6.8	5.8	5.8	5.8	5.8	5.8	5.8	4.9	5.8
70°	3.9	3.9	4.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.9
72.5°	1.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	3.9	3.9	4.9
75°	1.9	1.9	1.9	1.9	2.9	2.9	2.9	2.9	3.9	3.9	4.9
77.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.9	2.9	3.9	3.9	4.9
80°	1.0	1.0	1.0	1.9	1.9	1.9	1.9	2.9	3.9	3.9	4.9
82.5°	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9
85°	1.0	1.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9
87.5°	0.0	0.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3
2.5°	1620.1	1572.2	1524.4	1476.5	1474.6	1446.3	1404.4	1348.7	1302.9	1263.9	1225.8
5°	1953.9	1855.3	1756.7	1658.1	1628.9	1578.0	1487.4	1384.9	1297.0	1219.9	1145.7
7.5°	2288.6	2122.6	1966.5	1812.4	1750.8	1673.7	1532.2	1383.9	1257.0	1143.8	1033.5
10°	2587.3	2346.1	2126.5	1909.9	1821.2	1720.6	1530.3	1341.9	1180.9	1035.4	894.9
12.5°	2862.4	2526.7	2248.6	1975.3	1854.3	1732.3	1500.1	1275.6	1083.3	909.5	747.6
15°	3104.4	2692.7	2334.4	2004.5	1856.2	1709.9	1436.6	1183.8	968.2	769.0	593.3
17.5°	3277.2	2775.5	2362.8	1978.2	1805.6	1641.5	1342.9	1072.6	840.3	632.4	462.6
20°	3382.6	2809.8	2348.1	1929.5	1746.0	1576.1	1273.6	1011.0	785.6	606.1	490.8
22.5°	3452.0	2842.9	2354.0	1928.5	1745.0	1584.9	1302.9	1057.0	873.5	776.8	763.2
25°	3526.1	2889.7	2396.9	1972.4	1801.5	1653.2	1380.0	1139.9	986.7	945.7	951.6
27.5°	3522.2	2869.2	2356.0	1934.4	1754.7	1604.5	1284.4	980.8	837.4	722.2	680.2
30°	3312.3	2632.1	2076.8	1604.5	1392.7	1208.2	786.6	511.4	353.3	309.4	265.4
32.5°	2821.5	2132.4	1552.7	1109.6	871.5	651.0	309.4	163.9	139.5	117.1	106.4
35°	2346.1	1700.1	1161.4	670.5	423.6	262.5	111.3	73.2	69.3	65.4	65.4
37.5°	1939.2	1335.1	750.5	283.1	155.1	94.7	53.6	48.7	46.8	45.8	45.8
40°	1516.6	870.5	325.0	93.7	49.7	42.9	38.0	36.1	35.1	34.1	35.1
42.5°	894.9	350.3	94.7	35.1	33.1	31.2	28.3	27.3	27.3	26.3	27.3
45°	304.5	90.8	31.2	25.3	23.4	23.4	21.4	21.4	21.4	20.5	22.4
47.5°	79.1	28.3	20.5	18.5	17.5	17.5	16.6	16.6	16.6	16.6	17.5
50°	27.3	18.5	14.6	13.6	12.7	13.6	12.7	12.7	12.7	12.7	13.6
52.5°	16.6	12.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
55°	10.7	9.7	8.8	8.8	8.8	8.8	8.8	9.7	9.7	9.7	9.7
57.5°	8.8	7.8	7.8	7.8	7.8	7.8	8.8	7.8	7.8	8.8	9.7
60°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8	9.7
62.5°	6.8	7.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8	9.7
65°	6.8	6.8	6.8	7.8	7.8	7.8	8.8	8.8	8.8	9.7	9.7
67.5°	5.8	5.8	6.8	6.8	7.8	7.8	7.8	8.8	8.8	8.8	9.7
70°	5.8	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8
72.5°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	8.8
75°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	8.8
77.5°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	8.8
80°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
82.5°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8	7.8
85°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	6.8	7.8	7.8	7.8
87.5°	4.9	5.8	5.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3
2.5°	1173.1	1156.5	1097.9	1090.1	1080.4	1032.5	1013.0	979.9	933.1	919.3	902.7
5°	1058.9	1004.2	918.3	894.9	869.6	794.4	748.6	693.9	633.4	600.1	569.0
7.5°	913.4	837.4	723.2	677.3	649.0	567.0	493.9	420.7	331.8	281.1	248.8
10°	751.5	647.1	528.0	475.2	437.2	318.2	248.8	216.7	186.4	161.9	140.5
12.5°	588.4	470.4	335.7	275.3	244.9	203.0	165.0	124.9	111.3	110.3	106.4
15°	431.4	299.6	226.4	204.0	182.5	130.8	129.8	129.8	133.7	136.6	137.6
17.5°	318.2	263.5	206.9	193.3	203.0	210.8	224.5	244.9	261.5	308.4	298.7
20°	466.5	462.6	504.6	558.2	596.2	677.3	779.8	895.9	1016.9	1151.7	1254.0
22.5°	800.2	897.8	974.0	1038.3	1072.6	1164.3	1245.3	1285.3	1308.7	1297.0	1280.5
25°	977.9	1013.0	989.6	967.2	970.1	887.1	826.7	749.5	684.1	624.6	589.4
27.5°	584.5	534.8	464.5	415.8	406.0	350.3	309.4	266.4	253.7	214.7	198.1
30°	210.8	196.2	173.8	156.1	154.1	139.5	130.8	121.0	120.0	111.3	106.4
32.5°	95.7	95.7	87.9	89.8	87.9	84.9	84.0	81.0	81.0	78.1	76.2
35°	62.5	63.5	62.5	62.5	61.5	61.5	61.5	59.6	60.6	58.6	55.7
37.5°	45.8	46.8	44.8	45.8	45.8	45.8	45.8	44.8	43.9	41.9	40.9
40°	35.1	35.1	35.1	35.1	35.1	35.1	35.1	34.1	34.1	33.1	31.2
42.5°	27.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	28.3	27.3	27.3
45°	22.4	23.4	22.4	23.4	23.4	23.4	22.4	22.4	22.4	21.4	20.5
47.5°	17.5	17.5	16.6	16.6	16.6	16.6	16.6	16.6	16.6	16.6	15.6
50°	13.6	13.6	13.6	13.6	13.6	13.6	14.6	13.6	13.6	13.6	13.6
52.5°	10.7	11.7	11.7	12.7	12.7	12.7	12.7	12.7	11.7	11.7	10.7
55°	9.7	10.7	10.7	11.7	11.7	11.7	11.7	10.7	10.7	10.7	9.7
57.5°	9.7	10.7	10.7	10.7	10.7	10.7	10.7	9.7	9.7	8.8	8.8
60°	9.7	9.7	9.7	10.7	10.7	9.7	9.7	8.8	8.8	7.8	7.8
62.5°	9.7	9.7	9.7	10.7	10.7	9.7	9.7	8.8	7.8	7.8	6.8
65°	9.7	10.7	9.7	10.7	10.7	9.7	9.7	8.8	7.8	7.8	6.8
67.5°	9.7	10.7	10.7	10.7	9.7	9.7	9.7	8.8	7.8	7.8	6.8
70°	8.8	9.7	9.7	9.7	9.7	9.7	8.8	8.8	7.8	7.8	6.8
72.5°	8.8	9.7	8.8	9.7	9.7	8.8	8.8	8.8	7.8	7.8	6.8
75°	8.8	8.8	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8
77.5°	8.8	8.8	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8	6.8
80°	8.8	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8	5.8
82.5°	7.8	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8	5.8
85°	7.8	7.8	7.8	7.8	7.8	7.8	6.8	6.8	5.8	4.9	4.9
87.5°	6.8	7.8	6.8	6.8	6.8	6.8	5.8	4.9	3.9	3.9	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192528

CATALOG NUMBER: LDA6A60930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3	1288.3
2.5°	876.4	852.0	853.0	856.9	832.5	819.7	816.8	804.1
5°	527.0	498.8	493.9	489.9	455.7	442.1	431.4	445.0
7.5°	226.4	215.7	213.7	210.8	195.2	187.4	183.5	187.4
10°	112.2	105.4	106.4	107.4	102.5	99.6	98.6	97.6
12.5°	111.3	110.3	111.3	111.3	112.2	110.3	111.3	111.3
15°	144.4	144.4	147.3	149.3	154.1	153.2	155.1	157.1
17.5°	360.1	341.6	351.3	351.3	395.3	356.2	389.5	359.1
20°	1415.1	1481.5	1548.8	1605.5	1663.0	1680.5	1714.8	1705.0
22.5°	1255.0	1262.9	1253.1	1242.3	1239.4	1242.3	1189.7	1197.5
25°	538.7	534.8	519.2	502.7	507.5	511.4	492.9	475.2
27.5°	184.5	179.6	174.7	170.8	168.9	166.0	160.0	156.1
30°	104.4	101.5	99.6	98.6	96.6	94.7	91.8	89.8
32.5°	75.2	73.2	72.3	71.3	69.3	67.4	64.5	63.5
35°	55.7	53.6	52.6	51.7	49.7	47.8	46.8	45.8
37.5°	40.9	39.0	39.0	39.0	36.1	34.1	33.1	32.2
40°	31.2	30.2	30.2	30.2	28.3	27.3	26.3	26.3
42.5°	27.3	26.3	26.3	26.3	24.4	23.4	23.4	22.4
45°	20.5	19.5	19.5	18.5	17.5	17.5	16.6	15.6
47.5°	15.6	14.6	14.6	14.6	13.6	12.7	12.7	11.7
50°	12.7	12.7	11.7	12.7	10.7	10.7	10.7	9.7
52.5°	10.7	10.7	9.7	9.7	8.8	8.8	8.8	7.8
55°	9.7	8.8	8.8	8.8	7.8	7.8	7.8	6.8
57.5°	7.8	7.8	6.8	6.8	5.8	5.8	5.8	5.8
60°	6.8	6.8	5.8	5.8	4.9	4.9	4.9	4.9
62.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
65°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
67.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
70°	6.8	6.8	5.8	5.8	5.8	4.9	4.9	4.9
72.5°	6.8	6.8	5.8	5.8	5.8	5.8	4.9	4.9
75°	5.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
77.5°	5.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
80°	5.8	5.8	4.9	4.9	4.9	4.9	4.9	4.9
82.5°	5.8	4.9	4.9	4.9	4.9	3.9	3.9	3.9
85°	3.9	3.9	3.9	3.9	2.9	2.9	2.9	2.9
87.5°	2.9	1.9	1.9	1.9	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)