

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192539

Luminaire Tested: **LDA6A60930D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192539
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60930D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5245.7 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	44	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	56021	56021	56021
5°	148673	51937	19877
10°	324521	41994	5923
15°	489844	30687	5153
20°	569797	21072	8086
25°	628391	22731	53846
30°	695246	17117	16749
35°	705577	8754	6271
40°	721795	3557	2998
45°	727858	2194	1814
50°	613148	1492	1160
55°	202526	1023	650
60°	39810	965	428
65°	4683	1258	506
70°	1250	1410	625
75°	212	1864	1038
80°	0	3062	1547
85°	0	6101	2453



TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	2.6
10°-20°	686.7	13.1
20°-30°	1355.5	25.8
30°-40°	1528.9	29.1
40°-50°	1213.7	23.1
50°-60°	296.8	5.7
60°-70°	15.8	0.3
70°-80°	6.7	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2178.2	41.5
0°-40°	3707.1	70.7
0°-60°	5217.6	99.5
0°-90°	5245.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5245.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1022	1022	1022	1022	1022	
5°	2702	2024	944	474	361	357
15°	8631	4587	541	106	91	2421
25°	10389	5560	376	680	890	4812
35°	10543	3539	131	104	94	6631
45°	9388	1103	28	29	23	7036
55°	2119	48	11	11	7	2486
65°	36	9	10	8	4	88
75°	1	5	9	8	5	3
85°	0	5	10	7	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9
2.5°	1773.4	1739.3	1754.9	1730.5	1661.2	1639.7	1657.3	1630.9	1551.8	1521.6	1490.4
5°	2701.7	2671.3	2681.1	2625.5	2495.8	2450.8	2447.9	2367.8	2207.8	2118.0	2024.3
7.5°	4096.3	4054.4	4042.7	3908.9	3659.1	3565.4	3519.6	3322.4	3020.8	2807.1	2597.3
10°	5829.8	5870.8	5828.8	5612.1	5219.7	5044.1	4932.9	4560.0	4016.4	3609.4	3217.0
12.5°	7568.1	7593.5	7514.4	7245.0	6746.2	6535.4	6371.5	5894.2	5177.8	4486.8	3901.1
15°	8631.0	8751.0	8676.8	8488.6	8102.0	7846.3	7698.9	7109.4	6207.5	5448.2	4587.3
17.5°	9388.4	9499.6	9438.2	9283.9	8847.7	8641.7	8546.1	8061.0	7079.2	6113.8	5100.7
20°	9767.1	9902.7	9847.1	9672.4	9352.3	9180.5	9064.3	8591.0	7705.8	6608.7	5443.4
22.5°	10023.8	10174.1	10113.6	9954.5	9628.5	9428.4	9373.7	8925.8	8033.7	6905.4	5588.7
25°	10388.8	10514.7	10344.0	10147.8	9825.7	9614.9	9581.6	9123.9	8190.9	7017.6	5560.5
27.5°	10650.4	10799.7	10509.8	10310.7	9942.8	9721.3	9678.3	9247.9	8205.5	6928.8	5331.0
30°	10983.2	10886.6	10631.9	10343.0	9950.6	9714.4	9659.7	9175.6	8059.0	6601.8	4882.1
32.5°	10851.5	10828.1	10573.3	10233.7	9867.6	9629.5	9556.3	8953.1	7656.9	6037.7	4246.7
35°	10543.1	10617.2	10404.4	10193.6	9738.8	9490.8	9389.3	8625.2	7050.8	5311.5	3539.1
37.5°	10362.5	10409.3	10274.6	10017.0	9566.0	9240.1	9047.8	8073.6	6257.4	4396.0	2856.8
40°	10086.2	10205.3	10075.5	9779.8	9259.5	8812.6	8477.7	7077.2	5211.9	3465.9	2234.1
42.5°	9783.7	9890.0	9766.1	9411.9	8676.8	8077.5	7521.3	5905.9	4080.7	2648.0	1675.8
45°	9388.4	9484.0	9261.5	8710.1	7669.6	6842.9	6287.6	4638.1	3077.4	1945.2	1102.9
47.5°	8675.9	8650.5	8335.3	7478.4	6196.8	5456.0	4809.8	3322.4	2045.7	1102.0	548.5
50°	7189.4	6952.2	6488.6	5494.0	4158.9	3358.5	2917.4	1714.9	928.2	533.9	344.5
52.5°	4656.6	4392.1	3967.5	3049.1	1997.0	1602.7	1285.5	775.0	484.1	301.6	135.6
55°	2119.0	1931.6	1660.2	1231.7	856.9	712.5	603.2	392.4	259.7	112.2	47.8
57.5°	807.2	744.7	661.8	528.0	396.3	342.5	284.0	188.4	81.0	41.9	28.3
60°	363.1	336.7	309.4	242.0	169.9	122.0	92.7	50.7	34.1	24.4	18.5
62.5°	123.9	103.5	85.9	61.5	45.8	40.0	35.1	28.3	20.5	16.6	12.7
65°	36.1	35.1	33.1	29.2	23.4	21.4	20.5	16.6	12.7	10.7	8.8
67.5°	17.5	16.6	15.6	14.6	11.7	10.7	10.7	9.7	7.8	6.8	5.8
70°	7.8	7.8	6.8	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
72.5°	3.9	3.9	3.9	2.9	2.9	2.9	2.9	3.9	3.9	4.9	4.9
75°	1.0	1.9	1.9	1.9	1.9	2.9	2.9	3.9	3.9	4.9	4.9
77.5°	1.0	1.0	1.0	1.9	1.9	1.9	2.9	3.9	3.9	4.9	4.9
80°	0.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9	4.9
82.5°	0.0	1.0	1.0	1.9	1.9	1.9	2.9	2.9	3.9	4.9	4.9
85°	0.0	0.0	1.0	1.0	1.9	1.9	2.9	2.9	3.9	4.9	4.9
87.5°	0.0	0.0	1.0	1.0	1.9	1.9	2.9	2.9	3.9	4.9	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9
2.5°	1414.3	1393.8	1312.8	1250.3	1221.0	1219.1	1153.6	1113.7	1043.3	988.7	937.0
5°	1859.3	1768.5	1604.6	1474.8	1412.3	1380.2	1251.2	1158.5	1037.5	943.8	851.0
7.5°	2312.2	2139.4	1909.1	1662.1	1560.6	1498.2	1299.1	1150.7	989.7	858.8	743.7
10°	2775.8	2471.3	2127.7	1801.8	1655.3	1549.9	1294.2	1093.2	907.7	754.4	628.5
12.5°	3258.9	2778.7	2300.5	1892.6	1699.3	1560.6	1250.3	1009.2	807.2	644.1	524.1
15°	3665.9	3016.9	2409.8	1914.0	1685.6	1517.7	1156.5	902.8	699.8	540.7	431.4
17.5°	3980.2	3150.6	2430.3	1861.2	1609.5	1422.1	1035.5	785.7	586.6	446.0	337.7
20°	4138.4	3171.1	2365.9	1736.3	1471.8	1278.6	898.0	666.7	491.9	361.2	268.5
22.5°	4150.1	3075.4	2225.4	1575.2	1320.6	1124.4	784.8	574.9	431.4	324.0	254.8
25°	3997.8	2890.9	2037.0	1410.4	1165.3	988.7	703.7	551.4	434.3	375.8	345.5
27.5°	3708.8	2635.3	1830.0	1245.4	1031.6	895.0	670.6	551.4	470.5	424.5	435.3
30°	3308.8	2309.3	1542.1	1020.9	839.4	720.3	527.0	412.9	324.0	270.4	260.7
32.5°	2789.4	1889.6	1195.7	754.4	612.0	519.2	356.3	258.7	208.9	204.0	198.1
35°	2295.7	1492.4	907.7	557.3	450.9	367.0	227.4	152.2	138.6	130.8	124.9
37.5°	1813.5	1116.6	651.9	405.1	309.4	233.2	117.1	98.6	85.9	78.1	71.3
40°	1363.5	802.3	459.8	244.9	162.1	100.5	70.3	60.6	53.7	49.7	47.8
42.5°	964.3	533.9	285.0	103.5	77.1	63.5	48.7	42.9	39.0	37.0	35.1
45°	560.3	331.8	115.2	60.6	48.7	43.9	36.1	32.2	30.2	28.3	27.3
47.5°	350.3	133.7	59.6	39.0	34.1	31.2	26.3	25.3	23.4	22.4	22.4
50°	141.5	59.6	37.0	27.3	24.4	23.4	20.5	19.5	17.5	17.5	17.5
52.5°	53.7	35.1	25.3	19.5	17.5	16.6	14.6	14.6	13.6	13.6	13.6
55°	31.2	23.4	17.5	13.6	12.7	12.7	11.7	11.7	10.7	10.7	10.7
57.5°	20.5	15.6	12.7	9.7	9.7	9.7	8.8	8.8	8.8	8.8	8.8
60°	13.6	10.7	8.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8	8.8
62.5°	9.7	8.8	7.8	7.8	7.8	7.8	7.8	8.8	8.8	8.8	9.7
65°	7.8	6.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7	9.7
67.5°	5.8	5.8	5.8	5.8	6.8	6.8	7.8	8.8	8.8	8.8	9.7
70°	4.9	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7
72.5°	4.9	5.8	5.8	6.8	6.8	6.8	7.8	8.8	8.8	8.8	9.7
75°	4.9	5.8	5.8	6.8	6.8	6.8	7.8	8.8	8.8	8.8	9.7
77.5°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7	9.7
80°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7	9.7
82.5°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7	9.7
85°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	9.7	9.7
87.5°	5.8	5.8	6.8	6.8	6.8	7.8	7.8	8.8	8.8	8.8	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9
2.5°	911.6	866.8	817.9	802.3	786.7	756.4	737.8	704.7	680.3	655.8	636.3
5°	789.6	718.3	658.8	633.4	609.0	567.1	537.8	502.7	474.4	449.9	427.5
7.5°	662.8	580.8	521.2	495.8	471.5	425.5	388.5	344.5	311.3	284.0	261.6
10°	545.6	467.6	403.1	372.9	344.5	296.7	261.6	226.4	198.1	174.7	154.3
12.5°	444.0	360.2	294.8	272.4	244.9	205.9	172.8	134.7	118.1	111.3	106.4
15°	344.5	269.4	214.7	194.2	169.9	132.7	118.1	111.3	106.4	103.5	99.6
17.5°	262.6	200.1	146.4	132.7	124.9	117.1	113.2	108.3	105.4	104.4	101.5
20°	205.9	151.2	137.6	133.7	133.7	131.7	128.8	128.8	127.8	130.8	130.8
22.5°	211.8	211.8	223.5	222.5	238.1	253.7	265.5	303.5	325.0	370.9	402.1
25°	370.0	405.1	446.0	458.8	489.0	533.9	580.8	639.3	680.3	724.2	741.7
27.5°	461.7	467.6	461.7	476.3	456.7	445.0	448.9	455.7	455.7	458.8	470.5
30°	273.3	287.0	299.6	309.4	304.5	299.6	297.7	283.1	283.1	277.2	272.4
32.5°	185.5	183.5	181.6	185.5	181.6	181.6	178.6	179.6	173.8	169.9	167.9
35°	126.9	121.0	114.2	115.2	111.3	110.3	107.4	107.4	103.5	101.5	100.5
37.5°	70.3	70.3	67.4	68.4	67.4	67.4	67.4	68.4	67.4	67.4	68.4
40°	47.8	47.8	46.8	47.8	46.8	47.8	48.7	48.7	48.7	48.7	47.8
42.5°	36.1	36.1	35.1	36.1	35.1	36.1	37.0	37.0	37.0	37.0	37.0
45°	28.3	28.3	28.3	28.3	28.3	28.3	28.3	29.2	29.2	28.3	28.3
47.5°	22.4	23.4	22.4	22.4	22.4	22.4	23.4	23.4	22.4	22.4	22.4
50°	18.5	18.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5	17.5
52.5°	14.6	13.6	13.6	12.7	12.7	12.7	12.7	12.7	12.7	12.7	11.7
55°	10.7	10.7	9.7	9.7	9.7	10.7	10.7	10.7	10.7	9.7	9.7
57.5°	9.7	9.7	9.7	8.8	8.8	9.7	9.7	8.8	8.8	8.8	7.8
60°	8.8	9.7	8.8	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8
62.5°	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8	6.8
65°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8
67.5°	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	7.8	7.8	6.8
70°	9.7	9.7	9.7	9.7	9.7	8.8	8.8	8.8	7.8	7.8	6.8
72.5°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	8.8	7.8	7.8	6.8
75°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8
77.5°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8
80°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8
82.5°	9.7	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8
85°	9.7	9.7	8.8	8.8	8.8	8.8	7.8	7.8	6.8	6.8	5.8
87.5°	8.8	8.8	8.8	8.8	7.8	7.8	7.8	6.8	5.8	5.8	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192539

CATALOG NUMBER: LDA6A60930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9	1021.9
2.5°	612.9	609.0	606.1	612.0	610.0	585.6	588.6	587.6
5°	402.1	393.4	386.5	389.5	381.7	370.9	363.1	361.2
7.5°	239.1	229.3	223.5	217.6	215.7	202.0	196.2	200.1
10°	131.7	118.1	117.1	114.2	110.3	107.4	105.4	106.4
12.5°	101.5	100.5	98.6	97.6	95.7	94.7	93.7	92.7
15°	96.6	95.7	94.7	93.7	92.7	91.8	90.8	90.8
17.5°	99.6	99.6	98.6	97.6	97.6	98.6	97.6	96.6
20°	129.8	129.8	131.7	134.7	134.7	137.6	141.5	138.6
22.5°	421.6	443.1	469.5	477.3	523.1	560.3	628.5	598.3
25°	771.1	819.9	831.6	848.1	873.6	886.3	873.6	890.2
27.5°	468.5	485.1	487.1	488.0	493.9	492.9	480.2	488.0
30°	272.4	278.2	276.2	275.3	273.3	262.6	260.7	264.6
32.5°	170.8	168.9	167.9	166.9	166.9	161.1	164.0	162.1
35°	97.6	100.5	99.6	98.6	95.7	94.7	94.7	93.7
37.5°	65.4	66.4	65.4	64.5	62.5	61.5	60.6	59.6
40°	46.8	47.8	46.8	45.8	44.8	43.9	42.9	41.9
42.5°	35.1	36.1	35.1	35.1	33.1	32.2	31.2	30.2
45°	27.3	26.3	26.3	26.3	25.3	24.4	23.4	23.4
47.5°	22.4	22.4	22.4	21.4	20.5	20.5	20.5	19.5
50°	16.6	17.5	16.6	16.6	15.6	14.6	14.6	13.6
52.5°	11.7	11.7	10.7	10.7	9.7	8.8	8.8	8.8
55°	8.8	8.8	8.8	7.8	7.8	6.8	6.8	6.8
57.5°	7.8	6.8	6.8	6.8	5.8	5.8	4.9	4.9
60°	6.8	5.8	5.8	4.9	4.9	3.9	3.9	3.9
62.5°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
65°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
67.5°	5.8	5.8	4.9	4.9	4.9	3.9	3.9	3.9
70°	5.8	5.8	5.8	4.9	4.9	4.9	3.9	3.9
72.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
75°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
77.5°	6.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
80°	5.8	5.8	5.8	4.9	4.9	4.9	4.9	4.9
82.5°	5.8	5.8	5.8	5.8	4.9	4.9	4.9	4.9
85°	5.8	4.9	4.9	4.9	3.9	3.9	3.9	3.9
87.5°	4.9	3.9	3.9	2.9	2.9	2.9	1.9	1.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)