

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192553

Luminaire Tested: **LDA6A60935D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4294.3 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	104	97	92	88	101	96	91	87	92	88	85		89	86	83		86
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78
4	89	79	72	66	87	78	71	66	76	70	65		73	68	64		71
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65
6	77	65	57	51	75	64	57	51	62	56	51		61	55	50		59
7	71	59	51	46	70	58	51	46	57	50	45		56	50	45		54
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	36		46
10	58	46	38	33	57	45	38	33	44	38	33		43	37	33		42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67747	67747	67747
5°	107621	66910	43462
10°	161470	64205	29174
15°	231392	60846	21584
20°	305442	56892	17992
25°	366608	55461	26282
30°	409652	55597	39702
35°	421167	49784	33890
40°	405846	39588	25204
45°	357681	29398	19390
50°	278933	21773	13415
55°	161332	15933	8669
60°	75389	11074	3892
65°	35283	6084	1634
70°	16365	2677	1170
75°	6841	1758	1313
80°	2968	1957	1642
85°	692	3271	2579

TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.8	3.0
10°-20°	469.1	10.9
20°-30°	928.6	21.6
30°-40°	1200.7	28.0
40°-50°	986.6	23.0
50°-60°	456.1	10.6
60°-70°	104.1	2.4
70°-80°	17.0	0.4
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1525.5	35.5
0°-40°	2726.1	63.5
0°-60°	4168.9	97.1
0°-90°	4294.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4294.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1236	1236	1236	1236	1236	
5°	1956	1682	1216	879	790	216
15°	4077	2727	1072	480	380	1191
25°	6061	3392	917	450	434	2791
35°	6293	3105	744	494	506	3896
45°	4614	2096	379	252	250	3511
55°	1688	816	167	107	91	1587
65°	272	167	47	18	13	312
75°	32	19	8	7	6	43
85°	1	3	5	5	4	3
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1569.2	1545.1	1559.8	1567.1	1529.5	1537.8	1542.1	1512.9	1504.6	1489.0	1443.0
5°	1955.7	1927.5	1939.0	1939.0	1883.8	1887.0	1884.9	1829.7	1799.5	1759.9	1681.6
7.5°	2411.1	2382.9	2385.0	2374.5	2296.4	2291.2	2257.9	2190.1	2130.8	2057.8	1941.1
10°	2900.7	2884.1	2873.6	2847.6	2744.5	2726.8	2677.8	2570.5	2472.5	2361.0	2196.4
12.5°	3475.8	3442.6	3412.4	3370.7	3236.3	3202.9	3134.2	2978.9	2835.1	2678.8	2461.0
15°	4077.1	4051.0	4002.0	3936.5	3764.5	3711.4	3621.7	3413.3	3234.2	3006.0	2726.8
17.5°	4699.2	4651.2	4579.3	4486.5	4279.3	4204.2	4092.7	3825.9	3588.4	3303.9	2966.4
20°	5235.7	5198.2	5099.2	4979.4	4741.8	4641.8	4510.5	4183.4	3892.6	3555.1	3158.0
22.5°	5701.4	5651.5	5529.5	5384.7	5119.0	4995.0	4847.1	4481.4	4127.1	3735.3	3298.8
25°	6060.9	6023.4	5878.6	5709.7	5418.0	5274.2	5110.7	4696.0	4303.1	3872.9	3392.5
27.5°	6353.7	6290.1	6128.7	5938.0	5623.3	5455.5	5282.6	4828.3	4403.2	3942.7	3428.0
30°	6471.5	6405.8	6234.9	6023.4	5690.0	5505.6	5327.3	4843.0	4395.9	3918.7	3385.2
32.5°	6449.5	6375.6	6193.3	5969.3	5628.6	5431.7	5251.3	4748.0	4291.7	3810.3	3269.5
35°	6293.3	6231.8	6043.3	5808.8	5469.1	5261.8	5073.2	4575.1	4117.7	3642.6	3104.9
37.5°	6057.8	5970.3	5794.2	5558.8	5199.3	5006.5	4819.9	4328.2	3881.1	3410.3	2899.7
40°	5671.2	5566.1	5389.9	5184.7	4843.0	4651.2	4481.4	4021.9	3582.1	3142.4	2654.9
42.5°	5184.7	5102.4	4938.7	4727.2	4413.7	4230.3	4078.1	3636.3	3246.6	2839.3	2385.0
45°	4613.6	4534.5	4394.9	4204.2	3920.7	3761.4	3621.7	3229.0	2877.8	2505.9	2096.4
47.5°	3995.8	3917.7	3795.7	3628.0	3374.8	3237.3	3115.4	2793.5	2462.1	2137.0	1777.5
50°	3270.6	3163.3	3096.6	2956.0	2744.5	2627.7	2534.0	2245.3	2000.5	1739.0	1440.0
52.5°	2441.3	2406.9	2311.0	2212.1	2063.0	1976.5	1915.1	1729.6	1526.4	1336.8	1108.7
55°	1688.0	1656.6	1598.3	1537.8	1437.9	1394.2	1348.2	1235.8	1100.2	971.1	815.8
57.5°	1067.0	1089.9	1052.4	1018.0	957.6	942.0	906.5	840.8	757.5	676.2	579.3
60°	687.6	700.2	676.2	656.4	623.1	610.6	593.9	554.3	504.2	457.5	391.8
62.5°	435.5	441.7	428.2	416.8	398.0	392.9	381.3	358.4	328.2	300.1	258.5
65°	272.0	277.1	267.7	260.5	249.1	250.1	239.7	226.0	208.4	190.7	166.7
67.5°	167.8	170.8	164.6	160.5	153.2	153.2	147.0	138.6	127.1	116.7	101.0
70°	102.1	103.1	98.9	96.9	91.6	90.7	87.5	81.3	74.0	66.7	57.3
72.5°	59.3	60.4	57.3	55.2	52.2	52.2	50.0	46.9	43.7	37.5	32.3
75°	32.3	33.4	31.3	30.2	28.1	29.1	27.1	26.1	22.9	20.8	18.8
77.5°	16.7	17.7	16.7	15.6	15.6	15.6	14.6	13.5	13.5	11.5	11.5
80°	9.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	8.3	8.3	7.3
82.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.1
85°	1.1	1.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	3.2	3.2
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1429.5	1428.5	1380.5	1359.7	1343.1	1317.0	1298.3	1278.4	1260.7	1228.4	1201.4
5°	1642.1	1612.9	1533.7	1483.7	1452.4	1410.7	1364.9	1319.1	1274.3	1215.9	1168.0
7.5°	1865.0	1802.5	1683.8	1600.3	1552.5	1494.1	1417.1	1345.2	1272.2	1192.0	1123.2
10°	2077.7	1975.5	1824.4	1697.3	1631.7	1556.6	1450.3	1350.3	1254.5	1153.4	1068.0
12.5°	2294.3	2148.5	1951.5	1786.9	1703.6	1610.8	1474.3	1350.3	1231.6	1114.9	1013.9
15°	2508.9	2316.3	2071.3	1867.1	1766.1	1655.7	1491.0	1343.1	1203.5	1072.1	959.6
17.5°	2692.3	2453.7	2158.9	1922.4	1803.6	1678.6	1489.9	1321.2	1165.9	1024.2	904.4
20°	2835.1	2552.8	2220.4	1950.4	1817.1	1680.7	1473.3	1288.9	1123.2	975.2	852.3
22.5°	2932.0	2617.4	2251.7	1955.7	1813.0	1669.2	1447.3	1256.6	1084.6	936.7	813.8
25°	2992.4	2649.7	2260.9	1948.4	1798.4	1649.3	1423.3	1228.4	1059.7	916.9	802.3
27.5°	3003.9	2640.3	2242.3	1918.2	1764.0	1614.0	1388.9	1201.4	1037.7	905.4	802.3
30°	2947.6	2579.8	2178.7	1850.5	1699.4	1552.5	1331.5	1152.4	999.2	878.3	784.5
32.5°	2840.4	2468.3	2073.4	1750.5	1603.5	1465.9	1253.4	1082.6	934.6	823.1	738.7
35°	2685.1	2319.3	1936.9	1624.4	1481.7	1353.5	1144.0	987.8	847.2	743.9	665.8
37.5°	2496.5	2140.2	1777.5	1480.6	1345.2	1225.3	1025.3	878.3	748.1	651.2	581.4
40°	2267.3	1946.3	1598.3	1322.3	1193.0	1084.6	900.3	758.6	635.6	553.2	489.7
42.5°	2027.6	1729.6	1407.7	1145.1	1030.4	927.3	763.7	636.6	527.3	459.5	409.4
45°	1780.7	1489.0	1207.6	974.2	887.7	772.1	621.0	517.9	429.3	379.2	339.6
47.5°	1502.5	1255.5	996.1	790.9	700.2	622.1	496.0	412.6	355.3	311.6	281.4
50°	1203.5	1006.5	788.8	613.7	538.7	479.3	386.5	329.3	285.5	255.3	232.4
52.5°	925.3	770.0	593.9	450.1	403.2	358.4	301.1	261.5	230.3	207.4	190.7
55°	687.6	561.6	427.2	333.4	300.1	270.9	236.5	205.2	182.3	166.7	153.2
57.5°	484.5	391.8	300.1	241.8	224.0	205.2	179.3	158.4	142.7	130.3	119.8
60°	324.0	266.7	211.5	177.2	164.6	152.1	135.5	120.9	109.4	101.0	90.7
62.5°	217.8	179.3	147.9	127.1	118.8	110.4	98.9	88.6	80.2	71.9	63.6
65°	139.6	118.8	100.0	86.5	80.2	76.0	67.8	60.4	54.2	46.9	40.6
67.5°	85.4	74.0	62.5	54.2	51.1	47.9	42.8	37.5	33.4	28.1	24.0
70°	50.0	43.7	37.5	32.3	31.3	29.1	25.0	21.9	19.7	16.7	14.6
72.5°	29.1	26.1	21.9	19.7	18.8	16.7	15.6	13.5	11.5	10.5	9.4
75°	16.7	14.6	12.6	11.5	11.5	10.5	9.4	9.4	8.3	8.3	7.3
77.5°	10.5	9.4	8.3	8.3	8.3	7.3	7.3	7.3	7.3	6.2	6.2
80°	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	4.1	4.1	4.1	4.1	4.1	5.2	5.2	5.2	5.2	5.2	6.2
85°	3.2	4.1	4.1	4.1	4.1	4.1	5.2	5.2	5.2	5.2	5.2
87.5°	3.2	4.1	4.1	4.1	4.1	4.1	5.2	5.2	5.2	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1185.7	1169.1	1118.0	1135.7	1103.4	1077.3	1075.3	1059.7	1032.5	1018.0	1010.7
5°	1131.6	1094.0	1031.5	1035.7	998.1	957.6	935.6	914.8	879.4	857.5	842.9
7.5°	1064.9	1013.9	939.9	934.6	895.0	846.1	814.7	785.6	747.1	719.0	701.2
10°	995.1	932.6	846.1	839.8	798.2	745.0	709.6	676.2	636.6	608.4	589.8
12.5°	930.5	858.6	772.1	756.5	715.8	661.7	623.1	587.6	549.1	525.1	503.3
15°	869.0	790.9	699.1	684.6	645.0	590.8	548.1	516.8	480.4	457.5	437.6
17.5°	807.5	727.2	636.6	620.0	582.5	530.3	492.8	459.5	426.1	404.3	386.5
20°	754.4	674.1	585.5	569.0	534.5	484.5	450.1	418.8	388.6	367.8	353.3
22.5°	719.9	641.8	561.6	547.0	514.7	469.9	437.6	410.5	384.5	364.7	353.3
25°	717.9	650.1	578.3	569.9	542.9	505.3	482.4	465.7	450.1	434.5	430.3
27.5°	730.4	675.2	614.8	612.7	590.8	565.8	555.3	550.2	541.8	536.5	543.8
30°	723.1	676.2	625.1	625.1	608.4	590.8	585.5	583.5	578.3	579.3	587.6
32.5°	684.6	641.8	592.8	593.9	583.5	563.7	560.5	559.6	553.2	552.3	558.5
35°	614.8	575.2	534.5	535.6	527.3	508.5	504.2	502.2	493.9	489.7	493.9
37.5°	534.5	502.2	463.7	463.7	455.4	440.8	436.6	432.3	427.2	423.0	423.0
40°	452.2	426.1	394.9	393.8	387.6	373.0	368.9	365.7	360.5	353.3	355.3
42.5°	382.4	358.4	333.4	331.3	327.2	314.6	310.5	306.3	301.1	294.9	294.9
45°	317.8	302.2	280.3	279.3	275.0	264.7	261.5	256.3	252.1	245.9	245.9
47.5°	264.7	252.1	234.5	233.4	230.3	220.9	217.8	213.6	209.5	205.2	205.2
50°	221.9	209.5	194.8	193.8	191.7	184.4	180.2	177.2	174.0	170.8	168.8
52.5°	182.3	171.9	160.5	159.4	157.3	150.0	147.0	144.9	141.7	136.5	136.5
55°	147.0	138.6	128.2	127.1	125.0	118.8	115.6	111.5	107.4	102.1	101.0
57.5°	114.7	107.4	98.9	98.0	94.8	89.6	84.4	80.2	76.0	71.9	69.8
60°	86.5	78.1	70.8	68.7	66.7	59.3	55.2	51.1	46.9	43.7	41.7
62.5°	58.4	53.1	44.8	43.7	41.7	37.5	32.3	30.2	28.1	26.1	25.0
65°	36.4	32.3	28.1	27.1	25.0	21.9	19.7	18.8	17.7	16.7	15.6
67.5°	21.9	19.7	16.7	16.7	15.6	14.6	12.6	12.6	11.5	11.5	10.5
70°	13.5	12.6	11.5	10.5	10.5	10.5	9.4	9.4	9.4	9.4	9.4
72.5°	9.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3
75°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
77.5°	7.3	7.3	6.2	7.3	7.3	7.3	7.3	6.2	7.3	6.2	6.2
80°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
85°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	4.1
87.5°	5.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192553

CATALOG NUMBER: LDA6A60935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8	1235.8
2.5°	1012.8	983.6	995.1	978.4	973.2	969.0	962.8	982.5
5°	836.7	805.5	812.7	796.1	788.8	781.5	774.2	789.8
7.5°	690.8	660.6	663.8	649.1	641.8	633.5	626.2	638.7
10°	577.2	549.1	550.2	536.5	529.3	520.9	514.7	524.1
12.5°	490.7	464.8	464.8	454.3	448.1	438.7	433.4	440.8
15°	425.2	402.1	402.1	391.8	386.5	378.2	373.0	380.3
17.5°	375.1	354.2	354.2	346.9	341.8	334.5	330.2	336.6
20°	341.8	324.0	325.1	317.8	313.7	305.3	303.2	308.4
22.5°	344.9	328.2	330.2	325.1	321.0	314.6	312.6	319.9
25°	431.4	418.8	426.1	426.1	428.2	418.8	423.0	434.5
27.5°	554.3	548.1	559.6	555.3	563.7	563.7	567.9	582.5
30°	599.2	593.9	606.4	605.4	613.7	611.6	613.7	627.2
32.5°	566.8	561.6	572.0	571.0	577.2	572.0	573.1	584.5
35°	498.0	492.8	500.1	499.1	503.3	497.1	500.1	506.4
37.5°	425.2	419.9	424.1	423.0	424.1	416.8	420.9	424.1
40°	357.4	351.2	357.4	353.3	354.2	346.9	348.0	352.2
42.5°	299.0	291.7	297.0	297.0	297.0	291.7	292.8	297.0
45°	249.1	243.8	246.9	245.9	246.9	242.7	245.9	250.1
47.5°	206.3	202.2	204.2	203.1	203.1	199.0	200.1	200.1
50°	169.9	165.7	166.7	165.7	162.6	157.3	156.3	157.3
52.5°	134.4	129.2	129.2	127.1	125.0	120.9	120.9	121.9
55°	98.9	94.8	94.8	93.8	91.6	88.6	88.6	90.7
57.5°	66.7	63.6	64.6	63.6	63.6	59.3	61.4	61.4
60°	40.6	38.5	38.5	37.5	35.5	34.4	33.4	35.5
62.5°	24.0	22.9	22.9	21.9	21.9	20.8	20.8	20.8
65°	15.6	14.6	14.6	13.5	13.5	12.6	11.5	12.6
67.5°	10.5	9.4	9.4	9.4	9.4	8.3	8.3	8.3
70°	9.4	8.3	8.3	8.3	8.3	7.3	7.3	7.3
72.5°	8.3	7.3	8.3	7.3	7.3	7.3	7.3	7.3
75°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2
77.5°	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2
80°	6.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
82.5°	5.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1
85°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
87.5°	3.2	3.2	3.2	3.2	3.2	2.1	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)