

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192560

Luminaire Tested: **LDA6A60940D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60940D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5363.4 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	50		59
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		50
10	61	50	43	38	60	49	43	38	48	42	38		48	42	38		47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83009	83009	83009
5°	160835	79100	26684
10°	273264	69226	11979
15°	421081	55210	19047
20°	609566	35931	33136
25°	894336	34671	42601
30°	1039875	32847	32644
35°	1052533	17400	17253
40°	871426	6555	7249
45°	658146	2233	2644
50°	450288	819	819
55°	62631	707	105
60°	1634	691	0
65°	415	960	0
70°	176	1186	0
75°	0	1567	0
80°	0	2683	347
85°	0	5346	0



TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.9	3.0
10°-20°	671.5	12.5
20°-30°	1531.8	28.6
30°-40°	1772.6	33.1
40°-50°	1069.0	19.9
50°-60°	145.2	2.7
60°-70°	4.7	0.1
70°-80°	5.1	0.1
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2362.1	44.0
0°-40°	4134.7	77.1
0°-60°	5348.9	99.7
0°-90°	5363.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5363.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1514	1514	1514	1514	1514	
5°	2923	2393	1437	786	485	340
15°	7419	4171	973	299	336	2196
25°	14786	4942	573	690	704	6691
35°	15728	3768	260	265	258	9478
45°	8489	1026	29	35	34	6638
55°	655	7	7	5	1	1285
65°	3	4	7	4	0	5
75°	0	5	7	5	0	0
85°	0	5	8	5	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	2189.6	2169.4	2178.0	2155.7	2099.1	2087.4	2086.3	2071.4	2023.4	1986.1	1941.4
5°	2922.7	2921.8	2927.0	2879.1	2780.0	2749.1	2734.2	2697.9	2581.8	2492.3	2393.3
7.5°	3838.1	3831.7	3825.3	3738.0	3582.4	3522.6	3484.4	3353.3	3193.5	3034.7	2857.8
10°	4909.0	4905.8	4881.2	4727.8	4478.5	4368.7	4294.1	4086.4	3829.6	3603.7	3303.2
12.5°	6152.4	6123.7	6080.1	5855.2	5513.2	5393.8	5229.7	4900.5	4506.2	4160.0	3740.0
15°	7419.4	7377.8	7300.1	7011.3	6587.2	6383.7	6180.2	5746.5	5211.6	4708.7	4170.6
17.5°	8658.7	8612.9	8430.6	7940.4	7526.0	7277.7	7051.7	6456.1	5827.4	5180.8	4498.7
20°	10448.8	10282.5	9965.0	9192.5	8422.1	7974.6	7710.3	7080.6	6302.7	5549.4	4732.1
22.5°	12839.8	12471.2	11794.5	10539.3	9438.7	8793.0	8360.2	7522.7	6644.7	5790.2	4876.0
25°	14785.5	14618.2	13848.9	12063.1	10345.4	9584.5	8982.6	7874.4	6894.1	5951.1	4942.0
27.5°	16039.7	15998.1	15119.0	13324.7	11085.9	10087.6	9415.2	8106.7	7014.5	5985.1	4910.0
30°	16427.5	16492.5	15648.6	13753.0	11300.2	10188.7	9453.5	8109.8	6921.8	5830.7	4705.5
32.5°	16398.8	16402.0	15367.4	13383.3	10951.7	9894.7	9133.9	7840.3	6579.8	5443.8	4316.5
35°	15727.5	15562.4	14392.4	12247.4	10140.8	9208.5	8501.0	7318.1	6016.1	4862.1	3767.8
37.5°	14253.9	14037.6	12673.6	10792.9	9180.7	8318.7	7747.5	6633.0	5344.8	4240.9	3200.9
40°	12177.1	11870.2	10745.0	9440.8	8130.2	7482.3	7002.8	5866.9	4626.7	3631.3	2669.2
42.5°	10098.2	9947.9	9204.2	8143.9	7246.8	6637.3	6136.5	5064.5	3936.1	3030.5	1996.9
45°	8489.2	8360.2	7860.5	7161.5	6281.4	5725.2	5242.5	4228.1	3058.1	2033.1	1026.2
47.5°	7317.1	7212.7	6734.3	6000.1	5034.8	4426.3	3928.7	2772.6	1732.6	878.0	256.8
50°	5279.8	5173.2	4704.4	3854.1	2982.5	2473.1	2115.1	1238.2	491.2	177.9	26.7
52.5°	2588.2	2500.9	2182.2	1633.5	1096.5	788.5	576.5	232.3	56.4	19.1	12.8
55°	655.3	602.0	501.9	315.4	154.5	92.7	59.7	21.3	13.9	10.6	7.4
57.5°	37.3	36.2	33.0	24.5	18.2	16.0	13.9	10.6	7.4	6.3	5.4
60°	14.9	13.9	12.8	10.6	8.5	7.4	7.4	5.4	4.3	4.3	4.3
62.5°	6.3	6.3	6.3	5.4	4.3	4.3	4.3	3.2	4.3	4.3	4.3
65°	3.2	3.2	3.2	2.1	2.1	2.1	3.2	3.2	3.2	4.3	4.3
67.5°	2.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	4.3
70°	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4
72.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4
75°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4
77.5°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4
80°	0.0	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4
82.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4
85°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	4.3	4.3	5.4
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.3	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1883.9	1845.5	1789.1	1751.8	1715.5	1681.4	1625.0	1593.0	1535.4	1482.1	1436.3
5°	2273.9	2178.0	2061.8	1962.8	1898.8	1835.9	1722.0	1637.8	1532.2	1437.4	1350.1
7.5°	2668.2	2498.7	2308.0	2144.9	2045.9	1948.9	1778.4	1642.0	1492.9	1357.5	1228.6
10°	3026.2	2771.5	2501.8	2268.6	2134.3	2008.6	1783.7	1602.5	1410.7	1243.6	1081.5
12.5°	3358.6	3010.1	2658.6	2353.8	2187.6	2036.2	1761.3	1539.7	1311.7	1113.5	924.9
15°	3654.9	3207.3	2772.6	2402.8	2207.8	2028.8	1709.2	1451.3	1194.4	972.8	734.2
17.5°	3879.7	3329.9	2822.7	2395.3	2171.6	1972.4	1619.6	1340.4	1069.8	801.3	531.7
20°	4016.0	3382.0	2812.0	2337.8	2093.7	1882.8	1513.1	1220.0	919.5	615.9	468.8
22.5°	4073.6	3377.8	2761.9	2251.6	1997.8	1784.8	1410.7	1102.8	761.9	557.3	489.1
25°	4083.2	3334.1	2691.6	2156.6	1903.0	1691.0	1307.4	969.6	661.7	573.2	547.7
27.5°	4009.7	3231.8	2559.5	2020.3	1769.9	1550.4	1152.9	770.4	621.2	571.1	588.2
30°	3792.3	2998.4	2326.1	1780.6	1538.7	1319.1	823.6	604.2	515.7	518.9	523.1
32.5°	3409.8	2610.5	1951.1	1430.0	1165.7	869.4	512.5	403.8	392.1	392.1	389.9
35°	2899.3	2136.4	1531.1	904.7	579.7	417.7	265.3	266.4	261.0	260.0	258.9
37.5°	2371.9	1685.6	969.6	374.0	251.5	174.7	156.6	158.8	156.6	159.9	157.7
40°	1870.0	1041.0	353.8	119.3	88.5	85.3	87.4	89.6	89.6	91.6	91.6
42.5°	1086.8	345.2	92.7	47.9	47.9	45.8	46.9	49.0	50.1	51.2	50.1
45°	322.9	71.4	29.9	26.7	26.7	25.6	25.6	26.7	27.7	28.8	28.8
47.5°	51.2	20.2	17.1	14.9	14.9	14.9	14.9	14.9	16.0	16.0	17.1
50°	16.0	12.8	10.6	9.6	9.6	8.5	8.5	9.6	9.6	9.6	10.6
52.5°	9.6	7.4	7.4	6.3	7.4	7.4	6.3	7.4	7.4	7.4	8.5
55°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4	7.4
57.5°	5.4	5.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
60°	5.4	5.4	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	7.4
62.5°	5.4	5.4	6.3	6.3	6.3	6.3	6.3	6.3	7.4	7.4	7.4
65°	5.4	5.4	6.3	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4
67.5°	5.4	6.3	6.3	6.3	6.3	7.4	7.4	7.4	7.4	7.4	7.4
70°	5.4	6.3	6.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
72.5°	5.4	6.3	6.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
75°	6.3	6.3	6.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4	8.5
77.5°	6.3	6.3	7.4	7.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5
80°	6.3	6.3	7.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
82.5°	6.3	6.3	7.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
85°	6.3	6.3	7.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
87.5°	6.3	6.3	7.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1397.0	1347.9	1324.5	1291.4	1268.0	1215.8	1194.4	1158.3	1128.4	1079.4	1082.6
5°	1275.5	1182.7	1119.9	1070.9	1036.8	953.7	898.2	839.6	786.3	720.3	695.8
7.5°	1107.1	993.1	897.2	838.6	794.9	684.1	561.5	465.6	393.2	341.0	320.7
10°	938.8	790.6	638.3	547.7	484.9	378.2	323.9	298.3	274.9	246.2	227.0
12.5°	742.7	531.7	393.2	356.9	331.3	296.2	261.0	233.4	238.7	239.7	247.2
15°	507.2	382.5	338.9	314.4	286.6	266.4	278.1	285.5	299.4	300.5	310.1
17.5°	412.4	359.1	323.9	322.9	325.0	336.7	354.8	364.5	382.5	386.8	400.7
20°	412.4	381.4	411.3	411.3	416.6	432.6	456.1	469.9	490.1	497.7	514.6
22.5°	469.9	491.2	528.5	532.8	535.0	552.0	581.7	595.6	619.0	623.3	641.5
25°	573.2	592.5	626.6	629.8	630.9	643.6	665.9	673.4	689.5	680.9	691.5
27.5°	606.2	614.8	636.1	638.3	632.9	638.3	646.8	646.8	652.1	635.1	638.3
30°	532.8	535.0	545.6	546.7	535.0	537.0	538.1	537.0	535.9	517.9	517.9
32.5°	395.3	395.3	409.2	406.0	393.2	396.4	396.4	396.4	395.3	380.4	378.2
35°	262.1	263.2	274.9	272.8	263.2	265.3	265.3	268.6	265.3	256.8	254.7
37.5°	159.9	160.9	166.2	167.3	164.1	165.1	166.2	165.1	167.3	163.0	160.9
40°	92.7	94.8	99.1	100.2	99.1	99.1	100.2	101.3	105.5	100.2	98.0
42.5°	54.3	55.4	57.5	57.5	57.5	57.5	58.6	59.7	60.7	59.7	58.6
45°	31.0	31.9	33.0	33.0	34.1	33.0	34.1	34.1	35.2	34.1	34.1
47.5°	18.2	18.2	19.1	19.1	20.2	19.1	20.2	20.2	20.2	19.1	19.1
50°	10.6	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	10.6	10.6
52.5°	8.5	8.5	8.5	8.5	8.5	7.4	7.4	7.4	7.4	6.3	6.3
55°	7.4	7.4	7.4	7.4	7.4	7.4	6.3	5.4	5.4	4.3	4.3
57.5°	6.3	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	3.2	3.2
60°	7.4	7.4	7.4	7.4	6.3	6.3	6.3	5.4	4.3	3.2	3.2
62.5°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	3.2	3.2
65°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	3.2	3.2
67.5°	7.4	7.4	7.4	7.4	7.4	6.3	6.3	5.4	4.3	4.3	3.2
70°	7.4	8.5	8.5	7.4	7.4	7.4	6.3	5.4	5.4	4.3	3.2
72.5°	7.4	8.5	8.5	7.4	7.4	7.4	6.3	5.4	5.4	4.3	3.2
75°	8.5	8.5	8.5	8.5	7.4	7.4	6.3	6.3	5.4	4.3	3.2
77.5°	8.5	8.5	8.5	8.5	7.4	7.4	6.3	6.3	5.4	4.3	3.2
80°	8.5	8.5	8.5	8.5	8.5	7.4	7.4	6.3	5.4	4.3	4.3
82.5°	8.5	8.5	8.5	8.5	8.5	7.4	7.4	6.3	5.4	4.3	4.3
85°	8.5	8.5	8.5	8.5	8.5	7.4	7.4	6.3	5.4	4.3	3.2
87.5°	8.5	8.5	8.5	8.5	7.4	7.4	6.3	6.3	5.4	4.3	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192560

CATALOG NUMBER: LDA6A60940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1043.2	1018.6	1008.0	1025.1	1016.5	990.9	996.3	980.3
5°	622.3	585.0	561.5	572.2	538.1	507.2	507.2	484.9
7.5°	300.5	288.8	282.3	284.5	277.1	267.5	262.1	262.1
10°	210.9	206.7	207.8	207.8	214.2	213.1	216.3	215.2
12.5°	250.4	252.5	253.6	257.8	263.2	263.2	266.4	264.3
15°	320.7	318.7	325.0	326.1	334.6	335.6	339.9	335.6
17.5°	408.1	412.4	418.7	417.7	434.8	435.8	435.8	434.8
20°	525.3	528.5	535.0	537.0	557.3	559.4	566.9	568.0
22.5°	653.2	653.2	656.3	660.6	679.8	680.9	684.1	684.1
25°	696.9	690.4	691.5	696.9	707.5	703.2	706.4	704.3
27.5°	640.4	630.9	628.7	636.1	643.6	631.8	636.1	636.1
30°	520.0	511.4	509.4	516.8	522.2	509.4	513.6	515.7
32.5°	380.4	375.1	374.0	379.3	383.6	372.9	377.1	380.4
35°	256.8	254.7	252.5	253.6	260.0	251.5	255.8	257.8
37.5°	163.0	158.8	159.9	161.9	166.2	160.9	165.1	165.1
40°	100.2	98.0	98.0	100.2	102.2	98.0	100.2	101.3
42.5°	58.6	58.6	58.6	59.7	60.7	58.6	58.6	59.7
45°	34.1	33.0	33.0	34.1	35.2	33.0	34.1	34.1
47.5°	19.1	18.2	18.2	19.1	19.1	18.2	19.1	19.1
50°	10.6	9.6	9.6	10.6	10.6	9.6	9.6	9.6
52.5°	5.4	5.4	5.4	5.4	5.4	5.4	4.3	4.3
55°	3.2	3.2	2.1	2.1	2.1	2.1	2.1	1.1
57.5°	2.1	2.1	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.1	2.1	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.2	2.1	2.1	1.1	1.1	1.1	0.0	0.0
72.5°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
75°	3.2	2.1	2.1	2.1	1.1	1.1	0.0	0.0
77.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
80°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	1.1
82.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	1.1
85°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
87.5°	3.2	2.1	2.1	2.1	1.1	1.1	1.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)