

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192590

Luminaire Tested: **LDA6A60950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5955.8 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57
8	69	57	50	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	37	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63602	63602	63602
5°	168792	58964	22562
10°	368447	47678	6719
15°	556150	34841	5851
20°	646920	23919	9182
25°	713455	25804	61135
30°	789349	19427	19016
35°	801083	9938	7114
40°	819500	4043	3406
45°	826388	2496	2062
50°	696139	1697	1322
55°	229927	1166	736
60°	45205	1096	493
65°	5331	1427	584
70°	1410	1603	721
75°	233	2118	1186
80°	0	3473	1768
85°	0	6919	2830

TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.4	2.6
10°-20°	779.7	13.1
20°-30°	1538.9	25.8
30°-40°	1735.9	29.1
40°-50°	1378.1	23.1
50°-60°	336.9	5.7
60°-70°	18.0	0.3
70°-80°	7.7	0.1
80°-90°	6.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2473.0	41.5
0°-40°	4208.8	70.7
0°-60°	5923.8	99.5
0°-90°	5955.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5955.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1160	1160	1160	1160	1160	
5°	3067	2298	1072	539	410	405
15°	9799	5208	614	121	103	2749
25°	11795	6313	427	772	1011	5463
35°	11970	4018	148	118	106	7528
45°	10659	1252	32	33	27	7989
55°	2406	54	12	12	8	2822
65°	41	10	11	9	4	100
75°	1	6	10	9	6	3
85°	0	6	11	8	4	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2
2.5°	2013.5	1974.8	1992.4	1964.7	1886.0	1861.7	1881.6	1851.7	1762.0	1727.6	1692.1
5°	3067.3	3033.0	3044.1	2980.8	2833.5	2782.5	2779.2	2688.4	2506.6	2404.7	2298.3
7.5°	4650.9	4603.2	4589.9	4438.1	4154.4	4048.1	3996.0	3772.2	3429.7	3187.1	2948.8
10°	6618.9	6665.5	6617.8	6371.8	5926.3	5726.9	5600.5	5177.2	4560.1	4097.8	3652.4
12.5°	8592.5	8621.3	8531.5	8225.8	7659.5	7420.1	7233.9	6692.1	5878.7	5094.1	4429.3
15°	9799.3	9935.6	9851.3	9637.6	9198.7	8908.3	8741.0	8071.6	7047.8	6185.6	5208.3
17.5°	10659.3	10785.4	10715.7	10540.6	10045.3	9811.4	9702.9	9152.1	8037.3	6941.4	5791.1
20°	11089.1	11243.2	11180.0	10981.7	10618.2	10423.2	10291.3	9753.8	8748.8	7503.3	6180.1
22.5°	11380.6	11551.3	11482.5	11301.9	10931.9	10704.6	10642.6	10134.0	9121.1	7840.1	6345.1
25°	11795.1	11938.0	11744.1	11521.4	11155.7	10916.3	10878.6	10358.9	9299.6	7967.4	6313.1
27.5°	12092.1	12261.6	11932.5	11706.4	11288.6	11037.0	10988.3	10499.7	9316.1	7866.8	6052.7
30°	12469.8	12360.2	12071.1	11743.0	11297.4	11029.3	10967.2	10417.6	9149.9	7495.5	5543.0
32.5°	12320.4	12293.7	12004.5	11618.9	11203.3	10932.9	10849.8	10165.0	8693.4	6854.8	4821.5
35°	11970.2	12054.3	11812.7	11573.3	11057.1	10775.5	10660.2	9792.6	8005.2	6030.5	4018.1
37.5°	11765.1	11818.4	11665.4	11372.8	10860.8	10490.8	10272.5	9166.5	7104.3	4991.1	3243.6
40°	11451.5	11586.6	11439.3	11103.6	10512.8	10005.4	9625.2	8035.1	5917.5	3935.0	2536.6
42.5°	11108.0	11228.8	11088.1	10685.9	9851.3	9170.9	8539.2	6705.4	4633.2	3006.4	1902.6
45°	10659.3	10767.8	10515.1	9889.0	8707.7	7769.1	7138.7	5265.9	3494.0	2208.5	1252.3
47.5°	9850.4	9821.4	9463.6	8490.7	7035.6	6194.4	5460.8	3772.2	2322.6	1251.1	622.8
50°	8162.5	7893.3	7366.8	6237.7	4721.7	3813.1	3312.3	1947.0	1053.9	606.1	391.2
52.5°	5286.9	4986.6	4504.6	3461.7	2267.2	1819.6	1459.4	879.9	549.6	342.5	154.0
55°	2405.7	2192.9	1885.0	1398.5	972.9	808.9	684.8	445.4	294.7	127.5	54.3
57.5°	916.3	845.5	751.3	599.6	449.9	389.0	322.5	213.9	92.0	47.6	32.2
60°	412.3	382.3	351.3	274.9	192.7	138.5	105.4	57.6	38.8	27.8	21.0
62.5°	140.7	117.5	97.4	69.8	52.1	45.4	39.9	32.2	23.3	18.9	14.5
65°	41.1	39.9	37.6	33.2	26.6	24.3	23.3	18.9	14.5	12.2	10.0
67.5°	19.9	18.9	17.8	16.6	13.3	12.2	12.2	11.0	8.8	7.7	6.6
70°	8.8	8.8	7.7	7.7	6.6	6.6	6.6	5.6	5.6	5.6	5.6
72.5°	4.5	4.5	4.5	3.3	3.3	3.3	3.3	4.5	4.5	5.6	5.6
75°	1.1	2.2	2.2	2.2	2.2	3.3	3.3	4.5	4.5	5.6	5.6
77.5°	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6	5.6
80°	0.0	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	5.6	5.6
82.5°	0.0	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	5.6	5.6
85°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	5.6
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	3.3	3.3	4.5	5.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2
2.5°	1605.7	1582.4	1490.5	1419.5	1386.3	1384.0	1309.8	1264.4	1184.6	1122.6	1063.8
5°	2111.0	2007.9	1821.8	1674.4	1603.6	1566.9	1420.6	1315.4	1178.0	1071.5	966.4
7.5°	2625.3	2429.0	2167.5	1887.2	1772.0	1701.0	1474.9	1306.4	1123.6	975.2	844.4
10°	3151.5	2805.8	2415.7	2045.6	1879.4	1759.7	1469.4	1241.0	1030.5	856.5	713.6
12.5°	3700.0	3154.8	2612.0	2148.7	1929.2	1772.0	1419.5	1145.8	916.3	731.3	595.1
15°	4162.3	3425.3	2736.0	2173.1	1913.8	1723.2	1313.2	1025.0	794.5	613.9	489.8
17.5°	4519.0	3577.1	2759.3	2113.3	1827.4	1614.6	1175.7	892.1	666.0	506.4	383.3
20°	4698.5	3600.3	2686.1	1971.4	1671.1	1451.7	1019.4	756.8	558.5	410.0	304.8
22.5°	4711.8	3491.7	2526.5	1788.6	1499.4	1276.6	891.0	652.7	489.8	368.0	289.2
25°	4538.9	3282.3	2312.8	1601.3	1323.1	1122.6	798.9	626.1	493.1	426.6	392.2
27.5°	4210.9	2992.0	2077.7	1414.0	1171.2	1016.1	761.3	626.1	534.1	482.0	494.2
30°	3756.6	2621.8	1750.9	1159.1	953.1	817.8	598.4	468.7	368.0	306.9	295.9
32.5°	3167.0	2145.3	1357.4	856.5	694.7	589.6	404.6	293.6	237.1	231.5	225.0
35°	2606.3	1694.4	1030.5	632.7	512.0	416.7	258.1	172.8	157.4	148.5	141.9
37.5°	2058.9	1267.7	740.3	459.9	351.3	264.9	132.9	111.9	97.4	88.7	80.8
40°	1548.0	910.9	521.9	278.2	184.0	114.2	79.9	68.6	60.9	56.5	54.3
42.5°	1094.8	606.1	323.5	117.5	87.6	72.0	55.4	48.8	44.3	42.1	39.9
45°	636.1	376.8	130.8	68.6	55.4	49.8	41.1	36.6	34.3	32.2	31.1
47.5°	397.8	151.8	67.5	44.3	38.8	35.5	30.0	28.8	26.6	25.5	25.5
50°	160.7	67.5	42.1	31.1	27.8	26.6	23.3	22.2	19.9	19.9	19.9
52.5°	60.9	39.9	28.8	22.2	19.9	18.9	16.6	16.6	15.5	15.5	15.5
55°	35.5	26.6	19.9	15.5	14.5	14.5	13.3	13.3	12.2	12.2	12.2
57.5°	23.3	17.8	14.5	11.0	11.0	11.0	10.0	10.0	10.0	10.0	10.0
60°	15.5	12.2	10.0	8.8	8.8	8.8	8.8	10.0	10.0	10.0	10.0
62.5°	11.0	10.0	8.8	8.8	8.8	8.8	8.8	10.0	10.0	10.0	11.0
65°	8.8	7.7	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0	11.0
67.5°	6.6	6.6	6.6	6.6	7.7	7.7	8.8	10.0	10.0	10.0	11.0
70°	5.6	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0
72.5°	5.6	6.6	6.6	7.7	7.7	7.7	8.8	10.0	10.0	10.0	11.0
75°	5.6	6.6	6.6	7.7	7.7	7.7	8.8	10.0	10.0	10.0	11.0
77.5°	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0	11.0
80°	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0	11.0
82.5°	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0	11.0
85°	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	11.0	11.0
87.5°	6.6	6.6	7.7	7.7	7.7	8.8	8.8	10.0	10.0	10.0	11.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2
2.5°	1035.0	984.0	928.5	910.9	893.2	858.8	837.7	800.1	772.4	744.6	722.5
5°	896.5	815.7	748.0	719.2	691.5	643.8	610.6	570.6	538.6	510.8	485.4
7.5°	752.4	659.4	591.8	563.0	535.2	483.1	441.1	391.2	353.5	322.5	296.9
10°	619.4	530.7	457.6	423.3	391.2	336.9	296.9	257.1	225.0	198.3	175.1
12.5°	504.3	408.9	334.7	309.2	278.2	233.8	196.1	153.0	134.1	126.4	120.7
15°	391.2	305.8	243.9	220.5	192.7	150.7	134.1	126.4	120.7	117.5	113.0
17.5°	298.1	227.2	166.3	150.7	141.9	132.9	128.5	123.0	119.6	118.7	115.2
20°	233.8	171.7	156.2	151.8	151.8	149.6	146.2	146.2	145.1	148.5	148.5
22.5°	240.4	240.4	253.8	252.7	270.4	288.1	301.4	344.6	369.0	421.1	456.7
25°	420.0	459.9	506.4	520.8	555.3	606.1	659.4	725.8	772.4	822.2	842.1
27.5°	524.2	530.7	524.2	540.8	518.5	505.2	509.7	517.4	517.4	520.8	534.1
30°	310.2	325.8	340.2	351.3	345.7	340.2	338.0	321.4	321.4	314.7	309.2
32.5°	210.5	208.3	206.0	210.5	206.0	206.0	202.8	203.9	197.2	192.7	190.6
35°	144.1	137.4	129.7	130.8	126.4	125.2	121.9	121.9	117.5	115.2	114.2
37.5°	79.9	79.9	76.4	77.6	76.4	76.4	76.4	77.6	76.4	76.4	77.6
40°	54.3	54.3	53.2	54.3	53.2	54.3	55.4	55.4	55.4	55.4	54.3
42.5°	41.1	41.1	39.9	41.1	39.9	41.1	42.1	42.1	42.1	42.1	42.1
45°	32.2	32.2	32.2	32.2	32.2	32.2	32.2	33.2	33.2	32.2	32.2
47.5°	25.5	26.6	25.5	25.5	25.5	25.5	26.6	26.6	25.5	25.5	25.5
50°	21.0	21.0	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9
52.5°	16.6	15.5	15.5	14.5	14.5	14.5	14.5	14.5	14.5	14.5	13.3
55°	12.2	12.2	11.0	11.0	11.0	12.2	12.2	12.2	12.2	11.0	11.0
57.5°	11.0	11.0	11.0	10.0	10.0	11.0	11.0	10.0	10.0	10.0	8.8
60°	10.0	11.0	10.0	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7
62.5°	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7	7.7
65°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	7.7	7.7
67.5°	11.0	11.0	11.0	11.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7
70°	11.0	11.0	11.0	11.0	11.0	10.0	10.0	10.0	8.8	8.8	7.7
72.5°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	10.0	8.8	8.8	7.7
75°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7
77.5°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7
80°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7
82.5°	11.0	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	7.7	7.7
85°	11.0	11.0	10.0	10.0	10.0	10.0	8.8	8.8	7.7	7.7	6.6
87.5°	10.0	10.0	10.0	10.0	8.8	8.8	8.8	7.7	6.6	6.6	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192590

CATALOG NUMBER: LDA6A60950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2
2.5°	695.9	691.5	688.2	694.7	692.5	664.9	668.3	667.2
5°	456.7	446.6	438.9	442.2	433.3	421.1	412.3	410.0
7.5°	271.4	260.4	253.8	247.1	244.8	229.4	222.8	227.2
10°	149.6	134.1	132.9	129.7	125.2	121.9	119.6	120.7
12.5°	115.2	114.2	111.9	110.8	108.6	107.4	106.3	105.4
15°	109.7	108.6	107.4	106.3	105.4	104.2	103.1	103.1
17.5°	113.0	113.0	111.9	110.8	110.8	111.9	110.8	109.7
20°	147.4	147.4	149.6	153.0	153.0	156.2	160.7	157.4
22.5°	478.7	503.2	533.0	541.9	593.9	636.1	713.6	679.3
25°	875.5	930.8	944.1	963.0	991.8	1006.2	991.8	1010.7
27.5°	531.9	550.8	553.0	554.1	560.7	559.6	545.2	554.1
30°	309.2	315.8	313.7	312.5	310.2	298.1	295.9	300.4
32.5°	193.9	191.8	190.6	189.5	189.5	182.8	186.2	184.0
35°	110.8	114.2	113.0	111.9	108.6	107.4	107.4	106.3
37.5°	74.3	75.4	74.3	73.1	70.9	69.8	68.6	67.5
40°	53.2	54.3	53.2	52.1	51.0	49.8	48.8	47.6
42.5°	39.9	41.1	39.9	39.9	37.6	36.6	35.5	34.3
45°	31.1	30.0	30.0	30.0	28.8	27.8	26.6	26.6
47.5°	25.5	25.5	25.5	24.3	23.3	23.3	23.3	22.2
50°	18.9	19.9	18.9	18.9	17.8	16.6	16.6	15.5
52.5°	13.3	13.3	12.2	12.2	11.0	10.0	10.0	10.0
55°	10.0	10.0	10.0	8.8	8.8	7.7	7.7	7.7
57.5°	8.8	7.7	7.7	7.7	6.6	6.6	5.6	5.6
60°	7.7	6.6	6.6	5.6	5.6	4.5	4.5	4.5
62.5°	6.6	5.6	5.6	5.6	4.5	4.5	4.5	4.5
65°	6.6	5.6	5.6	5.6	4.5	4.5	4.5	4.5
67.5°	6.6	6.6	5.6	5.6	5.6	4.5	4.5	4.5
70°	6.6	6.6	6.6	5.6	5.6	5.6	4.5	4.5
72.5°	7.7	6.6	6.6	6.6	5.6	5.6	5.6	5.6
75°	7.7	6.6	6.6	6.6	5.6	5.6	5.6	5.6
77.5°	7.7	6.6	6.6	6.6	5.6	5.6	5.6	5.6
80°	6.6	6.6	6.6	5.6	5.6	5.6	5.6	5.6
82.5°	6.6	6.6	6.6	6.6	5.6	5.6	5.6	5.6
85°	6.6	5.6	5.6	5.6	4.5	4.5	4.5	4.5
87.5°	5.6	4.5	4.5	3.3	3.3	3.3	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)