

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192681

Luminaire Tested: **LDA6A70927D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4989.6 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	77867	77867	77867
5°	152239	74020	26998
10°	256247	63554	5990
15°	390235	48127	9835
20°	563905	38982	109665
25°	839232	63070	31695
30°	969333	21592	6260
35°	969642	4818	3386
40°	792528	2698	2075
45°	600140	1752	1341
50°	398554	1185	921
55°	64074	1032	717
60°	4002	1053	581
65°	1245	1401	687
70°	689	1539	850
75°	466	1822	1123
80°	316	2715	1673
85°	629	5409	2013



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	3.0
10°-20°	633.9	12.7
20°-30°	1492.4	29.9
30°-40°	1572.4	31.5
40°-50°	980.5	19.6
50°-60°	140.9	2.8
60°-70°	9.0	0.2
70°-80°	7.0	0.1
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2274.6	45.6
0°-40°	3847.0	77.1
0°-60°	4968.3	99.6
0°-90°	4989.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4989.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1420	1420	1420	1420	1420	
5°	2766	2239	1345	698	491	321
15°	6876	3892	848	147	173	2047
25°	13874	4666	1043	754	524	6243
35°	14489	3418	72	67	51	8740
45°	7741	946	23	25	17	6059
55°	670	17	11	12	8	1205
65°	10	8	11	9	5	14
75°	2	5	9	9	5	2
85°	1	5	9	6	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4
2.5°	2073.5	2059.6	2063.9	2031.6	1988.6	2007.8	1959.5	1960.5	1930.5	1854.0	1820.6
5°	2766.5	2764.3	2761.2	2701.9	2625.6	2634.2	2563.2	2536.3	2458.8	2324.2	2239.2
7.5°	3627.4	3628.4	3612.3	3468.1	3383.1	3377.6	3265.8	3185.1	3040.9	2828.9	2673.9
10°	4603.3	4633.4	4604.4	4382.8	4224.6	4226.7	4025.4	3870.6	3639.2	3330.3	3109.7
12.5°	5749.3	5753.6	5708.4	5416.8	5175.8	5157.4	4887.3	4591.4	4239.5	3836.1	3515.4
15°	6875.9	6906.0	6847.9	6488.5	6152.8	6102.3	5757.9	5367.3	4930.5	4333.2	3892.0
17.5°	8125.2	8077.9	7923.9	7409.7	7006.0	6931.8	6561.7	6050.5	5493.2	4771.2	4192.2
20°	9666.1	9682.2	9356.1	8587.9	7905.6	7616.2	7186.9	6627.3	5932.2	5092.8	4392.4
22.5°	11867.6	11780.5	11081.1	9838.2	8812.8	8426.5	7814.2	7042.7	6260.5	5337.1	4541.9
25°	13874.5	13645.3	13000.8	11290.9	9685.4	9207.7	8573.8	7396.7	6532.7	5517.9	4665.8
27.5°	15026.8	14924.6	14194.0	12469.1	10390.3	9717.7	8825.6	7657.1	6694.0	5607.2	4701.3
30°	15313.1	15331.4	14681.5	12859.7	10557.1	9788.8	8866.6	7649.5	6585.4	5448.0	4496.8
32.5°	15240.0	15141.0	14328.6	12428.3	10112.6	9413.2	8466.3	7307.4	6152.8	4973.5	3987.8
35°	14488.9	14343.7	13344.0	11306.0	9358.3	8678.2	7819.6	6746.8	5549.1	4368.7	3417.5
37.5°	13059.9	12892.1	11738.5	9958.8	8453.3	7877.7	7135.2	6122.7	4939.0	3804.8	2916.0
40°	11074.6	10865.8	9901.7	8667.5	7480.6	7078.2	6450.8	5410.3	4306.3	3271.2	2453.3
42.5°	9218.5	9118.4	8539.5	7480.6	6681.2	6292.7	5660.0	4691.5	3675.7	2725.7	1816.3
45°	7741.0	7674.3	7290.2	6617.6	5806.3	5442.5	4846.5	3901.8	2796.7	1835.7	945.9
47.5°	6775.8	6605.9	6230.3	5524.4	4622.6	4169.7	3601.5	2570.6	1577.4	813.5	290.5
50°	4673.2	4689.3	4265.4	3487.5	2720.2	2337.1	1930.5	1182.6	521.8	177.6	50.6
52.5°	2460.9	2279.0	1980.9	1479.5	1029.7	785.6	573.5	236.7	94.8	35.5	26.9
55°	670.4	588.6	470.2	332.5	179.7	126.0	82.8	44.1	31.2	24.7	17.3
57.5°	65.6	62.4	57.1	46.3	39.8	36.5	33.4	26.9	21.6	15.1	10.8
60°	36.5	35.5	33.4	29.0	25.9	23.7	21.6	18.3	12.9	9.6	8.6
62.5°	20.4	19.4	18.3	16.1	13.9	12.9	12.9	10.8	8.6	7.5	7.5
65°	9.6	9.6	9.6	9.6	9.6	8.6	7.5	7.5	7.5	7.5	7.5
67.5°	7.5	7.5	7.5	6.5	6.5	6.5	6.5	6.5	6.5	5.3	6.5
70°	4.3	4.3	5.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	5.3
72.5°	2.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
75°	2.2	2.2	2.2	2.2	3.2	3.2	3.2	3.2	4.3	4.3	5.3
77.5°	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3	5.3
80°	1.0	1.0	1.0	2.2	2.2	2.2	2.2	3.2	4.3	4.3	5.3
82.5°	1.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	4.3	5.3
85°	1.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3
87.5°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	3.2	4.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4
2.5°	1786.2	1733.5	1680.8	1628.1	1625.9	1594.7	1548.4	1487.1	1436.5	1393.5	1351.5
5°	2154.2	2045.5	1936.9	1828.2	1795.9	1739.9	1639.9	1527.0	1430.1	1345.1	1263.2
7.5°	2523.3	2340.4	2168.2	1998.2	1930.5	1845.5	1689.3	1525.8	1385.9	1261.1	1139.6
10°	2852.6	2586.8	2344.7	2105.8	2007.8	1897.1	1687.2	1479.5	1302.1	1141.7	986.7
12.5°	3156.0	2785.9	2479.2	2177.9	2044.5	1909.9	1653.9	1406.3	1194.4	1002.8	824.2
15°	3422.9	2968.8	2574.0	2210.1	2046.7	1885.2	1583.9	1305.2	1067.4	848.0	654.3
17.5°	3613.3	3060.3	2605.2	2181.1	1990.7	1810.0	1480.7	1182.6	926.5	697.3	510.0
20°	3729.5	3097.9	2588.9	2127.3	1925.0	1737.8	1404.2	1114.7	866.2	668.2	541.2
22.5°	3806.0	3134.5	2595.4	2126.3	1924.0	1747.6	1436.5	1165.3	963.0	856.6	841.5
25°	3887.7	3186.1	2642.7	2174.6	1986.4	1822.8	1521.5	1256.8	1087.8	1042.7	1049.1
27.5°	3883.4	3163.5	2597.5	2132.6	1934.8	1769.0	1416.1	1081.5	923.2	796.2	750.0
30°	3652.1	2902.1	2289.8	1769.0	1535.5	1332.1	867.2	563.8	389.5	341.1	292.6
32.5°	3110.9	2351.2	1712.0	1223.4	960.8	717.7	341.1	180.8	153.9	129.1	117.3
35°	2586.8	1874.5	1280.5	739.3	467.1	289.5	122.7	80.7	76.4	72.0	72.0
37.5°	2138.1	1472.0	827.4	312.0	171.1	104.4	59.2	53.8	51.6	50.6	50.6
40°	1672.2	959.8	358.3	103.2	54.9	47.3	42.0	39.8	38.7	37.7	38.7
42.5°	986.7	386.2	104.4	38.7	36.5	34.4	31.2	30.2	30.2	29.0	30.2
45°	335.8	100.1	34.4	28.0	25.9	25.9	23.7	23.7	23.7	22.6	24.7
47.5°	87.1	31.2	22.6	20.4	19.4	19.4	18.3	18.3	18.3	18.3	19.4
50°	30.2	20.4	16.1	15.1	13.9	15.1	13.9	13.9	13.9	13.9	15.1
52.5°	18.3	13.9	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8
55°	11.8	10.8	9.6	9.6	9.6	9.6	9.6	10.8	10.8	10.8	10.8
57.5°	9.6	8.6	8.6	8.6	8.6	8.6	9.6	8.6	8.6	9.6	10.8
60°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	9.6	9.6	10.8
62.5°	7.5	8.6	8.6	8.6	8.6	8.6	8.6	9.6	9.6	9.6	10.8
65°	7.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	10.8	10.8
67.5°	6.5	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	10.8
70°	6.5	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6
72.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6
75°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	9.6
77.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6
80°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
82.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
85°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6
87.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4
2.5°	1293.4	1275.0	1210.5	1202.0	1191.2	1138.4	1116.9	1080.3	1028.7	1013.6	995.4
5°	1167.5	1107.2	1012.6	986.7	958.7	875.9	825.4	765.0	698.4	661.8	627.4
7.5°	1007.1	923.2	797.4	746.7	715.5	625.2	544.4	463.7	365.8	309.9	274.4
10°	828.6	713.4	582.1	524.0	482.0	350.7	274.4	238.8	205.5	178.6	155.0
12.5°	648.8	518.7	370.1	303.4	270.0	223.7	181.9	137.8	122.7	121.7	117.3
15°	475.7	330.3	249.6	224.9	201.2	144.2	143.1	143.1	147.4	150.7	151.7
17.5°	350.7	290.5	228.1	213.1	223.7	232.4	247.5	270.0	288.3	340.1	329.3
20°	514.4	510.0	556.3	615.4	657.4	746.7	859.8	987.7	1121.2	1269.7	1382.7
22.5°	882.3	989.9	1073.9	1144.9	1182.6	1283.7	1373.0	1417.1	1443.0	1430.1	1411.8
25°	1078.2	1116.9	1091.1	1066.4	1069.6	978.1	911.4	826.4	754.4	688.6	650.0
27.5°	644.5	589.7	512.2	458.4	447.6	386.2	341.1	293.8	279.8	236.7	218.4
30°	232.4	216.3	191.5	172.1	170.0	153.9	144.2	133.4	132.3	122.7	117.3
32.5°	105.4	105.4	96.8	98.9	96.8	93.6	92.6	89.3	89.3	86.1	84.0
35°	68.9	69.9	68.9	68.9	67.7	67.7	67.7	65.6	66.7	64.6	61.4
37.5°	50.6	51.6	49.5	50.6	50.6	50.6	50.6	49.5	48.5	46.3	45.2
40°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	37.7	37.7	36.5	34.4
42.5°	30.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	31.2	30.2	30.2
45°	24.7	25.9	24.7	25.9	25.9	25.9	24.7	24.7	24.7	23.7	22.6
47.5°	19.4	19.4	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3	17.3
50°	15.1	15.1	15.1	15.1	15.1	15.1	16.1	15.1	15.1	15.1	15.1
52.5°	11.8	12.9	12.9	13.9	13.9	13.9	13.9	13.9	12.9	12.9	11.8
55°	10.8	11.8	11.8	12.9	12.9	12.9	12.9	11.8	11.8	11.8	10.8
57.5°	10.8	11.8	11.8	11.8	11.8	11.8	11.8	10.8	10.8	9.6	9.6
60°	10.8	10.8	10.8	11.8	11.8	10.8	10.8	9.6	9.6	8.6	8.6
62.5°	10.8	10.8	10.8	11.8	11.8	10.8	10.8	9.6	8.6	8.6	7.5
65°	10.8	11.8	10.8	11.8	11.8	10.8	10.8	9.6	8.6	8.6	7.5
67.5°	10.8	11.8	11.8	11.8	10.8	10.8	10.8	9.6	8.6	8.6	7.5
70°	9.6	10.8	10.8	10.8	10.8	10.8	9.6	9.6	8.6	8.6	7.5
72.5°	9.6	10.8	9.6	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5
75°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5
77.5°	9.6	9.6	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5	7.5
80°	9.6	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5	6.5
82.5°	8.6	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5	6.5
85°	8.6	8.6	8.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	5.3
87.5°	7.5	8.6	7.5	7.5	7.5	7.5	6.5	5.3	4.3	4.3	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192681

CATALOG NUMBER: LDA6A70927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4	1420.4
2.5°	966.3	939.4	940.4	944.7	917.9	903.9	900.6	886.6
5°	581.1	549.9	544.4	540.2	502.6	487.5	475.7	490.6
7.5°	249.6	237.8	235.7	232.4	215.3	206.6	202.3	206.6
10°	123.8	116.2	117.3	118.3	113.0	109.7	108.7	107.6
12.5°	122.7	121.7	122.7	122.7	123.8	121.7	122.7	122.7
15°	159.2	159.2	162.5	164.6	170.0	169.0	171.1	173.3
17.5°	397.0	376.6	387.4	387.4	435.8	392.7	429.4	396.0
20°	1560.2	1633.4	1707.7	1770.1	1833.5	1853.0	1890.6	1879.8
22.5°	1383.8	1392.4	1381.6	1369.8	1366.6	1369.8	1311.7	1320.3
25°	594.0	589.7	572.5	554.2	559.5	563.8	543.4	524.0
27.5°	203.3	198.0	192.5	188.4	186.2	182.9	176.4	172.1
30°	115.2	111.9	109.7	108.7	106.6	104.4	101.1	98.9
32.5°	82.8	80.7	79.7	78.5	76.4	74.2	71.0	69.9
35°	61.4	59.2	58.1	57.1	54.9	52.8	51.6	50.6
37.5°	45.2	43.0	43.0	43.0	39.8	37.7	36.5	35.5
40°	34.4	33.4	33.4	33.4	31.2	30.2	29.0	29.0
42.5°	30.2	29.0	29.0	29.0	26.9	25.9	25.9	24.7
45°	22.6	21.6	21.6	20.4	19.4	19.4	18.3	17.3
47.5°	17.3	16.1	16.1	16.1	15.1	13.9	13.9	12.9
50°	13.9	13.9	12.9	13.9	11.8	11.8	11.8	10.8
52.5°	11.8	11.8	10.8	10.8	9.6	9.6	9.6	8.6
55°	10.8	9.6	9.6	9.6	8.6	8.6	8.6	7.5
57.5°	8.6	8.6	7.5	7.5	6.5	6.5	6.5	6.5
60°	7.5	7.5	6.5	6.5	5.3	5.3	5.3	5.3
62.5°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
65°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
67.5°	7.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
70°	7.5	7.5	6.5	6.5	6.5	5.3	5.3	5.3
72.5°	7.5	7.5	6.5	6.5	6.5	6.5	5.3	5.3
75°	6.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
77.5°	6.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
80°	6.5	6.5	5.3	5.3	5.3	5.3	5.3	5.3
82.5°	6.5	5.3	5.3	5.3	5.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2
87.5°	3.2	2.2	2.2	2.2	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)