

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192726

Luminaire Tested: **LDA6A70935D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6607.8 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	44	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	70570	70570	70570
5°	187271	65425	25027
10°	408782	52899	7459
15°	617035	38661	6487
20°	717749	26532	10186
25°	791556	28635	67824
30°	875774	21554	21092
35°	888779	11029	7904
40°	909225	4487	3786
45°	916847	2768	2287
50°	772350	1885	1475
55°	255102	1290	822
60°	50149	1217	537
65°	5889	1583	636
70°	1571	1779	785
75°	275	2351	1313
80°	0	3852	1957
85°	0	7674	3082

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.3	2.6
10°-20°	865.0	13.1
20°-30°	1707.4	25.8
30°-40°	1925.9	29.1
40°-50°	1528.9	23.1
50°-60°	373.8	5.7
60°-70°	20.0	0.3
70°-80°	8.5	0.1
80°-90°	7.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2743.7	41.5
0°-40°	4669.6	70.7
0°-60°	6572.4	99.5
0°-90°	6607.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6607.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1287	1287	1287	1287	1287	
5°	3403	2550	1189	598	455	450
15°	10872	5778	681	134	114	3050
25°	13086	7004	473	857	1121	6061
35°	13281	4458	165	130	118	8352
45°	11826	1389	36	37	30	8864
55°	2669	60	14	14	9	3131
65°	45	11	12	10	5	111
75°	1	6	11	10	6	3
85°	0	6	12	9	5	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3
2.5°	2233.9	2190.9	2210.6	2179.8	2092.5	2065.5	2087.6	2054.4	1954.8	1916.7	1877.4
5°	3403.1	3365.0	3377.3	3307.2	3143.7	3087.2	3083.4	2982.6	2781.0	2667.9	2549.9
7.5°	5160.0	5107.2	5092.4	4924.0	4609.2	4491.2	4433.4	4185.0	3805.1	3535.9	3271.7
10°	7343.5	7395.2	7342.4	7069.3	6575.1	6353.8	6213.7	5744.1	5059.2	4546.5	4052.3
12.5°	9533.3	9565.2	9465.5	9126.3	8497.9	8232.5	8025.8	7424.6	6522.3	5651.8	4914.1
15°	10872.1	11023.3	10929.8	10692.5	10205.6	9883.5	9697.9	8955.3	7819.4	6862.8	5778.5
17.5°	11826.1	11966.3	11888.8	11694.5	11145.1	10885.7	10765.2	10154.0	8917.2	7701.3	6425.1
20°	12303.2	12474.0	12404.0	12183.9	11780.6	11564.2	11418.0	10821.7	9706.5	8324.7	6856.6
22.5°	12626.5	12815.8	12739.6	12539.2	12128.6	11876.6	11807.7	11243.4	10119.7	8698.4	7039.8
25°	13086.3	13244.9	13029.8	12782.6	12377.0	12111.4	12069.5	11492.9	10317.5	8839.7	7004.2
27.5°	13415.8	13604.0	13238.7	12988.0	12524.5	12245.4	12191.3	11649.1	10336.1	8727.9	6715.3
30°	13835.1	13713.4	13392.5	13028.5	12534.3	12236.8	12167.9	11558.1	10151.6	8316.0	6149.7
32.5°	13669.1	13639.6	13318.7	12890.9	12429.7	12129.8	12037.6	11277.8	9645.1	7605.4	5349.4
35°	13280.6	13374.1	13106.0	12840.4	12267.5	11955.2	11827.4	10864.7	8881.6	6690.7	4458.0
37.5°	13053.1	13112.2	12942.5	12617.8	12049.8	11639.3	11397.0	10170.0	7882.0	5537.4	3598.6
40°	12705.3	12855.2	12691.6	12319.2	11663.9	11100.8	10679.0	8914.8	6565.3	4365.8	2814.2
42.5°	12324.1	12458.1	12301.9	11855.6	10929.8	10175.0	9474.2	7439.4	5140.3	3335.5	2110.9
45°	11826.1	11946.6	11666.3	10971.7	9661.1	8619.7	7920.2	5842.4	3876.5	2450.3	1389.2
47.5°	10928.7	10896.7	10499.6	9420.1	7805.8	6872.6	6058.7	4185.0	2577.0	1388.1	690.9
50°	9056.1	8757.5	8173.4	6920.6	5238.6	4230.5	3674.9	2160.1	1169.2	672.5	434.0
52.5°	5865.7	5532.6	4997.8	3840.8	2515.4	2018.8	1619.1	976.2	609.8	379.9	170.8
55°	2669.1	2433.0	2091.4	1551.6	1079.5	897.4	759.8	494.2	327.0	141.4	60.3
57.5°	1016.8	938.1	833.6	665.2	499.1	431.5	357.8	237.3	102.1	52.9	35.7
60°	457.4	424.2	389.7	304.8	214.0	153.7	116.8	64.0	43.0	30.8	23.3
62.5°	156.2	130.3	108.1	77.5	57.8	50.5	44.3	35.7	25.9	20.9	16.0
65°	45.4	44.3	41.8	36.8	29.5	27.0	25.9	20.9	16.0	13.5	11.1
67.5°	22.1	20.9	19.7	18.4	14.8	13.5	13.5	12.2	9.8	8.6	7.3
70°	9.8	9.8	8.6	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
72.5°	4.9	4.9	4.9	3.7	3.7	3.7	3.7	4.9	4.9	6.2	6.2
75°	1.3	2.4	2.4	2.4	2.4	3.7	3.7	4.9	4.9	6.2	6.2
77.5°	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2	6.2
80°	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2	6.2
82.5°	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2	6.2
85°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3
2.5°	1781.5	1755.6	1653.7	1575.0	1538.0	1535.6	1453.2	1402.9	1314.3	1245.4	1180.3
5°	2342.2	2227.8	2021.2	1857.7	1779.0	1738.5	1576.2	1459.4	1307.0	1188.9	1072.1
7.5°	2912.6	2695.0	2404.8	2093.8	1965.8	1887.2	1636.4	1449.5	1246.7	1081.9	936.8
10°	3496.5	3113.0	2680.2	2269.5	2085.2	1952.3	1630.2	1377.0	1143.3	950.3	791.7
12.5°	4105.1	3500.3	2897.8	2383.9	2140.6	1965.8	1575.0	1271.3	1016.8	811.4	660.2
15°	4617.9	3800.2	3035.5	2411.0	2123.3	1911.8	1456.9	1137.3	881.5	681.2	543.4
17.5°	5013.7	3968.6	3061.3	2344.6	2027.4	1791.3	1304.5	989.7	739.0	561.8	425.3
20°	5212.9	3994.5	2980.2	2187.1	1854.0	1610.5	1131.1	839.8	619.6	454.8	338.1
22.5°	5227.7	3874.0	2803.2	1984.4	1663.4	1416.4	988.5	724.2	543.4	408.2	321.0
25°	5035.9	3641.6	2565.9	1776.6	1468.0	1245.4	886.5	694.7	547.1	473.4	435.3
27.5°	4671.9	3319.5	2305.2	1568.8	1299.5	1127.4	844.7	694.7	592.6	534.8	548.3
30°	4167.8	2908.9	1942.5	1286.0	1057.3	907.4	663.9	520.1	408.2	340.5	328.3
32.5°	3513.8	2380.3	1506.1	950.3	770.9	654.1	448.8	325.8	263.1	257.0	249.6
35°	2891.7	1879.8	1143.3	702.0	568.0	462.3	286.4	191.8	174.6	164.8	157.3
37.5°	2284.3	1406.5	821.2	510.2	389.7	293.8	147.5	124.2	108.1	98.4	89.7
40°	1717.5	1010.6	579.1	308.6	204.0	126.7	88.6	76.2	67.6	62.7	60.3
42.5°	1214.6	672.5	359.1	130.3	97.1	80.0	61.4	54.1	49.2	46.7	44.3
45°	705.8	418.0	145.1	76.2	61.4	55.4	45.4	40.6	38.1	35.7	34.4
47.5°	441.3	168.4	75.1	49.2	43.0	39.4	33.2	31.9	29.5	28.3	28.3
50°	178.3	75.1	46.7	34.4	30.8	29.5	25.9	24.6	22.1	22.1	22.1
52.5°	67.6	44.3	31.9	24.6	22.1	20.9	18.4	18.4	17.3	17.3	17.3
55°	39.4	29.5	22.1	17.3	16.0	16.0	14.8	14.8	13.5	13.5	13.5
57.5°	25.9	19.7	16.0	12.2	12.2	12.2	11.1	11.1	11.1	11.1	11.1
60°	17.3	13.5	11.1	9.8	9.8	9.8	9.8	11.1	11.1	11.1	11.1
62.5°	12.2	11.1	9.8	9.8	9.8	9.8	9.8	11.1	11.1	11.1	12.2
65°	9.8	8.6	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2	12.2
67.5°	7.3	7.3	7.3	7.3	8.6	8.6	9.8	11.1	11.1	11.1	12.2
70°	6.2	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2
72.5°	6.2	7.3	7.3	8.6	8.6	8.6	9.8	11.1	11.1	11.1	12.2
75°	6.2	7.3	7.3	8.6	8.6	8.6	9.8	11.1	11.1	11.1	12.2
77.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2	12.2
80°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2	12.2
82.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2	12.2
85°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	12.2	12.2
87.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3
2.5°	1148.4	1091.7	1030.3	1010.6	990.9	952.8	929.5	887.7	856.9	826.3	801.7
5°	994.6	904.9	829.8	797.9	767.2	714.4	677.4	633.1	597.5	566.8	538.5
7.5°	834.7	731.5	656.6	624.5	593.9	536.1	489.3	434.0	392.1	357.8	329.4
10°	687.2	588.8	507.7	469.6	434.0	373.7	329.4	285.3	249.6	220.0	194.3
12.5°	559.4	453.7	371.3	343.0	308.6	259.4	217.6	169.7	148.8	140.2	134.0
15°	434.0	339.4	270.5	244.6	214.0	167.2	148.8	140.2	134.0	130.3	125.4
17.5°	330.7	252.1	184.3	167.2	157.3	147.5	142.6	136.5	132.7	131.6	127.8
20°	259.4	190.5	173.4	168.4	168.4	165.9	162.3	162.3	161.1	164.8	164.8
22.5°	266.7	266.7	281.6	280.3	300.0	319.7	334.5	382.4	409.4	467.2	506.6
25°	465.9	510.2	561.8	577.8	616.0	672.5	731.5	805.3	856.9	912.2	934.4
27.5°	581.5	588.8	581.5	599.9	575.3	560.7	565.6	574.2	574.2	577.8	592.6
30°	344.2	361.5	377.5	389.7	383.6	377.5	375.0	356.5	356.5	349.1	343.0
32.5°	233.5	231.1	228.6	233.5	228.6	228.6	225.0	226.2	218.9	214.0	211.5
35°	159.8	152.4	143.8	145.1	140.2	138.9	135.2	135.2	130.3	127.8	126.7
37.5°	88.6	88.6	84.8	86.0	84.8	84.8	84.8	86.0	84.8	84.8	86.0
40°	60.3	60.3	59.0	60.3	59.0	60.3	61.4	61.4	61.4	61.4	60.3
42.5°	45.4	45.4	44.3	45.4	44.3	45.4	46.7	46.7	46.7	46.7	46.7
45°	35.7	35.7	35.7	35.7	35.7	35.7	35.7	36.8	36.8	35.7	35.7
47.5°	28.3	29.5	28.3	28.3	28.3	28.3	29.5	29.5	28.3	28.3	28.3
50°	23.3	23.3	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1	22.1
52.5°	18.4	17.3	17.3	16.0	16.0	16.0	16.0	16.0	16.0	16.0	14.8
55°	13.5	13.5	12.2	12.2	12.2	13.5	13.5	13.5	13.5	12.2	12.2
57.5°	12.2	12.2	12.2	11.1	11.1	12.2	12.2	11.1	11.1	11.1	9.8
60°	11.1	12.2	11.1	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6
62.5°	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6	8.6
65°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6
67.5°	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	9.8	9.8	8.6
70°	12.2	12.2	12.2	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6
72.5°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6
75°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6
77.5°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6
80°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6
82.5°	12.2	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6
85°	12.2	12.2	11.1	11.1	11.1	11.1	9.8	9.8	8.6	8.6	7.3
87.5°	11.1	11.1	11.1	11.1	9.8	9.8	9.8	8.6	7.3	7.3	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192726

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3	1287.3
2.5°	772.0	767.2	763.6	770.9	768.4	737.7	741.4	740.1
5°	506.6	495.5	486.9	490.5	480.7	467.2	457.4	454.8
7.5°	301.3	288.9	281.6	274.2	271.8	254.5	247.2	252.1
10°	165.9	148.8	147.5	143.8	138.9	135.2	132.7	134.0
12.5°	127.8	126.7	124.2	122.9	120.5	119.2	118.1	116.8
15°	121.7	120.5	119.2	118.1	116.8	115.6	114.3	114.3
17.5°	125.4	125.4	124.2	122.9	122.9	124.2	122.9	121.7
20°	163.5	163.5	165.9	169.7	169.7	173.4	178.3	174.6
22.5°	531.2	558.2	591.4	601.2	659.0	705.8	791.7	753.6
25°	971.2	1032.7	1047.6	1068.4	1100.3	1116.3	1100.3	1121.3
27.5°	590.1	611.0	613.4	614.7	622.1	620.9	605.0	614.7
30°	343.0	350.4	348.0	346.7	344.2	330.7	328.3	333.2
32.5°	215.1	212.7	211.5	210.2	210.2	202.9	206.5	204.0
35°	122.9	126.7	125.4	124.2	120.5	119.2	119.2	118.1
37.5°	82.4	83.5	82.4	81.1	78.7	77.5	76.2	75.1
40°	59.0	60.3	59.0	57.8	56.5	55.4	54.1	52.9
42.5°	44.3	45.4	44.3	44.3	41.8	40.6	39.4	38.1
45°	34.4	33.2	33.2	33.2	31.9	30.8	29.5	29.5
47.5°	28.3	28.3	28.3	27.0	25.9	25.9	25.9	24.6
50°	20.9	22.1	20.9	20.9	19.7	18.4	18.4	17.3
52.5°	14.8	14.8	13.5	13.5	12.2	11.1	11.1	11.1
55°	11.1	11.1	11.1	9.8	9.8	8.6	8.6	8.6
57.5°	9.8	8.6	8.6	8.6	7.3	7.3	6.2	6.2
60°	8.6	7.3	7.3	6.2	6.2	4.9	4.9	4.9
62.5°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
65°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
67.5°	7.3	7.3	6.2	6.2	6.2	4.9	4.9	4.9
70°	7.3	7.3	7.3	6.2	6.2	6.2	4.9	4.9
72.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
75°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
77.5°	8.6	7.3	7.3	7.3	6.2	6.2	6.2	6.2
80°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2
82.5°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
85°	7.3	6.2	6.2	6.2	4.9	4.9	4.9	4.9
87.5°	6.2	4.9	4.9	3.7	3.7	3.7	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)