

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192766

Luminaire Tested: **LDA6A75927D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5392.3 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	84154	84154	84154
5°	164527	79991	29177
10°	276932	68686	6468
15°	421733	52009	10630
20°	609420	42132	118520
25°	906966	68157	34254
30°	1047573	23333	6767
35°	1047908	5213	3661
40°	856498	2913	2247
45°	648579	1892	1442
50°	430724	1288	998
55°	69245	1118	774
60°	4331	1140	625
65°	1349	1518	739
70°	753	1667	914
75°	487	1970	1207
80°	347	2936	1799
85°	692	5850	2139

TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.2	3.0
10°-20°	685.1	12.7
20°-30°	1612.8	29.9
30°-40°	1699.3	31.5
40°-50°	1059.6	19.6
50°-60°	152.2	2.8
60°-70°	9.7	0.2
70°-80°	7.6	0.1
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2458.2	45.6
0°-40°	4157.5	77.1
0°-60°	5369.4	99.6
0°-90°	5392.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5392.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1535	1535	1535	1535	1535	
5°	2990	2420	1454	755	530	347
15°	7431	4206	916	159	187	2213
25°	14994	5042	1127	815	566	6747
35°	15658	3693	78	72	55	9445
45°	8366	1022	24	27	19	6548
55°	724	19	12	13	8	1302
65°	10	8	12	9	6	15
75°	2	6	9	9	6	3
85°	1	6	9	7	3	1
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1
2.5°	2240.9	2225.8	2230.5	2195.5	2149.1	2169.9	2117.7	2118.8	2086.3	2003.6	1967.6
5°	2989.8	2987.5	2984.0	2920.0	2837.5	2846.8	2770.1	2741.0	2657.2	2511.8	2419.9
7.5°	3920.2	3921.3	3903.9	3748.0	3656.2	3650.3	3529.3	3442.2	3286.3	3057.2	2889.7
10°	4974.9	5007.4	4976.0	4736.5	4565.6	4567.9	4350.3	4183.0	3932.9	3599.1	3360.7
12.5°	6213.3	6218.0	6169.2	5854.0	5593.6	5573.7	5281.8	4962.0	4581.7	4145.7	3799.1
15°	7430.9	7463.4	7400.6	7012.2	6649.4	6594.8	6222.6	5800.6	5328.4	4682.9	4206.1
17.5°	8781.0	8729.9	8563.5	8007.7	7571.5	7491.3	7091.3	6538.9	5936.5	5156.3	4530.6
20°	10446.3	10463.7	10111.3	9281.1	8543.7	8230.9	7767.0	7162.2	6411.0	5503.9	4746.9
22.5°	12825.5	12731.4	11975.5	10632.3	9524.2	9106.6	8444.9	7611.2	6765.8	5767.9	4908.5
25°	14994.3	14746.6	14050.1	12202.2	10467.1	9950.9	9265.9	7993.8	7059.9	5963.3	5042.3
27.5°	16239.7	16129.2	15339.6	13475.6	11228.9	10502.1	9538.0	8275.2	7234.3	6059.8	5080.7
30°	16549.1	16568.9	15866.5	13897.7	11409.2	10578.9	9582.3	8267.0	7117.0	5887.7	4859.8
32.5°	16470.0	16363.1	15485.1	13431.4	10928.8	10173.0	9149.6	7897.3	6649.4	5374.9	4309.6
35°	15658.4	15501.4	14421.1	12218.5	10113.6	9378.7	8450.8	7291.3	5997.0	4721.3	3693.3
37.5°	14114.0	13932.6	12686.0	10762.6	9135.7	8513.6	7711.1	6616.9	5337.6	4112.0	3151.4
40°	11968.5	11742.8	10700.9	9367.0	8084.4	7649.5	6971.5	5847.0	4653.8	3535.3	2651.3
42.5°	9962.6	9854.4	9228.7	8084.4	7220.5	6800.6	6116.8	5070.2	3972.4	2945.7	1962.9
45°	8365.8	8293.7	7878.6	7151.8	6275.0	5881.8	5237.7	4216.7	3022.4	1983.9	1022.2
47.5°	7322.7	7139.0	6733.1	5970.3	4995.7	4506.2	3892.2	2778.1	1704.8	879.1	313.9
50°	5050.4	5067.8	4609.7	3769.0	2939.8	2525.8	2086.3	1278.0	564.0	191.9	54.7
52.5°	2659.6	2463.0	2140.8	1598.9	1112.8	849.0	619.7	255.8	102.4	38.4	29.1
55°	724.5	636.1	508.2	359.3	194.3	136.1	89.5	47.7	33.7	26.7	18.6
57.5°	70.9	67.4	61.7	50.0	43.0	39.5	36.1	29.1	23.3	16.3	11.7
60°	39.5	38.4	36.1	31.4	28.0	25.6	23.3	19.7	14.0	10.4	9.3
62.5°	22.1	21.0	19.7	17.4	15.1	14.0	14.0	11.7	9.3	8.1	8.1
65°	10.4	10.4	10.4	10.4	10.4	9.3	8.1	8.1	8.1	8.1	8.1
67.5°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0	7.0	5.7	7.0
70°	4.7	4.7	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	5.7
72.5°	2.3	3.4	3.4	3.4	3.4	3.4	3.4	3.4	4.7	4.7	5.7
75°	2.3	2.3	2.3	2.3	3.4	3.4	3.4	3.4	4.7	4.7	5.7
77.5°	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7
80°	1.1	1.1	1.1	2.3	2.3	2.3	2.3	3.4	4.7	4.7	5.7
82.5°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
85°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1
2.5°	1930.4	1873.4	1816.5	1759.5	1757.1	1723.4	1673.4	1607.2	1552.5	1506.0	1460.6
5°	2328.1	2210.6	2093.3	1975.8	1940.8	1880.4	1772.2	1650.2	1545.5	1453.6	1365.2
7.5°	2727.0	2529.3	2343.2	2159.5	2086.3	1994.4	1825.7	1649.0	1497.8	1362.9	1231.6
10°	3082.9	2795.5	2534.0	2275.7	2169.9	2050.2	1823.3	1598.9	1407.2	1233.9	1066.4
12.5°	3410.8	3010.8	2679.3	2353.7	2209.5	2064.1	1787.4	1519.8	1290.8	1083.8	890.8
15°	3699.2	3208.4	2781.7	2388.5	2211.8	2037.3	1711.8	1410.6	1153.6	916.4	707.1
17.5°	3905.0	3307.3	2815.4	2357.1	2151.4	1956.1	1600.2	1278.0	1001.3	753.5	551.2
20°	4030.5	3348.0	2797.9	2299.0	2080.4	1878.0	1517.5	1204.7	936.1	722.2	584.9
22.5°	4113.2	3387.5	2804.9	2297.9	2079.3	1888.6	1552.5	1259.4	1040.7	925.7	909.4
25°	4201.5	3443.3	2856.0	2350.2	2146.7	1969.9	1644.3	1358.2	1175.6	1126.8	1133.8
27.5°	4196.8	3418.9	2807.2	2304.8	2090.9	1911.8	1530.4	1168.8	997.7	860.5	810.6
30°	3946.9	3136.3	2474.6	1911.8	1659.4	1439.6	937.2	609.3	421.0	368.6	316.2
32.5°	3362.0	2541.0	1850.2	1322.2	1038.4	775.6	368.6	195.3	166.3	139.6	126.8
35°	2795.5	2025.8	1383.9	798.9	504.7	312.8	132.6	87.2	82.5	77.9	77.9
37.5°	2310.7	1590.9	894.2	337.2	184.9	112.8	64.0	58.1	55.8	54.7	54.7
40°	1807.2	1037.3	387.3	111.6	59.4	51.1	45.4	43.0	41.8	40.7	41.8
42.5°	1066.4	417.4	112.8	41.8	39.5	37.1	33.7	32.6	32.6	31.4	32.6
45°	362.9	108.2	37.1	30.3	28.0	28.0	25.6	25.6	25.6	24.4	26.7
47.5°	94.2	33.7	24.4	22.1	21.0	21.0	19.7	19.7	19.7	19.7	21.0
50°	32.6	22.1	17.4	16.3	15.1	16.3	15.1	15.1	15.1	15.1	16.3
52.5°	19.7	15.1	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7
55°	12.7	11.7	10.4	10.4	10.4	10.4	10.4	11.7	11.7	11.7	11.7
57.5°	10.4	9.3	9.3	9.3	9.3	9.3	10.4	9.3	9.3	10.4	11.7
60°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.4	10.4	11.7
62.5°	8.1	9.3	9.3	9.3	9.3	9.3	9.3	10.4	10.4	10.4	11.7
65°	8.1	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4	11.7	11.7
67.5°	7.0	7.0	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4	11.7
70°	7.0	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	10.4	10.4
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	10.4
75°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	10.4
77.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	10.4
80°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
82.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
85°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3
87.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1
2.5°	1397.8	1378.0	1308.2	1299.0	1287.4	1230.3	1207.0	1167.5	1111.8	1095.4	1075.7
5°	1261.7	1196.6	1094.3	1066.4	1036.1	946.6	892.0	826.7	754.8	715.2	678.0
7.5°	1088.4	997.7	861.7	807.0	773.3	675.7	588.4	501.2	395.3	334.9	296.5
10°	895.4	771.0	629.1	566.3	520.9	379.0	296.5	258.1	222.1	193.0	167.5
12.5°	701.2	560.5	400.0	327.9	291.8	241.8	196.6	148.9	132.6	131.5	126.8
15°	514.1	357.0	269.8	243.0	217.4	155.9	154.6	154.6	159.3	162.9	163.9
17.5°	379.0	313.9	246.5	230.3	241.8	251.1	267.4	291.8	311.6	367.5	355.9
20°	555.9	551.2	601.3	665.1	710.5	807.0	929.2	1067.5	1211.7	1372.2	1494.4
22.5°	953.6	1069.8	1160.5	1237.3	1278.0	1387.3	1483.8	1531.5	1559.5	1545.5	1525.7
25°	1165.2	1207.0	1179.2	1152.5	1155.9	1057.0	984.9	893.1	815.2	744.2	702.4
27.5°	696.5	637.3	553.5	495.4	483.8	417.4	368.6	317.5	302.4	255.8	236.1
30°	251.1	233.7	207.0	186.0	183.7	166.3	155.9	144.2	143.0	132.6	126.8
32.5°	113.9	113.9	104.6	106.9	104.6	101.2	100.1	96.5	96.5	93.1	90.8
35°	74.4	75.5	74.4	74.4	73.2	73.2	73.2	70.9	72.1	69.8	66.4
37.5°	54.7	55.8	53.5	54.7	54.7	54.7	54.7	53.5	52.4	50.0	48.8
40°	41.8	41.8	41.8	41.8	41.8	41.8	41.8	40.7	40.7	39.5	37.1
42.5°	32.6	33.7	33.7	33.7	33.7	33.7	33.7	33.7	33.7	32.6	32.6
45°	26.7	28.0	26.7	28.0	28.0	28.0	26.7	26.7	26.7	25.6	24.4
47.5°	21.0	21.0	19.7	19.7	19.7	19.7	19.7	19.7	19.7	19.7	18.6
50°	16.3	16.3	16.3	16.3	16.3	16.3	17.4	16.3	16.3	16.3	16.3
52.5°	12.7	14.0	14.0	15.1	15.1	15.1	15.1	15.1	14.0	14.0	12.7
55°	11.7	12.7	12.7	14.0	14.0	14.0	14.0	12.7	12.7	12.7	11.7
57.5°	11.7	12.7	12.7	12.7	12.7	12.7	12.7	11.7	11.7	10.4	10.4
60°	11.7	11.7	11.7	12.7	12.7	11.7	11.7	10.4	10.4	9.3	9.3
62.5°	11.7	11.7	11.7	12.7	12.7	11.7	11.7	10.4	9.3	9.3	8.1
65°	11.7	12.7	11.7	12.7	12.7	11.7	11.7	10.4	9.3	9.3	8.1
67.5°	11.7	12.7	12.7	12.7	11.7	11.7	11.7	10.4	9.3	9.3	8.1
70°	10.4	11.7	11.7	11.7	11.7	11.7	10.4	10.4	9.3	9.3	8.1
72.5°	10.4	11.7	10.4	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1
75°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1
77.5°	10.4	10.4	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1	8.1
80°	10.4	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	7.0
82.5°	9.3	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	7.0
85°	9.3	9.3	9.3	9.3	9.3	9.3	8.1	8.1	7.0	5.7	5.7
87.5°	8.1	9.3	8.1	8.1	8.1	8.1	7.0	5.7	4.7	4.7	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192766

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1	1535.1
2.5°	1044.3	1015.2	1016.3	1021.0	991.9	976.9	973.3	958.2
5°	628.0	594.3	588.4	583.8	543.1	526.8	514.1	530.2
7.5°	269.8	257.0	254.7	251.1	232.6	223.3	218.7	223.3
10°	133.8	125.6	126.8	127.9	122.1	118.6	117.5	116.2
12.5°	132.6	131.5	132.6	132.6	133.8	131.5	132.6	132.6
15°	172.0	172.0	175.6	177.9	183.7	182.6	184.9	187.3
17.5°	429.1	407.0	418.7	418.7	471.0	424.4	464.0	428.0
20°	1686.1	1765.2	1845.6	1913.0	1981.5	2002.5	2043.2	2031.6
22.5°	1495.4	1504.8	1493.1	1480.4	1476.9	1480.4	1417.6	1426.9
25°	642.0	637.3	618.7	598.9	604.7	609.3	587.3	566.3
27.5°	219.7	214.0	208.1	203.6	201.2	197.7	190.7	186.0
30°	124.5	120.9	118.6	117.5	115.2	112.8	109.2	106.9
32.5°	89.5	87.2	86.1	84.8	82.5	80.2	76.8	75.5
35°	66.4	64.0	62.8	61.7	59.4	57.0	55.8	54.7
37.5°	48.8	46.5	46.5	46.5	43.0	40.7	39.5	38.4
40°	37.1	36.1	36.1	36.1	33.7	32.6	31.4	31.4
42.5°	32.6	31.4	31.4	31.4	29.1	28.0	28.0	26.7
45°	24.4	23.3	23.3	22.1	21.0	21.0	19.7	18.6
47.5°	18.6	17.4	17.4	17.4	16.3	15.1	15.1	14.0
50°	15.1	15.1	14.0	15.1	12.7	12.7	12.7	11.7
52.5°	12.7	12.7	11.7	11.7	10.4	10.4	10.4	9.3
55°	11.7	10.4	10.4	10.4	9.3	9.3	9.3	8.1
57.5°	9.3	9.3	8.1	8.1	7.0	7.0	7.0	7.0
60°	8.1	8.1	7.0	7.0	5.7	5.7	5.7	5.7
62.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
65°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
67.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
70°	8.1	8.1	7.0	7.0	7.0	5.7	5.7	5.7
72.5°	8.1	8.1	7.0	7.0	7.0	7.0	5.7	5.7
75°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
77.5°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
80°	7.0	7.0	5.7	5.7	5.7	5.7	5.7	5.7
82.5°	7.0	5.7	5.7	5.7	5.7	4.7	4.7	4.7
85°	4.7	4.7	4.7	4.7	3.4	3.4	3.4	3.4
87.5°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)