

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192809

Luminaire Tested: **LDA6A75935D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7684.6 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	66	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78957	78957	78957
5°	216712	72749	29683
10°	474891	59535	11317
15°	725384	45318	13275
20°	840441	33714	20617
25°	916801	27727	33274
30°	1023778	25143	33980
35°	1041644	17253	23296
40°	1059943	8172	11786
45°	1061668	3396	5148
50°	897540	1467	1586
55°	289022	1013	248
60°	57408	1162	0
65°	5863	1375	0
70°	641	1923	0
75°	0	2542	0
80°	0	4167	442
85°	0	8303	881

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	2.5
10°-20°	1011.1	13.2
20°-30°	1936.0	25.2
30°-40°	2280.9	29.7
40°-50°	1791.6	23.3
50°-60°	436.6	5.7
60°-70°	18.7	0.2
70°-80°	7.1	0.1
80°-90°	7.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3142.6	40.9
0°-40°	5423.6	70.6
0°-60°	7651.8	99.6
0°-90°	7684.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7684.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1440	1440	1440	1440	1440	
5°	3938	2850	1322	692	539	521
15°	12781	6565	798	229	234	3568
25°	15157	7982	458	480	550	7064
35°	15565	5046	258	332	348	9760
45°	13694	1560	44	61	66	10289
55°	3024	57	11	7	3	3599
65°	45	7	11	7	0	120
75°	0	7	12	8	0	1
85°	0	8	13	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3
2.5°	2468.6	2463.3	2427.4	2460.6	2359.6	2355.6	2310.5	2290.5	2232.0	2176.3	2096.5
5°	3938.1	3851.7	3781.3	3783.9	3590.0	3554.1	3453.0	3350.8	3194.0	3047.9	2849.9
7.5°	6002.7	5900.3	5751.6	5689.1	5318.5	5209.6	5000.9	4728.6	4387.2	4047.0	3680.2
10°	8531.1	8547.0	8354.3	8176.4	7615.7	7395.1	7057.6	6520.8	5873.8	5234.7	4585.0
12.5°	11075.4	11064.7	10834.8	10565.2	9874.3	9563.3	9114.4	8444.7	7587.7	6596.5	5580.2
15°	12781.2	12857.1	12760.1	12544.9	11955.0	11598.8	11092.6	10183.8	9139.5	7935.8	6564.7
17.5°	13852.1	13923.9	13889.4	13720.7	13199.9	12819.8	12397.4	11653.3	10445.5	8932.2	7340.6
20°	14406.3	14519.1	14503.3	14319.9	13926.6	13611.7	13145.4	12455.8	11410.1	9624.6	7842.9
22.5°	14775.5	14861.9	14885.9	14678.6	14272.0	13973.0	13631.6	12932.8	11949.5	10047.1	8042.1
25°	15156.9	15309.6	15159.5	14904.5	14531.1	14244.0	13880.1	13210.5	12207.3	10219.7	7982.4
27.5°	15624.5	15697.7	15357.5	15125.0	14710.4	14399.6	14013.0	13371.2	12252.6	10081.6	7640.8
30°	16173.2	15870.3	15632.6	15171.5	14701.2	14398.2	14005.0	13270.3	12014.6	9623.2	6979.3
32.5°	16082.9	15805.2	15535.6	15047.9	14583.0	14282.6	13844.2	12934.2	11452.7	8856.6	6066.5
35°	15564.8	15624.5	15333.6	14929.7	14403.5	14093.9	13615.8	12455.8	10498.7	7799.0	5046.1
37.5°	15127.7	15259.1	15069.2	14695.8	14161.7	13743.2	13097.5	11687.8	9253.8	6457.1	4078.9
40°	14811.4	14854.0	14751.6	14333.1	13691.4	13086.9	12340.2	10308.8	7741.8	5068.6	3219.3
42.5°	14321.1	14434.1	14253.4	13796.3	12823.8	12139.6	11058.1	8715.8	6013.3	3871.5	2423.3
45°	13694.1	13801.6	13578.5	12818.5	11465.9	10462.9	9143.6	6795.9	4448.2	2853.8	1559.8
47.5°	12671.1	12737.4	12305.7	11254.7	9288.4	8343.7	6991.3	4737.9	2865.8	1595.7	758.7
50°	10524.0	10492.2	9601.9	8309.2	6212.7	5221.5	4161.2	2568.2	1287.4	756.0	474.3
52.5°	6782.5	6709.5	5828.7	4652.8	3146.1	2400.8	1804.2	1108.0	671.0	422.5	187.3
55°	3024.0	2996.0	2452.6	1905.2	1287.4	1108.0	846.3	543.4	357.4	147.5	57.2
57.5°	1121.4	1096.1	966.0	810.4	621.8	516.9	410.6	260.5	91.7	49.1	30.6
60°	523.6	522.2	459.7	378.7	263.1	199.2	115.6	61.1	38.5	26.6	17.2
62.5°	167.4	163.5	114.2	83.8	59.8	51.7	41.2	30.6	19.9	14.6	10.6
65°	45.2	45.2	41.2	34.5	28.0	23.9	19.9	14.6	9.3	7.9	6.7
67.5°	17.2	17.2	16.0	14.6	10.6	9.3	7.9	6.7	5.3	6.7	6.7
70°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.3	5.3	6.7
72.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
75°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
77.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
80°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.3	6.7	6.7
82.5°	0.0	0.0	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7	7.9
85°	0.0	0.0	1.4	2.6	2.6	4.0	4.0	5.3	5.3	6.7	7.9
87.5°	0.0	0.0	1.4	2.6	2.6	4.0	4.0	5.3	5.3	6.7	7.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3
2.5°	2038.1	1950.5	1829.6	1759.2	1741.8	1704.6	1639.5	1542.5	1462.8	1385.7	1340.5
5°	2682.4	2475.3	2242.8	2079.3	2012.9	1923.9	1765.7	1602.4	1452.2	1322.0	1219.6
7.5°	3365.4	3024.0	2647.9	2345.0	2236.1	2095.3	1837.5	1594.3	1388.4	1207.8	1070.9
10°	4044.4	3494.2	2984.0	2545.7	2367.6	2176.3	1836.1	1521.2	1279.4	1069.5	918.1
12.5°	4723.3	3932.8	3231.1	2666.6	2435.3	2193.5	1781.7	1409.7	1141.3	927.4	782.6
15°	5350.4	4282.1	3398.7	2707.7	2428.8	2143.0	1671.4	1274.1	996.4	798.5	664.3
17.5°	5818.0	4465.5	3437.2	2645.3	2323.7	2007.5	1502.7	1114.7	858.3	684.2	547.3
20°	6047.8	4494.7	3345.5	2467.2	2143.0	1814.9	1318.0	961.9	740.0	577.9	462.3
22.5°	6047.8	4356.6	3146.1	2244.0	1917.2	1593.0	1139.9	835.8	647.1	503.5	406.5
25°	5818.0	4081.5	2879.1	1986.4	1668.7	1373.8	985.9	741.4	575.3	458.4	377.3
27.5°	5371.6	3701.5	2536.3	1699.3	1424.3	1178.4	863.6	655.0	520.8	413.2	414.5
30°	4757.8	3235.2	2143.0	1396.4	1173.1	968.6	726.8	548.7	417.3	397.2	409.2
32.5°	4048.2	2677.1	1697.9	1082.8	908.8	762.6	552.8	387.9	332.1	334.7	348.1
35°	3320.2	2107.3	1278.2	802.5	676.3	552.8	362.7	255.2	252.4	257.8	267.0
37.5°	2621.3	1577.0	924.6	587.3	454.4	340.2	195.3	175.4	175.4	180.7	186.0
40°	1963.7	1118.7	636.4	348.1	220.5	155.4	123.5	114.2	113.0	114.2	120.9
42.5°	1348.6	708.2	378.7	139.6	106.3	90.3	78.3	71.8	70.4	71.8	75.7
45°	757.3	435.7	147.5	74.4	63.7	57.2	49.1	45.2	43.8	43.8	46.5
47.5°	474.3	172.7	66.4	46.5	39.8	37.1	31.9	29.2	28.0	28.0	29.2
50°	182.0	67.8	41.2	30.6	26.6	23.9	21.3	18.6	17.2	17.2	18.6
52.5°	62.5	39.8	26.6	19.9	17.2	16.0	13.2	12.0	12.0	12.0	12.0
55°	34.5	23.9	16.0	12.0	10.6	10.6	10.6	10.6	10.6	10.6	10.6
57.5°	21.3	14.6	10.6	9.3	9.3	9.3	9.3	9.3	9.3	10.6	10.6
60°	12.0	9.3	7.9	7.9	7.9	7.9	9.3	9.3	9.3	10.6	10.6
62.5°	7.9	7.9	7.9	7.9	7.9	7.9	9.3	9.3	10.6	10.6	10.6
65°	6.7	6.7	6.7	7.9	7.9	7.9	9.3	9.3	10.6	10.6	10.6
67.5°	6.7	6.7	7.9	7.9	7.9	9.3	9.3	10.6	10.6	10.6	10.6
70°	6.7	7.9	7.9	9.3	9.3	9.3	10.6	10.6	10.6	12.0	12.0
72.5°	6.7	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0
75°	7.9	7.9	7.9	9.3	9.3	9.3	10.6	12.0	12.0	12.0	12.0
77.5°	7.9	7.9	9.3	9.3	9.3	10.6	10.6	12.0	12.0	12.0	12.0
80°	7.9	7.9	9.3	9.3	10.6	10.6	12.0	12.0	12.0	13.2	13.2
82.5°	7.9	7.9	9.3	10.6	10.6	10.6	12.0	12.0	13.2	13.2	13.2
85°	7.9	9.3	9.3	10.6	10.6	10.6	12.0	12.0	13.2	13.2	13.2
87.5°	7.9	9.3	9.3	10.6	10.6	10.6	12.0	12.0	13.2	13.2	13.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3
2.5°	1280.8	1225.0	1169.2	1128.1	1108.0	1088.1	1044.3	987.1	963.2	928.7	908.8
5°	1116.1	1021.8	947.3	898.1	868.9	830.3	780.0	724.0	692.2	656.3	632.5
7.5°	945.9	835.8	764.0	718.7	689.5	641.7	577.9	511.6	473.0	433.1	405.3
10°	797.2	692.2	611.2	559.3	522.2	466.4	402.6	356.0	322.9	288.3	260.5
12.5°	665.6	552.8	466.4	422.5	397.2	344.1	290.9	239.2	219.3	212.6	212.6
15°	539.4	437.1	364.1	326.8	300.2	243.2	232.5	229.8	228.6	227.2	229.8
17.5°	439.8	353.4	276.3	257.8	255.2	253.8	255.2	255.2	256.4	260.5	267.0
20°	369.4	289.7	284.4	285.6	285.6	290.9	297.6	302.9	308.2	314.8	326.8
22.5°	328.2	326.8	336.1	337.5	344.1	352.1	364.1	372.0	385.2	391.9	409.2
25°	378.7	387.9	405.3	410.6	421.1	434.5	453.0	463.7	479.6	487.7	507.5
27.5°	429.1	443.8	465.0	471.6	481.0	502.3	515.5	524.8	532.7	538.2	550.1
30°	425.2	438.4	459.7	461.1	474.3	488.9	497.0	504.9	510.2	508.8	515.5
32.5°	360.1	372.0	391.9	391.9	406.5	418.5	422.5	429.1	429.1	429.1	431.9
35°	276.3	284.4	297.6	301.6	313.6	321.5	324.2	332.1	332.1	329.5	329.5
37.5°	191.3	202.0	211.2	213.8	221.9	227.2	233.9	235.1	232.5	233.9	233.9
40°	124.9	131.5	138.2	139.6	146.1	150.1	156.8	156.8	158.0	156.8	159.4
42.5°	77.1	82.4	86.4	89.0	91.7	94.3	98.4	99.6	101.0	99.6	102.3
45°	47.9	50.5	53.1	54.5	55.8	57.2	61.1	61.1	61.1	61.1	62.5
47.5°	29.2	30.6	31.9	31.9	33.3	34.5	35.9	35.9	35.9	35.9	37.1
50°	17.2	18.6	18.6	18.6	19.9	19.9	21.3	21.3	21.3	19.9	21.3
52.5°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	10.6	12.0
55°	10.6	10.6	9.3	9.3	9.3	9.3	9.3	7.9	6.7	6.7	5.3
57.5°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	6.7	5.3	4.0
60°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	5.3	4.0
62.5°	10.6	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	5.3	4.0
65°	10.6	10.6	9.3	9.3	9.3	7.9	7.9	6.7	6.7	5.3	4.0
67.5°	10.6	10.6	10.6	9.3	10.6	9.3	7.9	7.9	6.7	5.3	5.3
70°	12.0	10.6	10.6	10.6	10.6	9.3	9.3	7.9	6.7	5.3	5.3
72.5°	12.0	12.0	10.6	10.6	10.6	9.3	9.3	7.9	6.7	6.7	5.3
75°	12.0	12.0	10.6	10.6	10.6	9.3	9.3	7.9	7.9	6.7	5.3
77.5°	12.0	12.0	12.0	10.6	10.6	10.6	9.3	9.3	7.9	6.7	5.3
80°	12.0	12.0	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	5.3
82.5°	13.2	12.0	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	6.7
85°	13.2	13.2	12.0	12.0	12.0	10.6	10.6	9.3	7.9	7.9	6.7
87.5°	13.2	12.0	12.0	12.0	12.0	10.6	10.6	9.3	7.9	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192809

CATALOG NUMBER: LDA6A75935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3	1440.3
2.5°	888.9	878.2	878.2	859.7	856.9	842.3	854.2	846.3
5°	605.9	588.5	583.2	564.7	558.1	540.8	546.1	539.4
7.5°	381.4	364.1	358.7	345.5	337.5	324.2	325.6	321.5
10°	232.5	216.6	212.6	208.6	204.7	203.3	204.7	203.3
12.5°	211.2	209.9	207.3	208.6	205.9	207.3	208.6	207.3
15°	229.8	232.5	229.8	231.2	229.8	232.5	233.9	233.9
17.5°	269.8	275.1	272.4	276.3	275.1	281.6	281.6	281.6
20°	330.9	340.2	337.5	342.8	342.8	350.7	350.7	353.4
22.5°	415.9	427.8	426.4	438.4	435.7	445.1	445.1	447.7
25°	518.1	530.1	531.5	539.4	538.2	547.3	547.3	550.1
27.5°	560.7	567.4	566.0	570.0	571.3	576.5	580.6	577.9
30°	526.2	531.5	530.1	532.7	532.7	536.8	540.8	536.8
32.5°	442.4	446.5	446.5	451.8	447.7	449.1	455.6	451.8
35°	338.8	341.4	338.8	341.4	342.8	342.8	349.5	348.1
37.5°	241.8	243.2	243.2	247.1	243.2	243.2	249.7	251.1
40°	162.1	163.5	162.1	167.4	164.7	164.7	168.8	164.7
42.5°	103.7	104.9	103.7	107.7	104.9	107.7	108.9	110.3
45°	63.7	63.7	62.5	65.1	63.7	65.1	66.4	66.4
47.5°	37.1	37.1	35.9	38.5	37.1	37.1	37.1	38.5
50°	19.9	19.9	19.9	21.3	19.9	19.9	19.9	18.6
52.5°	10.6	10.6	9.3	10.6	9.3	9.3	9.3	9.3
55°	5.3	4.0	4.0	4.0	2.6	2.6	2.6	2.6
57.5°	4.0	2.6	2.6	1.4	1.4	1.4	0.0	0.0
60°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	4.0	2.6	2.6	1.4	1.4	0.0	0.0	0.0
70°	4.0	2.6	2.6	1.4	1.4	0.0	0.0	0.0
72.5°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
75°	4.0	4.0	2.6	2.6	1.4	1.4	0.0	0.0
77.5°	5.3	4.0	2.6	2.6	1.4	1.4	0.0	0.0
80°	5.3	4.0	2.6	2.6	2.6	1.4	1.4	1.4
82.5°	5.3	4.0	4.0	2.6	2.6	1.4	1.4	1.4
85°	5.3	4.0	4.0	2.6	2.6	1.4	1.4	1.4
87.5°	5.3	4.0	4.0	2.6	2.6	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)