

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192826

Luminaire Tested: **LDA6A75940D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192826
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7859.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	88	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	80	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	66	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	53	49			59	53	49			57
8	69	57	49	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	36	59	48	41	36		47	41	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80745	80745	80745
5°	221626	74400	30360
10°	485662	60893	11573
15°	741854	46345	13576
20°	859506	34478	21089
25°	937603	28356	34030
30°	1047016	25713	34746
35°	1065281	17641	23825
40°	1084002	8366	12058
45°	1085764	3481	5264
50°	917914	1510	1620
55°	295569	1042	248
60°	58701	1195	0
65°	5993	1414	0
70°	641	1971	0
75°	0	2605	0
80°	0	4262	442
85°	0	8491	881

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	2.5
10°-20°	1034.1	13.2
20°-30°	1980.0	25.2
30°-40°	2332.7	29.7
40°-50°	1832.3	23.3
50°-60°	446.5	5.7
60°-70°	19.1	0.2
70°-80°	7.2	0.1
80°-90°	7.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3214.0	40.9
0°-40°	5546.7	70.6
0°-60°	7825.5	99.6
0°-90°	7859.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7859.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1473	1473	1473	1473	1473	
5°	4027	2915	1352	708	552	532
15°	13071	6714	817	234	239	3649
25°	15501	8164	469	490	563	7225
35°	15918	5161	264	340	356	9981
45°	14005	1595	45	62	68	10523
55°	3092	58	11	7	3	3681
65°	46	7	11	7	0	122
75°	0	7	12	8	0	1
85°	0	8	14	8	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9
2.5°	2524.7	2519.2	2482.4	2516.4	2413.2	2409.1	2362.9	2342.5	2282.7	2225.7	2144.1
5°	4027.4	3939.1	3867.0	3869.8	3671.4	3634.7	3531.4	3426.8	3266.4	3117.1	2914.6
7.5°	6138.9	6034.3	5882.1	5818.3	5439.1	5327.7	5114.5	4835.8	4486.6	4138.8	3763.9
10°	8724.6	8740.9	8543.9	8361.9	7788.5	7563.0	7217.8	6668.8	6007.1	5353.6	4689.1
12.5°	11326.7	11315.8	11080.8	10805.0	10098.4	9780.4	9321.2	8636.3	7759.9	6746.3	5706.9
15°	13071.4	13148.8	13049.6	12829.6	12226.1	11862.0	11344.4	10414.9	9347.0	8115.9	6713.7
17.5°	14166.5	14239.9	14204.6	14032.1	13499.4	13110.7	12678.7	11917.8	10682.7	9135.0	7507.2
20°	14733.1	14848.6	14832.4	14644.8	14242.7	13920.7	13443.7	12738.5	11669.2	9842.9	8020.8
22.5°	15110.9	15199.2	15223.7	15011.7	14595.9	14290.2	13941.0	13226.3	12220.7	10275.1	8224.7
25°	15500.8	15657.1	15503.6	15242.7	14860.8	14567.4	14195.1	13510.2	12484.4	10451.6	8163.5
27.5°	15979.1	16053.9	15706.1	15468.3	15044.4	14726.4	14330.9	13674.7	12530.6	10310.3	7814.3
30°	16540.3	16230.6	15987.4	15515.9	15034.7	14725.0	14322.8	13571.5	12287.4	9841.6	7137.6
32.5°	16448.0	16163.9	15888.1	15389.4	14913.8	14606.8	14158.4	13227.6	11712.5	9057.5	6204.1
35°	15918.0	15979.1	15681.5	15268.5	14730.5	14413.9	13924.7	12738.5	10737.1	7976.0	5160.6
37.5°	15471.0	15605.5	15411.1	15029.3	14483.1	14055.1	13394.8	11953.1	9463.9	6603.7	4171.5
40°	15147.6	15191.1	15086.5	14658.4	14002.1	13383.9	12620.2	10542.7	7917.6	5183.8	3292.4
42.5°	14646.2	14761.7	14576.9	14109.5	13114.9	12415.1	11309.1	8913.6	6149.7	3959.5	2478.4
45°	14004.9	14114.9	13886.6	13109.5	11726.2	10700.2	9351.0	6950.1	4549.1	2918.6	1595.2
47.5°	12958.6	13026.5	12585.0	11510.2	9499.1	8533.0	7149.9	4845.3	2930.9	1631.9	775.9
50°	10762.9	10730.2	9819.9	8497.7	6353.6	5339.9	4255.7	2626.5	1316.6	773.1	485.0
52.5°	6936.6	6861.8	5960.9	4758.4	3217.6	2455.4	1845.3	1133.2	686.1	432.0	191.6
55°	3092.5	3064.1	2508.4	1948.4	1316.6	1133.2	865.6	555.7	365.5	150.9	58.4
57.5°	1146.9	1120.9	987.9	828.9	635.9	528.5	419.9	266.4	93.7	50.4	31.2
60°	535.4	534.0	470.1	387.3	269.0	203.9	118.3	62.5	39.5	27.2	17.7
62.5°	171.3	167.1	116.9	85.6	61.1	53.0	42.1	31.2	20.4	14.9	10.9
65°	46.2	46.2	42.1	35.3	28.6	24.4	20.4	14.9	9.5	8.1	6.8
67.5°	17.7	17.7	16.3	14.9	10.9	9.5	8.1	6.8	5.4	6.8	6.8
70°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	5.4	5.4	6.8
72.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
75°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
77.5°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
80°	0.0	0.0	1.4	1.4	2.6	2.6	4.0	4.0	5.4	6.8	6.8
82.5°	0.0	0.0	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8	8.1
85°	0.0	0.0	1.4	2.6	2.6	4.0	4.0	5.4	5.4	6.8	8.1
87.5°	0.0	0.0	1.4	2.6	2.6	4.0	4.0	5.4	5.4	6.8	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9
2.5°	2084.4	1994.7	1871.0	1798.9	1781.4	1743.3	1676.8	1577.5	1496.1	1417.3	1371.0
5°	2743.3	2531.4	2293.6	2126.5	2058.5	1967.6	1805.8	1638.7	1485.2	1352.0	1247.4
7.5°	3441.7	3092.5	2708.0	2398.2	2286.7	2142.8	1879.1	1630.5	1419.9	1235.1	1095.1
10°	4136.0	3573.6	3051.8	2603.5	2421.3	2225.7	1877.9	1555.7	1308.5	1093.9	938.9
12.5°	4830.4	4022.0	3304.5	2727.0	2490.6	2243.4	1822.1	1441.7	1167.2	948.4	800.3
15°	5471.7	4379.2	3475.7	2769.1	2483.8	2191.6	1709.3	1303.1	1019.1	816.6	679.4
17.5°	5950.1	4566.8	3515.2	2705.2	2376.4	2053.0	1536.8	1140.0	877.7	699.8	559.8
20°	6185.2	4596.7	3421.3	2523.3	2191.6	1856.1	1348.0	983.7	756.8	591.0	472.9
22.5°	6185.2	4455.4	3217.6	2295.0	1960.7	1629.2	1165.8	854.7	661.7	515.0	415.9
25°	5950.1	4174.1	2944.4	2031.4	1706.6	1405.0	1008.3	758.2	588.4	468.8	385.9
27.5°	5493.5	3785.6	2593.8	1737.9	1456.6	1205.3	883.2	669.9	532.6	422.5	423.9
30°	4865.8	3308.7	2191.6	1428.0	1199.9	990.5	743.3	561.2	426.6	406.2	418.5
32.5°	4140.2	2737.9	1736.5	1107.4	929.5	780.0	565.2	396.7	339.7	342.4	356.0
35°	3395.5	2155.0	1307.1	820.7	691.5	565.2	370.9	260.9	258.1	263.6	273.0
37.5°	2680.9	1612.9	945.8	600.6	464.7	347.8	199.7	179.3	179.3	184.8	190.2
40°	2008.3	1144.1	650.8	356.0	225.5	159.0	126.3	116.9	115.5	116.9	123.7
42.5°	1379.2	724.2	387.3	142.7	108.6	92.5	80.2	73.4	72.0	73.4	77.4
45°	774.5	445.7	150.9	76.1	65.3	58.4	50.4	46.2	44.9	44.9	47.6
47.5°	485.0	176.7	67.9	47.6	40.7	38.1	32.6	29.8	28.6	28.6	29.8
50°	186.2	69.3	42.1	31.2	27.2	24.4	21.8	19.0	17.7	17.7	19.0
52.5°	63.9	40.7	27.2	20.4	17.7	16.3	13.5	12.3	12.3	12.3	12.3
55°	35.3	24.4	16.3	12.3	10.9	10.9	10.9	10.9	10.9	10.9	10.9
57.5°	21.8	14.9	10.9	9.5	9.5	9.5	9.5	9.5	9.5	10.9	10.9
60°	12.3	9.5	8.1	8.1	8.1	8.1	9.5	9.5	9.5	10.9	10.9
62.5°	8.1	8.1	8.1	8.1	8.1	8.1	9.5	9.5	10.9	10.9	10.9
65°	6.8	6.8	6.8	8.1	8.1	8.1	9.5	9.5	10.9	10.9	10.9
67.5°	6.8	6.8	8.1	8.1	8.1	9.5	9.5	10.9	10.9	10.9	10.9
70°	6.8	8.1	8.1	9.5	9.5	9.5	10.9	10.9	10.9	12.3	12.3
72.5°	6.8	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3
75°	8.1	8.1	8.1	9.5	9.5	9.5	10.9	12.3	12.3	12.3	12.3
77.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3	12.3
80°	8.1	8.1	9.5	9.5	10.9	10.9	12.3	12.3	12.3	13.5	13.5
82.5°	8.1	8.1	9.5	10.9	10.9	10.9	12.3	12.3	13.5	13.5	13.5
85°	8.1	9.5	9.5	10.9	10.9	10.9	12.3	12.3	13.5	13.5	13.5
87.5°	8.1	9.5	9.5	10.9	10.9	10.9	12.3	12.3	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9
2.5°	1309.9	1252.9	1195.7	1153.6	1133.2	1112.8	1067.9	1009.5	985.1	949.8	929.5
5°	1141.4	1044.9	968.8	918.6	888.6	849.3	797.5	740.5	707.9	671.2	646.8
7.5°	967.4	854.7	781.4	735.1	705.2	656.3	591.0	523.1	483.8	442.9	414.5
10°	815.2	707.9	625.0	572.0	534.0	476.9	411.7	364.1	330.2	294.8	266.4
12.5°	680.8	565.2	476.9	432.0	406.2	352.0	297.6	244.6	224.2	217.4	217.4
15°	551.7	447.1	372.3	334.3	307.1	248.6	237.8	235.1	233.7	232.3	235.1
17.5°	449.7	361.5	282.7	263.6	260.9	259.5	260.9	260.9	262.3	266.4	273.0
20°	377.8	296.2	290.8	292.2	292.2	297.6	304.4	309.9	315.3	322.0	334.3
22.5°	335.7	334.3	343.8	345.1	352.0	360.1	372.3	380.4	394.1	400.8	418.5
25°	387.3	396.7	414.5	419.9	430.8	444.3	463.4	474.1	490.5	498.7	519.0
27.5°	438.9	453.8	475.5	482.4	491.8	513.6	527.1	536.8	544.8	550.3	562.6
30°	434.8	448.3	470.1	471.5	485.0	500.1	508.2	516.4	521.8	520.4	527.1
32.5°	368.3	380.4	400.8	400.8	415.9	428.0	432.0	438.9	438.9	438.9	441.7
35°	282.7	290.8	304.4	308.5	320.6	328.8	331.5	339.7	339.7	336.9	336.9
37.5°	195.7	206.5	216.0	218.8	226.9	232.3	239.2	240.6	237.8	239.2	239.2
40°	127.7	134.6	141.3	142.7	149.5	153.5	160.4	160.4	161.6	160.4	163.0
42.5°	78.8	84.2	88.3	91.1	93.7	96.5	100.5	101.9	103.3	101.9	104.6
45°	49.0	51.6	54.4	55.6	57.0	58.4	62.5	62.5	62.5	62.5	63.9
47.5°	29.8	31.2	32.6	32.6	34.0	35.3	36.7	36.7	36.7	36.7	38.1
50°	17.7	19.0	19.0	19.0	20.4	20.4	21.8	21.8	21.8	20.4	21.8
52.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	10.9	12.3
55°	10.9	10.9	9.5	9.5	9.5	9.5	9.5	8.1	6.8	6.8	5.4
57.5°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	6.8	5.4	4.0
60°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.0
62.5°	10.9	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.0
65°	10.9	10.9	9.5	9.5	9.5	8.1	8.1	6.8	6.8	5.4	4.0
67.5°	10.9	10.9	10.9	9.5	10.9	9.5	8.1	8.1	6.8	5.4	5.4
70°	12.3	10.9	10.9	10.9	10.9	9.5	9.5	8.1	6.8	5.4	5.4
72.5°	12.3	12.3	10.9	10.9	10.9	9.5	9.5	8.1	6.8	6.8	5.4
75°	12.3	12.3	10.9	10.9	10.9	9.5	9.5	8.1	8.1	6.8	5.4
77.5°	12.3	12.3	12.3	10.9	10.9	10.9	9.5	9.5	8.1	6.8	5.4
80°	12.3	12.3	12.3	12.3	12.3	10.9	10.9	9.5	8.1	6.8	5.4
82.5°	13.5	12.3	12.3	12.3	12.3	10.9	10.9	9.5	8.1	6.8	6.8
85°	13.5	13.5	12.3	12.3	12.3	10.9	10.9	9.5	8.1	8.1	6.8
87.5°	13.5	12.3	12.3	12.3	12.3	10.9	10.9	9.5	8.1	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192826

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9	1472.9
2.5°	908.9	898.1	898.1	879.1	876.5	861.4	873.7	865.6
5°	619.6	601.9	596.4	577.5	570.6	553.1	558.5	551.7
7.5°	389.9	372.3	366.9	353.2	345.1	331.5	332.9	328.8
10°	237.8	221.4	217.4	213.4	209.3	207.9	209.3	207.9
12.5°	216.0	214.6	212.0	213.4	210.6	212.0	213.4	212.0
15°	235.1	237.8	235.1	236.4	235.1	237.8	239.2	239.2
17.5°	275.8	281.3	278.5	282.7	281.3	288.1	288.1	288.1
20°	338.3	347.8	345.1	350.6	350.6	358.7	358.7	361.5
22.5°	425.3	437.5	436.2	448.3	445.7	455.2	455.2	458.0
25°	529.9	542.2	543.4	551.7	550.3	559.8	559.8	562.6
27.5°	573.4	580.1	578.9	582.9	584.3	589.8	593.8	591.0
30°	538.0	543.4	542.2	544.8	544.8	548.9	553.1	548.9
32.5°	452.5	456.6	456.6	462.0	458.0	459.2	466.1	462.0
35°	346.5	349.2	346.5	349.2	350.6	350.6	357.4	356.0
37.5°	247.2	248.6	248.6	252.7	248.6	248.6	255.5	256.9
40°	165.8	167.1	165.8	171.3	168.5	168.5	172.5	168.5
42.5°	106.0	107.4	106.0	110.0	107.4	110.0	111.4	112.8
45°	65.3	65.3	63.9	66.5	65.3	66.5	67.9	67.9
47.5°	38.1	38.1	36.7	39.5	38.1	38.1	38.1	39.5
50°	20.4	20.4	20.4	21.8	20.4	20.4	20.4	19.0
52.5°	10.9	10.9	9.5	10.9	9.5	9.5	9.5	9.5
55°	5.4	4.0	4.0	4.0	2.6	2.6	2.6	2.6
57.5°	4.0	2.6	2.6	1.4	1.4	1.4	0.0	0.0
60°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.6	2.6	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	4.0	2.6	2.6	1.4	1.4	0.0	0.0	0.0
70°	4.0	2.6	2.6	1.4	1.4	0.0	0.0	0.0
72.5°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
75°	4.0	4.0	2.6	2.6	1.4	1.4	0.0	0.0
77.5°	5.4	4.0	2.6	2.6	1.4	1.4	0.0	0.0
80°	5.4	4.0	2.6	2.6	2.6	1.4	1.4	1.4
82.5°	5.4	4.0	4.0	2.6	2.6	1.4	1.4	1.4
85°	5.4	4.0	4.0	2.6	2.6	1.4	1.4	1.4
87.5°	5.4	4.0	4.0	2.6	2.6	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)