

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212562

Luminaire Tested: **LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3952.0 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	30690	30690	30690
5°	78734	27925	8696
10°	153470	21458	4175
15°	275506	14576	5607
20°	409034	11061	9251
25°	464929	9112	14509
30°	503995	9963	13647
35°	530869	6460	8457
40°	542352	2866	4120
45°	489847	1096	1528
50°	322455	435	435
55°	88307	375	0
60°	17636	431	0
65°	1243	591	0
70°	176	730	0
75°	0	1081	0
80°	0	1612	174
85°	0	3211	346

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.3	2.2
10°-20°	463.9	11.7
20°-30°	1051.5	26.6
30°-40°	1262.1	31.9
40°-50°	889.5	22.5
50°-60°	183.5	4.6
60°-70°	6.5	0.2
70°-80°	3.9	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1602.7	40.6
0°-40°	2864.8	72.5
0°-60°	3937.8	99.6
0°-90°	3952.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3952.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	713	713	713	713	713	
5°	1822	1327	646	269	201	224
15°	6181	2719	327	116	126	1834
25°	9787	3289	192	269	305	4516
35°	10100	2303	123	161	161	6279
45°	8045	790	18	24	25	5917
55°	1176	16	5	4	0	1550
65°	12	4	6	4	0	36
75°	0	4	6	4	0	0
85°	0	4	6	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8
2.5°	1215.1	1178.5	1192.9	1150.5	1141.1	1133.2	1141.1	1095.2	1069.3	1036.2	1009.7
5°	1821.7	1777.8	1787.9	1713.9	1680.1	1657.1	1652.8	1558.0	1486.8	1408.4	1327.3
7.5°	2535.9	2494.3	2488.5	2373.6	2303.8	2264.3	2247.8	2112.0	1989.1	1849.7	1697.4
10°	3510.3	3415.5	3386.0	3219.4	3086.4	3002.3	2898.9	2681.8	2466.3	2255.7	2061.6
12.5°	4644.3	4592.6	4519.3	4225.4	3992.6	3873.3	3718.8	3379.6	3053.3	2705.6	2380.7
15°	6180.8	5996.7	5871.7	5447.0	5071.9	4888.0	4662.3	4143.5	3650.5	3210.0	2719.2
17.5°	7681.9	7585.6	7390.1	6839.0	6261.2	5970.8	5634.6	4929.6	4233.3	3606.7	3007.4
20°	8927.2	8836.7	8613.9	8094.4	7453.4	7025.0	6601.8	5634.6	4724.8	3922.8	3200.0
22.5°	9523.7	9466.2	9284.4	8839.6	8293.4	7885.9	7431.1	6234.7	5088.4	4129.8	3287.6
25°	9786.6	9760.1	9643.0	9292.2	8777.8	8432.1	8002.3	6659.3	5314.8	4226.2	3289.0
27.5°	10053.3	10058.3	9799.6	9522.2	9034.3	8702.3	8288.4	6847.6	5355.8	4172.3	3181.2
30°	10137.4	10084.2	9969.9	9571.8	9108.3	8755.4	8311.4	6760.6	5187.6	3950.8	2966.4
32.5°	10102.8	10082.0	9956.3	9535.2	8982.5	8593.8	8089.4	6415.7	4855.6	3634.7	2661.7
35°	10100.0	10061.2	9773.0	9411.5	8731.1	8251.0	7586.3	5858.0	4385.6	3217.9	2303.1
37.5°	9917.4	9821.1	9604.8	9117.7	8220.9	7612.2	6867.0	5176.8	3810.8	2750.1	1947.5
40°	9649.5	9520.0	9235.5	8498.2	7337.0	6635.6	5908.3	4402.9	3202.1	2288.7	1569.5
42.5°	9089.7	8894.2	8491.7	7477.8	6159.1	5526.8	4921.8	3618.9	2611.4	1864.8	1197.9
45°	8044.8	7777.5	7233.5	6120.4	4975.6	4459.6	3973.2	2911.8	2090.4	1383.3	789.7
47.5°	6466.0	6218.0	5723.0	4872.1	3902.1	3465.8	3077.8	2165.9	1417.1	801.2	377.2
50°	4814.0	4601.3	4214.7	3386.0	2619.3	2276.6	1944.6	1230.3	664.0	380.9	156.7
52.5°	2872.3	2766.6	2423.9	1877.7	1293.5	1114.6	894.7	521.0	334.9	137.9	42.4
55°	1176.4	1085.8	957.2	768.2	562.7	477.1	408.1	257.2	104.2	28.8	15.8
57.5°	531.8	511.7	453.4	356.5	258.7	217.1	146.6	48.9	23.0	14.4	9.4
60°	204.8	184.7	158.1	85.5	36.6	30.9	25.1	16.5	11.5	7.9	5.8
62.5°	29.5	28.0	25.1	20.1	15.8	14.4	12.2	8.6	6.5	5.0	4.3
65°	12.2	12.2	10.8	8.6	7.1	6.5	5.8	4.3	3.6	3.6	3.6
67.5°	5.0	5.0	4.3	3.6	2.9	2.9	2.9	2.1	2.9	2.9	3.6
70°	1.4	1.4	1.4	1.4	1.4	1.4	2.1	2.1	2.9	2.9	3.6
72.5°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.9	3.6	3.6
75°	0.0	0.0	0.7	0.7	1.4	1.4	1.4	2.1	2.9	3.6	3.6
77.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	3.6
80°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	4.3
82.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	4.3
85°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	4.3
87.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8
2.5°	986.7	940.7	927.7	887.5	853.7	837.1	816.4	769.6	734.4	687.7	659.7
5°	1270.5	1183.5	1114.6	1030.4	975.2	939.2	883.1	797.6	728.7	646.1	587.1
7.5°	1577.4	1418.6	1294.2	1155.5	1075.7	1013.2	917.7	794.8	693.5	583.5	492.3
10°	1873.4	1636.3	1440.8	1241.8	1136.8	1049.8	918.4	763.9	629.5	490.8	394.5
12.5°	2134.3	1828.2	1552.9	1297.0	1167.0	1058.5	893.9	708.6	546.2	403.9	319.1
15°	2352.0	1976.9	1632.0	1317.9	1169.1	1039.8	842.9	629.5	453.4	327.0	267.3
17.5°	2517.3	2055.2	1656.4	1292.8	1127.5	986.7	764.6	529.7	367.9	277.3	224.9
20°	2602.8	2070.3	1621.1	1224.5	1050.6	906.2	661.8	429.8	311.9	241.4	188.3
22.5°	2613.6	2027.9	1537.1	1126.7	953.6	808.4	548.3	358.6	278.1	213.4	166.0
25°	2549.6	1936.0	1417.1	1016.1	847.3	696.3	446.3	321.2	253.0	191.8	191.2
27.5°	2413.1	1777.8	1273.4	887.5	718.6	566.3	378.7	290.3	225.7	203.3	216.3
30°	2220.4	1575.2	1096.6	725.1	561.2	435.5	319.1	239.3	198.3	200.4	211.3
32.5°	1959.6	1323.7	888.9	531.0	401.7	327.7	239.3	163.2	164.6	165.3	174.7
35°	1632.0	1061.3	664.0	357.1	282.5	230.7	135.1	120.0	122.2	122.9	129.3
37.5°	1307.9	815.6	441.3	237.8	177.5	121.4	84.0	80.5	81.9	81.2	88.4
40°	1001.7	568.4	264.5	117.9	68.3	56.8	51.8	49.6	50.3	51.0	55.4
42.5°	709.2	308.3	130.8	44.5	35.9	33.0	30.9	29.5	30.1	30.1	33.0
45°	360.0	145.9	44.5	24.4	22.3	20.1	18.6	18.0	18.0	18.0	19.4
47.5°	155.9	48.1	20.9	15.1	13.6	12.9	11.5	10.8	10.8	10.8	11.5
50°	48.9	19.4	12.9	10.0	8.6	7.9	7.1	7.1	7.1	6.5	7.1
52.5°	18.0	12.2	8.6	6.5	5.8	5.8	5.8	5.0	5.8	5.0	5.8
55°	10.8	7.9	5.8	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
57.5°	7.1	5.8	5.0	5.0	4.3	4.3	5.0	5.0	5.0	5.0	5.0
60°	5.0	5.0	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.0	5.0
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.0	5.8
65°	3.6	4.3	4.3	4.3	4.3	4.3	5.0	5.0	5.8	5.8	5.8
67.5°	3.6	4.3	4.3	5.0	5.0	5.0	5.0	5.8	5.8	5.8	5.8
70°	4.3	4.3	5.0	5.0	5.0	5.0	5.8	5.8	5.8	5.8	6.5
72.5°	4.3	4.3	5.0	5.0	5.0	5.0	5.8	5.8	6.5	6.5	6.5
75°	4.3	5.0	5.0	5.0	5.0	5.8	5.8	5.8	6.5	6.5	6.5
77.5°	4.3	5.0	5.0	5.8	5.8	5.8	5.8	6.5	6.5	6.5	6.5
80°	4.3	5.0	5.0	5.8	5.8	5.8	6.5	6.5	6.5	6.5	7.1
82.5°	4.3	5.0	5.0	5.8	5.8	5.8	6.5	6.5	6.5	6.5	7.1
85°	5.0	5.0	5.8	5.8	5.8	5.8	6.5	6.5	6.5	6.5	7.1
87.5°	5.0	5.0	5.8	5.8	5.8	5.8	6.5	6.5	7.1	6.5	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8
2.5°	622.3	580.7	551.9	541.2	520.3	487.3	467.8	449.9	416.1	408.9	390.2
5°	519.5	452.8	405.3	387.4	363.6	335.6	308.3	290.3	268.7	260.1	247.2
7.5°	409.6	342.7	301.8	287.5	270.9	247.9	223.5	205.6	183.3	171.8	160.9
10°	322.0	272.3	237.8	223.5	206.2	181.8	156.7	132.9	113.5	101.3	99.2
12.5°	261.6	220.6	183.9	168.9	148.8	124.3	106.4	105.7	104.2	103.5	104.9
15°	214.2	174.7	135.8	119.3	113.5	112.8	115.0	117.2	116.4	118.5	120.0
17.5°	176.1	133.7	125.0	125.8	126.4	128.7	132.2	137.9	138.7	142.3	145.2
20°	143.7	141.5	145.2	148.0	150.2	154.5	162.4	169.6	171.8	176.8	182.5
22.5°	163.2	169.6	177.5	181.1	183.9	191.8	200.4	211.9	216.3	222.8	230.7
25°	196.9	207.7	219.9	224.2	228.6	241.4	251.5	265.2	268.7	276.7	284.6
27.5°	224.9	236.4	249.3	255.1	258.7	271.6	280.2	288.8	288.8	293.2	299.0
30°	220.6	229.9	240.7	245.1	246.5	255.8	264.5	267.3	265.8	268.1	272.3
32.5°	183.3	190.4	199.1	202.7	204.1	210.6	217.7	217.7	217.1	217.1	219.9
35°	135.8	140.8	145.2	148.8	150.9	155.2	161.7	160.9	160.9	159.5	161.7
37.5°	91.3	94.2	99.2	100.6	101.3	104.2	109.3	109.3	107.8	108.5	109.9
40°	55.4	58.9	61.8	62.5	63.9	66.1	69.7	69.7	69.7	69.7	70.4
42.5°	33.0	35.3	37.4	37.4	38.1	41.0	42.4	42.4	42.4	42.4	43.1
45°	19.4	20.1	21.5	22.3	22.3	23.7	24.4	24.4	24.4	24.4	25.1
47.5°	11.5	12.2	12.2	12.9	12.9	13.6	14.4	14.4	13.6	13.6	13.6
50°	7.1	7.1	7.1	7.1	7.9	7.9	7.9	7.9	7.9	7.9	7.1
52.5°	5.8	5.8	5.8	5.8	5.0	5.0	5.0	5.0	4.3	4.3	3.6
55°	5.0	5.0	5.0	5.0	5.0	4.3	4.3	4.3	3.6	2.9	2.1
57.5°	5.0	5.0	5.0	5.0	5.0	4.3	4.3	3.6	2.9	2.9	2.1
60°	5.0	5.0	5.0	5.0	5.0	4.3	4.3	3.6	2.9	2.9	2.1
62.5°	5.8	5.8	5.0	5.0	5.0	4.3	4.3	3.6	3.6	2.9	2.1
65°	5.8	5.8	5.0	5.0	5.0	5.0	4.3	4.3	3.6	2.9	2.1
67.5°	5.8	5.8	5.8	5.8	5.0	5.0	5.0	4.3	3.6	2.9	2.1
70°	6.5	6.5	5.8	5.8	5.8	5.0	5.0	4.3	3.6	3.6	2.9
72.5°	6.5	6.5	5.8	5.8	5.8	5.8	5.0	4.3	4.3	3.6	2.9
75°	6.5	6.5	6.5	6.5	5.8	5.8	5.0	5.0	4.3	3.6	2.9
77.5°	6.5	6.5	6.5	6.5	5.8	5.8	5.8	5.0	4.3	3.6	2.9
80°	6.5	6.5	6.5	6.5	6.5	5.8	5.8	5.0	4.3	3.6	2.9
82.5°	7.1	7.1	6.5	6.5	6.5	5.8	5.8	5.0	4.3	3.6	3.6
85°	7.1	7.1	6.5	6.5	6.5	5.8	5.8	5.0	4.3	4.3	3.6
87.5°	7.1	7.1	6.5	6.5	6.5	5.8	5.8	5.0	4.3	4.3	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212562

CATALOG NUMBER: LDSQA6A40940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	712.8	712.8	712.8	712.8	712.8	712.8	712.8	712.8
2.5°	378.7	357.1	350.0	355.0	349.2	345.0	339.2	336.3
5°	237.2	221.3	216.3	217.7	212.7	208.4	202.7	201.2
7.5°	145.9	130.8	125.0	125.0	119.3	114.3	110.7	108.5
10°	97.8	94.9	95.5	96.3	95.5	96.3	94.2	95.5
12.5°	104.9	103.5	104.9	105.7	105.7	107.0	104.2	106.4
15°	122.2	120.8	122.9	124.3	124.3	126.4	123.6	125.8
17.5°	149.4	148.8	152.3	153.8	154.5	158.1	154.5	157.4
20°	188.9	188.3	193.3	195.4	194.7	201.9	196.9	201.9
22.5°	240.1	238.6	245.8	247.9	248.6	258.0	253.7	257.2
25°	291.1	292.5	296.1	299.7	300.3	308.3	301.8	305.4
27.5°	301.8	299.7	301.8	306.1	306.8	310.5	304.7	307.6
30°	273.1	269.5	270.2	275.2	276.7	278.1	273.1	274.5
32.5°	222.1	216.3	216.3	221.3	222.8	224.9	216.3	219.9
35°	163.8	158.8	158.8	162.4	163.2	164.6	158.1	160.9
37.5°	112.1	107.8	109.3	110.7	111.4	112.8	112.1	111.4
40°	71.9	69.0	71.1	71.1	71.9	72.5	72.5	73.3
42.5°	43.9	41.6	43.1	43.1	43.9	43.9	43.9	44.5
45°	25.1	24.4	24.4	25.1	25.1	25.1	24.4	25.1
47.5°	13.6	12.9	13.6	13.6	13.6	13.6	13.6	13.6
50°	7.1	6.5	6.5	6.5	6.5	6.5	6.5	6.5
52.5°	3.6	2.9	2.9	2.9	2.1	2.9	2.1	2.1
55°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
57.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
60°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.1	1.4	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.1	1.4	1.4	0.7	0.7	0.0	0.0	0.0
72.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	2.1	2.1	1.4	1.4	0.7	0.7	0.7	0.0
80°	2.9	2.1	1.4	1.4	1.4	0.7	0.7	0.7
82.5°	2.9	2.1	1.4	1.4	1.4	0.7	0.7	0.7
85°	2.9	2.1	2.1	1.4	1.4	0.7	0.7	0.7
87.5°	2.9	2.1	2.1	1.4	1.4	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)