

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212564

Luminaire Tested: **LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4156.1 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	33536	33536	33536
5°	92050	30898	12607
10°	201715	25288	4805
15°	308121	19252	5634
20°	356989	14323	8761
25°	389426	11777	14133
30°	434869	10679	14433
35°	442455	7327	9897
40°	450232	3473	5008
45°	450957	1443	2186
50°	381246	630	670
55°	122762	435	105
60°	24378	499	0
65°	2486	591	0
70°	264	818	0
75°	0	1081	0
80°	0	1760	174
85°	0	3507	346

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.7	2.5
10°-20°	546.9	13.2
20°-30°	1047.1	25.2
30°-40°	1233.6	29.7
40°-50°	968.9	23.3
50°-60°	236.1	5.7
60°-70°	10.1	0.2
70°-80°	3.8	0.1
80°-90°	3.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1699.6	40.9
0°-40°	2933.2	70.6
0°-60°	4138.3	99.6
0°-90°	4156.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4156.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	779	779	779	779	779	
5°	2130	1541	715	374	292	282
15°	6912	3550	432	124	126	1930
25°	8197	4317	248	259	298	3821
35°	8418	2729	139	180	188	5278
45°	7406	844	24	33	36	5565
55°	1635	31	6	4	1	1947
65°	24	4	6	4	0	65
75°	0	4	6	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9
2.5°	1335.1	1332.2	1312.8	1330.8	1276.2	1274.0	1249.6	1238.8	1207.2	1177.0	1133.9
5°	2129.8	2083.1	2045.0	2046.5	1941.6	1922.1	1867.6	1812.2	1727.4	1648.4	1541.3
7.5°	3246.4	3191.1	3110.6	3076.9	2876.4	2817.4	2704.6	2557.4	2372.7	2188.8	1990.4
10°	4613.8	4622.5	4518.3	4422.0	4118.7	3999.5	3817.0	3526.7	3176.8	2831.2	2479.7
12.5°	5989.9	5984.2	5859.9	5714.0	5340.3	5172.2	4929.3	4567.2	4103.7	3567.6	3018.0
15°	6912.5	6953.5	6901.0	6784.6	6465.5	6273.0	5999.2	5507.7	4942.9	4291.9	3550.4
17.5°	7491.7	7530.5	7511.8	7420.5	7138.8	6933.4	6704.8	6302.5	5649.3	4830.9	3970.1
20°	7791.3	7852.4	7843.7	7744.6	7531.9	7361.6	7109.4	6736.5	6171.0	5205.2	4241.6
22.5°	7991.0	8037.8	8050.7	7938.6	7718.7	7557.0	7372.4	6994.4	6462.7	5433.8	4349.4
25°	8197.3	8280.0	8198.7	8060.8	7858.9	7703.7	7506.8	7144.6	6602.1	5527.2	4317.1
27.5°	8450.2	8489.8	8305.8	8180.1	7955.9	7787.7	7578.7	7231.6	6626.6	5452.4	4132.5
30°	8747.0	8583.2	8454.5	8205.2	7950.9	7787.0	7574.3	7177.0	6497.9	5204.5	3774.5
32.5°	8698.2	8547.9	8402.1	8138.4	7886.9	7724.5	7487.4	6995.2	6194.0	4789.9	3280.9
35°	8417.9	8450.2	8292.8	8074.4	7789.9	7622.4	7363.8	6736.5	5678.1	4217.9	2729.0
37.5°	8181.4	8252.6	8149.9	7948.0	7659.1	7432.8	7083.5	6321.1	5004.7	3492.2	2206.0
40°	8010.5	8033.4	7978.1	7751.8	7404.7	7077.8	6674.0	5575.3	4187.0	2741.3	1741.0
42.5°	7745.3	7806.4	7708.7	7461.5	6935.5	6565.4	5980.5	4713.7	3252.2	2093.9	1310.7
45°	7406.1	7464.4	7343.6	6932.6	6201.1	5658.6	4945.1	3675.4	2405.7	1543.5	843.6
47.5°	6852.9	6888.8	6655.3	6086.9	5023.4	4512.6	3781.0	2562.4	1549.9	863.0	410.3
50°	5691.7	5674.5	5193.0	4493.8	3359.9	2823.9	2250.5	1389.0	696.3	408.8	256.6
52.5°	3668.2	3628.7	3152.3	2516.4	1701.5	1298.4	975.8	599.3	362.8	228.5	101.3
55°	1635.4	1620.4	1326.4	1030.4	696.3	599.3	457.7	293.9	193.3	79.8	30.9
57.5°	606.5	592.8	522.4	438.3	336.3	279.6	222.0	140.8	49.6	26.6	16.5
60°	283.1	282.4	248.6	204.8	142.3	107.8	62.5	33.0	20.9	14.4	9.4
62.5°	90.5	88.4	61.8	45.3	32.4	28.0	22.3	16.5	10.8	7.9	5.8
65°	24.4	24.4	22.3	18.6	15.1	12.9	10.8	7.9	5.0	4.3	3.6
67.5°	9.4	9.4	8.6	7.9	5.8	5.0	4.3	3.6	2.9	3.6	3.6
70°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.9	2.9	3.6
72.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	3.6
75°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	3.6
77.5°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	3.6
80°	0.0	0.0	0.7	0.7	1.4	1.4	2.1	2.1	2.9	3.6	3.6
82.5°	0.0	0.0	0.7	1.4	1.4	1.4	2.1	2.9	2.9	3.6	4.3
85°	0.0	0.0	0.7	1.4	1.4	2.1	2.1	2.9	2.9	3.6	4.3
87.5°	0.0	0.0	0.7	1.4	1.4	2.1	2.1	2.9	2.9	3.6	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9
2.5°	1102.3	1054.9	989.5	951.4	942.0	922.0	886.7	834.2	791.2	749.4	725.0
5°	1450.7	1338.7	1212.9	1124.5	1088.6	1040.5	955.0	866.6	785.4	714.9	659.7
7.5°	1820.1	1635.4	1432.1	1268.3	1209.3	1133.1	993.7	862.3	750.9	653.2	579.1
10°	2187.3	1889.8	1613.9	1376.7	1280.4	1177.0	993.0	822.7	691.9	578.4	496.5
12.5°	2554.5	2126.9	1747.5	1442.1	1317.1	1186.3	963.6	762.4	617.3	501.5	423.2
15°	2893.7	2315.9	1838.1	1464.5	1313.6	1159.0	904.0	689.0	538.9	431.9	359.3
17.5°	3146.6	2415.1	1858.9	1430.6	1256.8	1085.8	812.7	602.9	464.2	370.1	296.1
20°	3270.9	2430.8	1809.3	1334.3	1159.0	981.6	712.8	520.2	400.2	312.6	250.1
22.5°	3270.9	2356.2	1701.5	1213.7	1036.9	861.6	616.5	452.0	350.0	272.3	219.9
25°	3146.6	2207.4	1557.1	1074.3	902.5	743.0	533.1	401.0	311.1	247.9	204.1
27.5°	2905.1	2001.9	1371.7	919.1	770.3	637.4	467.1	354.2	281.7	223.4	224.2
30°	2573.1	1749.7	1159.0	755.2	634.5	523.9	393.1	296.8	225.7	214.8	221.3
32.5°	2189.4	1447.9	918.3	585.6	491.5	412.5	298.9	209.8	179.7	181.0	188.3
35°	1795.7	1139.6	691.3	434.0	365.7	298.9	196.2	137.9	136.5	139.4	144.4
37.5°	1417.7	852.9	500.1	317.6	245.8	183.9	105.6	94.9	94.9	97.8	100.6
40°	1062.0	605.0	344.2	188.3	119.3	84.0	66.8	61.8	61.1	61.8	65.4
42.5°	729.3	383.0	204.8	75.4	57.5	48.9	42.4	38.8	38.1	38.8	41.0
45°	409.6	235.7	79.8	40.3	34.5	30.9	26.6	24.4	23.7	23.7	25.1
47.5°	256.6	93.4	35.9	25.1	21.5	20.1	17.3	15.8	15.1	15.1	15.8
50°	98.4	36.6	22.3	16.5	14.4	12.9	11.5	10.0	9.4	9.4	10.0
52.5°	33.8	21.5	14.4	10.8	9.4	8.6	7.1	6.5	6.5	6.5	6.5
55°	18.6	12.9	8.6	6.5	5.8	5.8	5.8	5.8	5.8	5.8	5.8
57.5°	11.5	7.9	5.8	5.0	5.0	5.0	5.0	5.0	5.0	5.8	5.8
60°	6.5	5.0	4.3	4.3	4.3	4.3	5.0	5.0	5.0	5.8	5.8
62.5°	4.3	4.3	4.3	4.3	4.3	4.3	5.0	5.0	5.8	5.8	5.8
65°	3.6	3.6	3.6	4.3	4.3	4.3	5.0	5.0	5.8	5.8	5.8
67.5°	3.6	3.6	4.3	4.3	4.3	5.0	5.0	5.8	5.8	5.8	5.8
70°	3.6	4.3	4.3	5.0	5.0	5.0	5.8	5.8	5.8	6.5	6.5
72.5°	3.6	4.3	4.3	5.0	5.0	5.0	5.8	5.8	6.5	6.5	6.5
75°	4.3	4.3	4.3	5.0	5.0	5.0	5.8	6.5	6.5	6.5	6.5
77.5°	4.3	4.3	5.0	5.0	5.0	5.8	5.8	6.5	6.5	6.5	6.5
80°	4.3	4.3	5.0	5.0	5.8	5.8	6.5	6.5	6.5	7.1	7.1
82.5°	4.3	4.3	5.0	5.8	5.8	5.8	6.5	6.5	7.1	7.1	7.1
85°	4.3	5.0	5.0	5.8	5.8	5.8	6.5	6.5	7.1	7.1	7.1
87.5°	4.3	5.0	5.0	5.8	5.8	5.8	6.5	6.5	7.1	7.1	7.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9
2.5°	692.7	662.5	632.3	610.0	599.3	588.5	564.8	533.9	521.0	502.2	491.5
5°	603.6	552.6	512.4	485.7	470.0	449.1	421.8	391.6	374.3	355.0	342.1
7.5°	511.6	452.0	413.2	388.7	373.0	347.1	312.6	276.7	255.8	234.3	219.2
10°	431.1	374.3	330.6	302.6	282.4	252.2	217.7	192.6	174.7	155.9	140.8
12.5°	360.0	298.9	252.2	228.5	214.8	186.1	157.4	129.3	118.5	115.0	115.0
15°	291.7	236.4	196.9	176.8	162.4	131.5	125.8	124.3	123.6	122.9	124.3
17.5°	237.8	191.2	149.4	139.4	137.9	137.3	137.9	137.9	138.7	140.8	144.4
20°	199.8	156.7	153.8	154.5	154.5	157.4	160.9	163.8	166.7	170.3	176.8
22.5°	177.5	176.8	181.8	182.5	186.1	190.4	196.9	201.2	208.4	211.9	221.3
25°	204.8	209.8	219.2	222.0	227.8	234.9	245.1	250.8	259.4	263.7	274.4
27.5°	232.1	240.0	251.4	255.1	260.1	271.6	278.8	283.8	288.2	291.1	297.5
30°	229.9	237.2	248.6	249.3	256.6	264.4	268.7	273.1	275.9	275.2	278.8
32.5°	194.7	201.2	211.9	211.9	219.9	226.3	228.5	232.1	232.1	232.1	233.6
35°	149.4	153.8	160.9	163.2	169.5	173.9	175.3	179.7	179.7	178.2	178.2
37.5°	103.5	109.3	114.3	115.7	120.0	122.9	126.4	127.2	125.8	126.4	126.4
40°	67.5	71.1	74.8	75.4	79.0	81.2	84.8	84.8	85.5	84.8	86.3
42.5°	41.6	44.5	46.8	48.1	49.6	51.0	53.1	53.9	54.6	53.9	55.4
45°	25.9	27.3	28.8	29.5	30.1	30.9	33.0	33.0	33.0	33.0	33.8
47.5°	15.8	16.5	17.3	17.3	18.0	18.6	19.4	19.4	19.4	19.4	20.1
50°	9.4	10.0	10.0	10.0	10.8	10.8	11.5	11.5	11.5	10.8	11.5
52.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	5.8	6.5
55°	5.8	5.8	5.0	5.0	5.0	5.0	5.0	4.3	3.6	3.6	2.9
57.5°	5.0	5.0	5.0	5.0	5.0	4.3	4.3	3.6	3.6	2.9	2.1
60°	5.0	5.0	5.0	5.0	5.0	4.3	4.3	3.6	2.9	2.9	2.1
62.5°	5.8	5.0	5.0	5.0	5.0	4.3	4.3	3.6	2.9	2.9	2.1
65°	5.8	5.8	5.0	5.0	5.0	4.3	4.3	3.6	3.6	2.9	2.1
67.5°	5.8	5.8	5.8	5.0	5.8	5.0	4.3	4.3	3.6	2.9	2.9
70°	6.5	5.8	5.8	5.8	5.8	5.0	5.0	4.3	3.6	2.9	2.9
72.5°	6.5	6.5	5.8	5.8	5.8	5.0	5.0	4.3	3.6	3.6	2.9
75°	6.5	6.5	5.8	5.8	5.8	5.0	5.0	4.3	4.3	3.6	2.9
77.5°	6.5	6.5	6.5	5.8	5.8	5.8	5.0	5.0	4.3	3.6	2.9
80°	6.5	6.5	6.5	6.5	6.5	5.8	5.8	5.0	4.3	3.6	2.9
82.5°	7.1	6.5	6.5	6.5	6.5	5.8	5.8	5.0	4.3	3.6	3.6
85°	7.1	7.1	6.5	6.5	6.5	5.8	5.8	5.0	4.3	4.3	3.6
87.5°	7.1	6.5	6.5	6.5	6.5	5.8	5.8	5.0	4.3	3.6	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212564

CATALOG NUMBER: LDSQA6A40940D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	778.9	778.9	778.9	778.9	778.9	778.9	778.9	778.9
2.5°	480.7	475.0	475.0	464.9	463.5	455.6	462.0	457.7
5°	327.7	318.3	315.4	305.4	301.8	292.4	295.3	291.7
7.5°	206.2	196.9	194.0	186.8	182.5	175.3	176.0	173.9
10°	125.8	117.1	115.0	112.8	110.7	109.9	110.7	109.9
12.5°	114.3	113.5	112.1	112.8	111.4	112.1	112.8	112.1
15°	124.3	125.8	124.3	125.0	124.3	125.8	126.4	126.4
17.5°	145.9	148.8	147.3	149.4	148.8	152.3	152.3	152.3
20°	178.9	183.9	182.5	185.4	185.4	189.7	189.7	191.2
22.5°	224.9	231.4	230.7	237.2	235.7	240.7	240.7	242.2
25°	280.2	286.7	287.4	291.7	291.1	296.1	296.1	297.5
27.5°	303.2	306.8	306.1	308.3	309.0	311.8	314.0	312.6
30°	284.6	287.4	286.7	288.2	288.2	290.3	292.4	290.3
32.5°	239.3	241.4	241.4	244.3	242.2	242.9	246.4	244.3
35°	183.3	184.7	183.3	184.7	185.4	185.4	188.9	188.3
37.5°	130.8	131.5	131.5	133.7	131.5	131.5	135.0	135.8
40°	87.6	88.4	87.6	90.5	89.1	89.1	91.3	89.1
42.5°	56.0	56.8	56.0	58.2	56.8	58.2	58.9	59.6
45°	34.5	34.5	33.8	35.2	34.5	35.2	35.9	35.9
47.5°	20.1	20.1	19.4	20.9	20.1	20.1	20.1	20.9
50°	10.8	10.8	10.8	11.5	10.8	10.8	10.8	10.0
52.5°	5.8	5.8	5.0	5.8	5.0	5.0	5.0	5.0
55°	2.9	2.1	2.1	2.1	1.4	1.4	1.4	1.4
57.5°	2.1	1.4	1.4	0.7	0.7	0.7	0.0	0.0
60°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.4	1.4	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.1	1.4	1.4	0.7	0.7	0.0	0.0	0.0
70°	2.1	1.4	1.4	0.7	0.7	0.0	0.0	0.0
72.5°	2.1	1.4	1.4	1.4	0.7	0.7	0.0	0.0
75°	2.1	2.1	1.4	1.4	0.7	0.7	0.0	0.0
77.5°	2.9	2.1	1.4	1.4	0.7	0.7	0.0	0.0
80°	2.9	2.1	1.4	1.4	1.4	0.7	0.7	0.7
82.5°	2.9	2.1	2.1	1.4	1.4	0.7	0.7	0.7
85°	2.9	2.1	2.1	1.4	1.4	0.7	0.7	0.7
87.5°	2.9	2.1	2.1	1.4	1.4	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)