

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219623

Luminaire Tested: **LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4322.3 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	34879	34879	34879
5°	95733	32134	13113
10°	209785	26297	4997
15°	320446	20023	5862
20°	371270	14896	9109
25°	405004	12247	14699
30°	452265	11107	15009
35°	460153	7621	10291
40°	468240	3614	5210
45°	468992	1498	2271
50°	396497	656	697
55°	127671	450	113
60°	25351	517	0
65°	2588	611	0
70°	277	856	0
75°	0	1131	0
80°	0	1835	174
85°	0	3656	346

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.0	2.5
10°-20°	568.7	13.2
20°-30°	1088.9	25.2
30°-40°	1282.9	29.7
40°-50°	1007.7	23.3
50°-60°	245.6	5.7
60°-70°	10.5	0.2
70°-80°	4.0	0.1
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1767.6	40.9
0°-40°	3050.6	70.6
0°-60°	4303.9	99.6
0°-90°	4322.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4322.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	810	810	810	810	810	
5°	2215	1603	744	389	303	293
15°	7189	3692	449	128	132	2007
25°	8525	4490	258	270	309	3974
35°	8755	2838	145	187	196	5490
45°	7702	877	25	34	37	5787
55°	1701	32	6	4	2	2024
65°	25	4	6	4	0	67
75°	0	4	7	4	0	0
85°	0	4	7	4	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1
2.5°	1388.5	1385.5	1365.3	1384.0	1327.2	1325.0	1299.6	1288.4	1255.5	1224.1	1179.3
5°	2215.0	2166.4	2126.8	2128.4	2019.3	1999.0	1942.3	1884.7	1796.5	1714.3	1603.0
7.5°	3376.3	3318.7	3235.0	3200.0	2991.5	2930.1	2812.8	2659.7	2467.6	2276.4	2070.0
10°	4798.4	4807.4	4699.0	4598.9	4283.4	4159.5	3969.7	3667.8	3303.9	2944.4	2578.9
12.5°	6229.5	6223.6	6094.3	5942.6	5553.9	5379.1	5126.5	4749.9	4267.8	3710.3	3138.7
15°	7189.0	7231.6	7177.0	7056.0	6724.1	6523.9	6239.2	5728.0	5140.6	4463.6	3692.4
17.5°	7791.4	7831.7	7812.3	7717.3	7424.4	7210.7	6973.0	6554.6	5875.3	5024.1	4128.9
20°	8103.0	8166.5	8157.4	8054.4	7833.2	7656.1	7393.8	7006.0	6417.8	5413.4	4411.3
22.5°	8310.6	8359.3	8372.7	8256.1	8027.4	7859.3	7667.3	7274.2	6721.2	5651.2	4523.4
25°	8525.2	8611.2	8526.6	8383.2	8173.3	8011.8	7807.1	7430.4	6866.2	5748.3	4489.8
27.5°	8788.2	8829.4	8638.0	8507.3	8274.1	8099.2	7881.8	7520.9	6891.7	5670.5	4297.8
30°	9096.9	8926.5	8792.7	8533.4	8268.9	8098.5	7877.3	7464.1	6757.8	5412.7	3925.5
32.5°	9046.1	8889.8	8738.2	8463.9	8202.4	8033.5	7786.9	7275.0	6441.8	4981.5	3412.1
35°	8754.6	8788.2	8624.5	8397.4	8101.5	7927.3	7658.4	7006.0	5905.2	4386.6	2838.2
37.5°	8508.7	8582.7	8475.9	8265.9	7965.5	7730.1	7366.8	6573.9	5204.9	3631.9	2294.2
40°	8330.9	8354.7	8297.2	8061.9	7700.9	7360.9	6941.0	5798.3	4354.5	2851.0	1810.6
42.5°	8055.1	8118.7	8017.0	7760.0	7212.9	6828.0	6219.7	4902.2	3382.3	2177.7	1363.1
45°	7702.3	7763.0	7637.3	7209.9	6449.1	5884.9	5142.9	3822.4	2501.9	1605.2	877.3
47.5°	7127.0	7164.4	6921.5	6330.4	5224.3	4693.1	3932.2	2664.9	1611.9	897.5	426.7
50°	5919.4	5901.5	5400.7	4673.6	3494.3	2936.9	2340.5	1444.6	724.2	425.2	266.9
52.5°	3814.9	3773.8	3278.4	2617.1	1769.6	1350.3	1014.8	623.3	377.3	237.6	105.4
55°	1700.8	1685.2	1379.5	1071.6	724.2	623.3	476.0	305.7	201.0	83.0	32.1
57.5°	630.8	616.5	543.3	455.8	349.8	290.8	230.9	146.4	51.6	27.7	17.2
60°	294.4	293.7	258.5	213.0	148.0	112.1	65.0	34.3	21.7	15.0	9.8
62.5°	94.1	91.9	64.3	47.1	33.7	29.1	23.2	17.2	11.2	8.2	6.0
65°	25.4	25.4	23.2	19.3	15.7	13.4	11.2	8.2	5.2	4.5	3.7
67.5°	9.8	9.8	8.9	8.2	6.0	5.2	4.5	3.7	3.0	3.7	3.7
70°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.0	3.0	3.7
72.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	3.7
75°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	3.7
77.5°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	3.7
80°	0.0	0.0	0.7	0.7	1.5	1.5	2.2	2.2	3.0	3.7	3.7
82.5°	0.0	0.0	0.7	1.5	1.5	1.5	2.2	3.0	3.0	3.7	4.5
85°	0.0	0.0	0.7	1.5	1.5	2.2	2.2	3.0	3.0	3.7	4.5
87.5°	0.0	0.0	0.7	1.5	1.5	2.2	2.2	3.0	3.0	3.7	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1
2.5°	1146.4	1097.1	1029.1	989.5	979.7	958.9	922.2	867.6	822.8	779.4	754.0
5°	1508.7	1392.2	1261.4	1169.5	1132.1	1082.1	993.2	901.3	816.8	743.5	686.1
7.5°	1892.9	1700.8	1489.4	1319.0	1257.7	1178.4	1033.4	896.8	780.9	679.3	602.3
10°	2274.8	1965.4	1678.5	1431.8	1331.6	1224.1	1032.7	855.6	719.6	601.5	516.4
12.5°	2656.7	2212.0	1817.4	1499.8	1369.8	1233.8	1002.1	792.9	642.0	521.6	440.1
15°	3009.4	2408.5	1911.6	1523.1	1366.1	1205.4	940.2	716.6	560.5	449.2	373.7
17.5°	3272.5	2511.7	1933.3	1487.8	1307.1	1129.2	845.2	627.0	482.8	384.9	307.9
20°	3401.7	2528.0	1881.7	1387.7	1205.4	1020.9	741.3	541.0	416.2	325.1	260.1
22.5°	3401.7	2450.4	1769.6	1262.2	1078.4	896.1	641.2	470.1	364.0	283.2	228.7
25°	3272.5	2295.7	1619.4	1117.3	938.6	772.7	554.4	417.0	323.5	257.8	212.3
27.5°	3021.3	2082.0	1426.6	955.9	801.1	662.9	485.8	368.4	293.0	232.3	233.2
30°	2676.0	1819.7	1205.4	785.4	659.9	544.9	408.8	308.7	234.7	223.4	230.2
32.5°	2277.0	1505.8	955.0	609.0	511.2	429.0	310.9	218.2	186.9	188.2	195.8
35°	1867.5	1185.2	719.0	451.4	380.3	310.9	204.0	143.4	142.0	145.0	150.2
37.5°	1474.4	887.0	520.1	330.3	255.6	191.3	109.8	98.7	98.7	101.7	104.6
40°	1104.5	629.2	358.0	195.8	124.1	87.4	69.5	64.3	63.5	64.3	68.0
42.5°	758.5	398.3	213.0	78.4	59.8	50.9	44.1	40.4	39.6	40.4	42.6
45°	426.0	245.1	83.0	41.9	35.9	32.1	27.7	25.4	24.6	24.6	26.1
47.5°	266.9	97.1	37.3	26.1	22.4	20.9	18.0	16.4	15.7	15.7	16.4
50°	102.3	38.1	23.2	17.2	15.0	13.4	12.0	10.4	9.8	9.8	10.4
52.5°	35.2	22.4	15.0	11.2	9.8	8.9	7.4	6.8	6.8	6.8	6.8
55°	19.3	13.4	8.9	6.8	6.0	6.0	6.0	6.0	6.0	6.0	6.0
57.5°	12.0	8.2	6.0	5.2	5.2	5.2	5.2	5.2	5.2	6.0	6.0
60°	6.8	5.2	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0
62.5°	4.5	4.5	4.5	4.5	4.5	4.5	5.2	5.2	6.0	6.0	6.0
65°	3.7	3.7	3.7	4.5	4.5	4.5	5.2	5.2	6.0	6.0	6.0
67.5°	3.7	3.7	4.5	4.5	4.5	5.2	5.2	6.0	6.0	6.0	6.0
70°	3.7	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0	6.8	6.8
72.5°	3.7	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8
75°	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.8	6.8	6.8	6.8
77.5°	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.8	6.8	6.8	6.8
80°	4.5	4.5	5.2	5.2	6.0	6.0	6.8	6.8	6.8	7.4	7.4
82.5°	4.5	4.5	5.2	6.0	6.0	6.0	6.8	6.8	7.4	7.4	7.4
85°	4.5	5.2	5.2	6.0	6.0	6.0	6.8	6.8	7.4	7.4	7.4
87.5°	4.5	5.2	5.2	6.0	6.0	6.0	6.8	6.8	7.4	7.4	7.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1
2.5°	720.4	689.0	657.6	634.4	623.3	612.0	587.4	555.3	541.8	522.3	511.2
5°	627.7	574.7	532.9	505.1	488.8	467.1	438.7	407.3	389.3	369.2	355.8
7.5°	532.1	470.1	429.7	404.2	387.9	361.0	325.1	287.8	266.0	243.7	228.0
10°	448.3	389.3	343.8	314.7	293.7	262.3	226.4	200.3	181.7	162.1	146.4
12.5°	374.4	310.9	262.3	237.6	223.4	193.5	163.7	134.5	123.2	119.6	119.6
15°	303.4	245.9	204.8	183.9	168.9	136.8	130.8	129.3	128.5	127.8	129.3
17.5°	247.3	198.8	155.4	145.0	143.4	142.8	143.4	143.4	144.2	146.4	150.2
20°	207.8	163.0	160.0	160.7	160.7	163.7	167.3	170.4	173.4	177.1	183.9
22.5°	184.6	183.9	189.1	189.8	193.5	198.0	204.8	209.2	216.7	220.4	230.2
25°	213.0	218.2	228.0	230.9	236.9	244.3	254.9	260.8	269.8	274.2	285.4
27.5°	241.4	249.6	261.5	265.3	270.5	282.5	290.0	295.2	299.7	302.7	309.4
30°	239.1	246.7	258.5	259.3	266.9	275.0	279.4	284.0	286.9	286.2	290.0
32.5°	202.5	209.2	220.4	220.4	228.7	235.4	237.6	241.4	241.4	241.4	242.9
35°	155.4	160.0	167.3	169.7	176.3	180.9	182.3	186.9	186.9	185.3	185.3
37.5°	107.6	113.7	118.9	120.3	124.8	127.8	131.5	132.3	130.8	131.5	131.5
40°	70.2	73.9	77.8	78.4	82.2	84.4	88.2	88.2	88.9	88.2	89.8
42.5°	43.3	46.3	48.7	50.0	51.6	53.0	55.2	56.1	56.8	56.1	57.6
45°	26.9	28.4	30.0	30.7	31.3	32.1	34.3	34.3	34.3	34.3	35.2
47.5°	16.4	17.2	18.0	18.0	18.7	19.3	20.2	20.2	20.2	20.2	20.9
50°	9.8	10.4	10.4	10.4	11.2	11.2	12.0	12.0	12.0	11.2	12.0
52.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.0	6.8
55°	6.0	6.0	5.2	5.2	5.2	5.2	5.2	4.5	3.7	3.7	3.0
57.5°	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.7	3.0	2.2
60°	5.2	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	3.0	2.2
62.5°	6.0	5.2	5.2	5.2	5.2	4.5	4.5	3.7	3.0	3.0	2.2
65°	6.0	6.0	5.2	5.2	5.2	4.5	4.5	3.7	3.7	3.0	2.2
67.5°	6.0	6.0	6.0	5.2	6.0	5.2	4.5	4.5	3.7	3.0	3.0
70°	6.8	6.0	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.0	3.0
72.5°	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.7	3.0
75°	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.5	4.5	3.7	3.0
77.5°	6.8	6.8	6.8	6.0	6.0	6.0	5.2	5.2	4.5	3.7	3.0
80°	6.8	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.5	3.7	3.0
82.5°	7.4	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.5	3.7	3.7
85°	7.4	7.4	6.8	6.8	6.8	6.0	6.0	5.2	4.5	4.5	3.7
87.5°	7.4	6.8	6.8	6.8	6.8	6.0	6.0	5.2	4.5	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219623

CATALOG NUMBER: LDSQA6A40950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	810.1	810.1	810.1	810.1	810.1	810.1	810.1	810.1
2.5°	499.9	494.0	494.0	483.5	482.0	473.8	480.5	476.0
5°	340.8	331.0	328.0	317.6	313.9	304.1	307.1	303.4
7.5°	214.4	204.8	201.8	194.3	189.8	182.3	183.0	180.9
10°	130.8	121.8	119.6	117.3	115.1	114.3	115.1	114.3
12.5°	118.9	118.0	116.6	117.3	115.9	116.6	117.3	116.6
15°	129.3	130.8	129.3	130.0	129.3	130.8	131.5	131.5
17.5°	151.7	154.8	153.2	155.4	154.8	158.4	158.4	158.4
20°	186.1	191.3	189.8	192.8	192.8	197.3	197.3	198.8
22.5°	233.9	240.7	239.9	246.7	245.1	250.3	250.3	251.9
25°	291.4	298.2	298.9	303.4	302.7	307.9	307.9	309.4
27.5°	315.3	319.1	318.3	320.6	321.4	324.3	326.6	325.1
30°	296.0	298.9	298.2	299.7	299.7	301.9	304.1	301.9
32.5°	248.9	251.1	251.1	254.1	251.9	252.6	256.3	254.1
35°	190.6	192.1	190.6	192.1	192.8	192.8	196.5	195.8
37.5°	136.0	136.8	136.8	139.0	136.8	136.8	140.4	141.2
40°	91.1	91.9	91.1	94.1	92.7	92.7	95.0	92.7
42.5°	58.2	59.1	58.2	60.5	59.1	60.5	61.3	62.0
45°	35.9	35.9	35.2	36.6	35.9	36.6	37.3	37.3
47.5°	20.9	20.9	20.2	21.7	20.9	20.9	20.9	21.7
50°	11.2	11.2	11.2	12.0	11.2	11.2	11.2	10.4
52.5°	6.0	6.0	5.2	6.0	5.2	5.2	5.2	5.2
55°	3.0	2.2	2.2	2.2	1.5	1.5	1.5	1.5
57.5°	2.2	1.5	1.5	0.7	0.7	0.7	0.0	0.0
60°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
62.5°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
65°	1.5	1.5	0.7	0.7	0.0	0.0	0.0	0.0
67.5°	2.2	1.5	1.5	0.7	0.7	0.0	0.0	0.0
70°	2.2	1.5	1.5	0.7	0.7	0.0	0.0	0.0
72.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
75°	2.2	2.2	1.5	1.5	0.7	0.7	0.0	0.0
77.5°	3.0	2.2	1.5	1.5	0.7	0.7	0.0	0.0
80°	3.0	2.2	1.5	1.5	1.5	0.7	0.7	0.7
82.5°	3.0	2.2	2.2	1.5	1.5	0.7	0.7	0.7
85°	3.0	2.2	2.2	1.5	1.5	0.7	0.7	0.7
87.5°	3.0	2.2	2.2	1.5	1.5	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)