

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212590

Luminaire Tested: **LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3781.6 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 57.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45962	45962	45962
5°	89068	43804	14773
10°	151323	38329	6632
15°	233183	30574	10551
20°	337557	19895	18350
25°	495252	19202	23597
30°	575845	18191	18082
35°	582852	9640	9556
40°	482566	3636	4013
45°	364456	1236	1467
50°	249357	449	449
55°	34688	398	53
60°	904	388	0
65°	224	540	0
70°	88	667	0
75°	0	882	0
80°	0	1488	174
85°	0	2964	0

TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.0	3.0
10°-20°	473.4	12.5
20°-30°	1080.0	28.6
30°-40°	1249.8	33.0
40°-50°	753.8	19.9
50°-60°	102.4	2.7
60°-70°	3.3	0.1
70°-80°	3.6	0.1
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1665.4	44.0
0°-40°	2915.3	77.1
0°-60°	3771.4	99.7
0°-90°	3781.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3781.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1068	1068	1068	1068	1068	
5°	2061	1687	1014	554	342	240
15°	5231	2941	686	211	237	1549
25°	10425	3484	404	486	497	4718
35°	11089	2656	183	187	182	6683
45°	5986	724	20	25	24	4680
55°	462	5	5	4	1	906
65°	2	3	5	3	0	3
75°	0	4	5	4	0	0
85°	0	4	6	4	0	0
90°	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	1543.9	1529.6	1535.7	1519.8	1480.1	1471.8	1471.0	1460.5	1426.7	1400.4	1368.8
5°	2060.8	2060.0	2063.8	2030.0	1960.1	1938.4	1927.8	1902.3	1820.4	1757.3	1687.4
7.5°	2706.1	2701.6	2697.1	2635.5	2525.8	2483.8	2456.8	2364.4	2251.7	2139.7	2015.0
10°	3461.2	3458.9	3441.7	3333.5	3157.7	3080.3	3027.6	2881.2	2700.2	2540.9	2329.0
12.5°	4337.9	4317.6	4286.8	4128.3	3887.2	3803.0	3687.4	3455.2	3177.1	2933.0	2637.1
15°	5231.3	5201.9	5147.0	4943.5	4644.5	4501.0	4357.5	4051.8	3674.5	3319.9	2940.6
17.5°	6105.0	6072.6	5944.2	5598.6	5306.3	5131.3	4972.0	4552.1	4108.8	3652.8	3172.0
20°	7367.2	7249.9	7026.1	6481.4	5938.2	5622.7	5436.4	4992.3	4443.9	3912.8	3336.4
22.5°	9053.1	8793.1	8316.0	7431.0	6655.0	6199.6	5894.6	5304.1	4685.1	4082.6	3437.9
25°	10424.9	10306.9	9764.5	8505.3	7294.3	6757.9	6333.4	5552.0	4860.9	4196.0	3484.5
27.5°	11309.2	11279.9	10660.1	9394.9	7816.4	7112.4	6638.4	5715.8	4945.7	4220.0	3462.0
30°	11582.6	11628.4	11033.5	9696.9	7967.5	7183.8	6665.5	5718.0	4880.4	4111.1	3317.7
32.5°	11562.3	11564.6	10835.1	9436.2	7721.8	6976.5	6440.1	5527.9	4639.2	3838.3	3043.5
35°	11089.0	10972.6	10147.6	8635.4	7150.1	6492.6	5993.8	5159.9	4241.7	3428.1	2656.5
37.5°	10050.1	9897.5	8935.9	7609.8	6473.1	5865.3	5462.7	4676.8	3768.4	2990.1	2256.9
40°	8585.8	8369.4	7576.1	6656.4	5732.3	5275.5	4937.5	4136.6	3262.1	2560.4	1882.0
42.5°	7120.0	7014.0	6489.6	5742.1	5109.5	4679.8	4326.7	3570.9	2775.2	2136.6	1408.0
45°	5985.5	5894.6	5542.2	5049.5	4428.9	4036.7	3696.4	2981.2	2156.2	1433.5	723.5
47.5°	5159.1	5085.4	4748.2	4230.5	3549.8	3120.9	2770.0	1954.9	1221.7	619.0	181.0
50°	3722.7	3647.5	3317.0	2717.4	2102.9	1743.8	1491.3	873.0	346.3	125.4	18.8
52.5°	1824.9	1763.3	1538.6	1151.7	773.1	555.9	406.4	163.8	39.8	13.6	9.0
55°	462.1	424.4	353.9	222.4	108.9	65.4	42.1	15.0	9.8	7.6	5.3
57.5°	26.3	25.5	23.2	17.2	12.7	11.3	9.8	7.6	5.3	4.5	3.8
60°	10.5	9.8	9.0	7.6	6.0	5.3	5.3	3.8	2.9	2.9	2.9
62.5°	4.5	4.5	4.5	3.8	2.9	2.9	2.9	2.2	2.9	2.9	2.9
65°	2.2	2.2	2.2	1.5	1.5	1.5	2.2	2.2	2.2	2.9	2.9
67.5°	1.5	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	2.9	2.9
70°	0.7	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	2.9	3.8
72.5°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.2	2.9	3.8
75°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8
77.5°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8
80°	0.0	0.7	0.7	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8
82.5°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8
85°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	2.9	2.9	3.8
87.5°	0.0	0.0	0.7	0.7	1.5	1.5	1.5	2.2	2.2	2.9	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	1328.3	1301.2	1261.4	1235.1	1209.6	1185.5	1145.7	1123.1	1082.6	1045.0	1012.8
5°	1603.3	1535.7	1453.8	1383.9	1338.8	1294.5	1214.1	1154.7	1080.4	1013.5	951.9
7.5°	1881.3	1761.7	1627.3	1512.4	1442.4	1374.1	1253.9	1157.7	1052.6	957.1	866.2
10°	2133.7	1954.1	1764.0	1599.5	1504.9	1416.2	1257.6	1130.0	994.7	876.7	762.5
12.5°	2368.0	2122.3	1874.4	1659.6	1542.4	1435.7	1241.8	1085.6	924.9	785.1	652.1
15°	2576.9	2261.4	1954.9	1694.1	1556.7	1430.5	1205.0	1023.3	842.2	685.9	517.7
17.5°	2735.5	2347.7	1990.2	1688.9	1531.2	1390.6	1142.0	945.2	754.3	565.0	374.9
20°	2831.6	2384.5	1982.6	1648.3	1476.3	1327.5	1066.8	860.2	648.4	434.2	330.5
22.5°	2872.2	2381.6	1947.4	1587.5	1408.7	1258.5	994.7	777.6	537.1	392.9	344.8
25°	2879.0	2350.8	1897.8	1520.7	1341.8	1192.3	921.8	683.7	466.6	404.2	386.2
27.5°	2827.2	2278.7	1804.6	1424.5	1247.8	1093.2	812.9	543.2	438.0	402.7	414.8
30°	2673.9	2114.1	1640.1	1255.4	1084.9	930.1	580.8	426.0	363.7	365.9	368.9
32.5°	2404.1	1840.7	1375.6	1008.2	821.9	613.0	361.3	284.7	276.5	276.5	274.9
35°	2044.2	1506.4	1079.6	637.8	408.8	294.5	187.0	187.9	184.1	183.4	182.5
37.5°	1672.4	1188.5	683.7	263.7	177.4	123.2	110.4	112.0	110.4	112.7	111.2
40°	1318.5	734.0	249.5	84.1	62.3	60.1	61.6	63.1	63.1	64.7	64.7
42.5°	766.3	243.4	65.4	33.9	33.9	32.3	33.0	34.6	35.3	36.1	35.3
45°	227.6	50.4	21.0	18.8	18.8	18.1	18.1	18.8	19.6	20.3	20.3
47.5°	36.1	14.3	12.0	10.5	10.5	10.5	10.5	10.5	11.3	11.3	12.0
50°	11.3	9.0	7.6	6.7	6.7	6.0	6.0	6.7	6.7	6.7	7.6
52.5°	6.7	5.3	5.3	4.5	5.3	5.3	4.5	5.3	5.3	5.3	6.0
55°	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.3	5.3	5.3
57.5°	3.8	3.8	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5
60°	3.8	3.8	4.5	4.5	4.5	4.5	4.5	4.5	4.5	4.5	5.3
62.5°	3.8	3.8	4.5	4.5	4.5	4.5	4.5	4.5	5.3	5.3	5.3
65°	3.8	3.8	4.5	4.5	4.5	4.5	4.5	5.3	5.3	5.3	5.3
67.5°	3.8	4.5	4.5	4.5	4.5	5.3	5.3	5.3	5.3	5.3	5.3
70°	3.8	4.5	4.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
72.5°	3.8	4.5	4.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
75°	4.5	4.5	4.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3	6.0
77.5°	4.5	4.5	5.3	5.3	5.3	5.3	5.3	5.3	6.0	6.0	6.0
80°	4.5	4.5	5.3	5.3	5.3	5.3	5.3	6.0	6.0	6.0	6.0
82.5°	4.5	4.5	5.3	5.3	5.3	5.3	5.3	6.0	6.0	6.0	6.0
85°	4.5	4.5	5.3	5.3	5.3	5.3	5.3	6.0	6.0	6.0	6.0
87.5°	4.5	4.5	5.3	5.3	5.3	5.3	5.3	6.0	6.0	6.0	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	984.9	950.4	933.9	910.6	894.1	857.3	842.2	816.7	795.7	761.1	763.3
5°	899.3	833.9	789.7	755.1	731.0	672.4	633.3	592.0	554.5	507.9	490.6
7.5°	780.6	700.2	632.6	591.3	560.5	482.4	395.9	328.3	277.2	240.4	226.1
10°	661.9	557.4	450.1	386.2	341.8	266.7	228.4	210.4	193.9	173.6	160.0
12.5°	523.7	374.9	277.2	251.7	233.6	208.9	184.1	164.5	168.3	169.1	174.3
15°	357.7	269.7	239.0	221.6	202.1	187.9	196.1	201.3	211.1	211.8	218.7
17.5°	290.8	253.2	228.4	227.6	229.2	237.4	250.2	256.9	269.7	272.7	282.5
20°	290.8	268.9	290.0	290.0	293.7	305.0	321.6	331.3	345.6	350.8	362.8
22.5°	331.3	346.3	372.6	375.6	377.1	389.2	410.2	420.0	436.5	439.6	452.3
25°	404.2	417.7	441.8	444.0	444.7	453.8	469.5	474.8	486.0	480.0	487.6
27.5°	427.5	433.5	448.5	450.1	446.3	450.1	456.1	456.1	459.8	447.8	450.1
30°	375.6	377.1	384.7	385.4	377.1	378.7	379.4	378.7	378.0	365.1	365.1
32.5°	278.7	278.7	288.5	286.3	277.2	279.4	279.4	279.4	278.7	268.2	266.7
35°	184.8	185.6	193.9	192.3	185.6	187.0	187.0	189.3	187.0	181.0	179.6
37.5°	112.7	113.4	117.2	118.0	115.6	116.5	117.2	116.5	118.0	114.9	113.4
40°	65.4	66.9	69.9	70.6	69.9	69.9	70.6	71.4	74.3	70.6	69.1
42.5°	38.4	39.1	40.6	40.6	40.6	40.6	41.3	42.1	42.8	42.1	41.3
45°	21.8	22.5	23.2	23.2	24.1	23.2	24.1	24.1	24.8	24.1	24.1
47.5°	12.7	12.7	13.6	13.6	14.3	13.6	14.3	14.3	14.3	13.6	13.6
50°	7.6	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	7.6	7.6
52.5°	6.0	6.0	6.0	6.0	6.0	5.3	5.3	5.3	5.3	4.5	4.5
55°	5.3	5.3	5.3	5.3	5.3	5.3	4.5	3.8	3.8	2.9	2.9
57.5°	4.5	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.2	2.2
60°	5.3	5.3	5.3	5.3	4.5	4.5	4.5	3.8	2.9	2.2	2.2
62.5°	5.3	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.2	2.2
65°	5.3	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.2	2.2
67.5°	5.3	5.3	5.3	5.3	5.3	4.5	4.5	3.8	2.9	2.9	2.2
70°	5.3	6.0	6.0	5.3	5.3	5.3	4.5	3.8	3.8	2.9	2.2
72.5°	5.3	6.0	6.0	5.3	5.3	5.3	4.5	3.8	3.8	2.9	2.2
75°	6.0	6.0	6.0	6.0	5.3	5.3	4.5	4.5	3.8	2.9	2.2
77.5°	6.0	6.0	6.0	6.0	5.3	5.3	4.5	4.5	3.8	2.9	2.2
80°	6.0	6.0	6.0	6.0	6.0	5.3	5.3	4.5	3.8	2.9	2.9
82.5°	6.0	6.0	6.0	6.0	6.0	5.3	5.3	4.5	3.8	2.9	2.9
85°	6.0	6.0	6.0	6.0	6.0	5.3	5.3	4.5	3.8	2.9	2.2
87.5°	6.0	6.0	6.0	6.0	5.3	5.3	4.5	4.5	3.8	2.9	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212590

CATALOG NUMBER: LDSQA6A50927D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	735.5	718.3	710.7	722.8	716.7	698.7	702.5	691.2
5°	438.7	412.4	395.9	403.4	379.4	357.7	357.7	341.8
7.5°	211.8	203.5	199.1	200.6	195.3	188.6	184.8	184.8
10°	148.8	145.7	146.6	146.6	151.0	150.2	152.5	151.7
12.5°	176.5	178.1	178.8	181.8	185.6	185.6	187.9	186.3
15°	226.1	224.7	229.2	229.9	235.9	236.7	239.7	236.7
17.5°	287.8	290.8	295.2	294.5	306.6	307.3	307.3	306.6
20°	370.4	372.6	377.1	378.7	392.9	394.5	399.7	400.5
22.5°	460.6	460.6	462.8	465.7	479.3	480.0	482.4	482.4
25°	491.4	486.9	487.6	491.4	498.9	495.8	498.1	496.7
27.5°	451.5	444.7	443.2	448.5	453.8	445.6	448.5	448.5
30°	366.6	360.6	359.1	364.4	368.2	359.1	362.1	363.7
32.5°	268.2	264.4	263.7	267.5	270.5	262.9	266.0	268.2
35°	181.0	179.6	178.1	178.8	183.4	177.4	180.3	181.8
37.5°	114.9	112.0	112.7	114.2	117.2	113.4	116.5	116.5
40°	70.6	69.1	69.1	70.6	72.1	69.1	70.6	71.4
42.5°	41.3	41.3	41.3	42.1	42.8	41.3	41.3	42.1
45°	24.1	23.2	23.2	24.1	24.8	23.2	24.1	24.1
47.5°	13.6	12.7	12.7	13.6	13.6	12.7	13.6	13.6
50°	7.6	6.7	6.7	7.6	7.6	6.7	6.7	6.7
52.5°	3.8	3.8	3.8	3.8	3.8	3.8	2.9	2.9
55°	2.2	2.2	1.5	1.5	1.5	1.5	1.5	0.7
57.5°	1.5	1.5	0.7	0.7	0.7	0.7	0.0	0.0
60°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
62.5°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
65°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
67.5°	1.5	1.5	0.7	0.7	0.7	0.0	0.0	0.0
70°	2.2	1.5	1.5	0.7	0.7	0.7	0.0	0.0
72.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
75°	2.2	1.5	1.5	1.5	0.7	0.7	0.0	0.0
77.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
80°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.7
82.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.7
85°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
87.5°	2.2	1.5	1.5	1.5	0.7	0.7	0.7	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)