

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219649

Luminaire Tested: **LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 20° SPOT, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6064.8 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73720	73720	73720
5°	142843	70246	23698
10°	242685	61479	10641
15°	373962	49036	16916
20°	541359	31908	29425
25°	794269	30794	37834
30°	923527	29174	28990
35°	934760	15453	15327
40°	773917	5823	6435
45°	584506	1985	2344
50°	399900	723	723
55°	55631	631	90
60°	1447	620	0
65°	367	856	0
70°	151	1057	0
75°	0	1397	0
80°	0	2405	298
85°	0	4792	0

TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.6	3.0
10°-20°	759.3	12.5
20°-30°	1732.1	28.6
30°-40°	2004.4	33.1
40°-50°	1208.8	19.9
50°-60°	164.2	2.7
60°-70°	5.3	0.1
70°-80°	5.7	0.1
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2671.0	44.0
0°-40°	4675.4	77.1
0°-60°	6048.4	99.7
0°-90°	6064.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6064.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1712	1712	1712	1712	1712	
5°	3305	2706	1625	889	548	385
15°	8390	4716	1100	339	380	2484
25°	16719	5588	648	780	796	7566
35°	17784	4261	294	300	292	10718
45°	9599	1160	33	40	38	7506
55°	741	8	8	6	1	1453
65°	4	5	8	5	0	5
75°	0	6	8	6	0	0
85°	0	6	10	6	0	0
90°	0	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2
2.5°	2476.0	2453.2	2462.8	2437.6	2373.6	2360.4	2359.1	2342.3	2288.1	2245.9	2195.2
5°	3305.0	3303.8	3309.8	3255.6	3143.6	3108.7	3091.7	3050.7	2919.5	2818.2	2706.2
7.5°	4339.9	4332.8	4325.7	4226.7	4050.9	3983.3	3940.0	3791.8	3611.1	3431.5	3231.6
10°	5550.9	5547.3	5519.6	5346.0	5064.2	4940.1	4855.7	4620.7	4330.5	4074.9	3735.2
12.5°	6957.1	6924.4	6875.1	6621.0	6234.1	6099.2	5913.6	5541.3	5095.5	4703.9	4229.3
15°	8389.6	8342.7	8254.7	7928.1	7448.6	7218.5	6988.4	6498.0	5893.1	5324.4	4716.0
17.5°	9791.0	9739.2	9533.2	8978.9	8510.2	8229.4	7974.0	7300.5	6589.6	5858.2	5087.1
20°	11815.2	11627.2	11268.2	10394.6	9523.5	9017.4	8718.5	8006.5	7126.9	6275.2	5351.0
22.5°	14518.9	14102.1	13337.1	11917.6	10673.0	9942.7	9453.6	8506.6	7513.8	6547.4	5513.6
25°	16719.1	16530.0	15660.0	13640.5	11698.3	10837.9	10157.3	8904.2	7795.6	6729.3	5588.3
27.5°	18137.3	18090.3	17096.2	15067.2	12535.6	11406.7	10646.5	9166.8	7931.9	6767.9	5552.1
30°	18575.9	18649.4	17695.1	15551.5	12778.0	11521.1	10689.8	9170.5	7827.0	6593.2	5320.7
32.5°	18543.3	18546.9	17376.9	15133.6	12383.9	11188.7	10328.3	8865.6	7440.2	6155.9	4881.0
35°	17784.2	17597.4	16274.5	13849.1	11466.9	10412.8	9612.6	8275.3	6802.7	5498.0	4260.6
37.5°	16117.8	15873.3	14331.0	12204.3	10381.4	9406.7	8760.8	7500.5	6043.8	4795.5	3619.5
40°	13769.5	13422.4	12150.1	10675.4	9193.4	8460.7	7918.6	6634.2	5231.7	4106.3	3018.3
42.5°	11418.7	11248.8	10407.8	9209.0	8194.5	7505.4	6939.0	5726.9	4450.8	3426.8	2257.9
45°	9599.4	9453.6	8888.5	8098.1	7102.9	6473.8	5928.1	4781.1	3458.1	2298.9	1160.3
47.5°	8274.0	8156.0	7615.0	6784.8	5693.2	5005.2	4442.4	3135.2	1959.2	992.9	290.5
50°	5970.2	5849.8	5319.6	4358.1	3372.5	2796.6	2391.7	1400.0	555.5	201.2	30.1
52.5°	2926.7	2827.9	2467.6	1847.0	1239.8	891.6	651.9	262.6	63.8	21.6	14.5
55°	741.1	680.8	567.5	356.6	174.6	104.8	67.5	24.0	15.6	12.1	8.4
57.5°	42.1	41.0	37.3	27.7	20.5	18.1	15.6	12.1	8.4	7.2	6.0
60°	16.8	15.6	14.5	12.1	9.7	8.4	8.4	6.0	4.8	4.8	4.8
62.5°	7.2	7.2	7.2	6.0	4.8	4.8	4.8	3.6	4.8	4.8	4.8
65°	3.6	3.6	3.6	2.4	2.4	2.4	3.6	3.6	3.6	4.8	4.8
67.5°	2.4	1.2	1.2	1.2	2.4	2.4	2.4	3.6	3.6	4.8	4.8
70°	1.2	1.2	1.2	1.2	2.4	2.4	2.4	3.6	3.6	4.8	6.0
72.5°	0.0	1.2	1.2	1.2	2.4	2.4	2.4	3.6	3.6	4.8	6.0
75°	0.0	1.2	1.2	1.2	2.4	2.4	2.4	3.6	4.8	4.8	6.0
77.5°	0.0	1.2	1.2	1.2	2.4	2.4	2.4	3.6	4.8	4.8	6.0
80°	0.0	1.2	1.2	1.2	2.4	2.4	2.4	3.6	4.8	4.8	6.0
82.5°	0.0	0.0	1.2	1.2	2.4	2.4	2.4	3.6	4.8	4.8	6.0
85°	0.0	0.0	1.2	1.2	2.4	2.4	2.4	3.6	4.8	4.8	6.0
87.5°	0.0	0.0	1.2	1.2	2.4	2.4	2.4	3.6	3.6	4.8	6.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2
2.5°	2130.2	2087.0	2023.0	1980.9	1939.8	1901.3	1837.5	1801.3	1736.2	1676.1	1624.2
5°	2571.3	2462.8	2331.5	2219.5	2147.1	2075.9	1947.1	1851.8	1732.6	1625.3	1526.6
7.5°	3017.0	2825.5	2609.8	2425.5	2313.5	2203.8	2010.9	1856.8	1688.0	1535.0	1389.2
10°	3421.8	3133.9	2829.1	2565.3	2413.3	2271.3	2017.0	1812.2	1595.3	1406.2	1222.9
12.5°	3797.9	3403.8	3006.2	2661.7	2473.6	2302.5	1991.7	1741.2	1483.2	1259.1	1045.8
15°	4132.9	3626.7	3135.2	2717.0	2496.5	2294.0	1932.6	1641.1	1350.6	1100.1	830.1
17.5°	4387.0	3765.2	3191.8	2708.6	2455.5	2230.3	1831.4	1515.7	1209.7	906.0	601.2
20°	4541.2	3824.3	3179.7	2643.5	2367.7	2129.1	1710.9	1379.6	1039.8	696.4	530.2
22.5°	4606.4	3819.5	3123.1	2546.0	2259.2	2018.2	1595.3	1247.1	861.5	630.2	553.1
25°	4617.2	3770.2	3043.6	2438.7	2152.0	1912.1	1478.4	1096.5	748.3	648.2	619.2
27.5°	4534.0	3654.4	2894.2	2284.5	2001.4	1753.1	1303.7	871.2	702.4	645.8	665.1
30°	4288.2	3390.6	2630.3	2013.4	1739.8	1491.7	931.3	683.2	583.1	586.8	591.6
32.5°	3855.6	2951.9	2206.2	1616.9	1318.2	983.2	579.5	456.7	443.5	443.5	441.0
35°	3278.5	2415.7	1731.4	1022.9	655.5	472.3	300.0	301.3	295.3	294.0	292.9
37.5°	2682.2	1906.1	1096.5	423.0	284.4	197.6	177.0	179.6	177.0	180.8	178.4
40°	2114.6	1177.3	400.1	134.9	100.0	96.4	98.8	101.2	101.2	103.6	103.6
42.5°	1229.0	390.3	104.8	54.3	54.3	51.9	52.9	55.3	56.6	57.9	56.6
45°	365.0	80.8	33.7	30.1	30.1	28.9	28.9	30.1	31.3	32.6	32.6
47.5°	57.9	22.9	19.2	16.8	16.8	16.8	16.8	16.8	18.1	18.1	19.2
50°	18.1	14.5	12.1	10.8	10.8	9.7	9.7	10.8	10.8	10.8	12.1
52.5°	10.8	8.4	8.4	7.2	8.4	8.4	7.2	8.4	8.4	8.4	9.7
55°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	8.4	8.4	8.4
57.5°	6.0	6.0	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
60°	6.0	6.0	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	8.4
62.5°	6.0	6.0	7.2	7.2	7.2	7.2	7.2	7.2	8.4	8.4	8.4
65°	6.0	6.0	7.2	7.2	7.2	7.2	7.2	8.4	8.4	8.4	8.4
67.5°	6.0	7.2	7.2	7.2	7.2	8.4	8.4	8.4	8.4	8.4	8.4
70°	6.0	7.2	7.2	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
72.5°	6.0	7.2	7.2	8.4	8.4	8.4	8.4	8.4	8.4	8.4	8.4
75°	7.2	7.2	7.2	8.4	8.4	8.4	8.4	8.4	8.4	8.4	9.7
77.5°	7.2	7.2	8.4	8.4	8.4	8.4	8.4	8.4	9.7	9.7	9.7
80°	7.2	7.2	8.4	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7
82.5°	7.2	7.2	8.4	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7
85°	7.2	7.2	8.4	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7
87.5°	7.2	7.2	8.4	8.4	8.4	8.4	8.4	9.7	9.7	9.7	9.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2
2.5°	1579.7	1524.2	1497.6	1460.4	1433.8	1374.8	1350.6	1309.8	1276.0	1220.5	1224.2
5°	1442.3	1337.4	1266.3	1211.0	1172.3	1078.3	1015.8	949.4	889.2	814.5	786.8
7.5°	1251.8	1123.0	1014.5	948.2	898.9	773.6	635.0	526.6	444.6	385.5	362.6
10°	1061.4	894.1	721.7	619.2	548.3	427.8	366.3	337.4	310.9	278.4	256.6
12.5°	839.9	601.2	444.6	403.7	374.7	335.0	295.3	263.8	269.9	271.0	279.4
15°	573.6	432.5	383.1	355.5	324.2	301.3	314.5	322.9	338.6	339.8	350.6
17.5°	466.2	406.1	366.3	365.0	367.4	380.7	401.1	412.2	432.5	437.4	453.0
20°	466.2	431.4	465.1	465.1	471.1	489.1	515.7	531.3	554.2	562.6	582.0
22.5°	531.3	555.5	597.6	602.4	604.9	624.2	657.9	673.5	700.0	704.8	725.3
25°	648.2	670.0	708.4	712.1	713.2	727.7	753.1	761.5	779.6	769.9	782.0
27.5°	685.6	695.2	719.3	721.7	715.6	721.7	731.4	731.4	737.5	718.1	721.7
30°	602.4	604.9	616.8	618.2	604.9	607.3	608.4	607.3	606.0	585.5	585.5
32.5°	447.0	447.0	462.7	459.1	444.6	448.2	448.2	448.2	447.0	430.1	427.8
35°	296.4	297.6	310.9	308.5	297.6	300.0	300.0	303.7	300.0	290.5	287.9
37.5°	180.8	182.0	188.0	189.2	185.6	186.8	188.0	186.8	189.2	184.4	182.0
40°	104.8	107.2	112.0	113.3	112.0	112.0	113.3	114.5	119.3	113.3	110.9
42.5°	61.4	62.7	65.1	65.1	65.1	65.1	66.4	67.5	68.7	67.5	66.4
45°	34.9	36.1	37.3	37.3	38.5	37.3	38.5	38.5	39.7	38.5	38.5
47.5°	20.5	20.5	21.6	21.6	22.9	21.6	22.9	22.9	22.9	21.6	21.6
50°	12.1	13.2	13.2	13.2	13.2	13.2	13.2	13.2	13.2	12.1	12.1
52.5°	9.7	9.7	9.7	9.7	9.7	8.4	8.4	8.4	8.4	7.2	7.2
55°	8.4	8.4	8.4	8.4	8.4	8.4	7.2	6.0	6.0	4.8	4.8
57.5°	7.2	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	3.6	3.6
60°	8.4	8.4	8.4	8.4	7.2	7.2	7.2	6.0	4.8	3.6	3.6
62.5°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	3.6	3.6
65°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	3.6	3.6
67.5°	8.4	8.4	8.4	8.4	8.4	7.2	7.2	6.0	4.8	4.8	3.6
70°	8.4	9.7	9.7	8.4	8.4	8.4	7.2	6.0	6.0	4.8	3.6
72.5°	8.4	9.7	9.7	8.4	8.4	8.4	7.2	6.0	6.0	4.8	3.6
75°	9.7	9.7	9.7	9.7	8.4	8.4	7.2	7.2	6.0	4.8	3.6
77.5°	9.7	9.7	9.7	9.7	8.4	8.4	7.2	7.2	6.0	4.8	3.6
80°	9.7	9.7	9.7	9.7	9.7	8.4	8.4	7.2	6.0	4.8	4.8
82.5°	9.7	9.7	9.7	9.7	9.7	8.4	8.4	7.2	6.0	4.8	4.8
85°	9.7	9.7	9.7	9.7	9.7	8.4	8.4	7.2	6.0	4.8	3.6
87.5°	9.7	9.7	9.7	9.7	8.4	8.4	7.2	7.2	6.0	4.8	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219649

CATALOG NUMBER: LDSQA6A65950D010TE LARH20SP 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2	1712.2
2.5°	1179.7	1151.9	1139.8	1159.1	1149.4	1120.6	1126.5	1108.5
5°	703.7	661.5	635.0	647.1	608.4	573.6	573.6	548.3
7.5°	339.8	326.6	319.3	321.7	313.2	302.4	296.4	296.4
10°	238.6	233.8	234.9	234.9	242.2	241.0	244.6	243.4
12.5°	283.1	285.5	286.8	291.6	297.6	297.6	301.3	298.9
15°	362.6	360.3	367.4	368.7	378.2	379.5	384.3	379.5
17.5°	461.4	466.2	473.5	472.3	491.6	492.8	492.8	491.6
20°	593.9	597.6	604.9	607.3	630.2	632.6	641.1	642.2
22.5°	738.5	738.5	742.2	747.0	768.8	769.9	773.6	773.6
25°	788.0	780.7	782.0	788.0	800.1	795.2	798.8	796.4
27.5°	724.0	713.2	710.8	719.3	727.7	714.5	719.3	719.3
30°	588.0	578.3	576.0	584.4	590.4	576.0	580.7	583.1
32.5°	430.1	424.1	423.0	429.0	433.8	421.7	426.5	430.1
35°	290.5	287.9	285.5	286.8	294.0	284.4	289.2	291.6
37.5°	184.4	179.6	180.8	183.1	188.0	182.0	186.8	186.8
40°	113.3	110.9	110.9	113.3	115.6	110.9	113.3	114.5
42.5°	66.4	66.4	66.4	67.5	68.7	66.4	66.4	67.5
45°	38.5	37.3	37.3	38.5	39.7	37.3	38.5	38.5
47.5°	21.6	20.5	20.5	21.6	21.6	20.5	21.6	21.6
50°	12.1	10.8	10.8	12.1	12.1	10.8	10.8	10.8
52.5°	6.0	6.0	6.0	6.0	6.0	6.0	4.8	4.8
55°	3.6	3.6	2.4	2.4	2.4	2.4	2.4	1.2
57.5°	2.4	2.4	1.2	1.2	1.2	1.2	0.0	0.0
60°	2.4	2.4	1.2	1.2	1.2	0.0	0.0	0.0
62.5°	2.4	2.4	1.2	1.2	1.2	0.0	0.0	0.0
65°	2.4	2.4	1.2	1.2	1.2	0.0	0.0	0.0
67.5°	2.4	2.4	1.2	1.2	1.2	0.0	0.0	0.0
70°	3.6	2.4	2.4	1.2	1.2	1.2	0.0	0.0
72.5°	3.6	2.4	2.4	2.4	1.2	1.2	0.0	0.0
75°	3.6	2.4	2.4	2.4	1.2	1.2	0.0	0.0
77.5°	3.6	2.4	2.4	2.4	1.2	1.2	1.2	0.0
80°	3.6	2.4	2.4	2.4	1.2	1.2	1.2	1.2
82.5°	3.6	2.4	2.4	2.4	1.2	1.2	1.2	1.2
85°	3.6	2.4	2.4	2.4	1.2	1.2	1.2	0.0
87.5°	3.6	2.4	2.4	2.4	1.2	1.2	1.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)