

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1212706

Luminaire Tested: **LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1212706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 30° NARROW FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5806.2 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	45092	45092	45092
5°	115670	41020	12776
10°	225481	31526	6138
15°	404763	21414	8233
20°	600947	16257	13594
25°	683070	13387	21321
30°	740456	14646	20051
35°	779941	9493	12431
40°	796809	4215	6048
45°	719670	1607	2247
50°	473735	636	636
55°	129728	555	0
60°	25920	637	0
65°	1824	866	0
70°	264	1070	0
75°	0	1580	0
80°	0	2356	248
85°	0	4693	494



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	2.2
10°-20°	681.6	11.7
20°-30°	1544.8	26.6
30°-40°	1854.3	31.9
40°-50°	1306.8	22.5
50°-60°	269.6	4.6
60°-70°	9.6	0.2
70°-80°	5.7	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2354.6	40.6
0°-40°	4208.9	72.5
0°-60°	5785.4	99.6
0°-90°	5806.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5806.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1047	1047	1047	1047	1047	
5°	2676	1950	949	395	296	329
15°	9081	3995	480	171	185	2695
25°	14378	4832	282	395	449	6636
35°	14839	3384	181	236	236	9225
45°	11819	1160	26	36	37	8693
55°	1728	23	7	5	0	2277
65°	18	5	8	5	0	53
75°	0	5	10	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3
2.5°	1785.3	1731.5	1752.5	1690.3	1676.5	1664.9	1676.5	1609.0	1570.9	1522.4	1483.3
5°	2676.3	2612.0	2626.8	2518.0	2468.3	2434.6	2428.3	2288.9	2184.4	2069.3	1950.0
7.5°	3725.8	3664.6	3656.1	3487.1	3384.8	3326.7	3302.4	3102.8	2922.4	2717.5	2493.7
10°	5157.4	5018.0	4974.7	4729.8	4534.5	4410.9	4258.9	3940.0	3623.4	3314.0	3029.0
12.5°	6823.3	6747.4	6639.6	6207.9	5865.7	5690.5	5463.5	4965.2	4485.9	3974.9	3497.8
15°	9080.6	8810.4	8626.5	8002.7	7451.6	7181.2	6849.7	6087.5	5363.3	4716.0	3995.0
17.5°	11286.1	11144.6	10857.5	10047.7	9198.8	8772.3	8278.1	7242.6	6219.5	5298.8	4418.3
20°	13115.7	12982.7	12655.4	11892.0	10950.3	10321.1	9699.3	8278.1	6941.6	5763.4	4701.3
22.5°	13991.9	13907.5	13640.4	12986.9	12184.5	11585.9	10917.5	9159.8	7475.8	6067.5	4830.2
25°	14378.4	14339.3	14167.3	13652.0	12896.1	12388.2	11756.9	9783.7	7808.3	6208.9	4832.2
27.5°	14770.1	14777.5	14397.4	13989.8	13273.0	12785.2	12177.1	10060.3	7868.5	6129.8	4673.9
30°	14893.6	14815.4	14647.6	14062.8	13381.7	12863.4	12210.9	9932.5	7621.5	5804.5	4358.1
32.5°	14842.9	14812.3	14627.5	14008.8	13197.0	12625.9	11884.6	9425.8	7133.8	5340.0	3910.5
35°	14838.7	14781.6	14358.2	13827.3	12827.5	12122.2	11145.7	8606.5	6443.3	4727.7	3383.6
37.5°	14570.5	14429.1	14111.2	13395.5	12077.9	11183.6	10088.8	7605.6	5598.7	4040.4	2861.0
40°	14176.8	13986.7	13568.6	12485.3	10779.3	9748.8	8680.5	6468.7	4704.4	3362.6	2305.8
42.5°	13354.2	13067.1	12475.8	10986.2	9048.9	8119.8	7230.9	5316.7	3836.6	2739.8	1759.9
45°	11819.2	11426.5	10627.2	8991.8	7310.0	6552.0	5837.3	4277.9	3071.2	2032.3	1160.2
47.5°	9499.8	9135.5	8408.0	7158.1	5732.7	5092.0	4521.8	3182.0	2082.0	1177.2	554.3
50°	7072.5	6760.0	6192.0	4974.7	3848.3	3344.6	2856.9	1807.5	975.5	559.5	230.1
52.5°	4219.8	4064.7	3561.1	2758.7	1900.3	1637.5	1314.4	765.4	491.9	202.7	62.3
55°	1728.2	1595.2	1406.2	1128.7	826.7	701.0	599.7	377.9	153.1	42.2	23.3
57.5°	781.3	751.7	666.1	523.6	380.1	318.9	215.4	71.8	33.8	21.1	13.8
60°	301.0	271.3	232.3	125.6	53.8	45.4	36.9	24.3	16.9	11.6	8.5
62.5°	43.3	41.2	36.9	29.5	23.3	21.1	17.9	12.6	9.5	7.4	6.4
65°	17.9	17.9	15.9	12.6	10.5	9.5	8.5	6.4	5.3	5.3	5.3
67.5°	7.4	7.4	6.4	5.3	4.2	4.2	4.2	3.1	4.2	4.2	5.3
70°	2.1	2.1	2.1	2.1	2.1	2.1	3.1	3.1	4.2	4.2	5.3
72.5°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	5.3	5.3
75°	0.0	0.0	1.0	1.0	2.1	2.1	2.1	3.1	4.2	5.3	5.3
77.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.3	5.3
80°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.3	6.4
82.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.3	6.4
85°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.3	6.4
87.5°	0.0	0.0	1.0	1.0	2.1	2.1	3.1	3.1	4.2	5.3	6.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3
2.5°	1449.5	1382.0	1362.9	1303.9	1254.2	1229.9	1199.4	1130.7	1079.0	1010.4	969.2
5°	1866.5	1738.9	1637.5	1514.0	1432.6	1379.8	1297.5	1172.0	1070.6	949.1	862.6
7.5°	2317.4	2084.0	1901.4	1697.7	1580.4	1488.6	1348.2	1167.7	1018.8	857.2	723.2
10°	2752.4	2404.0	2116.8	1824.3	1670.2	1542.4	1349.3	1122.3	924.8	721.1	579.7
12.5°	3135.6	2685.8	2281.5	1905.7	1714.6	1555.2	1313.4	1041.0	802.4	593.3	468.8
15°	3455.5	2904.3	2397.6	1936.2	1717.7	1527.6	1238.4	924.8	666.1	480.4	392.7
17.5°	3698.4	3019.5	2433.5	1899.3	1656.5	1449.5	1123.3	778.1	540.5	407.6	330.5
20°	3824.0	3041.6	2381.7	1799.1	1543.5	1331.3	972.4	631.3	458.2	354.8	276.6
22.5°	3839.8	2979.3	2258.2	1655.4	1401.0	1187.7	805.5	526.8	408.6	313.6	243.9
25°	3745.8	2844.3	2082.0	1492.8	1244.8	1023.0	655.6	471.9	371.7	281.8	280.8
27.5°	3545.2	2612.0	1870.8	1303.9	1055.7	832.0	556.4	426.5	331.5	298.7	317.7
30°	3262.4	2314.3	1611.1	1065.2	824.6	639.7	468.8	351.5	291.3	294.6	310.4
32.5°	2879.1	1944.7	1306.0	780.3	590.2	481.4	351.5	239.7	241.8	242.8	256.5
35°	2397.6	1559.4	975.5	524.7	415.0	338.9	198.5	176.3	179.5	180.6	190.1
37.5°	1921.5	1198.3	648.2	349.4	260.8	178.4	123.5	118.3	120.4	119.3	129.9
40°	1471.7	835.1	388.6	173.2	100.4	83.5	76.0	72.8	73.8	75.0	81.2
42.5°	1042.1	452.9	192.1	65.5	52.8	48.6	45.4	43.3	44.3	44.3	48.6
45°	529.0	214.4	65.5	35.9	32.8	29.5	27.4	26.4	26.4	26.4	28.5
47.5°	229.1	70.7	30.7	22.2	20.0	19.0	16.9	15.9	15.9	15.9	16.9
50°	71.8	28.5	19.0	14.8	12.6	11.6	10.5	10.5	10.5	9.5	10.5
52.5°	26.4	17.9	12.6	9.5	8.5	8.5	8.5	7.4	8.5	7.4	8.5
55°	15.9	11.6	8.5	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
57.5°	10.5	8.5	7.4	7.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4
60°	7.4	7.4	6.4	6.4	6.4	6.4	7.4	7.4	7.4	7.4	7.4
62.5°	6.4	6.4	6.4	6.4	6.4	6.4	7.4	7.4	7.4	7.4	8.5
65°	5.3	6.4	6.4	6.4	6.4	6.4	7.4	7.4	8.5	8.5	8.5
67.5°	5.3	6.4	6.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5
70°	6.4	6.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	8.5	9.5
72.5°	6.4	6.4	7.4	7.4	7.4	7.4	8.5	8.5	9.5	9.5	9.5
75°	6.4	7.4	7.4	7.4	7.4	8.5	8.5	8.5	9.5	9.5	9.5
77.5°	6.4	7.4	7.4	8.5	8.5	8.5	8.5	9.5	9.5	9.5	9.5
80°	6.4	7.4	7.4	8.5	8.5	8.5	9.5	9.5	9.5	9.5	10.5
82.5°	6.4	7.4	7.4	8.5	8.5	8.5	9.5	9.5	9.5	9.5	10.5
85°	7.4	7.4	8.5	8.5	8.5	8.5	9.5	9.5	9.5	9.5	10.5
87.5°	7.4	7.4	8.5	8.5	8.5	8.5	9.5	9.5	10.5	9.5	10.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3
2.5°	914.3	853.1	810.8	795.0	764.4	715.8	687.3	660.9	611.3	600.7	573.3
5°	763.4	665.1	595.4	569.0	534.2	493.1	452.9	426.5	394.8	382.2	363.2
7.5°	601.8	503.6	443.4	422.2	398.1	364.3	328.4	302.0	269.2	252.3	236.5
10°	472.9	400.1	349.4	328.4	303.0	267.2	230.1	195.3	166.8	148.8	145.7
12.5°	384.3	324.1	270.3	248.0	218.5	182.6	156.3	155.2	153.1	152.0	154.2
15°	314.6	256.5	199.6	175.2	166.8	165.8	168.9	172.1	171.1	174.2	176.3
17.5°	258.7	196.4	183.7	184.7	185.8	189.0	194.2	202.7	203.7	209.0	213.2
20°	211.1	208.0	213.2	217.5	220.6	227.0	238.6	249.2	252.3	259.7	268.2
22.5°	239.7	249.2	260.8	266.1	270.3	281.8	294.6	311.5	317.7	327.3	338.9
25°	289.2	305.1	323.0	329.4	335.8	354.8	369.5	389.6	394.8	406.5	418.1
27.5°	330.5	347.4	366.3	374.8	380.1	399.1	411.7	424.4	424.4	430.7	439.1
30°	324.1	337.9	353.7	360.0	362.2	375.8	388.6	392.7	390.7	393.8	400.1
32.5°	269.2	279.8	292.5	297.7	299.8	309.4	319.9	319.9	318.9	318.9	323.0
35°	199.6	207.0	213.2	218.5	221.6	228.0	237.5	236.5	236.5	234.4	237.5
37.5°	134.0	138.3	145.7	147.8	148.8	153.1	160.4	160.4	158.3	159.4	161.6
40°	81.2	86.6	90.7	91.9	94.0	97.1	102.4	102.4	102.4	102.4	103.5
42.5°	48.6	51.7	54.9	54.9	55.9	60.2	62.3	62.3	62.3	62.3	63.3
45°	28.5	29.5	31.7	32.8	32.8	34.8	35.9	35.9	35.9	35.9	36.9
47.5°	16.9	17.9	17.9	19.0	19.0	20.0	21.1	21.1	20.0	20.0	20.0
50°	10.5	10.5	10.5	10.5	11.6	11.6	11.6	11.6	11.6	11.6	10.5
52.5°	8.5	8.5	8.5	8.5	7.4	7.4	7.4	7.4	6.4	6.4	5.3
55°	7.4	7.4	7.4	7.4	7.4	6.4	6.4	6.4	5.3	4.2	3.1
57.5°	7.4	7.4	7.4	7.4	7.4	6.4	6.4	5.3	4.2	4.2	3.1
60°	7.4	7.4	7.4	7.4	7.4	6.4	6.4	5.3	4.2	4.2	3.1
62.5°	8.5	8.5	7.4	7.4	7.4	6.4	6.4	5.3	5.3	4.2	3.1
65°	8.5	8.5	7.4	7.4	7.4	7.4	6.4	6.4	5.3	4.2	3.1
67.5°	8.5	8.5	8.5	8.5	7.4	7.4	7.4	6.4	5.3	4.2	3.1
70°	9.5	9.5	8.5	8.5	8.5	7.4	7.4	6.4	5.3	5.3	4.2
72.5°	9.5	9.5	8.5	8.5	8.5	8.5	7.4	6.4	6.4	5.3	4.2
75°	9.5	9.5	9.5	9.5	8.5	8.5	7.4	7.4	6.4	5.3	4.2
77.5°	9.5	9.5	9.5	9.5	8.5	8.5	8.5	7.4	6.4	5.3	4.2
80°	9.5	9.5	9.5	9.5	9.5	8.5	8.5	7.4	6.4	5.3	4.2
82.5°	10.5	10.5	9.5	9.5	9.5	8.5	8.5	7.4	6.4	5.3	5.3
85°	10.5	10.5	9.5	9.5	9.5	8.5	8.5	7.4	6.4	6.4	5.3
87.5°	10.5	10.5	9.5	9.5	9.5	8.5	8.5	7.4	6.4	6.4	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1212706

CATALOG NUMBER: LDSQA6A70940D010TE LARH30NF 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3
2.5°	556.4	524.7	514.2	521.6	513.1	506.7	498.3	494.1
5°	348.4	325.1	317.7	319.9	312.5	306.2	297.7	295.6
7.5°	214.4	192.1	183.7	183.7	175.2	167.8	162.6	159.4
10°	143.5	139.4	140.4	141.4	140.4	141.4	138.3	140.4
12.5°	154.2	152.0	154.2	155.2	155.2	157.3	153.1	156.3
15°	179.5	177.3	180.6	182.6	182.6	185.8	181.6	184.7
17.5°	219.6	218.5	223.9	225.9	227.0	232.3	227.0	231.3
20°	277.7	276.6	284.0	287.2	286.1	296.7	289.2	296.7
22.5°	352.6	350.5	361.0	364.3	365.3	379.1	372.7	377.9
25°	427.6	429.6	435.0	440.3	441.4	452.9	443.4	448.8
27.5°	443.4	440.3	443.4	449.8	450.8	456.0	447.6	451.9
30°	401.2	395.8	397.0	404.3	406.5	408.6	401.2	403.3
32.5°	326.2	317.7	317.7	325.1	327.3	330.5	317.7	323.0
35°	240.8	233.4	233.4	238.6	239.7	241.8	232.3	236.5
37.5°	164.7	158.3	160.4	162.6	163.7	165.8	164.7	163.7
40°	105.6	101.4	104.5	104.5	105.6	106.6	106.6	107.6
42.5°	64.4	61.2	63.3	63.3	64.4	64.4	64.4	65.5
45°	36.9	35.9	35.9	36.9	36.9	36.9	35.9	36.9
47.5°	20.0	19.0	20.0	20.0	20.0	20.0	20.0	20.0
50°	10.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
52.5°	5.3	4.2	4.2	4.2	3.1	4.2	3.1	3.1
55°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
57.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
60°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.1	1.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.1	2.1	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.1	2.1	2.1	1.0	1.0	0.0	0.0	0.0
72.5°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
75°	3.1	2.1	2.1	2.1	1.0	1.0	0.0	0.0
77.5°	3.1	3.1	2.1	2.1	1.0	1.0	1.0	0.0
80°	4.2	3.1	2.1	2.1	2.1	1.0	1.0	1.0
82.5°	4.2	3.1	2.1	2.1	2.1	1.0	1.0	1.0
85°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
87.5°	4.2	3.1	3.1	2.1	2.1	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)