

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1219663

Luminaire Tested: **LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1219663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°
Description: PORTFOLIO 6" SQUARE ADJUSTABLE REFLECTOR, ANGLE-CUT TRIM,
SELF-FLANGED, 40° FLOOD, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7828.8 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 82.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	66	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63171	63171	63171
5°	173399	58205	23749
10°	379978	47637	9059
15°	580409	36261	10618
20°	672461	26978	16495
25°	733565	22186	26623
30°	819162	20125	27185
35°	833453	13803	18638
40°	848097	6548	9437
45°	849475	2722	4116
50°	718155	1179	1266
55°	231254	811	203
60°	45923	930	0
65°	4686	1100	0
70°	516	1536	0
75°	0	2030	0
80°	0	3347	347
85°	0	6669	692



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.2	2.5
10°-20°	1030.1	13.2
20°-30°	1972.3	25.2
30°-40°	2323.7	29.7
40°-50°	1825.2	23.3
50°-60°	444.8	5.7
60°-70°	19.1	0.2
70°-80°	7.2	0.1
80°-90°	7.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3201.6	40.9
0°-40°	5525.3	70.6
0°-60°	7795.3	99.6
0°-90°	7828.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7828.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1467	1467	1467	1467	1467	
5°	4012	2903	1347	705	550	530
15°	13021	6688	814	233	238	3635
25°	15441	8132	467	489	560	7197
35°	15857	5141	263	338	355	9943
45°	13951	1589	45	62	68	10482
55°	3081	58	11	7	3	3667
65°	46	7	11	7	0	122
75°	0	7	12	8	0	1
85°	0	8	14	8	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2
2.5°	2514.9	2509.5	2472.9	2506.8	2403.9	2399.8	2353.7	2333.6	2274.0	2217.1	2136.0
5°	4012.0	3923.9	3852.2	3854.9	3657.3	3620.8	3517.9	3413.6	3254.0	3105.0	2903.3
7.5°	6115.3	6011.1	5859.5	5795.8	5418.2	5307.2	5094.8	4817.3	4469.5	4122.9	3749.3
10°	8691.2	8707.4	8511.2	8329.8	7758.5	7533.8	7190.0	6643.2	5984.1	5332.9	4671.1
12.5°	11283.2	11272.4	11038.1	10763.4	10059.6	9742.8	9285.3	8603.2	7730.1	6720.4	5684.8
15°	13021.1	13098.3	12999.5	12780.1	12179.2	11816.5	11300.7	10374.8	9311.0	8084.6	6687.8
17.5°	14112.1	14185.2	14150.0	13978.0	13447.4	13060.3	12630.0	11871.9	10641.6	9099.9	7478.3
20°	14676.5	14791.6	14775.3	14588.5	14187.9	13867.2	13392.0	12689.5	11624.3	9805.1	7989.9
22.5°	15052.8	15140.7	15165.1	14954.0	14539.7	14235.3	13887.3	13175.4	12173.8	10235.5	8193.0
25°	15441.3	15596.9	15443.9	15184.0	14803.7	14511.4	14140.6	13458.3	12436.3	10411.4	8132.1
27.5°	15917.6	15992.2	15645.6	15408.7	14986.4	14669.7	14275.9	13622.0	12482.4	10270.7	7784.3
30°	16476.7	16168.2	15925.8	15456.1	14977.0	14668.4	14267.7	13519.2	12240.1	9803.8	7110.2
32.5°	16384.7	16101.7	15826.9	15330.3	14856.5	14550.6	14104.0	13176.8	11667.6	9022.7	6180.3
35°	15856.8	15917.6	15621.3	15209.8	14673.8	14358.3	13871.2	12689.5	10695.7	7945.3	5140.7
37.5°	15411.4	15545.4	15351.9	14971.6	14427.5	14001.1	13343.2	11907.2	9427.5	6578.3	4155.4
40°	15089.3	15132.6	15028.4	14602.1	13948.3	13332.4	12571.7	10502.1	7887.0	5163.8	3279.6
42.5°	14589.8	14705.0	14520.9	14055.3	13064.4	12367.4	11265.6	8879.3	6126.2	3944.2	2468.9
45°	13951.0	14060.6	13833.2	13059.0	11681.1	10659.2	9315.1	6923.4	4531.7	2907.3	1589.1
47.5°	12908.8	12976.4	12536.6	11465.9	9462.5	8500.2	7122.3	4826.7	2919.6	1625.5	772.9
50°	10721.5	10688.9	9782.0	8465.1	6329.1	5319.4	4239.4	2616.4	1311.6	770.2	483.3
52.5°	6909.9	6835.4	5938.1	4740.1	3205.2	2445.8	1838.1	1128.9	683.6	430.4	190.8
55°	3080.7	3052.3	2498.7	1941.0	1311.6	1128.9	862.3	553.6	364.1	150.2	58.1
57.5°	1142.4	1116.6	983.9	825.7	633.5	526.4	418.2	265.3	93.4	50.0	31.2
60°	533.3	532.0	468.3	385.7	268.0	203.0	117.8	62.2	39.3	27.1	17.6
62.5°	170.6	166.5	116.5	85.3	60.8	52.7	42.0	31.2	20.3	14.9	10.8
65°	46.0	46.0	42.0	35.3	28.5	24.4	20.3	14.9	9.5	8.1	6.8
67.5°	17.6	17.6	16.2	14.9	10.8	9.5	8.1	6.8	5.4	6.8	6.8
70°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	5.4	5.4	6.8
72.5°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	6.8
75°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	6.8
77.5°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	6.8
80°	0.0	0.0	1.4	1.4	2.7	2.7	4.1	4.1	5.4	6.8	6.8
82.5°	0.0	0.0	1.4	2.7	2.7	2.7	4.1	5.4	5.4	6.8	8.1
85°	0.0	0.0	1.4	2.7	2.7	4.1	4.1	5.4	5.4	6.8	8.1
87.5°	0.0	0.0	1.4	2.7	2.7	4.1	4.1	5.4	5.4	6.8	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2
2.5°	2076.3	1986.9	1863.9	1792.1	1774.6	1736.6	1670.2	1571.4	1490.3	1411.8	1365.7
5°	2732.8	2521.7	2284.8	2118.3	2050.7	1960.0	1798.8	1632.4	1479.4	1346.7	1242.6
7.5°	3428.6	3080.7	2697.7	2389.0	2278.0	2134.6	1872.0	1624.2	1414.5	1230.4	1091.0
10°	4120.2	3559.8	3040.0	2593.4	2412.1	2217.1	1870.6	1549.8	1303.4	1089.6	935.3
12.5°	4811.9	4006.4	3291.8	2716.5	2481.0	2234.8	1815.1	1436.0	1162.6	944.8	797.2
15°	5450.7	4362.5	3462.5	2758.5	2474.3	2183.3	1702.7	1298.0	1015.1	813.5	676.8
17.5°	5927.2	4549.3	3501.6	2695.0	2367.4	2045.3	1530.8	1135.7	874.4	697.0	557.6
20°	6161.3	4579.0	3408.2	2513.6	2183.3	1848.9	1342.6	979.9	753.9	588.8	471.0
22.5°	6161.3	4438.3	3205.2	2286.1	1953.2	1622.8	1161.3	851.4	659.2	512.9	414.1
25°	5927.2	4158.1	2933.1	2023.5	1700.1	1399.6	1004.3	755.2	586.1	467.0	384.4
27.5°	5472.4	3770.9	2583.9	1731.2	1451.0	1200.6	879.7	667.4	530.6	420.9	422.2
30°	4847.0	3295.9	2183.3	1422.6	1195.2	986.8	740.4	559.0	424.9	404.8	416.8
32.5°	4124.2	2727.4	1729.8	1103.1	925.8	777.0	563.1	395.3	338.3	341.0	354.6
35°	3382.5	2146.8	1302.1	817.5	689.0	563.1	369.5	259.9	257.2	262.6	272.1
37.5°	2670.5	1606.7	942.1	598.2	462.9	346.5	199.0	178.7	178.7	184.1	189.5
40°	2000.5	1139.7	648.3	354.6	224.7	158.3	125.9	116.5	115.1	116.5	123.2
42.5°	1373.8	721.4	385.7	142.1	108.3	92.0	79.9	73.1	71.8	73.1	77.2
45°	771.6	444.0	150.2	75.8	64.9	58.1	50.0	46.0	44.7	44.7	47.3
47.5°	483.3	176.0	67.6	47.3	40.7	38.0	32.6	29.8	28.5	28.5	29.8
50°	185.4	69.1	42.0	31.2	27.1	24.4	21.6	18.9	17.6	17.6	18.9
52.5°	63.5	40.7	27.1	20.3	17.6	16.2	13.5	12.2	12.2	12.2	12.2
55°	35.3	24.4	16.2	12.2	10.8	10.8	10.8	10.8	10.8	10.8	10.8
57.5°	21.6	14.9	10.8	9.5	9.5	9.5	9.5	9.5	9.5	10.8	10.8
60°	12.2	9.5	8.1	8.1	8.1	8.1	9.5	9.5	9.5	10.8	10.8
62.5°	8.1	8.1	8.1	8.1	8.1	8.1	9.5	9.5	10.8	10.8	10.8
65°	6.8	6.8	6.8	8.1	8.1	8.1	9.5	9.5	10.8	10.8	10.8
67.5°	6.8	6.8	8.1	8.1	8.1	9.5	9.5	10.8	10.8	10.8	10.8
70°	6.8	8.1	8.1	9.5	9.5	9.5	10.8	10.8	10.8	12.2	12.2
72.5°	6.8	8.1	8.1	9.5	9.5	9.5	10.8	10.8	12.2	12.2	12.2
75°	8.1	8.1	8.1	9.5	9.5	9.5	10.8	12.2	12.2	12.2	12.2
77.5°	8.1	8.1	9.5	9.5	9.5	10.8	10.8	12.2	12.2	12.2	12.2
80°	8.1	8.1	9.5	9.5	10.8	10.8	12.2	12.2	12.2	13.5	13.5
82.5°	8.1	8.1	9.5	10.8	10.8	10.8	12.2	12.2	13.5	13.5	13.5
85°	8.1	9.5	9.5	10.8	10.8	10.8	12.2	12.2	13.5	13.5	13.5
87.5°	8.1	9.5	9.5	10.8	10.8	10.8	12.2	12.2	13.5	13.5	13.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2
2.5°	1304.8	1247.9	1191.1	1149.2	1128.9	1108.5	1063.8	1005.7	981.2	946.2	925.8
5°	1137.0	1040.9	965.1	915.0	885.1	845.9	794.5	737.7	705.1	668.7	644.3
7.5°	963.8	851.4	778.3	732.3	702.4	653.7	588.8	521.0	481.9	441.3	412.9
10°	812.1	705.1	622.6	569.8	532.0	475.1	410.2	362.8	328.8	293.7	265.3
12.5°	678.2	563.1	475.1	430.4	404.8	350.6	296.4	243.6	223.4	216.6	216.6
15°	549.5	445.3	370.9	332.9	306.0	247.6	236.8	234.1	232.8	231.4	234.1
17.5°	448.0	360.0	281.5	262.6	259.9	258.5	259.9	259.9	261.2	265.3	272.1
20°	376.3	295.0	289.6	291.0	291.0	296.4	303.3	308.7	314.1	320.8	332.9
22.5°	334.3	332.9	342.4	343.8	350.6	358.7	370.9	379.0	392.6	399.4	416.8
25°	385.7	395.3	412.9	418.2	429.0	442.6	461.6	472.4	488.7	496.8	517.0
27.5°	437.2	452.1	473.7	480.5	490.0	511.6	525.1	534.7	542.8	548.2	560.4
30°	433.1	446.7	468.3	469.7	483.3	498.2	506.3	514.3	519.7	518.3	525.1
32.5°	366.8	379.0	399.4	399.4	414.1	426.3	430.4	437.2	437.2	437.2	439.9
35°	281.5	289.6	303.3	307.3	319.5	327.5	330.2	338.3	338.3	335.6	335.6
37.5°	194.9	205.7	215.3	218.0	226.1	231.4	238.2	239.5	236.8	238.2	238.2
40°	127.3	134.1	140.7	142.1	148.8	152.9	159.6	159.6	161.1	159.6	162.4
42.5°	78.5	83.9	88.0	90.7	93.4	96.1	100.2	101.5	102.9	101.5	104.2
45°	48.7	51.4	54.1	55.4	56.8	58.1	62.2	62.2	62.2	62.2	63.5
47.5°	29.8	31.2	32.6	32.6	33.9	35.3	36.6	36.6	36.6	36.6	38.0
50°	17.6	18.9	18.9	18.9	20.3	20.3	21.6	21.6	21.6	20.3	21.6
52.5°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	10.8	12.2
55°	10.8	10.8	9.5	9.5	9.5	9.5	9.5	8.1	6.8	6.8	5.4
57.5°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	6.8	5.4	4.1
60°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.1
62.5°	10.8	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.1
65°	10.8	10.8	9.5	9.5	9.5	8.1	8.1	6.8	6.8	5.4	4.1
67.5°	10.8	10.8	10.8	9.5	10.8	9.5	8.1	8.1	6.8	5.4	5.4
70°	12.2	10.8	10.8	10.8	10.8	9.5	9.5	8.1	6.8	5.4	5.4
72.5°	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	6.8	6.8	5.4
75°	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	8.1	6.8	5.4
77.5°	12.2	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	6.8	5.4
80°	12.2	12.2	12.2	12.2	12.2	10.8	10.8	9.5	8.1	6.8	5.4
82.5°	13.5	12.2	12.2	12.2	12.2	10.8	10.8	9.5	8.1	6.8	6.8
85°	13.5	13.5	12.2	12.2	12.2	10.8	10.8	9.5	8.1	8.1	6.8
87.5°	13.5	12.2	12.2	12.2	12.2	10.8	10.8	9.5	8.1	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1219663

CATALOG NUMBER: LDSQA6A75950D010TE LARH40FL 6LSQA1H 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2	1467.2
2.5°	905.5	894.7	894.7	875.7	873.1	858.2	870.4	862.3
5°	617.1	599.6	594.3	575.3	568.5	550.9	556.3	549.5
7.5°	388.4	370.9	365.5	351.9	343.8	330.2	331.6	327.5
10°	236.8	220.7	216.6	212.6	208.5	207.2	208.5	207.2
12.5°	215.3	213.9	211.2	212.6	209.9	211.2	212.6	211.2
15°	234.1	236.8	234.1	235.5	234.1	236.8	238.2	238.2
17.5°	274.8	280.2	277.5	281.5	280.2	286.9	286.9	286.9
20°	337.0	346.5	343.8	349.2	349.2	357.3	357.3	360.0
22.5°	423.6	435.9	434.4	446.7	444.0	453.4	453.4	456.1
25°	527.9	540.1	541.4	549.5	548.2	557.6	557.6	560.4
27.5°	571.2	578.0	576.7	580.7	582.1	587.5	591.6	588.8
30°	536.0	541.4	540.1	542.8	542.8	546.8	550.9	546.8
32.5°	450.7	454.8	454.8	460.2	456.1	457.5	464.3	460.2
35°	345.2	347.9	345.2	347.9	349.2	349.2	356.0	354.6
37.5°	246.3	247.6	247.6	251.7	247.6	247.6	254.5	255.8
40°	165.2	166.5	165.2	170.6	167.9	167.9	171.9	167.9
42.5°	105.6	106.9	105.6	109.6	106.9	109.6	111.0	112.3
45°	64.9	64.9	63.5	66.2	64.9	66.2	67.6	67.6
47.5°	38.0	38.0	36.6	39.3	38.0	38.0	38.0	39.3
50°	20.3	20.3	20.3	21.6	20.3	20.3	20.3	18.9
52.5°	10.8	10.8	9.5	10.8	9.5	9.5	9.5	9.5
55°	5.4	4.1	4.1	4.1	2.7	2.7	2.7	2.7
57.5°	4.1	2.7	2.7	1.4	1.4	1.4	0.0	0.0
60°	2.7	2.7	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.7	2.7	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.7	2.7	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	4.1	2.7	2.7	1.4	1.4	0.0	0.0	0.0
70°	4.1	2.7	2.7	1.4	1.4	0.0	0.0	0.0
72.5°	4.1	2.7	2.7	2.7	1.4	1.4	0.0	0.0
75°	4.1	4.1	2.7	2.7	1.4	1.4	0.0	0.0
77.5°	5.4	4.1	2.7	2.7	1.4	1.4	0.0	0.0
80°	5.4	4.1	2.7	2.7	2.7	1.4	1.4	1.4
82.5°	5.4	4.1	4.1	2.7	2.7	1.4	1.4	1.4
85°	5.4	4.1	4.1	2.7	2.7	1.4	1.4	1.4
87.5°	5.4	4.1	4.1	2.7	2.7	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)