

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152020

Luminaire Tested: **AVS-E01-LED-E-U-SL4-HSS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152020
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33728)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-E01-LED-E-U-SL4-HSS
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL AND HOUSE SIDE SHIELD
Light Source: (21) 4000K CCT, 70 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2034.8 lumens
Efficiency: N/A
Efficacy: 82.4 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Semi-Cutoff
BUG Rating: B0 - U0 - G1

Input Watts (W): 24.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.6 fc
Type IV - Short - Semi-Cutoff

REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

Luminous Intensity Polar Plot



REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	60.6	0.0	60.6
	% Fixture	3.0	0.0	3.0
Street Side	Lumens	1974.2	0.0	1974.2
	% Fixture	97.0	0.0	97.0
Total	Lumens	2034.8	0.0	2034.8
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.8	0.8
10°-20°	54.5	2.7
20°-30°	104.2	5.1
30°-40°	173.3	8.5
40°-50°	234.5	11.5
50°-60°	366.8	18.0
60°-70°	754.1	37.1
70°-80°	303.5	14.9
80°-90°	28.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2034.8	100.0
0°-180°	2034.8	100.0

Coefficient of Utilization



REPORT NUMBER: P152020


CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	151.4	7.4			
FM	(30°-60°)	747.0	36.7			
FH	(60°-80°)	1048.7	51.5			G1/1800
FVH	(80°-90°)	27.0	1.3			G1/100
BL	(0°-30°)	23.0	1.1	B0/110		
BM	(30°-60°)	27.7	1.4	B0/220		
BH	(60°-80°)	8.8	0.4	B0/110		G0/110
BVH	(80°-90°)	1.1	0.1			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type IV Short





REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7
2.5°	205.0	202.7	200.0	200.0	196.7	196.7	194.7	189.3	188.7	185.7	182.7
5°	261.7	259.7	256.4	253.4	250.7	246.0	242.7	236.4	229.3	222.7	216.7
7.5°	317.0	316.0	310.1	309.0	304.7	297.0	290.4	281.0	269.0	259.7	248.7
10°	368.3	366.0	364.7	359.0	352.6	344.4	334.0	322.7	308.7	294.0	278.3
12.5°	409.0	407.7	401.7	399.4	392.6	384.4	371.3	356.7	342.7	323.6	305.3
15°	439.4	437.0	433.0	429.3	421.3	414.0	402.0	386.0	369.0	348.3	326.3
17.5°	464.7	460.3	459.4	453.7	445.3	436.7	423.3	408.7	388.7	368.0	344.0
20°	498.7	492.6	490.7	482.4	472.6	460.6	445.3	427.0	406.0	383.3	358.7
22.5°	538.7	534.3	529.9	522.7	510.4	493.4	471.0	451.0	424.4	399.4	372.6
25°	595.3	591.7	584.7	574.7	559.4	539.0	512.0	482.7	451.3	419.4	388.0
27.5°	650.4	647.0	642.0	634.3	617.0	594.7	561.3	524.0	484.4	445.7	411.0
30°	702.0	699.0	694.0	686.3	671.0	649.0	611.3	571.3	522.0	477.0	435.3
32.5°	757.6	756.7	751.0	740.0	726.6	697.0	656.0	613.0	563.0	511.0	462.4
35°	820.6	813.0	807.7	796.7	774.0	742.4	694.3	647.4	594.7	541.3	487.0
37.5°	874.0	866.6	860.0	846.0	818.3	778.0	723.6	672.0	617.6	563.3	508.0
40°	913.0	909.3	901.3	883.0	852.0	804.0	745.3	689.0	634.3	579.7	525.0
42.5°	942.0	936.4	927.4	908.3	871.7	817.0	754.0	696.0	642.0	589.6	536.0
45°	952.6	948.0	939.7	919.0	879.4	820.6	753.7	694.0	642.4	592.6	543.3
47.5°	946.3	941.7	934.3	915.0	876.0	816.4	747.7	688.3	639.0	593.7	550.1
50°	925.3	922.7	917.0	900.6	865.7	808.0	742.4	685.3	638.3	598.7	559.4
52.5°	923.3	921.7	914.7	898.3	862.7	805.3	741.7	687.0	644.0	605.0	566.0
55°	1128.3	1104.7	1051.7	1006.6	932.6	844.7	775.3	714.0	668.0	629.9	602.7
57.5°	1603.6	1568.3	1498.7	1413.0	1243.0	1076.0	942.4	845.7	798.0	780.6	791.0
60°	1826.3	1820.0	1809.0	1768.3	1681.3	1537.6	1377.6	1204.7	1135.3	1129.3	1150.4
62.5°	1932.0	1928.0	1931.3	1926.3	1899.4	1857.3	1811.3	1736.7	1668.0	1623.6	1529.6
65°	1980.6	1983.3	2002.4	2017.3	2020.6	2031.7	2065.3	2158.3	2226.3	2112.0	1851.0
67.5°	1857.0	1872.6	1916.4	1971.0	2035.0	2097.0	2197.0	2393.0	2532.6	2398.3	2027.7
69°	1537.3	1545.0	1651.7	1754.7	1911.0	2020.3	2165.3	2422.4	2579.4	2427.7	2013.7
70°	1210.4	1217.3	1331.7	1471.7	1736.0	1876.7	2066.3	2372.6	2535.6	2388.7	1941.7
72.5°	546.0	536.0	576.4	651.3	938.7	1162.0	1493.7	1922.4	2092.0	1913.7	1452.6
75°	381.3	377.0	381.3	381.7	426.3	550.1	694.0	1042.0	1288.7	1112.0	694.0
77.5°	295.3	292.3	289.3	286.0	291.3	326.3	340.3	369.6	480.0	454.0	264.7
80°	233.7	231.0	238.3	236.0	236.0	240.0	237.3	226.3	205.7	190.7	170.7
82.5°	108.7	109.3	109.3	118.7	143.0	167.0	174.7	163.6	145.3	123.6	99.7
85°	10.4	11.7	19.7	30.4	60.3	68.0	68.3	56.7	56.7	44.7	36.0
87.5°	0.0	0.3	0.3	0.3	3.0	8.3	7.0	2.0	1.0	1.0	1.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7
2.5°	177.3	176.4	172.3	168.3	164.7	160.6	157.0	153.4	149.3	146.3	142.7
5°	207.4	200.0	191.7	183.6	175.6	167.4	158.7	151.0	143.0	135.6	128.7
7.5°	237.6	223.3	212.0	197.6	184.7	171.7	159.7	147.4	136.0	125.3	115.3
10°	263.3	246.0	228.3	209.9	191.3	174.0	157.3	142.7	127.7	114.7	102.4
12.5°	284.4	262.4	240.6	217.6	196.7	174.7	154.0	136.4	118.7	104.0	91.3
15°	303.3	278.0	252.0	225.3	198.7	173.7	150.7	128.7	110.7	94.0	79.7
17.5°	318.7	289.6	260.3	230.4	201.7	172.3	146.3	123.3	102.4	85.0	71.0
20°	332.0	301.7	270.1	236.4	203.6	172.0	142.7	116.7	95.0	76.7	63.0
22.5°	344.4	314.0	280.0	244.0	206.6	171.7	139.4	111.7	88.7	70.4	56.7
25°	358.3	326.3	290.7	252.0	212.0	173.0	137.3	107.7	83.0	64.4	51.7
27.5°	374.0	340.3	303.3	262.0	219.0	175.6	136.7	103.3	78.0	58.7	47.7
30°	396.0	357.0	316.0	272.0	225.3	178.7	136.0	100.6	73.0	54.3	43.6
32.5°	415.3	373.4	329.9	282.4	232.3	181.7	135.6	97.0	68.3	49.9	40.6
35°	435.6	388.3	342.0	292.3	238.3	185.0	135.3	94.3	64.0	45.7	37.6
37.5°	453.4	401.0	351.3	301.0	245.0	188.0	135.6	92.0	60.0	42.0	35.0
40°	468.3	414.0	361.7	309.0	252.0	192.6	136.0	89.6	56.0	38.7	32.6
42.5°	481.7	426.3	372.6	318.0	260.0	198.0	138.0	87.7	52.6	35.6	30.4
45°	492.0	437.6	384.7	330.7	273.0	206.6	141.7	86.3	49.3	33.0	28.3
47.5°	502.7	454.3	405.0	350.7	292.0	220.3	148.0	86.0	46.6	31.0	26.6
50°	517.3	471.0	423.0	371.0	309.3	234.3	155.6	86.3	43.3	29.0	25.0
52.5°	528.0	488.0	446.3	406.3	350.7	277.0	185.3	92.3	41.7	27.4	23.0
55°	591.0	584.0	585.0	591.7	548.7	471.3	310.1	133.4	49.0	31.0	22.7
57.5°	833.4	858.0	872.3	872.0	801.0	664.4	416.4	171.3	54.7	36.0	27.0
60°	1152.0	1133.4	1107.0	1042.0	947.7	758.3	465.7	184.4	47.4	28.7	24.7
62.5°	1433.7	1324.4	1227.4	1122.0	998.3	791.0	475.6	183.3	41.3	21.7	17.3
65°	1609.3	1412.6	1256.0	1124.0	978.3	763.6	449.9	168.3	35.0	17.6	14.3
67.5°	1651.3	1365.0	1143.3	975.0	817.3	594.3	330.4	126.6	27.4	14.7	12.6
69°	1559.7	1213.4	947.4	756.4	594.7	394.3	204.4	80.0	21.0	13.4	11.7
70°	1434.7	1055.3	771.7	607.0	440.3	277.0	143.0	56.4	17.0	12.3	10.7
72.5°	923.0	554.3	379.4	264.0	181.7	110.4	56.0	25.3	13.0	10.4	8.7
75°	358.0	205.0	148.7	113.0	88.3	61.3	34.0	16.4	11.0	8.7	6.6
77.5°	176.4	135.0	110.4	75.6	44.0	27.4	18.3	12.6	9.0	6.3	4.4
80°	139.4	92.6	55.3	34.3	26.0	19.7	14.0	10.4	6.6	4.0	3.0
82.5°	71.3	39.0	28.7	23.3	19.4	15.3	11.3	7.4	4.4	2.7	2.4
85°	22.4	16.4	14.7	14.3	13.4	11.0	8.0	4.7	2.7	1.7	1.7
87.5°	1.7	2.4	3.0	2.4	2.7	2.4	3.0	2.0	1.3	1.3	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7
2.5°	140.0	136.0	132.3	129.9	125.7	124.0	122.4	121.7	118.7	119.4	116.7
5°	122.4	115.3	110.1	104.7	99.7	96.0	93.0	89.3	86.3	85.0	82.4
7.5°	106.3	97.3	90.4	84.7	78.7	74.0	70.1	67.4	64.7	62.0	60.6
10°	92.3	82.7	74.7	69.0	63.3	59.4	56.4	54.3	52.6	51.7	51.3
12.5°	79.4	70.1	62.7	57.6	53.4	51.3	49.9	49.0	48.7	48.3	48.3
15°	69.3	60.0	54.3	50.7	48.7	47.7	47.4	46.6	46.0	45.7	45.7
17.5°	60.0	53.0	49.0	47.0	46.0	45.3	44.7	44.0	43.3	43.0	43.0
20°	53.7	48.0	46.0	44.7	43.6	43.0	42.0	41.3	41.0	40.6	40.3
22.5°	48.7	45.0	43.6	42.7	41.3	40.3	39.7	39.0	38.3	38.0	37.6
25°	45.0	42.7	41.7	40.3	39.0	38.0	37.0	36.0	35.3	35.0	34.3
27.5°	42.4	40.6	39.4	37.6	36.4	35.3	34.3	33.4	32.6	32.0	31.7
30°	40.0	38.3	36.7	35.3	33.7	32.6	31.3	30.4	30.1	29.3	28.7
32.5°	37.6	36.0	34.3	32.6	31.0	29.6	29.0	27.7	27.0	26.6	26.0
35°	35.0	33.4	31.3	30.1	28.3	27.0	26.0	25.0	24.4	23.6	23.3
37.5°	32.6	30.7	28.7	27.0	25.7	24.4	23.3	22.4	21.7	21.0	20.6
40°	30.1	28.0	26.0	24.4	23.0	22.0	21.0	20.0	19.4	19.0	19.0
42.5°	27.7	25.3	23.3	22.0	21.0	19.7	18.7	17.6	17.3	17.0	17.3
45°	25.3	23.0	21.3	20.0	19.0	17.6	16.7	16.0	15.6	16.0	16.4
47.5°	23.3	21.0	19.4	18.3	17.3	16.4	15.3	14.7	14.7	15.3	16.0
50°	21.3	19.0	17.6	17.0	16.0	15.0	13.7	13.4	13.7	14.3	15.0
52.5°	19.4	16.7	15.6	15.3	14.3	13.4	12.3	12.0	12.3	13.0	12.6
55°	17.3	14.7	14.3	14.0	13.0	11.7	10.7	10.7	10.7	10.4	9.6
57.5°	16.7	13.0	12.6	12.3	11.3	9.9	9.3	8.7	8.3	7.4	7.0
60°	17.3	11.7	11.7	11.0	9.9	8.7	7.7	6.6	6.0	5.3	5.3
62.5°	14.0	10.7	10.4	9.6	8.3	7.0	6.0	5.0	4.7	4.4	4.4
65°	11.3	9.6	9.0	8.0	7.0	5.7	4.7	4.0	3.6	3.6	4.0
67.5°	10.4	8.7	7.7	6.6	5.7	4.4	3.6	3.3	3.3	3.6	3.6
69°	9.6	8.0	7.0	6.0	5.0	4.0	3.3	3.3	3.3	3.3	3.6
70°	9.0	7.7	6.6	5.7	4.4	3.3	3.0	3.0	3.3	3.3	3.6
72.5°	7.0	6.0	5.7	4.7	3.3	3.0	2.7	3.0	3.0	3.3	3.3
75°	5.3	4.4	4.4	3.6	2.7	2.4	2.4	2.7	2.7	3.0	3.0
77.5°	3.6	3.0	3.0	2.7	2.4	2.0	2.0	2.4	2.7	2.7	3.0
80°	2.7	2.4	2.0	2.4	2.0	1.7	2.0	2.4	2.4	2.7	2.7
82.5°	2.0	2.0	2.0	2.0	1.7	1.7	2.0	2.0	2.4	2.7	2.7
85°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	2.0	2.0	2.4	2.4
87.5°	1.0	1.0	1.0	1.3	1.3	1.7	1.7	1.7	1.7	2.0	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152020

CATALOG NUMBER: AVS-E01-LED-E-U-SL4-HSS

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	153.7	153.7	153.7	153.7
2.5°	116.0	115.6	114.3	114.7
5°	81.3	79.4	80.6	80.3
7.5°	59.7	59.4	59.0	59.7
10°	51.0	51.0	50.7	51.0
12.5°	48.0	48.0	48.0	48.0
15°	45.7	45.7	45.3	45.3
17.5°	43.0	43.0	43.0	42.7
20°	40.3	40.0	40.0	40.0
22.5°	37.3	37.0	37.0	37.0
25°	34.3	34.0	34.0	34.0
27.5°	31.3	31.0	30.7	30.7
30°	28.3	28.0	27.7	27.7
32.5°	25.3	25.0	24.7	24.7
35°	22.7	22.7	22.4	22.0
37.5°	20.3	20.3	20.3	20.3
40°	18.7	19.0	19.0	19.0
42.5°	17.6	18.0	18.3	18.7
45°	17.0	17.6	18.0	18.0
47.5°	16.7	17.0	17.3	17.3
50°	15.3	15.0	15.0	15.0
52.5°	12.3	11.7	11.3	11.0
55°	9.0	8.7	8.0	8.0
57.5°	6.3	6.3	6.0	6.0
60°	5.0	5.0	4.7	5.0
62.5°	4.4	4.4	4.4	4.4
65°	4.0	4.0	4.0	4.0
67.5°	4.0	4.0	4.0	4.0
69°	3.6	3.6	3.6	3.6
70°	3.6	3.6	3.6	3.6
72.5°	3.3	3.3	3.3	3.3
75°	3.0	3.3	3.3	3.3
77.5°	3.0	3.0	3.0	3.0
80°	2.7	2.7	3.0	3.0
82.5°	2.7	2.7	2.7	2.7
85°	2.4	2.4	2.7	2.7
87.5°	2.0	2.0	2.4	2.4
90°	0.0	0.0	0.0	0.0

(END OF REPORT)