

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P152593

Luminaire Tested: **AVS-F01-LED-E-U-SL4-8030**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P152593
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P33680)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: AVS-F01-LED-E-U-SL4-8030
Description: VISION SITE SMALL LED LUMINAIRE
(1) LIGHTBARS WITH AccuLED OPTICS - TYPE 4 W/ SPILL LIGHT CONTROL
Light Source: (7) 3000K CCT, 80 CRI LEDs
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2058.2 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Luminous Opening: Rectangular (W 0.17' x L: 1' x H: 0')
IES Classification: Type IV - Short - Full Cutoff
BUG Rating: B1 - U0 - G1

Input Watts (W): 25.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 4.4 fc
 Type IV - Short - Full Cutoff

REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

Luminous Intensity Polar Plot



REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	427.3	0.0	427.3
	% Fixture	20.8	0.0	20.8
Street Side	Lumens	1631.0	0.0	1631.0
	% Fixture	79.2	0.0	79.2
Total	Lumens	2058.2	0.0	2058.2
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	2.0
10°-20°	112.3	5.5
20°-30°	166.3	8.1
30°-40°	210.1	10.2
40°-50°	237.6	11.5
50°-60°	338.2	16.4
60°-70°	629.8	30.6
70°-80°	288.6	14.0
80°-90°	34.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2058.2	100.0
0°-180°	2058.2	100.0

Coefficient of Utilization



REPORT NUMBER: P152593


CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	187.4	9.1			
FM	(30°-60°)	603.0	29.3			
FH	(60°-80°)	815.1	39.6			G1/1800
FVH	(80°-90°)	25.4	1.2			G1/100
BL	(0°-30°)	132.2	6.4	B1/500		
BM	(30°-60°)	182.9	8.9	B0/220		
BH	(60°-80°)	103.3	5.0	B0/110		G0/110
BVH	(80°-90°)	8.8	0.4			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Short





REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2
2.5°	445.9	447.0	445.7	445.5	445.5	445.2	443.8	443.6	441.8	442.0	442.4
5°	449.1	449.6	448.7	448.5	448.0	447.0	445.9	444.6	443.1	441.8	440.5
7.5°	452.4	451.9	451.3	451.3	450.6	449.1	446.8	445.0	442.0	440.3	438.2
10°	457.1	456.4	455.4	454.9	453.8	451.7	448.5	445.9	442.2	439.0	435.4
12.5°	461.5	461.2	459.9	459.2	457.3	455.2	451.3	447.3	442.4	437.3	432.6
15°	469.3	468.4	467.0	465.7	462.6	459.9	453.8	449.1	442.2	435.4	428.3
17.5°	483.1	481.5	480.0	477.0	473.3	468.4	459.6	451.7	442.2	432.4	424.4
20°	508.2	504.7	502.8	498.9	492.3	483.5	469.8	457.1	442.9	430.4	419.5
22.5°	536.5	534.2	531.6	529.0	518.9	506.1	487.5	468.4	447.0	429.4	415.4
25°	568.3	565.3	563.9	559.5	549.9	535.3	510.1	483.5	456.6	433.2	415.4
27.5°	596.7	595.8	595.4	590.4	581.3	564.1	534.2	502.4	469.6	440.8	419.0
30°	622.4	621.5	621.0	618.2	607.8	587.4	554.8	519.1	483.7	451.5	425.5
32.5°	649.8	646.8	645.4	640.1	628.2	604.4	567.2	529.9	494.9	462.0	432.6
35°	672.1	669.5	666.7	659.1	642.4	614.1	572.4	533.7	499.4	467.8	436.4
37.5°	688.4	685.8	681.9	672.1	651.4	617.3	572.2	532.5	497.7	466.8	437.1
40°	695.5	693.1	688.8	676.6	653.1	615.4	567.9	527.2	492.8	462.0	434.3
42.5°	692.7	690.9	685.6	673.8	648.0	607.0	559.0	517.2	483.5	454.0	428.0
45°	682.1	680.7	675.6	663.1	636.4	593.6	546.0	504.7	472.4	444.2	419.7
47.5°	666.1	665.6	660.5	648.2	621.8	580.1	532.5	492.3	461.2	434.7	412.7
50°	648.4	646.1	643.5	632.1	608.0	568.5	522.8	484.7	454.9	431.3	409.6
52.5°	637.3	636.6	634.3	624.0	600.8	561.8	518.3	481.9	454.5	430.6	408.1
55°	736.2	737.8	716.5	672.1	633.1	580.4	531.6	496.1	465.9	441.8	425.3
57.5°	1089.0	1081.8	1045.1	957.1	857.7	726.4	631.9	574.6	537.2	541.3	549.7
60°	1268.7	1267.4	1260.6	1226.5	1160.3	1060.4	949.6	822.6	782.2	786.6	789.8
62.5°	1349.1	1351.2	1356.3	1343.5	1326.1	1297.1	1241.9	1190.7	1136.6	1116.4	1062.3
65°	1386.3	1389.9	1401.6	1408.8	1415.5	1420.6	1442.5	1502.4	1541.9	1468.0	1296.2
67.5°	1309.4	1327.3	1365.6	1403.0	1436.5	1484.0	1557.9	1697.0	1793.9	1703.0	1453.9
70°	954.5	979.0	1022.8	1138.4	1262.0	1370.1	1513.1	1724.9	1871.0	1800.8	1492.8
72.5°	598.4	605.2	624.8	667.3	759.0	897.6	1147.8	1465.5	1634.1	1578.1	1261.8
75°	379.7	382.1	381.3	391.1	406.6	436.9	535.8	865.6	1119.4	1032.1	703.2
77.5°	226.2	229.7	231.1	234.1	241.6	252.2	260.3	294.5	469.3	455.6	255.2
80°	189.5	192.3	189.9	189.3	184.7	181.3	185.3	181.3	168.4	162.1	149.3
82.5°	100.3	100.1	99.4	106.1	119.8	130.6	138.7	136.8	123.8	105.4	89.4
85°	55.0	56.9	56.9	59.2	57.1	57.4	59.2	62.5	57.8	48.3	39.5
87.5°	4.7	7.2	5.8	7.2	9.7	6.9	6.7	6.7	5.8	4.1	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2
2.5°	441.2	440.8	439.9	439.2	439.2	438.0	437.3	436.9	436.6	435.6	435.6
5°	439.9	438.2	436.6	435.4	434.7	433.6	431.7	430.8	429.6	428.7	428.3
7.5°	436.9	433.8	431.3	429.4	427.2	425.3	422.9	420.8	418.8	417.8	417.3
10°	432.2	428.3	424.4	420.8	417.6	414.3	411.3	408.3	405.7	403.8	402.0
12.5°	427.8	421.8	416.7	411.5	406.4	402.5	398.3	393.9	390.2	386.7	385.8
15°	421.8	414.8	408.3	402.0	395.8	389.2	384.1	379.3	373.3	369.2	366.2
17.5°	416.2	407.8	399.9	392.5	384.9	378.1	370.5	363.9	357.9	351.8	347.5
20°	410.2	401.0	392.7	384.4	376.0	367.5	358.5	350.3	342.8	335.5	328.4
22.5°	404.8	395.5	387.4	378.3	369.0	359.3	349.0	338.7	330.1	320.7	312.3
25°	401.6	391.3	383.0	374.2	363.9	353.3	341.7	329.3	318.9	308.2	298.2
27.5°	401.6	388.3	379.7	370.9	360.4	349.0	336.3	322.8	311.0	299.2	286.8
30°	405.1	388.8	377.2	367.9	357.2	344.9	330.7	316.6	303.5	289.6	277.7
32.5°	408.3	389.7	375.3	363.4	351.2	339.1	324.7	309.5	295.2	282.0	269.4
35°	410.4	389.7	371.8	356.7	342.8	331.0	316.8	301.7	287.0	274.1	262.5
37.5°	410.6	387.9	366.2	349.0	334.4	322.1	308.7	294.5	280.5	268.5	258.8
40°	408.3	384.1	360.7	340.9	325.6	313.1	300.7	288.0	275.4	265.5	257.1
42.5°	404.1	380.2	355.3	334.4	318.4	305.4	294.0	283.1	272.2	263.6	256.6
45°	397.8	374.8	350.5	330.5	314.7	301.0	289.8	280.8	271.5	264.2	257.3
47.5°	392.2	373.0	352.1	333.1	316.6	302.4	291.0	283.3	276.2	271.3	261.8
50°	391.1	372.0	352.7	335.1	318.4	304.0	294.0	290.1	288.0	285.0	270.4
52.5°	387.9	371.8	357.9	348.2	337.4	330.7	320.3	323.9	321.7	311.0	284.5
55°	422.0	426.6	439.7	458.2	475.4	479.4	478.2	473.8	450.4	387.4	318.7
57.5°	580.1	606.4	631.0	642.0	640.5	628.2	619.4	601.6	567.6	491.0	386.0
60°	799.9	804.0	791.0	771.7	739.3	712.0	683.0	649.6	600.3	525.4	427.4
62.5°	1002.2	945.9	888.1	833.8	784.2	741.1	700.7	654.0	589.9	511.6	422.0
65°	1145.0	1026.0	934.8	856.8	786.8	726.4	676.1	615.4	543.2	472.6	391.1
67.5°	1218.5	1036.3	896.3	787.6	688.4	604.8	537.6	478.7	425.0	394.1	342.3
70°	1136.4	879.5	684.5	561.6	442.9	355.1	280.5	235.5	219.9	249.2	259.2
72.5°	846.7	572.4	407.2	314.9	241.3	192.3	147.5	115.9	94.3	99.0	128.4
75°	400.4	247.2	174.6	132.8	105.7	87.6	71.5	65.5	54.8	45.5	42.7
77.5°	155.9	113.6	93.8	68.7	48.8	39.3	33.5	32.3	33.0	32.0	31.6
80°	118.7	80.3	50.4	36.9	31.8	28.1	24.9	23.9	24.4	25.6	26.7
82.5°	66.2	41.3	30.7	26.7	23.9	20.4	18.5	17.2	17.4	18.9	21.3
85°	25.6	20.0	18.3	17.6	16.5	13.3	11.4	11.6	13.3	15.8	15.8
87.5°	2.8	2.8	3.7	2.8	2.8	2.8	2.6	3.0	3.2	4.1	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2	439.2
2.5°	435.2	435.2	435.2	434.7	435.0	434.1	434.1	433.4	434.5	433.8	433.6
5°	428.5	428.3	427.4	427.4	427.4	427.4	428.0	426.2	427.6	427.6	426.8
7.5°	417.1	417.1	414.5	416.0	415.4	416.2	417.1	416.2	417.6	418.5	417.8
10°	401.3	401.3	399.3	400.8	400.2	401.8	403.4	402.5	403.4	404.8	405.3
12.5°	383.9	383.0	381.1	381.8	381.8	382.7	383.4	384.6	385.8	387.7	388.5
15°	363.7	362.3	360.0	360.0	358.5	359.1	360.4	360.9	363.2	365.8	368.8
17.5°	343.0	339.6	337.0	334.0	331.6	333.5	335.1	336.3	338.1	342.1	344.1
20°	323.5	316.6	311.7	307.8	305.2	306.3	308.4	309.8	311.4	312.3	313.1
22.5°	304.2	296.4	289.6	284.8	280.5	281.8	280.8	280.1	281.2	278.2	278.0
25°	287.6	278.2	269.2	263.3	258.2	256.6	251.7	250.6	247.4	244.8	242.9
27.5°	275.4	263.3	253.4	246.6	238.5	232.4	226.2	219.9	216.5	212.2	210.2
30°	265.9	253.2	241.3	229.9	219.3	209.9	201.6	193.5	187.9	181.9	177.9
32.5°	257.1	245.3	230.9	215.3	200.9	190.5	179.5	170.3	161.5	153.5	147.7
35°	251.1	237.8	219.5	200.4	184.1	171.8	160.2	147.0	136.4	126.1	119.8
37.5°	247.8	231.5	209.0	187.9	169.7	155.9	141.5	126.1	113.1	103.6	94.1
40°	245.3	225.3	199.7	176.8	157.7	140.9	124.2	106.1	91.7	81.8	74.3
42.5°	242.5	218.3	191.6	167.9	146.7	127.3	107.0	87.8	74.1	67.2	63.8
45°	239.5	212.2	183.9	159.6	136.1	112.4	89.2	71.3	63.2	60.8	60.8
47.5°	238.8	208.3	178.3	151.4	124.0	95.2	72.6	61.6	59.2	59.7	60.6
50°	241.6	207.2	173.5	141.9	108.0	77.1	61.6	57.8	58.3	59.7	61.0
52.5°	248.3	208.1	168.4	128.7	88.9	63.6	56.9	56.7	58.0	60.1	61.6
55°	259.7	208.1	158.7	108.9	71.1	57.1	55.2	56.2	58.0	59.9	61.0
57.5°	284.0	206.0	141.5	87.0	59.5	54.8	54.8	56.0	57.6	59.5	60.4
60°	313.1	203.2	117.3	67.4	53.7	53.0	54.6	56.0	57.4	59.0	59.9
62.5°	314.9	196.1	92.8	55.8	50.7	51.8	54.3	56.2	56.7	57.8	59.0
65°	289.3	170.9	73.9	49.9	49.2	51.1	53.7	55.0	55.2	55.8	56.9
67.5°	253.4	139.4	59.7	47.2	47.9	49.9	51.3	52.5	53.2	54.3	54.6
70°	208.1	111.9	51.1	44.4	45.1	47.4	48.5	49.7	51.1	52.5	51.8
72.5°	147.5	87.0	44.9	41.3	42.3	44.4	45.8	46.6	47.9	49.2	48.3
75°	62.7	60.8	38.8	37.4	38.8	40.2	41.6	43.0	44.1	44.9	44.9
77.5°	32.0	35.8	33.5	33.5	34.4	35.8	36.9	38.3	39.1	39.7	40.6
80°	27.2	27.7	28.1	29.0	29.9	31.4	32.5	33.7	33.9	34.1	34.6
82.5°	22.5	23.4	23.9	25.3	26.0	26.4	27.2	27.2	27.7	27.7	26.9
85°	16.3	17.4	18.1	18.3	18.1	18.3	18.5	19.1	20.2	20.2	19.3
87.5°	4.7	4.5	5.6	5.8	6.3	7.2	8.1	9.7	10.3	10.7	10.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P152593

CATALOG NUMBER: AVS-F01-LED-E-U-SL4-8030

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	439.2	439.2	439.2	439.2
2.5°	433.4	433.8	433.0	433.2
5°	426.8	427.8	426.6	428.0
7.5°	418.5	419.9	419.7	419.5
10°	406.4	408.3	408.3	409.0
12.5°	391.1	392.2	393.2	393.7
15°	370.5	372.5	373.7	373.7
17.5°	345.6	346.9	347.7	346.7
20°	314.0	313.6	313.8	311.4
22.5°	277.5	278.2	276.2	276.6
25°	241.8	240.6	241.6	240.1
27.5°	207.2	207.4	204.9	206.0
30°	174.2	173.1	169.7	171.4
32.5°	142.4	139.4	135.9	133.8
35°	112.4	107.8	106.1	105.4
37.5°	88.3	83.1	81.6	79.7
40°	70.2	68.3	67.6	68.1
42.5°	62.9	62.9	63.4	63.6
45°	61.0	61.8	62.5	62.7
47.5°	61.3	62.0	62.9	63.2
50°	61.8	62.5	63.2	63.4
52.5°	62.0	62.0	62.5	62.7
55°	61.6	61.3	61.6	61.8
57.5°	60.6	60.1	60.4	61.0
60°	60.1	59.5	59.9	60.4
62.5°	59.0	58.8	59.2	59.5
65°	56.5	56.7	57.4	57.4
67.5°	54.1	54.3	54.6	54.8
70°	51.3	51.6	52.0	52.2
72.5°	48.1	49.0	49.7	50.7
75°	45.5	46.4	47.9	48.8
77.5°	41.1	41.8	43.4	44.6
80°	34.8	34.6	34.8	35.5
82.5°	26.7	26.7	26.4	26.2
85°	18.9	18.5	17.9	17.9
87.5°	10.3	9.9	9.7	9.3
90°	0.0	0.0	0.0	0.0

(END OF REPORT)