

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320796

Luminaire Tested: **GAN-SA2B-830-U-SLR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P320796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA2B-830-U-SLR
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(2) 80 CRI, 3000K, 800mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8166 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G3

Input Watts (W): 85
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4 fc
 Type IV - Medium - N/A

REPORT NUMBER: P320796
CATALOG NUMBER: GAN-SA2B-830-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1411.7	0.0	1411.7
	% Fixture	17.3	0.0	17.3
Street Side	Lumens	6754.3	0.0	6754.3
	% Fixture	82.7	0.0	82.7
Total	Lumens	8166.0	0.0	8166.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.0	2.4
10°-20°	398.9	4.9
20°-30°	567.3	6.9
30°-40°	817.4	10.0
40°-50°	1152.0	14.1
50°-60°	1601.5	19.6
60°-70°	1936.7	23.7
70°-80°	1190.4	14.6
80°-90°	309.8	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	8166.0	100.0
0°-180°	8166.0	100.0

Coefficient of Utilization



REPORT NUMBER: P320796


CATALOG NUMBER: GAN-SA2B-830-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	815.4	10.0			
FM	(30°-60°)	2952.2	36.2			
FH	(60°-80°)	2715.7	33.3			G2/5000
FVH	(80°-90°)	270.9	3.3			G3/500
BL	(0°-30°)	342.8	4.2	B1/500		
BM	(30°-60°)	618.7	7.6	B1/1000		
BH	(60°-80°)	411.4	5.0	B1/500		G1/500
BVH	(80°-90°)	38.8	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G3

Type IV Medium



REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2665.1	2641.6	2606.0	2570.4	2544.0	2517.2	2486.8	2456.5	2421.9	2386.9	2366.4
5°	2621.0	2555.7	2470.9	2386.0	2329.8	2273.7	2210.0	2146.3	2083.3	2020.3	1986.3
7.5°	2422.5	2324.6	2214.2	2103.9	2022.3	1940.3	1852.2	1763.7	1685.3	1606.6	1558.0
10°	2227.3	2109.8	1983.1	1856.1	1751.6	1647.1	1558.6	1469.8	1410.7	1351.7	1306.9
12.5°	2087.2	1957.0	1817.6	1677.8	1573.3	1468.9	1412.7	1356.6	1307.6	1258.6	1207.0
15°	2031.7	1884.5	1741.8	1598.8	1503.8	1408.8	1346.4	1283.7	1218.1	1152.2	1088.8
17.5°	2080.7	1908.3	1753.2	1598.2	1473.8	1349.4	1262.2	1174.7	1088.2	1001.7	928.2
20°	2233.5	2013.4	1810.7	1607.6	1442.1	1276.6	1159.7	1042.5	931.5	820.5	737.2
22.5°	2448.0	2156.8	1892.0	1627.2	1413.4	1199.2	1052.6	905.7	774.4	643.2	561.6
25°	2708.5	2346.8	2009.2	1671.3	1401.6	1131.6	951.4	771.2	632.7	494.0	435.9
27.5°	2983.1	2573.4	2154.8	1735.9	1403.6	1071.2	866.2	660.8	536.1	411.4	371.5
30°	3212.0	2832.3	2324.6	1816.6	1411.1	1005.6	785.9	566.1	463.3	360.4	334.6
32.5°	3421.3	3012.8	2452.6	1892.0	1419.6	946.8	723.8	500.5	416.6	332.4	311.1
35°	3637.4	3173.1	2542.0	1910.6	1404.9	898.8	681.4	463.9	386.6	308.9	290.9
37.5°	3875.4	3346.5	2628.2	1909.6	1380.1	850.5	648.4	446.0	367.0	287.6	274.6
40°	4140.8	3538.1	2721.6	1905.0	1357.5	809.7	623.9	437.8	356.2	274.2	263.1
42.5°	4400.4	3721.0	2808.4	1895.9	1339.2	782.3	599.8	417.2	346.4	275.2	259.6
45°	4595.3	3880.6	2883.9	1886.8	1325.5	764.3	580.8	397.3	337.3	277.2	257.3
47.5°	4743.2	4040.9	2967.4	1893.6	1324.2	754.8	567.4	380.0	320.0	259.6	251.4
50°	4931.3	4233.6	3089.2	1944.9	1342.2	739.5	551.8	363.7	303.3	242.9	254.0
52.5°	5165.3	4508.5	3277.9	2047.1	1379.7	712.4	526.9	341.5	283.1	224.3	241.6
55°	5509.1	4860.7	3519.2	2177.3	1425.1	672.6	489.4	305.9	256.3	206.3	221.7
57.5°	5817.7	5216.6	3750.7	2284.4	1453.5	622.3	442.1	261.8	226.3	190.7	199.5
60°	5955.1	5400.1	3859.1	2317.7	1436.5	555.4	388.8	222.0	199.8	177.6	176.0
62.5°	5901.6	5283.5	3752.3	2221.1	1353.6	486.1	341.8	197.5	180.9	163.9	160.3
65°	5744.9	4917.2	3453.2	1989.3	1213.6	437.8	312.1	186.4	167.8	149.2	145.3
67.5°	5436.0	4395.8	3029.5	1663.1	1035.6	408.1	295.1	182.2	159.7	136.8	132.2
70°	4881.6	3768.3	2541.4	1314.1	852.1	389.8	284.0	178.3	150.8	123.1	118.8
72.5°	4009.6	3021.3	2029.4	1037.2	712.4	387.5	282.7	177.9	143.7	109.4	105.5
75°	2870.8	2294.9	1549.2	803.2	583.4	363.7	268.4	173.0	133.9	94.4	90.8
77.5°	1931.8	1588.4	1076.8	564.8	432.9	301.0	225.6	150.2	114.6	79.0	75.4
80°	1240.6	1099.3	721.5	343.8	280.8	217.8	161.3	104.8	83.6	62.0	59.1
82.5°	910.2	818.2	501.5	184.8	156.1	127.0	98.6	70.2	57.1	44.1	42.8
85°	578.5	638.0	369.3	100.6	82.3	64.0	52.9	41.8	33.0	24.2	24.2
87.5°	112.3	155.4	102.2	48.6	35.6	22.5	19.3	15.7	8.8	1.6	2.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2345.5	2323.0	2300.4	2275.0	2249.2	2225.3	2201.2	2174.7	2179.6	2159.4	2139.1
5°	1952.4	1916.5	1880.2	1848.9	1817.6	1790.5	1763.0	1738.5	1759.8	1745.4	1731.0
7.5°	1509.0	1464.6	1419.9	1382.3	1344.8	1315.7	1286.4	1266.1	1287.0	1284.4	1281.8
10°	1262.2	1219.1	1175.7	1134.2	1092.8	1057.5	1021.9	991.9	986.6	971.6	956.3
12.5°	1155.1	1096.0	1036.6	993.2	949.7	907.6	865.5	830.3	814.3	789.4	764.3
15°	1025.5	955.6	885.8	836.5	786.8	746.0	704.9	674.5	664.4	645.1	625.9
17.5°	854.7	778.3	701.9	652.0	601.7	569.1	536.1	515.8	515.8	510.3	504.7
20°	654.0	585.7	517.5	479.3	441.1	423.8	406.1	397.7	400.3	400.6	400.6
22.5°	479.6	437.8	396.0	380.7	365.0	358.8	352.6	349.0	350.3	350.6	351.0
25°	377.7	361.7	345.4	337.6	329.4	325.5	321.6	320.3	323.2	323.5	323.5
27.5°	331.7	321.9	311.8	306.9	301.7	300.0	298.4	296.1	299.1	299.1	298.7
30°	308.5	298.1	287.6	281.4	275.2	275.9	276.2	275.6	277.5	278.8	279.8
32.5°	289.6	279.5	269.4	263.1	256.6	255.6	254.7	254.0	258.3	260.5	262.8
35°	272.6	261.5	250.4	244.5	238.7	236.4	234.1	232.5	236.4	239.3	242.3
37.5°	261.2	249.8	238.0	232.5	226.6	223.6	220.7	218.7	220.4	221.7	223.0
40°	252.0	240.3	228.2	221.7	215.2	212.2	209.3	207.6	208.6	209.0	209.3
42.5°	243.6	232.1	220.7	213.5	206.0	202.4	198.8	196.9	197.5	198.2	198.5
45°	237.4	225.9	214.2	205.7	196.9	193.0	189.0	186.8	187.1	187.1	187.1
47.5°	243.2	226.6	209.6	199.8	189.7	185.1	180.5	178.3	177.6	177.0	176.3
50°	264.8	236.4	207.6	195.2	182.5	177.6	172.4	169.8	168.1	167.5	166.8
52.5°	258.6	234.1	209.3	193.3	177.0	171.1	165.2	161.0	159.3	158.3	157.4
55°	236.7	221.4	205.7	186.4	167.2	161.9	156.4	153.4	150.5	149.9	149.2
57.5°	208.0	201.8	195.6	176.0	156.4	151.5	146.3	144.3	141.7	141.7	141.4
60°	174.0	183.2	192.3	169.8	146.9	141.4	135.8	134.2	133.2	132.9	132.6
62.5°	156.4	171.4	186.1	162.3	138.1	132.2	126.4	124.4	124.1	124.4	124.4
65°	141.4	145.9	150.5	139.4	128.3	122.4	116.2	114.3	114.9	115.9	116.9
67.5°	127.7	126.7	125.7	121.8	117.5	112.6	107.4	105.5	105.8	107.1	108.4
70°	114.6	113.3	111.7	108.7	105.8	101.5	97.3	96.0	95.7	97.3	98.6
72.5°	101.5	99.9	97.9	95.7	93.0	89.5	85.9	84.9	85.2	86.2	87.2
75°	87.2	85.9	84.2	82.3	80.0	76.7	73.5	72.8	73.5	74.4	75.4
77.5°	71.5	71.2	70.5	68.9	67.3	63.7	59.7	59.4	60.4	61.4	62.0
80°	55.8	56.2	56.5	55.2	53.9	50.0	45.7	45.4	46.4	47.3	48.3
82.5°	41.1	42.1	42.8	41.1	39.5	34.9	30.4	29.7	33.0	34.0	34.9
85°	23.8	25.1	26.4	25.1	23.8	19.3	14.7	14.4	17.3	18.9	20.6
87.5°	2.0	2.6	3.3	2.9	2.6	1.3	0.0	0.0	0.3	1.6	2.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2126.4	2113.7	2109.8	2105.8	2091.5	2076.8	2091.8	2106.5	2112.7	2118.9	2102.9
5°	1729.1	1726.8	1726.8	1726.5	1713.4	1700.0	1710.1	1719.9	1698.1	1676.2	1673.9
7.5°	1295.8	1309.9	1321.3	1332.4	1328.1	1323.9	1333.4	1342.8	1315.1	1287.0	1273.3
10°	959.5	962.5	974.9	987.3	990.2	992.8	1004.6	1016.0	994.5	972.9	963.5
12.5°	748.6	733.0	734.6	735.9	741.8	747.3	759.7	771.8	763.0	753.9	754.8
15°	606.3	586.4	578.2	569.7	576.2	582.8	591.6	600.1	600.4	600.4	608.9
17.5°	495.0	484.8	476.7	468.2	477.0	485.5	486.5	487.4	487.8	488.1	487.4
20°	405.5	410.4	407.8	405.2	408.4	411.4	414.0	416.3	413.3	410.1	401.9
22.5°	355.5	359.8	363.1	366.0	371.5	376.8	374.2	371.2	365.3	359.1	352.9
25°	326.5	329.4	332.7	336.0	340.5	344.8	340.2	335.6	331.4	327.1	322.9
27.5°	302.0	304.9	307.9	310.5	314.7	318.7	314.4	310.2	306.6	303.0	299.7
30°	282.1	284.0	286.3	288.6	292.5	296.1	292.5	288.6	286.0	283.1	280.8
32.5°	265.1	267.1	268.0	269.0	272.6	276.2	273.6	271.0	268.7	266.4	264.8
35°	246.5	250.4	251.1	251.7	255.3	258.9	257.3	255.3	252.7	250.1	247.2
37.5°	227.6	232.1	234.7	237.0	240.6	244.2	242.6	240.9	237.4	233.8	228.5
40°	211.6	213.5	218.4	223.0	228.9	234.4	231.2	227.6	222.0	216.5	213.8
42.5°	198.2	197.9	202.4	207.0	215.8	224.3	218.4	212.5	207.3	202.1	201.4
45°	186.4	185.4	187.7	190.0	199.5	208.6	202.7	196.5	193.6	190.7	190.7
47.5°	176.0	175.3	177.0	178.3	184.1	189.7	186.8	183.8	182.2	180.5	180.9
50°	166.5	165.9	167.5	168.8	171.1	173.0	173.7	174.0	173.0	172.1	172.7
52.5°	157.7	157.7	158.3	158.7	161.6	164.5	164.5	164.2	164.2	164.2	164.9
55°	150.2	150.8	150.8	150.8	155.4	159.7	158.3	157.0	157.4	157.4	158.0
57.5°	142.7	143.7	144.3	145.0	149.5	154.1	152.8	151.5	151.5	151.5	151.8
60°	134.2	135.5	136.8	138.1	142.7	147.2	145.9	144.3	144.6	145.0	145.3
62.5°	126.0	127.3	128.6	129.9	134.5	139.1	137.8	136.1	137.1	137.8	137.8
65°	118.2	119.2	120.5	121.8	126.0	130.3	129.0	127.7	129.0	129.9	130.6
67.5°	109.4	110.0	111.3	112.6	116.9	121.1	119.8	118.2	119.8	121.1	122.4
70°	99.3	99.9	101.5	102.8	107.1	111.3	109.7	108.1	109.7	111.3	112.6
72.5°	88.2	88.8	90.4	91.7	96.6	101.5	99.6	97.6	99.6	101.5	102.2
75°	76.1	76.7	78.7	80.3	85.2	90.1	88.5	86.5	88.2	89.8	90.1
77.5°	63.0	64.0	66.6	69.2	73.1	77.1	76.1	75.1	76.1	77.1	77.1
80°	49.3	50.3	53.5	56.5	58.8	61.1	61.4	61.7	62.0	62.4	62.0
82.5°	36.6	37.9	40.8	43.7	43.7	43.7	46.4	48.6	48.6	48.3	48.0
85°	22.5	24.2	26.8	29.4	27.8	26.1	30.4	34.3	34.3	34.0	33.3
87.5°	4.6	6.2	8.8	11.1	9.5	7.8	12.1	16.3	16.7	16.7	16.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2086.6	2112.0	2137.2	2143.7	2153.5	2157.8	2161.7	2193.7	2225.3	2262.6	2299.8
5°	1671.3	1690.2	1709.2	1712.1	1722.2	1727.4	1732.7	1771.5	1810.0	1862.0	1913.9
7.5°	1259.6	1264.2	1268.7	1268.1	1276.6	1288.0	1299.1	1340.6	1381.7	1437.5	1493.0
10°	954.0	964.4	974.6	984.0	1002.6	1024.2	1045.4	1087.9	1130.3	1185.5	1240.3
12.5°	755.8	767.9	779.7	790.1	811.6	840.4	868.8	919.7	970.6	1036.6	1102.2
15°	617.1	616.1	615.1	622.3	641.2	672.6	703.6	757.4	811.3	883.8	956.0
17.5°	486.8	481.9	477.0	482.5	500.2	526.0	551.4	597.1	642.5	712.7	782.9
20°	393.7	390.5	387.2	392.4	403.5	414.3	425.1	458.1	490.7	547.8	604.7
22.5°	346.4	346.1	345.4	348.4	353.6	359.1	364.4	380.4	396.0	432.9	469.5
25°	318.7	318.3	318.0	319.3	323.5	327.8	332.0	342.5	352.9	370.6	388.2
27.5°	296.4	295.8	295.1	295.5	296.4	303.0	309.2	314.1	318.7	330.7	342.5
30°	278.5	278.2	277.8	277.8	276.9	279.1	281.4	288.9	296.1	308.5	320.9
32.5°	263.1	261.5	259.9	256.3	254.0	257.3	260.5	268.4	276.2	287.6	299.1
35°	243.9	239.6	235.1	233.1	233.4	236.7	240.0	247.8	255.3	267.7	279.8
37.5°	223.0	221.7	220.1	219.7	220.7	224.0	227.2	234.1	240.6	253.0	265.1
40°	211.2	210.6	209.9	209.3	209.9	213.2	216.5	223.0	229.2	241.3	253.0
42.5°	200.8	200.5	200.1	200.1	200.5	204.1	207.6	214.2	220.4	231.2	241.9
45°	190.7	191.0	191.0	191.6	192.6	196.2	199.5	206.7	213.8	224.3	234.7
47.5°	181.2	182.2	182.8	184.5	185.4	189.4	193.0	200.8	208.6	221.7	234.4
50°	173.0	174.0	174.7	176.0	178.6	183.2	187.7	197.2	206.3	228.2	249.8
52.5°	165.5	166.5	167.5	168.8	172.1	177.3	182.5	194.3	205.7	231.2	256.6
55°	158.7	159.7	160.3	162.3	165.5	170.1	174.3	188.7	203.1	221.7	240.3
57.5°	152.1	153.1	153.8	155.1	156.7	161.6	166.2	181.5	196.9	209.9	222.7
60°	145.3	145.9	146.3	146.3	147.6	153.1	158.7	178.3	197.5	195.2	192.6
62.5°	137.8	138.4	138.8	137.8	139.4	145.3	151.2	176.6	202.1	186.4	170.8
65°	130.9	130.6	130.3	129.3	131.2	137.1	142.7	155.4	168.1	161.9	155.7
67.5°	123.4	122.4	121.5	120.1	122.1	127.3	132.2	136.5	140.7	141.4	142.0
70°	113.9	112.6	111.3	111.0	112.0	116.2	120.5	123.4	126.0	127.3	128.3
72.5°	102.8	101.9	100.9	100.2	100.6	104.1	107.4	110.0	112.6	113.6	114.3
75°	90.4	90.4	90.1	88.2	88.2	91.1	93.7	96.0	98.3	99.6	100.9
77.5°	77.1	77.4	77.4	74.8	74.4	77.4	80.0	81.9	83.6	84.9	85.9
80°	61.7	61.1	60.4	58.8	58.1	61.7	65.0	66.6	67.9	68.2	68.2
82.5°	47.3	46.0	44.4	40.8	41.1	45.1	48.6	50.0	51.3	51.3	51.3
85°	32.3	29.7	26.8	23.8	24.2	28.4	32.3	33.6	34.9	35.6	35.9
87.5°	15.3	12.7	9.8	7.5	7.5	11.1	14.4	15.0	15.7	17.0	18.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2328.2	2356.3	2385.3	2414.4	2447.7	2481.0	2519.8	2558.3	2591.3	2624.3	2651.7
5°	1958.6	2003.3	2055.9	2108.5	2175.4	2242.3	2324.3	2405.9	2478.7	2551.5	2636.1
7.5°	1551.5	1609.6	1678.1	1746.7	1833.2	1919.7	2025.8	2132.0	2234.8	2337.3	2467.3
10°	1301.4	1362.4	1430.0	1497.3	1585.4	1673.2	1785.6	1897.5	2013.1	2128.4	2275.3
12.5°	1170.1	1237.7	1297.1	1356.6	1428.1	1499.2	1607.9	1716.7	1852.5	1988.0	2129.3
15°	1030.1	1103.9	1175.0	1246.2	1324.2	1401.9	1507.7	1613.5	1762.0	1910.6	2073.2
17.5°	860.6	938.3	1025.2	1111.7	1213.6	1315.1	1450.6	1586.1	1762.0	1937.7	2129.3
20°	684.0	763.3	867.1	971.0	1097.6	1224.0	1399.6	1575.3	1812.3	2049.0	2293.6
22.5°	539.7	609.6	722.8	835.8	982.1	1128.3	1353.6	1578.6	1888.4	2197.9	2528.0
25°	437.5	486.8	598.1	709.1	877.9	1046.7	1325.5	1604.0	1999.1	2393.8	2803.2
27.5°	374.8	407.1	511.0	614.4	798.9	983.1	1314.1	1644.8	2139.5	2634.1	3102.6
30°	343.5	366.0	453.8	541.3	728.7	916.1	1300.4	1684.7	2274.6	2864.3	3336.7
32.5°	317.3	335.3	410.4	485.2	668.0	850.8	1274.0	1696.8	2369.0	3041.2	3534.9
35°	295.1	310.2	375.5	440.8	620.3	799.9	1229.5	1659.2	2428.1	3197.0	3741.2
37.5°	277.2	288.9	349.3	409.7	579.2	748.6	1178.9	1609.3	2480.6	3352.0	3973.3
40°	263.1	273.3	329.8	386.2	540.0	693.8	1135.5	1576.9	2553.1	3529.3	4218.5
42.5°	255.3	268.4	312.8	356.8	502.8	648.7	1100.6	1552.4	2620.4	3688.0	4433.0
45°	253.4	272.0	304.0	336.0	475.0	614.1	1069.6	1524.7	2663.8	3802.9	4594.6
47.5°	250.1	265.4	297.1	328.8	461.3	593.6	1052.9	1512.0	2707.2	3902.2	4728.8
50°	252.0	254.0	291.6	328.8	459.4	590.0	1071.9	1553.8	2801.3	4048.4	4882.3
52.5°	248.5	240.0	281.1	322.2	459.0	595.8	1126.4	1656.9	2975.9	4294.6	5048.5
55°	229.5	218.4	261.5	304.6	452.2	599.4	1191.3	1782.9	3210.3	4637.4	5347.2
57.5°	212.9	202.7	239.3	275.6	431.3	587.0	1258.3	1929.2	3458.1	4986.8	5683.8
60°	190.7	188.4	214.5	240.6	399.0	557.0	1313.5	2069.6	3624.7	5179.4	5813.4
62.5°	172.4	173.7	193.0	212.2	358.5	504.4	1331.7	2158.7	3620.1	5081.4	5682.8
65°	158.3	160.6	179.6	198.5	323.9	449.2	1271.7	2093.8	3436.9	4779.8	5424.6
67.5°	144.6	147.2	169.8	192.0	293.2	394.1	1121.5	1848.6	3107.5	4366.1	5096.1
70°	131.6	134.8	159.3	183.8	271.0	357.8	927.9	1497.9	2695.1	3892.0	4715.8
72.5°	117.5	120.8	146.9	173.0	256.9	340.5	756.5	1172.1	2187.1	3201.9	4033.7
75°	103.2	105.5	133.9	161.9	237.7	313.4	593.6	873.4	1673.9	2474.4	3046.8
77.5°	88.8	91.7	115.6	139.1	201.8	264.1	447.3	630.4	1228.2	1825.7	2118.9
80°	70.8	73.5	90.4	107.1	155.7	204.1	307.6	411.0	845.3	1279.5	1444.7
82.5°	54.2	57.1	68.6	79.7	111.0	142.3	186.4	230.5	561.6	892.3	906.0
85°	37.2	38.2	46.4	54.2	68.6	82.9	106.8	130.6	371.5	612.5	510.3
87.5°	18.6	18.6	24.2	29.7	36.9	44.1	56.5	68.6	118.8	169.1	97.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2686.7	2710.5	2734.7	2752.9	2771.5	2798.3	2825.1	2830.0	2835.2	2824.8	2814.3
5°	2721.3	2793.4	2865.9	2932.8	2999.8	3039.9	3080.1	3088.2	3096.4	3071.3	3045.8
7.5°	2593.0	2718.7	2844.4	2959.6	3074.9	3144.7	3214.9	3230.6	3246.6	3205.4	3164.3
10°	2421.6	2576.0	2730.4	2882.2	3034.0	3135.6	3237.1	3257.4	3277.6	3226.3	3175.1
12.5°	2289.0	2453.9	2618.7	2778.7	2939.0	3044.2	3149.3	3174.4	3199.6	3162.3	3124.8
15°	2248.2	2403.3	2558.3	2697.8	2837.5	2923.4	3009.6	3019.7	3030.1	3024.2	3018.4
17.5°	2322.3	2462.4	2602.8	2678.5	2754.6	2788.8	2823.5	2834.6	2846.0	2860.7	2875.7
20°	2501.9	2600.5	2699.4	2696.1	2692.5	2675.9	2658.9	2656.0	2653.0	2695.1	2737.6
22.5°	2769.9	2809.1	2848.6	2756.9	2665.1	2609.3	2553.1	2542.0	2530.6	2575.3	2620.4
25°	3060.8	3053.6	3046.1	2871.5	2696.5	2590.0	2483.6	2471.2	2458.8	2497.0	2535.5
27.5°	3348.8	3301.8	3254.7	3017.4	2780.0	2625.6	2471.2	2458.8	2446.4	2480.3	2514.3
30°	3560.0	3484.6	3409.2	3140.5	2871.8	2688.3	2504.8	2484.6	2464.0	2505.8	2547.6
32.5°	3724.9	3623.7	3522.5	3240.4	2958.3	2759.8	2561.3	2529.6	2497.9	2553.8	2609.6
35°	3889.4	3747.1	3604.4	3329.5	3054.3	2844.4	2634.1	2595.2	2556.4	2633.1	2709.8
37.5°	4096.4	3892.0	3687.3	3429.7	3172.1	2971.0	2769.6	2729.8	2689.9	2787.5	2885.5
40°	4321.1	4048.4	3775.8	3539.4	3303.1	3146.4	2989.3	2951.4	2913.2	3032.1	3150.9
42.5°	4507.8	4194.0	3880.3	3671.7	3462.7	3352.4	3241.7	3241.4	3240.7	3361.2	3481.7
45°	4659.6	4315.5	3971.1	3800.6	3629.9	3572.4	3515.0	3561.0	3607.0	3715.7	3824.8
47.5°	4772.9	4417.4	4061.5	3948.2	3834.9	3843.4	3851.9	3945.6	4039.3	4109.2	4179.4
50°	4846.7	4509.8	4172.5	4137.6	4102.6	4178.7	4255.1	4362.5	4470.3	4517.9	4565.6
52.5°	4954.1	4635.1	4315.8	4355.0	4394.2	4549.6	4705.0	4813.7	4922.4	4940.1	4958.0
55°	5202.6	4865.6	4528.4	4603.5	4678.9	4906.8	5135.0	5219.9	5304.8	5311.3	5317.8
57.5°	5555.5	5188.5	4821.6	4902.5	4983.5	5246.6	5510.1	5601.5	5693.3	5680.5	5667.5
60°	5819.6	5495.1	5170.2	5251.9	5333.5	5590.1	5846.7	5951.9	6057.3	6029.2	6001.2
62.5°	5835.9	5662.6	5488.9	5562.7	5636.8	5888.2	6139.6	6247.6	6355.7	6306.7	6257.8
65°	5576.4	5654.1	5731.8	5756.3	5780.8	6015.2	6249.9	6332.5	6415.5	6390.7	6365.8
67.5°	5218.9	5505.2	5791.9	5742.6	5693.3	5803.3	5913.3	5998.5	6083.8	6069.7	6055.3
70°	4862.0	5244.4	5626.7	5384.4	5141.8	5096.5	5051.1	5142.8	5234.9	5178.1	5120.9
72.5°	4254.4	4661.9	5069.7	4623.4	4177.1	4022.0	3866.9	3983.5	4100.0	4009.6	3918.8
75°	3339.6	3789.9	4240.4	3707.9	3175.4	2968.4	2761.4	2861.7	2961.9	2899.9	2837.5
77.5°	2486.2	2929.9	3373.6	2832.3	2290.6	2136.9	1982.8	2012.5	2042.5	2032.1	2021.3
80°	1686.3	1995.5	2305.0	1944.6	1584.1	1595.9	1607.9	1593.9	1579.5	1600.4	1621.3
82.5°	1076.1	1314.8	1553.8	1362.4	1171.1	1280.8	1390.5	1336.6	1282.4	1302.4	1322.6
85°	614.1	847.6	1081.3	1007.9	934.1	998.1	1062.4	978.8	895.2	931.8	968.7
87.5°	161.9	468.8	776.1	704.6	633.1	550.1	467.2	356.5	245.8	359.1	472.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796

CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8	2487.8
2.5°	2808.8	2803.2	2783.3	2763.1	2733.0	2708.2	2665.1
5°	3010.5	2975.3	2914.5	2853.5	2785.6	2707.6	2621.0
7.5°	3082.0	2999.4	2882.9	2766.0	2660.9	2537.5	2422.5
10°	3051.7	2927.9	2776.4	2624.6	2497.0	2354.9	2227.3
12.5°	2993.6	2862.0	2695.1	2528.0	2382.7	2230.2	2087.2
15°	2913.6	2808.4	2652.1	2495.7	2349.4	2201.2	2031.7
17.5°	2826.1	2776.1	2663.2	2549.9	2423.2	2279.5	2080.7
20°	2755.5	2773.8	2728.8	2683.7	2582.2	2456.8	2233.5
22.5°	2707.9	2795.7	2830.3	2865.2	2804.2	2706.2	2448.0
25°	2681.1	2826.7	2942.6	3058.9	3031.8	2956.3	2708.5
27.5°	2692.9	2871.5	3051.3	3231.6	3256.7	3235.8	2983.1
30°	2728.1	2909.0	3128.1	3347.5	3447.7	3475.8	3212.0
32.5°	2786.9	2964.2	3202.8	3441.8	3593.3	3682.8	3421.3
35°	2875.7	3041.5	3290.3	3539.1	3735.0	3898.3	3637.4
37.5°	3028.2	3170.8	3400.4	3630.2	3884.2	4129.4	3875.4
40°	3251.5	3352.4	3546.3	3740.6	4060.2	4391.2	4140.8
42.5°	3533.2	3585.2	3738.9	3892.7	4244.0	4628.9	4400.4
45°	3838.5	3852.2	3948.9	4045.8	4389.6	4790.9	4595.3
47.5°	4132.3	4085.3	4123.9	4162.4	4501.3	4906.4	4743.2
50°	4434.7	4303.7	4283.5	4263.3	4612.9	5042.6	4931.3
52.5°	4742.2	4526.4	4446.4	4366.1	4746.1	5223.1	5165.3
55°	5043.2	4768.7	4660.9	4553.2	4949.9	5443.5	5509.1
57.5°	5356.3	5045.2	4945.3	4845.4	5249.3	5722.7	5817.7
60°	5693.3	5385.1	5305.1	5224.8	5621.4	6024.3	5955.1
62.5°	6012.9	5768.0	5725.9	5683.5	5997.9	6256.1	5901.6
65°	6226.4	6086.7	6125.9	6165.4	6282.6	6313.9	5744.9
67.5°	6083.8	6112.2	6277.7	6443.5	6362.9	6142.2	5436.0
70°	5291.0	5461.5	5853.6	6246.0	6067.1	5682.2	4881.6
72.5°	4110.1	4301.8	4883.9	5466.4	5301.5	4830.0	4009.6
75°	3053.6	3270.1	3912.6	4555.1	4326.3	3612.9	2870.8
77.5°	2166.2	2311.2	2945.6	3580.3	3207.1	2404.9	1931.8
80°	1576.9	1532.5	1886.1	2239.7	2177.7	1590.6	1240.6
82.5°	1214.2	1105.8	1272.3	1438.8	1429.7	1103.9	910.2
85°	925.3	881.8	1029.1	1176.3	1050.3	747.7	578.5
87.5°	539.4	606.6	780.0	953.7	715.7	226.9	112.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320796
 CATALOG NUMBER: GAN-SA2B-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)