

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P320806

Luminaire Tested: **GAN-SA2C-830-U-SLR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P320806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1903-205-26)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: GAN-SA2C-830-U-SLR
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(2) 80 CRI, 3000K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10107 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 113
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.9 fc
 Type IV - Medium - N/A

REPORT NUMBER: P320806
CATALOG NUMBER: GAN-SA2C-830-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1747.3	0.0	1747.3
	% Fixture	17.3	0.0	17.3
Street Side	Lumens	8359.7	0.0	8359.7
	% Fixture	82.7	0.0	82.7
Total	Lumens	10107.0	0.0	10107.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.6	2.4
10°-20°	493.7	4.9
20°-30°	702.1	6.9
30°-40°	1011.7	10.0
40°-50°	1425.8	14.1
50°-60°	1982.2	19.6
60°-70°	2397.0	23.7
70°-80°	1473.4	14.6
80°-90°	383.4	3.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	10107.0	100.0
0°-180°	10107.0	100.0

Coefficient of Utilization



REPORT NUMBER: P320806


CATALOG NUMBER: GAN-SA2C-830-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1009.2	10.0			
FM	(30°-60°)	3653.9	36.2			
FH	(60°-80°)	3361.2	33.3			G2/5000
FVH	(80°-90°)	335.3	3.3			G3/500
BL	(0°-30°)	424.2	4.2	B1/500		
BM	(30°-60°)	765.8	7.6	B1/1000		
BH	(60°-80°)	509.2	5.0	B2/1000		G2/1000
BVH	(80°-90°)	48.1	0.5			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type IV Medium





REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	3298.6	3269.5	3225.4	3181.4	3148.7	3115.5	3078.0	3040.4	2997.5	2954.3	2928.8
5°	3244.0	3163.2	3058.2	2953.1	2883.6	2814.1	2735.3	2656.5	2578.5	2500.5	2458.5
7.5°	2998.3	2877.1	2740.5	2604.0	2502.9	2401.5	2292.4	2182.9	2085.9	1988.5	1928.3
10°	2756.7	2611.2	2454.4	2297.3	2167.9	2038.6	1929.1	1819.2	1746.1	1672.9	1617.6
12.5°	2583.3	2422.1	2249.6	2076.6	1947.3	1818.0	1748.5	1679.0	1618.4	1557.8	1493.9
15°	2514.7	2332.4	2155.8	1978.8	1861.2	1743.6	1666.5	1588.9	1507.7	1426.0	1347.6
17.5°	2575.3	2361.9	2170.0	1978.0	1824.1	1670.1	1562.2	1453.9	1346.8	1239.7	1148.8
20°	2764.4	2492.0	2241.1	1989.7	1784.9	1580.0	1435.3	1290.3	1152.9	1015.5	912.4
22.5°	3029.9	2669.4	2341.7	2014.0	1749.3	1484.2	1302.8	1120.9	958.5	796.1	695.0
25°	3352.3	2904.6	2486.8	2068.5	1734.8	1400.6	1177.5	954.5	783.1	611.4	539.5
27.5°	3692.2	3185.0	2667.0	2148.5	1737.2	1325.8	1072.1	817.9	663.5	509.2	459.9
30°	3975.4	3505.5	2877.1	2248.4	1746.5	1244.6	972.6	700.7	573.4	446.1	414.2
32.5°	4234.5	3728.9	3035.5	2341.7	1757.0	1171.9	895.9	619.5	515.6	411.4	385.1
35°	4502.0	3927.4	3146.2	2364.7	1738.8	1112.5	843.3	574.2	478.4	382.3	360.0
37.5°	4796.6	4141.9	3252.9	2363.5	1708.1	1052.7	802.5	552.0	454.2	356.0	339.8
40°	5125.1	4379.1	3368.5	2357.9	1680.2	1002.1	772.2	541.9	440.9	339.4	325.7
42.5°	5446.3	4605.4	3476.0	2346.6	1657.6	968.2	742.3	516.4	428.7	340.6	321.3
45°	5687.6	4803.0	3569.3	2335.2	1640.6	946.0	718.9	491.8	417.4	343.1	318.4
47.5°	5870.6	5001.4	3672.8	2343.7	1639.0	934.3	702.3	470.4	396.0	321.3	311.1
50°	6103.4	5239.8	3823.5	2407.2	1661.2	915.3	682.9	450.2	375.4	300.6	314.4
52.5°	6393.1	5580.1	4057.1	2533.6	1707.7	881.7	652.2	422.7	350.3	277.6	299.0
55°	6818.6	6016.1	4355.7	2694.9	1763.9	832.4	605.7	378.6	317.2	255.4	274.4
57.5°	7200.5	6456.6	4642.2	2827.4	1799.0	770.2	547.1	324.1	280.0	236.0	246.9
60°	7370.6	6683.7	4776.3	2868.6	1778.0	687.4	481.3	274.8	247.3	219.8	217.8
62.5°	7304.3	6539.4	4644.2	2749.0	1675.4	601.7	423.1	244.5	223.9	202.9	198.4
65°	7110.4	6086.0	4274.1	2462.1	1502.0	541.9	386.3	230.7	207.7	184.7	179.8
67.5°	6728.1	5440.7	3749.6	2058.4	1281.8	505.1	365.3	225.5	197.6	169.3	163.7
70°	6042.0	4664.0	3145.4	1626.5	1054.7	482.5	351.6	220.6	186.7	152.3	147.1
72.5°	4962.6	3739.5	2511.8	1283.8	881.7	479.7	349.9	220.2	177.8	135.4	130.5
75°	3553.2	2840.4	1917.4	994.1	722.1	450.2	332.2	214.2	165.7	116.8	112.3
77.5°	2391.0	1965.9	1332.7	699.1	535.8	372.6	279.2	185.9	141.8	97.8	93.3
80°	1535.5	1360.6	893.0	425.5	347.5	269.5	199.6	129.7	103.4	76.8	73.1
82.5°	1126.6	1012.7	620.7	228.7	193.2	157.2	122.0	86.9	70.7	54.6	52.9
85°	716.0	789.6	457.0	124.5	101.8	79.2	65.5	51.7	40.8	29.9	29.9
87.5°	139.0	192.3	126.5	60.2	44.0	27.9	23.8	19.4	10.9	2.0	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	2903.0	2875.1	2847.2	2815.7	2783.8	2754.3	2724.4	2691.6	2697.7	2672.7	2647.6
5°	2416.5	2372.0	2327.2	2288.4	2249.6	2216.0	2182.1	2151.8	2178.0	2160.3	2142.5
7.5°	1867.7	1812.7	1757.4	1710.9	1664.4	1628.5	1592.1	1567.1	1592.9	1589.7	1586.5
10°	1562.2	1508.9	1455.1	1403.8	1352.5	1308.8	1264.8	1227.6	1221.2	1202.6	1183.6
12.5°	1429.7	1356.5	1283.0	1229.2	1175.5	1123.4	1071.2	1027.6	1007.8	977.1	946.0
15°	1269.2	1182.8	1096.3	1035.3	973.9	923.3	872.4	834.9	822.3	798.5	774.6
17.5°	1057.9	963.4	868.8	807.0	744.7	704.3	663.5	638.5	638.5	631.6	624.7
20°	809.4	724.9	640.5	593.2	545.9	524.5	502.7	492.2	495.4	495.8	495.8
22.5°	593.6	541.9	490.2	471.2	451.8	444.1	436.4	432.0	433.6	434.0	434.4
25°	467.5	447.7	427.5	417.8	407.7	402.9	398.0	396.4	400.0	400.5	400.5
27.5°	410.6	398.4	385.9	379.8	373.4	371.4	369.3	366.5	370.1	370.1	369.7
30°	381.9	368.9	356.0	348.3	340.6	341.5	341.9	341.1	343.5	345.1	346.3
32.5°	358.4	345.9	333.4	325.7	317.6	316.4	315.2	314.4	319.6	322.5	325.3
35°	337.4	323.7	309.9	302.7	295.4	292.6	289.7	287.7	292.6	296.2	299.8
37.5°	323.3	309.1	294.6	287.7	280.4	276.8	273.2	270.7	272.8	274.4	276.0
40°	312.0	297.4	282.5	274.4	266.3	262.7	259.0	257.0	258.2	258.6	259.0
42.5°	301.5	287.3	273.2	264.3	255.0	250.5	246.1	243.7	244.5	245.3	245.7
45°	293.8	279.6	265.1	254.6	243.7	238.8	234.0	231.1	231.5	231.5	231.5
47.5°	301.0	280.4	259.4	247.3	234.8	229.1	223.5	220.6	219.8	219.0	218.2
50°	327.7	292.6	257.0	241.6	225.9	219.8	213.4	210.1	208.1	207.3	206.5
52.5°	320.0	289.7	259.0	239.2	219.0	211.7	204.5	199.2	197.2	196.0	194.8
55°	293.0	274.0	254.6	230.7	206.9	200.4	193.6	189.9	186.3	185.5	184.7
57.5°	257.4	249.7	242.1	217.8	193.6	187.5	181.0	178.6	175.4	175.4	175.0
60°	215.4	226.7	238.0	210.1	181.8	175.0	168.1	166.1	164.9	164.5	164.1
62.5°	193.6	212.1	230.3	200.8	170.9	163.7	156.4	154.0	153.6	154.0	154.0
65°	175.0	180.6	186.3	172.5	158.8	151.5	143.9	141.4	142.2	143.5	144.7
67.5°	158.0	156.8	155.6	150.7	145.5	139.4	132.9	130.5	130.9	132.5	134.2
70°	141.8	140.2	138.2	134.6	130.9	125.7	120.4	118.8	118.4	120.4	122.0
72.5°	125.7	123.7	121.2	118.4	115.2	110.7	106.3	105.1	105.5	106.7	107.9
75°	107.9	106.3	104.3	101.8	99.0	95.0	90.9	90.1	90.9	92.1	93.3
77.5°	88.5	88.1	87.3	85.3	83.2	78.8	73.9	73.5	74.8	76.0	76.8
80°	69.1	69.5	69.9	68.3	66.7	61.8	56.6	56.2	57.4	58.6	59.8
82.5°	50.9	52.1	52.9	50.9	48.9	43.2	37.6	36.8	40.8	42.0	43.2
85°	29.5	31.1	32.7	31.1	29.5	23.8	18.2	17.8	21.4	23.4	25.5
87.5°	2.4	3.2	4.0	3.6	3.2	1.6	0.0	0.0	0.4	2.0	3.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	2631.8	2616.1	2611.2	2606.4	2588.6	2570.4	2589.0	2607.2	2614.9	2622.5	2602.7
5°	2140.1	2137.2	2137.2	2136.8	2120.7	2104.1	2116.6	2128.7	2101.7	2074.6	2071.8
7.5°	1603.8	1621.2	1635.4	1649.1	1643.8	1638.6	1650.3	1662.0	1627.7	1592.9	1576.0
10°	1187.6	1191.3	1206.6	1222.0	1225.6	1228.8	1243.4	1257.5	1230.9	1204.2	1192.5
12.5°	926.6	907.2	909.2	910.8	918.1	925.0	940.3	955.3	944.4	933.0	934.3
15°	750.4	725.7	715.6	705.1	713.2	721.3	732.2	742.7	743.1	743.1	753.6
17.5°	612.6	600.1	590.0	579.5	590.4	600.9	602.1	603.3	603.7	604.1	603.3
20°	501.9	507.9	504.7	501.5	505.5	509.2	512.4	515.2	511.6	507.5	497.4
22.5°	440.1	445.3	449.3	453.0	459.9	466.3	463.1	459.5	452.2	444.5	436.8
25°	404.1	407.7	411.8	415.8	421.5	426.7	421.1	415.4	410.2	404.9	399.6
27.5°	373.8	377.4	381.1	384.3	389.5	394.4	389.1	383.9	379.4	375.0	371.0
30°	349.1	351.6	354.4	357.2	362.1	366.5	362.1	357.2	354.0	350.3	347.5
32.5°	328.1	330.5	331.8	333.0	337.4	341.9	338.6	335.4	332.6	329.7	327.7
35°	305.1	309.9	310.7	311.6	316.0	320.4	318.4	316.0	312.8	309.5	305.9
37.5°	281.7	287.3	290.5	293.4	297.8	302.3	300.2	298.2	293.8	289.3	282.9
40°	261.9	264.3	270.3	276.0	283.3	290.1	286.1	281.7	274.8	267.9	264.7
42.5°	245.3	244.9	250.5	256.2	267.1	277.6	270.3	263.1	256.6	250.1	249.3
45°	230.7	229.5	232.4	235.2	246.9	258.2	250.9	243.3	239.6	236.0	236.0
47.5°	217.8	217.0	219.0	220.6	227.9	234.8	231.1	227.5	225.5	223.5	223.9
50°	206.1	205.3	207.3	208.9	211.7	214.2	215.0	215.4	214.2	213.0	213.8
52.5°	195.2	195.2	196.0	196.4	200.0	203.7	203.7	203.3	203.3	203.3	204.1
55°	185.9	186.7	186.7	186.7	192.3	197.6	196.0	194.4	194.8	194.8	195.6
57.5°	176.6	177.8	178.6	179.4	185.1	190.7	189.1	187.5	187.5	187.5	187.9
60°	166.1	167.7	169.3	170.9	176.6	182.2	180.6	178.6	179.0	179.4	179.8
62.5°	156.0	157.6	159.2	160.8	166.5	172.1	170.5	168.5	169.7	170.5	170.5
65°	146.3	147.5	149.1	150.7	156.0	161.2	159.6	158.0	159.6	160.8	161.6
67.5°	135.4	136.2	137.8	139.4	144.7	149.9	148.3	146.3	148.3	149.9	151.5
70°	122.8	123.7	125.7	127.3	132.5	137.8	135.8	133.8	135.8	137.8	139.4
72.5°	109.1	109.9	111.9	113.5	119.6	125.7	123.2	120.8	123.2	125.7	126.5
75°	94.2	95.0	97.4	99.4	105.5	111.5	109.5	107.1	109.1	111.1	111.5
77.5°	78.0	79.2	82.4	85.7	90.5	95.4	94.2	92.9	94.2	95.4	95.4
80°	61.0	62.2	66.3	69.9	72.7	75.6	76.0	76.4	76.8	77.2	76.8
82.5°	45.3	46.9	50.5	54.1	54.1	54.1	57.4	60.2	60.2	59.8	59.4
85°	27.9	29.9	33.1	36.4	34.3	32.3	37.6	42.4	42.4	42.0	41.2
87.5°	5.7	7.7	10.9	13.7	11.7	9.7	15.0	20.2	20.6	20.6	19.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	2582.5	2614.1	2645.2	2653.3	2665.4	2670.6	2675.5	2715.1	2754.3	2800.3	2846.4
5°	2068.5	2092.0	2115.4	2119.0	2131.6	2138.0	2144.5	2192.6	2240.3	2304.5	2368.8
7.5°	1559.0	1564.6	1570.3	1569.5	1580.0	1594.1	1607.9	1659.2	1710.1	1779.2	1847.9
10°	1180.8	1193.7	1206.2	1217.9	1241.0	1267.6	1293.9	1346.4	1399.0	1467.3	1535.1
12.5°	935.5	950.4	965.0	977.9	1004.6	1040.1	1075.3	1138.3	1201.4	1283.0	1364.2
15°	763.7	762.5	761.3	770.2	793.6	832.4	870.8	937.5	1004.2	1093.9	1183.2
17.5°	602.5	596.4	590.4	597.2	619.1	651.0	682.5	739.1	795.2	882.1	969.0
20°	487.3	483.3	479.3	485.7	499.5	512.8	526.1	566.9	607.3	678.1	748.4
22.5°	428.7	428.3	427.5	431.2	437.6	444.5	451.0	470.8	490.2	535.8	581.1
25°	394.4	394.0	393.6	395.2	400.5	405.7	411.0	423.9	436.8	458.6	480.5
27.5°	366.9	366.1	365.3	365.7	366.9	375.0	382.7	388.7	394.4	409.3	423.9
30°	344.7	344.3	343.9	343.9	342.7	345.5	348.3	357.6	366.5	381.9	397.2
32.5°	325.7	323.7	321.7	317.2	314.4	318.4	322.5	332.2	341.9	356.0	370.1
35°	301.9	296.6	290.9	288.5	288.9	293.0	297.0	306.7	316.0	331.4	346.3
37.5°	276.0	274.4	272.4	272.0	273.2	277.2	281.2	289.7	297.8	313.2	328.1
40°	261.4	260.6	259.8	259.0	259.8	263.9	267.9	276.0	283.7	298.6	313.2
42.5°	248.5	248.1	247.7	247.7	248.1	252.6	257.0	265.1	272.8	286.1	299.4
45°	236.0	236.4	236.4	237.2	238.4	242.9	246.9	255.8	264.7	277.6	290.5
47.5°	224.3	225.5	226.3	228.3	229.5	234.4	238.8	248.5	258.2	274.4	290.1
50°	214.2	215.4	216.2	217.8	221.0	226.7	232.4	244.1	255.4	282.5	309.1
52.5°	204.9	206.1	207.3	208.9	213.0	219.4	225.9	240.4	254.6	286.1	317.6
55°	196.4	197.6	198.4	200.8	204.9	210.5	215.8	233.6	251.3	274.4	297.4
57.5°	188.3	189.5	190.3	191.9	194.0	200.0	205.7	224.7	243.7	259.8	275.6
60°	179.8	180.6	181.0	181.0	182.6	189.5	196.4	220.6	244.5	241.6	238.4
62.5°	170.5	171.3	171.7	170.5	172.5	179.8	187.1	218.6	250.1	230.7	211.3
65°	162.0	161.6	161.2	160.0	162.4	169.7	176.6	192.3	208.1	200.4	192.8
67.5°	152.7	151.5	150.3	148.7	151.1	157.6	163.7	168.9	174.2	175.0	175.8
70°	141.0	139.4	137.8	137.4	138.6	143.9	149.1	152.7	156.0	157.6	158.8
72.5°	127.3	126.1	124.9	124.1	124.5	128.9	132.9	136.2	139.4	140.6	141.4
75°	111.9	111.9	111.5	109.1	109.1	112.7	116.0	118.8	121.6	123.2	124.9
77.5°	95.4	95.8	95.8	92.5	92.1	95.8	99.0	101.4	103.4	105.1	106.3
80°	76.4	75.6	74.8	72.7	71.9	76.4	80.4	82.4	84.1	84.5	84.5
82.5°	58.6	57.0	55.0	50.5	50.9	55.8	60.2	61.8	63.4	63.4	63.4
85°	40.0	36.8	33.1	29.5	29.9	35.2	40.0	41.6	43.2	44.0	44.4
87.5°	19.0	15.8	12.1	9.3	9.3	13.7	17.8	18.6	19.4	21.0	22.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	2881.6	2916.3	2952.3	2988.2	3029.5	3070.7	3118.8	3166.5	3207.3	3248.1	3282.0
5°	2424.1	2479.5	2544.6	2609.6	2692.5	2775.3	2876.7	2977.7	3067.9	3158.0	3262.6
7.5°	1920.2	1992.2	2077.0	2161.9	2269.0	2376.1	2507.4	2638.7	2766.0	2892.9	3053.7
10°	1610.7	1686.3	1769.9	1853.2	1962.3	2071.0	2210.0	2348.6	2491.6	2634.3	2816.1
12.5°	1448.3	1531.9	1605.5	1679.0	1767.5	1855.6	1990.1	2124.7	2292.8	2460.5	2635.5
15°	1274.9	1366.2	1454.3	1542.4	1639.0	1735.2	1866.1	1997.0	2180.9	2364.7	2566.0
17.5°	1065.2	1161.4	1268.8	1375.9	1502.0	1627.7	1795.4	1963.1	2180.9	2398.3	2635.5
20°	846.6	944.8	1073.3	1201.8	1358.6	1514.9	1732.3	1949.7	2243.1	2536.1	2838.7
22.5°	668.0	754.4	894.7	1034.5	1215.5	1396.5	1675.4	1953.8	2337.3	2720.3	3128.9
25°	541.5	602.5	740.3	877.7	1086.6	1295.5	1640.6	1985.3	2474.2	2962.8	3469.5
27.5°	463.9	503.9	632.4	760.5	988.8	1216.7	1626.5	2035.8	2648.0	3260.2	3840.1
30°	425.1	453.0	561.7	670.0	901.9	1133.9	1609.5	2085.1	2815.3	3545.1	4129.8
32.5°	392.8	415.0	507.9	600.5	826.8	1053.1	1576.8	2100.1	2932.1	3764.1	4375.1
35°	365.3	383.9	464.7	545.5	767.8	990.0	1521.8	2053.6	3005.2	3956.9	4630.5
37.5°	343.1	357.6	432.4	507.1	716.9	926.6	1459.2	1991.8	3070.3	4148.8	4917.8
40°	325.7	338.2	408.1	478.0	668.4	858.7	1405.4	1951.8	3160.0	4368.2	5221.2
42.5°	316.0	332.2	387.1	441.7	622.3	802.9	1362.2	1921.4	3243.2	4564.6	5486.7
45°	313.6	336.6	376.2	415.8	588.0	760.1	1323.8	1887.1	3297.0	4706.8	5686.8
47.5°	309.5	328.5	367.7	406.9	571.0	734.6	1303.2	1871.3	3350.7	4829.7	5852.8
50°	312.0	314.4	360.9	406.9	568.6	730.2	1326.6	1923.1	3467.1	5010.7	6042.8
52.5°	307.5	297.0	347.9	398.8	568.2	737.5	1394.1	2050.8	3683.3	5315.4	6248.4
55°	284.1	270.3	323.7	377.0	559.7	741.9	1474.5	2206.7	3973.4	5739.7	6618.2
57.5°	263.5	250.9	296.2	341.1	533.8	726.6	1557.4	2387.8	4280.1	6172.1	7034.8
60°	236.0	233.2	265.5	297.8	493.8	689.4	1625.7	2561.5	4486.2	6410.5	7195.2
62.5°	213.4	215.0	238.8	262.7	443.7	624.3	1648.3	2671.8	4480.6	6289.3	7033.6
65°	196.0	198.8	222.2	245.7	400.9	556.0	1573.9	2591.4	4253.9	5915.9	6714.0
67.5°	179.0	182.2	210.1	237.6	362.9	487.7	1388.0	2288.0	3846.1	5403.9	6307.4
70°	162.8	166.9	197.2	227.5	335.4	442.9	1148.4	1854.0	3335.8	4817.2	5836.7
72.5°	145.5	149.5	181.8	214.2	318.0	421.5	936.3	1450.7	2707.0	3962.9	4992.5
75°	127.7	130.5	165.7	200.4	294.2	387.9	734.6	1080.9	2071.8	3062.6	3771.0
77.5°	109.9	113.5	143.0	172.1	249.7	326.9	553.6	780.3	1520.2	2259.7	2622.5
80°	87.7	90.9	111.9	132.5	192.8	252.6	380.7	508.7	1046.2	1583.6	1788.1
82.5°	67.1	70.7	84.9	98.6	137.4	176.2	230.7	285.3	695.0	1104.4	1121.4
85°	46.1	47.3	57.4	67.1	84.9	102.6	132.1	161.6	459.9	758.1	631.6
87.5°	23.0	23.0	29.9	36.8	45.7	54.6	69.9	84.9	147.1	209.3	120.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	3325.3	3354.8	3384.7	3407.3	3430.3	3463.5	3496.6	3502.7	3509.1	3496.2	3483.3
5°	3368.1	3457.4	3547.1	3629.9	3712.8	3762.5	3812.2	3822.3	3832.4	3801.3	3769.8
7.5°	3209.3	3364.9	3520.4	3663.1	3805.7	3892.2	3979.1	3998.5	4018.3	3967.4	3916.4
10°	2997.1	3188.3	3379.4	3567.3	3755.2	3880.9	4006.6	4031.6	4056.7	3993.2	3929.8
12.5°	2833.1	3037.1	3241.2	3439.2	3637.6	3767.7	3897.9	3929.0	3960.1	3914.0	3867.5
15°	2782.6	2974.5	3166.5	3339.0	3511.9	3618.2	3724.9	3737.4	3750.4	3743.1	3735.8
17.5°	2874.3	3047.6	3221.4	3315.2	3409.3	3451.7	3494.6	3508.3	3522.5	3540.6	3559.2
20°	3096.5	3218.6	3341.0	3337.0	3332.5	3311.9	3290.9	3287.3	3283.6	3335.8	3388.3
22.5°	3428.3	3476.8	3525.7	3412.1	3298.6	3229.5	3160.0	3146.2	3132.1	3187.5	3243.2
25°	3788.3	3779.5	3770.2	3554.0	3337.4	3205.6	3073.9	3058.6	3043.2	3090.5	3138.2
27.5°	4144.8	4086.6	4028.4	3734.6	3440.8	3249.7	3058.6	3043.2	3027.8	3069.9	3111.9
30°	4406.2	4312.9	4219.5	3886.9	3554.4	3327.3	3100.2	3075.1	3049.7	3101.4	3153.1
32.5°	4610.3	4485.0	4359.7	4010.6	3661.5	3415.8	3170.1	3130.9	3091.7	3160.8	3229.9
35°	4813.9	4637.7	4461.2	4120.9	3780.3	3520.4	3260.2	3212.1	3164.0	3259.0	3353.9
37.5°	5070.1	4817.2	4563.8	4245.0	3926.1	3677.2	3427.9	3378.6	3329.3	3450.1	3571.3
40°	5348.1	5010.7	4673.3	4380.7	4088.2	3894.2	3699.9	3653.0	3605.7	3752.8	3899.9
42.5°	5579.3	5190.9	4802.6	4544.4	4285.8	4149.2	4012.2	4011.8	4011.0	4160.1	4309.2
45°	5767.2	5341.3	4914.9	4704.0	4492.7	4421.6	4350.4	4407.4	4464.4	4599.0	4733.9
47.5°	5907.4	5467.3	5026.9	4886.7	4746.4	4757.0	4767.5	4883.4	4999.4	5085.9	5172.8
50°	5998.7	5581.7	5164.3	5121.0	5077.8	5172.0	5266.5	5399.5	5532.8	5591.8	5650.8
52.5°	6131.7	5736.9	5341.7	5390.2	5438.7	5631.0	5823.3	5957.9	6092.5	6114.3	6136.5
55°	6439.2	6022.2	5604.7	5697.7	5791.0	6073.1	6355.5	6460.6	6565.7	6573.7	6581.8
57.5°	6876.0	6421.8	5967.6	6067.8	6168.0	6493.7	6819.8	6933.0	7046.5	7030.8	7014.6
60°	7202.9	6801.2	6399.2	6500.2	6601.2	6918.8	7236.4	7366.6	7497.1	7462.3	7427.6
62.5°	7223.1	7008.5	6793.6	6884.9	6976.6	7287.8	7598.9	7732.7	7866.4	7805.8	7745.2
65°	6901.9	6998.0	7094.2	7124.5	7154.8	7445.0	7735.5	7837.7	7940.4	7909.7	7879.0
67.5°	6459.4	6813.8	7168.6	7107.5	7046.5	7182.7	7318.9	7424.3	7529.8	7512.4	7494.7
70°	6017.7	6490.9	6964.1	6664.3	6364.0	6307.8	6251.7	6365.2	6479.2	6408.9	6338.2
72.5°	5265.7	5770.0	6274.7	5722.3	5169.9	4978.0	4786.0	4930.3	5074.6	4962.6	4850.3
75°	4133.4	4690.7	5248.3	4589.3	3930.2	3674.0	3417.8	3541.9	3665.9	3589.1	3511.9
77.5°	3077.1	3626.3	4175.5	3505.5	2835.1	2644.8	2454.0	2490.8	2528.0	2515.1	2501.7
80°	2087.1	2469.8	2852.9	2406.8	1960.6	1975.2	1990.1	1972.8	1955.0	1980.9	2006.7
82.5°	1331.9	1627.3	1923.1	1686.3	1449.5	1585.2	1721.0	1654.3	1587.3	1611.9	1637.0
85°	760.1	1049.0	1338.3	1247.4	1156.1	1235.3	1314.9	1211.5	1108.0	1153.3	1198.9
87.5°	200.4	580.3	960.5	872.0	783.5	680.9	578.3	441.3	304.3	444.5	584.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P320806

CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2	3079.2
2.5°	3476.4	3469.5	3444.9	3419.8	3382.6	3351.9	3298.6
5°	3726.1	3682.5	3607.3	3531.7	3447.7	3351.1	3244.0
7.5°	3814.6	3712.4	3568.1	3423.5	3293.3	3140.6	2998.3
10°	3777.0	3623.9	3436.4	3248.5	3090.5	2914.7	2756.7
12.5°	3705.1	3542.3	3335.8	3128.9	2949.1	2760.3	2583.3
15°	3606.1	3476.0	3282.4	3088.9	2907.8	2724.4	2514.7
17.5°	3497.8	3436.0	3296.2	3155.9	2999.2	2821.4	2575.3
20°	3410.5	3433.2	3377.4	3321.6	3195.9	3040.8	2764.4
22.5°	3351.5	3460.2	3503.1	3546.3	3470.7	3349.5	3029.9
25°	3318.4	3498.6	3642.1	3785.9	3752.4	3659.0	3352.3
27.5°	3332.9	3554.0	3776.6	3999.7	4030.8	4004.9	3692.2
30°	3376.6	3600.4	3871.6	4143.1	4267.2	4301.9	3975.4
32.5°	3449.3	3668.7	3964.1	4259.9	4447.4	4558.1	4234.5
35°	3559.2	3764.5	4072.4	4380.3	4622.8	4824.8	4502.0
37.5°	3747.9	3924.5	4208.6	4493.1	4807.5	5110.9	4796.6
40°	4024.3	4149.2	4389.2	4629.7	5025.3	5435.0	5125.1
42.5°	4373.1	4437.3	4627.6	4818.0	5252.8	5729.2	5446.3
45°	4750.9	4767.9	4887.5	5007.5	5433.0	5929.6	5687.6
47.5°	5114.6	5056.4	5104.1	5151.7	5571.2	6072.7	5870.6
50°	5488.8	5326.7	5301.7	5276.6	5709.4	6241.2	6103.4
52.5°	5869.4	5602.3	5503.3	5403.9	5874.3	6464.6	6393.1
55°	6242.0	5902.1	5768.8	5635.4	6126.4	6737.4	6818.6
57.5°	6629.5	6244.4	6120.8	5997.1	6497.0	7082.9	7200.5
60°	7046.5	6665.1	6566.1	6466.7	6957.6	7456.3	7370.6
62.5°	7442.1	7139.1	7086.9	7034.4	7423.5	7743.2	7304.3
65°	7706.4	7533.5	7581.9	7630.8	7775.9	7814.7	7110.4
67.5°	7529.8	7565.0	7769.8	7975.1	7875.3	7602.1	6728.1
70°	6548.7	6759.6	7244.9	7730.7	7509.2	7032.8	6042.0
72.5°	5087.1	5324.3	6044.8	6765.7	6561.6	5978.1	4962.6
75°	3779.5	4047.4	4842.6	5637.9	5354.6	4471.7	3553.2
77.5°	2681.1	2860.6	3645.7	4431.3	3969.4	2976.5	2391.0
80°	1951.8	1896.8	2334.4	2772.1	2695.3	1968.7	1535.5
82.5°	1502.8	1368.7	1574.7	1780.8	1769.5	1366.2	1126.6
85°	1145.2	1091.4	1273.7	1455.9	1300.0	925.4	716.0
87.5°	667.6	750.8	965.4	1180.3	885.8	280.8	139.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P320806
 CATALOG NUMBER: GAN-SA2C-830-U-SLR

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)