

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: STREETWORKS

Report Number: P560043

Luminaire Tested: **SDL-PA1-20-740-U-T4W**

Issue Date: 7/26/2021

Test Information

Test Method: LM-79-08
Report Number: P560043
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/26/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: STREETWORKS
Catalog Number: SDL-PA1-20-740-U-T4W
Description: Springdale
(1) 70 CRI, 4000K, 260mA LIGHT ENGINE WITH 24 LEDS AND TYPE IV WIDE OPTICS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2708.9 lumens
Efficiency: N/A
Efficacy: 129.0 lumens/watt
Luminous Opening: Rectangular w/ Sides (W: 1.17' x L: 1.17' x H: 1.08')
IES Classification: Type IV - Medium
BUG Rating: B1 - U0 - G1

Input Watts (W): 21
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
--- 1/2 Max cd




Based on 10 foot mounting height. Maximum calculated value = 3.2 fc
Type IV - Medium - N/A

REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

Luminous Intensity Polar Plot



REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	582.4	0.0	582.4
	% Fixture	21.5	0.0	21.5
Street Side	Lumens	2126.5	0.0	2126.5
	% Fixture	78.5	0.0	78.5
Total	Lumens	2708.9	0.0	2708.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.2	1.0
10°-20°	65.9	2.4
20°-30°	115.3	4.3
30°-40°	203.0	7.5
40°-50°	306.3	11.3
50°-60°	487.1	18.0
60°-70°	714.3	26.4
70°-80°	669.9	24.7
80°-90°	121.0	4.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	2708.9	100.0
0°-180°	2708.9	100.0



REPORT NUMBER: P560043


CATALOG NUMBER: SDL-PA1-20-740-U-T4W

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	111.7	4.1			
FM	(30°-60°)	729.8	26.9			
FH	(60°-80°)	1185.4	43.8			G1/1800
FVH	(80°-90°)	99.6	3.7			G1/100
BL	(0°-30°)	95.6	3.5	B0/110		
BM	(30°-60°)	266.6	9.8	B1/1000		
BH	(60°-80°)	198.8	7.3	B1/500		G1/500
BVH	(80°-90°)	21.4	0.8			G1/100
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type IV Medium



REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	315	315	315	315	315	315	315	315	315	315	315
2.5°	286	298	304	310	312	314	314	313	313	313	315
5°	291	290	290	290	289	288	287	285	284	282	281
7.5°	267	287	288	289	289	288	290	292	290	287	283
10°	317	316	314	312	309	306	283	259	261	263	244
12.5°	275	294	302	310	311	311	295	278	256	234	225
15°	336	334	330	326	299	271	255	239	239	239	212
17.5°	283	282	300	318	308	298	275	252	218	183	205
20°	347	347	342	337	291	244	247	249	250	250	240
22.5°	291	289	291	292	292	292	250	208	231	253	230
25°	347	348	347	346	304	261	268	275	243	210	232
27.5°	303	302	297	292	293	294	272	249	262	275	252
30°	371	372	369	365	323	281	279	276	267	258	266
32.5°	448	448	417	386	360	333	311	289	298	307	297
35°	489	487	477	466	418	369	339	308	311	313	313
37.5°	562	561	547	533	468	402	363	323	329	334	327
40°	653	653	642	630	547	463	408	353	352	350	342
42.5°	741	744	737	730	633	536	464	392	383	374	366
45°	799	803	809	815	719	623	539	454	437	419	405
47.5°	858	852	860	868	786	704	612	520	492	464	449
50°	913	911	914	917	850	783	688	593	559	524	507
52.5°	985	978	974	970	913	856	766	675	635	594	574
55°	1054	1051	1045	1038	989	940	845	750	708	666	643
57.5°	1125	1123	1122	1121	1078	1035	938	840	792	743	724
60°	1192	1193	1201	1208	1175	1142	1044	946	885	823	804
62.5°	1232	1235	1255	1274	1256	1238	1137	1035	971	906	893
65°	1181	1196	1254	1312	1312	1312	1220	1127	1071	1015	1004
67.5°	1067	1082	1165	1247	1290	1333	1273	1213	1175	1136	1122
70°	973	982	1060	1137	1245	1353	1314	1274	1272	1269	1231
72.5°	894	914	978	1041	1190	1339	1338	1337	1378	1419	1346
75°	715	713	773	833	1001	1168	1262	1355	1473	1590	1478
77.5°	319	341	398	455	606	756	937	1118	1378	1637	1523
80°	91	96	112	127	198	268	458	647	974	1300	1223
82.5°	48	50	60	69	89	108	180	251	532	812	742
85°	23	21	27	32	43	54	83	112	206	300	259
87.5°	5	5	6	6	9	12	18	24	23	21	25
90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	315	315	315	315	315	315	315	315	315	315	315
2.5°	316	317	318	317	316	315	315	314	314	313	311
5°	280	294	308	309	310	310	309	308	306	305	303
7.5°	279	274	269	270	271	272	272	269	268	260	252
10°	224	219	214	217	220	231	237	235	233	219	204
12.5°	216	214	212	197	182	195	204	203	200	187	174
15°	185	186	186	203	220	231	239	237	235	219	203
17.5°	226	215	203	200	197	202	195	184	191	189	187
20°	229	202	174	202	230	237	252	251	248	234	220
22.5°	207	223	238	223	208	198	193	191	190	194	197
25°	254	224	193	230	266	274	278	275	274	256	238
27.5°	228	244	260	272	284	294	324	295	294	277	259
30°	273	290	307	338	369	386	392	390	385	358	331
32.5°	287	321	354	368	381	399	408	407	402	370	337
35°	313	338	363	382	400	417	425	428	422	382	341
37.5°	320	352	384	404	424	437	444	453	446	398	349
40°	334	372	409	429	448	460	472	483	474	416	357
42.5°	357	396	434	457	479	496	510	525	508	433	357
45°	391	427	463	494	524	545	565	586	552	455	357
47.5°	434	469	503	552	601	620	644	664	609	483	357
50°	489	528	567	632	696	714	744	759	685	526	366
52.5°	553	596	638	714	790	820	860	870	762	569	375
55°	620	678	735	819	902	931	988	996	861	622	382
57.5°	705	773	840	922	1003	1044	1133	1136	976	687	397
60°	785	870	954	1032	1110	1174	1277	1278	1084	736	387
62.5°	880	981	1081	1148	1215	1294	1418	1400	1160	742	324
65°	992	1096	1200	1257	1313	1403	1537	1468	1181	708	234
67.5°	1107	1204	1301	1346	1391	1505	1624	1476	1150	657	163
70°	1193	1284	1375	1414	1453	1576	1650	1424	1063	595	127
72.5°	1272	1358	1443	1463	1482	1545	1518	1255	896	501	105
75°	1366	1421	1475	1439	1403	1318	1165	915	656	373	90
77.5°	1409	1396	1382	1259	1136	908	724	529	333	205	77
80°	1146	1094	1041	835	629	430	282	179	122	92	62
82.5°	671	550	429	315	201	141	92	73	57	54	50
85°	217	192	167	132	97	60	35	32	30	33	35
87.5°	29	29	28	21	13	7	4	3	3	4	4
90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	315	315	315	315	315	315	315	315	315	315	315
2.5°	311	310	309	308	307	305	297	289	286	282	279
5°	293	283	276	269	266	262	263	264	265	265	265
7.5°	254	256	257	257	260	262	264	265	261	257	252
10°	202	199	203	206	211	215	228	241	253	265	270
12.5°	184	194	186	178	194	209	227	245	256	266	257
15°	187	170	172	173	193	212	201	190	221	251	260
17.5°	184	181	192	202	183	164	191	217	231	245	241
20°	199	177	177	177	194	211	198	185	200	215	240
22.5°	206	214	198	181	192	203	203	202	219	235	231
25°	208	178	192	205	198	190	199	207	212	217	239
27.5°	238	217	201	184	197	210	207	204	208	212	217
30°	282	233	215	196	189	181	190	198	213	228	248
32.5°	295	252	223	193	192	190	193	195	212	228	256
35°	293	244	216	187	181	175	180	184	209	234	261
37.5°	291	232	203	174	170	165	170	175	194	213	238
40°	288	218	190	161	156	151	156	160	175	190	210
42.5°	281	204	176	147	143	138	142	146	159	172	184
45°	273	188	161	134	130	126	129	131	143	154	160
47.5°	264	171	146	121	117	113	116	118	127	136	138
50°	262	157	134	110	107	103	105	107	114	120	120
52.5°	258	140	121	101	99	96	97	98	103	108	107
55°	255	128	111	94	92	89	90	91	96	100	99
57.5°	258	118	103	87	85	83	85	87	92	97	97
60°	248	108	94	80	79	77	82	86	94	101	103
62.5°	212	99	87	75	76	76	85	93	104	114	116
65°	163	92	82	71	76	81	93	105	115	125	122
67.5°	125	87	79	70	81	91	102	113	118	122	117
70°	105	82	76	69	80	91	102	113	115	117	112
72.5°	92	78	72	66	75	84	97	109	111	112	107
75°	82	73	66	59	68	76	89	102	104	105	101
77.5°	72	67	59	51	60	69	81	93	96	99	94
80°	60	57	51	45	55	64	75	86	89	92	87
82.5°	48	46	42	38	48	58	69	79	82	84	78
85°	35	35	33	31	41	50	57	64	63	62	58
87.5°	5	5	7	9	12	14	18	21	22	22	17
90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P560043

CATALOG NUMBER: SDL-PA1-20-740-U-T4W

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°
0°	315	315	315	315
2.5°	276	276	275	277
5°	265	266	266	267
7.5°	247	242	236	237
10°	275	276	277	277
12.5°	247	243	238	239
15°	268	271	274	275
17.5°	236	235	234	233
20°	264	269	274	274
22.5°	227	227	227	228
25°	261	267	272	272
27.5°	221	235	249	260
30°	267	270	273	274
32.5°	283	298	312	315
35°	287	294	300	303
37.5°	263	269	275	279
40°	229	234	239	242
42.5°	195	196	197	202
45°	166	161	156	155
47.5°	139	132	125	124
50°	119	113	107	107
52.5°	105	101	97	97
55°	98	96	93	93
57.5°	97	96	95	95
60°	104	105	105	105
62.5°	117	118	118	118
65°	118	116	114	114
67.5°	112	109	106	104
70°	106	104	101	98
72.5°	101	99	96	93
75°	96	93	89	87
77.5°	89	87	84	82
80°	81	79	76	72
82.5°	72	73	73	63
85°	53	50	46	38
87.5°	11	10	8	7
90°	0	0	0	0



Report Generated By 670245982



--- HS --- SS



u



(END OF REPORT)