

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581501

Luminaire Tested: **HCC4W07D010MW-HM40525930-41WDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010MW-HM40525930-41WDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 802.6 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581501

CATALOG NUMBER: HCC4W07D010MW-HM40525930-41WDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P581501

CATALOG NUMBER: HCC4W07D010MW-HM40525930-41WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	104	110	108	105	103		103	101	100			100	98	97			96
2	106	101	96	92	104	99	95	91		96	92	89			93	90	87			90
3	100	93	87	82	98	91	86	82		88	84	80			86	82	79			84
4	94	85	79	74	92	84	78	74		82	77	73			80	75	72			78
5	88	79	72	67	86	78	72	67		76	70	66			74	69	66			72
6	83	73	66	61	81	72	66	61		70	65	61			69	64	60			68
7	78	68	61	56	77	67	60	56		65	60	55			64	59	55			63
8	74	63	56	51	72	62	56	51		61	55	51			60	55	51			59
9	69	59	52	47	68	58	52	47		57	51	47			56	51	47			55
10	66	55	48	44	65	54	48	44		53	48	44			53	47	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67470
5°	67988
10°	68824
15°	70565
20°	71091
25°	69042
30°	63309
35°	52100
40°	37968
45°	24648
50°	13893
55°	6602
60°	2615
65°	1634
70°	1118
75°	715
80°	355
85°	708



TEST NUMBER: P581501

CATALOG NUMBER: HCC4W07D010MW-HM40525930-41WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	6.5
10°-20°	155.8	19.4
20°-30°	231.1	28.8
30°-40°	213.4	26.6
40°-50°	111.4	13.9
50°-60°	30.6	3.8
60°-70°	5.9	0.7
70°-80°	1.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.3	54.7
0°-40°	652.7	81.3
0°-60°	794.7	99.0
0°-90°	802.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	802.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	547	
5°	549	52
15°	553	156
25°	507	231
35°	346	213
45°	141	111
55°	31	31
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P581501

CATALOG NUMBER: HCC4W07D010MW-HM40525930-41WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	547.0
2.5°	545.6
5°	549.1
7.5°	550.6
10°	549.5
12.5°	550.6
15°	552.6
17.5°	550.6
20°	541.6
22.5°	526.9
25°	507.3
27.5°	480.7
30°	444.5
32.5°	398.8
35°	346.0
37.5°	290.6
40°	235.8
42.5°	185.5
45°	141.3
47.5°	103.6
50°	72.4
52.5°	48.3
55°	30.7
57.5°	18.1
60°	10.6
62.5°	7.5
65°	5.6
67.5°	4.0
70°	3.1
72.5°	2.0
75°	1.5
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)