

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581505

Luminaire Tested: **HCC4S07D010SL-HM40525930-41WDC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S07D010SL-HM40525930-41WDC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 852.8 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.11
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581505

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDC

Luminous Intensity Polar Plot





TEST NUMBER: P581505

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92						
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85						
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77						
4	95	86	80	76	93	85	79	75	83	78	74	81	77	73	79	75	72	71						
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65						
6	84	74	67	63	82	73	67	62	72	66	62	70	65	62	69	65	61	60						
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55						
8	75	64	57	53	73	63	57	53	62	57	53	61	56	52	60	56	52	51						
9	70	60	53	49	69	59	53	49	58	53	49	57	52	48	56	52	48	47						
10	67	56	50	45	66	55	49	45	55	49	45	54	49	45	53	48	45	43						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68889
5°	69907
10°	72093
15°	77039
20°	81632
25°	80733
30°	72467
35°	56391
40°	38209
45°	23863
50°	10324
55°	3441
60°	863
65°	584
70°	361
75°	238
80°	355
85°	0



TEST NUMBER: P581505

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	6.4
10°-20°	171.3	20.1
20°-30°	268.3	31.5
30°-40°	231.6	27.2
40°-50°	106.5	12.5
50°-60°	18.1	2.1
60°-70°	2.0	0.2
70°-80°	0.7	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.8	57.9
0°-40°	725.4	85.1
0°-60°	850.0	99.7
0°-90°	852.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	565	54
15°	603	171
25°	593	268
35°	374	232
45°	137	107
55°	16	18
65°	2	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P581505

CATALOG NUMBER: HCC4S07D010SL-HM40525930-41WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	558.5
2.5°	558.5
5°	564.6
7.5°	570.1
10°	575.6
12.5°	587.2
15°	603.3
17.5°	616.8
20°	621.9
22.5°	614.3
25°	593.2
27.5°	559.0
30°	508.8
32.5°	445.4
35°	374.5
37.5°	303.2
40°	237.3
42.5°	181.5
45°	136.8
47.5°	96.0
50°	53.8
52.5°	29.7
55°	16.0
57.5°	8.1
60°	3.5
62.5°	2.5
65°	2.0
67.5°	1.5
70°	1.0
72.5°	1.0
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)