

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581508

Luminaire Tested: **HCC4W07D010BZ-HM40525930-41PSMDW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P581508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W07D010BZ-HM40525930-41PSMDW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.6 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 0.99
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581508

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P581508

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94
2	103	97	92	87	101	95	90	86	92	88	84		89	85	82		86
3	96	88	81	76	94	86	80	75	84	78	74		81	77	73		79
4	90	80	73	68	88	79	72	67	77	71	66		74	69	65		72
5	84	74	66	61	82	72	66	60	71	64	60		69	63	59		67
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	63	55	50	73	62	55	50	61	54	50		59	54	49		58
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54
9	66	54	47	42	65	54	47	42	53	47	42		52	46	42		51
10	62	51	44	39	61	50	44	39	49	43	39		49	43	39		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61722
5°	61339
10°	60032
15°	58715
20°	55983
25°	51826
30°	45078
35°	34046
40°	24684
45°	19275
50°	16483
55°	14258
60°	13149
65°	12025
70°	11252
75°	10294
80°	9589
85°	9199



TEST NUMBER: P581508

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	6.6
10°-20°	128.8	18.1
20°-30°	173.1	24.4
30°-40°	142.4	20.0
40°-50°	87.4	12.3
50°-60°	60.5	8.5
60°-70°	41.3	5.8
70°-80°	23.0	3.2
80°-90°	7.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.7	49.1
0°-40°	491.1	69.1
0°-60°	639.0	89.9
0°-90°	710.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	500	
5°	495	47
15°	460	129
25°	381	173
35°	226	142
45°	110	87
55°	66	61
65°	41	41
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P581508

CATALOG NUMBER: HCC4W07D010BZ-HM40525930-41PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	500.4
2.5°	496.9
5°	495.4
7.5°	489.8
10°	479.3
12.5°	469.8
15°	459.8
17.5°	445.2
20°	426.5
22.5°	404.4
25°	380.8
27.5°	352.2
30°	316.5
32.5°	272.8
35°	226.1
37.5°	185.8
40°	153.3
42.5°	128.1
45°	110.5
47.5°	97.0
50°	85.9
52.5°	75.9
55°	66.3
57.5°	59.3
60°	53.3
62.5°	47.2
65°	41.2
67.5°	36.2
70°	31.2
72.5°	26.2
75°	21.6
77.5°	17.1
80°	13.5
82.5°	10.0
85°	6.5
87.5°	3.5
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)