

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582076

Luminaire Tested: **HCC6W25D010MW-HM60525930-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W25D010MW-HM60525930-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2330.6 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582076

CATALOG NUMBER: HCC6W25D010MW-HM60525930-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582076

CATALOG NUMBER: HCC6W25D010MW-HM60525930-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106		111	109	107	105		105	103	101			101	100	98			98
2	108	103	99	96		106	102	98	95		98	96	93			96	93	91			93
3	103	97	92	88		101	95	91	87		93	89	86			90	87	84			88
4	98	90	85	81		96	89	84	80		87	83	79			85	81	79			83
5	93	85	79	75		91	84	79	75		82	77	74			80	76	73			79
6	88	80	74	70		87	79	73	69		77	73	69			76	72	68			75
7	84	75	69	65		83	74	69	65		73	68	64			72	67	64			71
8	80	71	65	61		79	70	65	61		69	64	60			68	64	60			67
9	76	67	61	57		75	66	61	57		65	60	57			65	60	57			64
10	73	63	58	54		72	63	57	54		62	57	54			61	57	53			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139188
5°	139461
10°	141759
15°	142793
20°	130532
25°	102568
30°	75081
35°	53257
40°	25190
45°	9606
50°	4307
55°	1176
60°	504
65°	389
70°	240
75°	318
80°	0
85°	0



TEST NUMBER: P582076

CATALOG NUMBER: HCC6W25D010MW-HM60525930-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.4	10.4
10°-20°	695.4	29.8
20°-30°	773.5	33.2
30°-40°	483.2	20.7
40°-50°	114.8	4.9
50°-60°	16.4	0.7
60°-70°	3.4	0.1
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1711.4	73.4
0°-40°	2194.6	94.2
0°-60°	2325.8	99.8
0°-90°	2330.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2330.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2539	
5°	2534	242
15°	2516	695
25°	1696	774
35°	796	483
45°	124	115
55°	12	16
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P582076

CATALOG NUMBER: HCC6W25D010MW-HM60525930-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2539.0
2.5°	2528.2
5°	2534.3
7.5°	2543.6
10°	2546.6
12.5°	2545.1
15°	2516.0
17.5°	2418.0
20°	2237.5
22.5°	1983.4
25°	1695.7
27.5°	1420.3
30°	1186.1
32.5°	991.7
35°	795.8
37.5°	584.6
40°	352.0
42.5°	203.5
45°	123.9
47.5°	79.6
50°	50.5
52.5°	29.1
55°	12.3
57.5°	6.1
60°	4.6
62.5°	4.6
65°	3.0
67.5°	3.0
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)