

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582086

Luminaire Tested: **HCC6S25D010MW-HM60525930-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S25D010MW-HM60525930-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2407.1 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582086

CATALOG NUMBER: HCC6S25D010MW-HM60525930-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P582086

CATALOG NUMBER: HCC6S25D010MW-HM60525930-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	102		103	100	98		99	97	95		95	94	93
2	106	100	95	91		103	98	94	90		95	91	88		92	89	86		89	86	84
3	99	92	86	81		97	90	85	81		88	83	79		85	81	78		83	80	77
4	93	85	78	73		91	83	78	73		81	76	72		79	75	71		77	73	70
5	88	78	72	67		86	77	71	66		75	70	66		74	69	65		72	68	65
6	83	73	66	61		81	72	66	61		70	65	60		69	64	60		67	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	57	52		73	63	56	52		61	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	51	48		56	51	48
10	66	56	49	45		65	55	49	45		54	48	45		53	48	44		53	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89779
5°	90540
10°	93808
15°	101890
20°	105983
25°	101371
30°	87488
35°	62995
40°	35488
45°	18390
50°	10968
55°	7904
60°	6721
65°	7731
70°	9825
75°	10379
80°	10165
85°	9624



TEST NUMBER: P582086

CATALOG NUMBER: HCC6S25D010MW-HM60525930-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.3	6.6
10°-20°	506.4	21.0
20°-30°	756.8	31.4
30°-40°	578.5	24.0
40°-50°	202.1	8.4
50°-60°	77.0	3.2
60°-70°	60.4	2.5
70°-80°	51.1	2.1
80°-90°	16.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1421.5	59.1
0°-40°	2000.1	83.1
0°-60°	2279.2	94.7
0°-90°	2407.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2407.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1638	
5°	1645	158
15°	1795	506
25°	1676	757
35°	941	579
45°	237	202
55°	83	77
65°	60	60
75°	49	51
85°	15	16
90°	0	



TEST NUMBER: P582086

CATALOG NUMBER: HCC6S25D010MW-HM60525930-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1637.7
2.5°	1633.0
5°	1645.3
7.5°	1662.2
10°	1685.2
12.5°	1737.2
15°	1795.3
17.5°	1830.5
20°	1816.7
22.5°	1761.7
25°	1675.9
27.5°	1553.5
30°	1382.1
32.5°	1176.9
35°	941.3
37.5°	697.9
40°	495.9
42.5°	347.5
45°	237.2
47.5°	166.8
50°	128.6
52.5°	101.0
55°	82.7
57.5°	67.3
60°	61.3
62.5°	59.6
65°	59.6
67.5°	62.8
70°	61.3
72.5°	56.6
75°	49.0
77.5°	41.3
80°	32.2
82.5°	22.9
85°	15.3
87.5°	6.1
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)