

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582174

Luminaire Tested: **HCC6S30D010BZ-HM63040835-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582174  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S30D010BZ-HM63040835-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3370.9 lumens  
Efficiency: N/A  
Efficacy: 120.4 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582174  
CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582174

CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132012
5°	132896
10°	134433
15°	137186
20°	137959
25°	133665
30°	121259
35°	98591
40°	65444
45°	36422
50°	20426
55°	11326
60°	6249
65°	4735
70°	3302
75°	2415
80°	1421
85°	1447



TEST NUMBER: P582174  
 CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.5	6.8
10°-20°	681.6	20.2
20°-30°	1004.6	29.8
30°-40°	898.5	26.7
40°-50°	389.8	11.6
50°-60°	114.5	3.4
60°-70°	36.6	1.1
70°-80°	12.9	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1916.7	56.9
0°-40°	2815.2	83.5
0°-60°	3319.5	98.5
0°-90°	3370.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3370.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2408	
5°	2415	231
15°	2417	682
25°	2210	1005
35°	1473	899
45°	470	390
55°	118	115
65°	36	37
75°	11	13
85°	2	2
90°	0	



TEST NUMBER: P582174  
CATALOG NUMBER: HCC6S30D010BZ-HM63040835-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2408.1
2.5°	2401.3
5°	2415.0
7.5°	2419.5
10°	2415.0
12.5°	2415.0
15°	2417.2
17.5°	2403.6
20°	2364.8
22.5°	2298.7
25°	2209.8
27.5°	2084.3
30°	1915.6
32.5°	1714.9
35°	1473.2
37.5°	1197.2
40°	914.5
42.5°	668.2
45°	469.8
47.5°	335.2
50°	239.5
52.5°	171.0
55°	118.5
57.5°	79.8
60°	57.0
62.5°	45.7
65°	36.5
67.5°	27.3
70°	20.6
72.5°	15.9
75°	11.4
77.5°	9.2
80°	4.5
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)