

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582780

Luminaire Tested: **HCC6W50D010MW-HM64560927-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MW-HM64560927-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3654.3 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582780
CATALOG NUMBER: HCC6W50D010MW-HM64560927-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582780
 CATALOG NUMBER: HCC6W50D010MW-HM64560927-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91		89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81		79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72		70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65		63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59		57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54		52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49		48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46		44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42		41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39		38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138404
5°	137750
10°	134711
15°	131550
20°	126606
25°	119735
30°	108808
35°	88077
40°	59397
45°	40818
50°	33440
55°	29265
60°	27684
65°	26138
70°	24539
75°	23320
80°	21215
85°	18555



TEST NUMBER: P582780
 CATALOG NUMBER: HCC6W50D010MW-HM64560927-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.3	6.5
10°-20°	650.9	17.8
20°-30°	904.4	24.7
30°-40°	805.2	22.0
40°-50°	427.4	11.7
50°-60°	279.5	7.6
60°-70°	200.3	5.5
70°-80°	116.2	3.2
80°-90°	34.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1791.6	49.0
0°-40°	2596.8	71.1
0°-60°	3303.8	90.4
0°-90°	3654.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3654.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2525	
5°	2503	236
15°	2318	651
25°	1980	904
35°	1316	805
45°	526	427
55°	306	280
65°	202	200
75°	110	116
85°	30	34
90°	0	



TEST NUMBER: P582780
CATALOG NUMBER: HCC6W50D010MW-HM64560927-61NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2524.7
2.5°	2511.4
5°	2503.2
7.5°	2473.7
10°	2420.0
12.5°	2371.7
15°	2317.9
17.5°	2250.9
20°	2170.2
22.5°	2078.9
25°	1979.5
27.5°	1864.1
30°	1718.9
32.5°	1544.4
35°	1316.1
37.5°	1063.6
40°	830.0
42.5°	644.6
45°	526.5
47.5°	448.5
50°	392.1
52.5°	346.5
55°	306.2
57.5°	276.7
60°	252.5
62.5°	228.3
65°	201.5
67.5°	177.3
70°	153.1
72.5°	131.6
75°	110.1
77.5°	88.7
80°	67.2
82.5°	48.3
85°	29.5
87.5°	13.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)