

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584681

Luminaire Tested: **HCC8W45D010BZ-HM82555835-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8W45D010BZ-HM82555835-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4615.5 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584681

CATALOG NUMBER: HCC8W45D010BZ-HM82555835-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584681

CATALOG NUMBER: HCC8W45D010BZ-HM82555835-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107		112	109	107	106		105	104	102			102	100	99			98
2	109	105	101	98		107	103	100	97		100	97	95			97	95	93			94
3	104	99	94	91		102	97	93	90		95	91	88			92	90	87			90
4	100	93	88	84		98	92	87	84		90	86	83			88	85	82			86
5	96	88	83	79		94	87	82	79		86	81	78			84	80	77			82
6	92	84	78	75		90	83	78	74		81	77	74			80	76	73			79
7	88	80	74	70		87	79	74	70		78	73	70			77	73	70			76
8	84	76	71	67		83	75	70	67		74	70	66			73	69	66			72
9	81	72	67	64		80	72	67	63		71	66	63			70	66	63			69
10	78	69	64	61		77	69	64	61		68	63	60			67	63	60			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367267
5°	311151
10°	225753
15°	169533
20°	133765
25°	107897
30°	79958
35°	32393
40°	13666
45°	7326
50°	3291
55°	1656
60°	1055
65°	752
70°	613
75°	405
80°	604
85°	1203



TEST NUMBER: P584681

CATALOG NUMBER: HCC8W45D010BZ-HM82555835-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	863.1	18.7
10°-20°	1491.5	32.3
20°-30°	1442.1	31.2
30°-40°	633.4	13.7
40°-50°	136.9	3.0
50°-60°	30.8	0.7
60°-70°	10.5	0.2
70°-80°	4.0	0.1
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3796.7	82.3
0°-40°	4430.1	96.0
0°-60°	4597.7	99.6
0°-90°	4615.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4615.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11910	
5°	10052	863
15°	5310	1492
25°	3171	1442
35°	860	633
45°	168	137
55°	31	31
65°	10	11
75°	3	4
85°	3	3
90°	0	



TEST NUMBER: P584681

CATALOG NUMBER: HCC8W45D010BZ-HM82555835-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11910.2
1°	11821.0
2°	11577.6
3°	11138.8
4°	10614.2
5°	10052.0
6°	9438.3
7°	8821.2
8°	8241.8
9°	7703.6
10°	7209.8
11°	6743.6
12°	6325.4
13°	5944.8
14°	5608.8
15°	5310.5
17.5°	4642.0
20°	4076.3
22.5°	3579.2
25°	3171.2
27.5°	2756.4
30°	2245.6
32.5°	1525.6
35°	860.5
37.5°	507.4
40°	339.5
42.5°	240.0
45°	168.0
47.5°	109.7
50°	68.6
52.5°	41.2
55°	30.8
57.5°	24.0
60°	17.1
62.5°	13.7
65°	10.3
67.5°	6.8
70°	6.8
72.5°	3.4
75°	3.4
77.5°	3.4
80°	3.4
82.5°	3.4

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P584681

CATALOG NUMBER: HCC8W45D010BZ-HM82555835-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



85°	3.4
87.5°	3.4

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)