

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584773

Luminaire Tested: **HCC8S45D010MW-HM82555940-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MW-HM82555940-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5590.7 lumens
Efficiency: N/A
Efficacy: 127.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584773

CATALOG NUMBER: HCC8S45D010MW-HM82555940-81WDH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584773

CATALOG NUMBER: HCC8S45D010MW-HM82555940-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	72		79	74	71		77
5	87	78	71	66	86	77	70	66	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	64	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	58	51	46	67	57	51	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	43	53	47	43		52	46	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127992
5°	125107
10°	121271
15°	118818
20°	117751
25°	115992
30°	109875
35°	91291
40°	53763
45°	35559
50°	27992
55°	20596
60°	14302
65°	8719
70°	3805
75°	1680
80°	1243
85°	0



TEST NUMBER: P584773

CATALOG NUMBER: HCC8S45D010MW-HM82555940-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.6	6.8
10°-20°	1052.2	18.8
20°-30°	1559.0	27.9
30°-40°	1440.6	25.8
40°-50°	664.2	11.9
50°-60°	349.4	6.2
60°-70°	123.5	2.2
70°-80°	19.4	0.3
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2991.8	53.5
0°-40°	4432.4	79.3
0°-60°	5445.9	97.4
0°-90°	5590.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5590.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4151	
5°	4042	381
15°	3722	1052
25°	3409	1559
35°	2425	1441
45°	815	664
55°	383	349
65°	120	123
75°	14	19
85°	0	2
90°	0	



TEST NUMBER: P584773

CATALOG NUMBER: HCC8S45D010MW-HM82555940-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4150.7
2.5°	4115.5
5°	4041.7
7.5°	3960.9
10°	3873.0
12.5°	3788.7
15°	3721.9
17.5°	3662.1
20°	3588.3
22.5°	3507.5
25°	3409.1
27.5°	3275.6
30°	3085.8
32.5°	2815.2
35°	2425.1
37.5°	1862.7
40°	1335.6
42.5°	1001.6
45°	815.4
47.5°	692.4
50°	583.5
52.5°	478.0
55°	383.1
57.5°	302.3
60°	231.9
62.5°	175.7
65°	119.5
67.5°	70.3
70°	42.2
72.5°	24.6
75°	14.1
77.5°	10.6
80°	7.0
82.5°	3.5
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)