

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584768

Luminaire Tested: **HCC8S45D010BZ-HM82555940-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010BZ-HM82555940-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5225.2 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584768

CATALOG NUMBER: HCC8S45D010BZ-HM82555940-81PSMDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584768

CATALOG NUMBER: HCC8S45D010BZ-HM82555940-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	108	105	102		109	106	103	100		101	99	97		98	96	94		94	93	91
2	104	98	92	88		102	96	91	87		92	88	85		89	86	83		86	84	81
3	97	89	83	77		95	87	82	77		85	80	76		82	78	74		80	76	73
4	91	81	74	69		89	80	74	69		78	72	68		76	71	67		74	70	66
5	85	75	68	62		83	74	67	62		72	66	61		70	65	61		68	64	60
6	80	69	62	57		78	68	61	56		67	61	56		65	60	56		64	59	55
7	75	64	57	52		74	63	57	52		62	56	51		61	55	51		60	55	51
8	71	60	53	48		70	59	52	48		58	52	47		57	51	47		56	51	47
9	67	56	49	44		66	55	49	44		54	48	44		53	48	44		52	47	44
10	64	52	46	41		62	52	45	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122651
5°	121055
10°	116622
15°	112060
20°	108960
25°	105682
30°	94835
35°	62169
40°	34369
45°	28656
50°	26126
55°	24935
60°	23183
65°	21021
70°	19006
75°	17157
80°	15609
85°	14895



TEST NUMBER: P584768

CATALOG NUMBER: HCC8S45D010BZ-HM82555940-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.4	7.0
10°-20°	990.3	19.0
20°-30°	1409.4	27.0
30°-40°	1043.1	20.0
40°-50°	516.7	9.9
50°-60°	412.4	7.9
60°-70°	286.2	5.5
70°-80°	154.3	3.0
80°-90°	45.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2767.1	53.0
0°-40°	3810.3	72.9
0°-60°	4739.3	90.7
0°-90°	5225.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5225.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3978	
5°	3911	367
15°	3510	990
25°	3106	1409
35°	1652	1043
45°	657	517
55°	464	412
65°	288	286
75°	144	154
85°	42	45
90°	0	



TEST NUMBER: P584768

CATALOG NUMBER: HCC8S45D010BZ-HM82555940-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3977.5
2.5°	3959.9
5°	3910.8
7.5°	3833.5
10°	3724.5
12.5°	3612.0
15°	3510.2
17.5°	3411.8
20°	3320.4
22.5°	3229.0
25°	3106.1
27.5°	2926.9
30°	2663.4
32.5°	2259.3
35°	1651.5
37.5°	1127.8
40°	853.8
42.5°	730.9
45°	657.1
47.5°	597.3
50°	544.6
52.5°	499.0
55°	463.8
57.5°	421.7
60°	375.9
62.5°	330.3
65°	288.1
67.5°	246.0
70°	210.8
72.5°	175.7
75°	144.0
77.5°	116.0
80°	87.9
82.5°	63.2
85°	42.1
87.5°	17.6
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)