

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191906

Luminaire Tested: **LDA4A35935D010TE LAR15SP 4LA1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25628)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A35935D010TE LAR15SP 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 15° Spot
Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3087.1 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.35
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191906

CATALOG NUMBER: LDA4A35935D010TE LAR15SP 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P1191906

CATALOG NUMBER: LDA4A35935D010TE LAR15SP 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	115	113	112	110	113	111	110	108		107	106	105			104	103	102			100
2	112	109	106	104	110	107	105	102		104	102	100			101	100	98			98
3	109	105	101	99	107	103	100	98		101	98	96			99	97	95			97
4	106	101	97	95	104	100	97	94		98	95	93			96	94	92			95
5	103	98	94	91	102	97	94	91		95	92	90			94	91	89			93
6	101	95	91	89	99	94	91	88		93	90	88			92	89	87			91
7	98	92	89	86	97	92	88	86		91	88	85			90	87	85			89
8	96	90	86	84	95	90	86	84		89	86	83			88	85	83			87
9	94	88	84	82	93	87	84	82		87	84	81			86	83	81			85
10	92	86	82	80	91	85	82	80		85	82	80			84	81	79			84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2478581
5°	2067790
10°	1124205
15°	597174
20°	340178
25°	66592
30°	13773
35°	4081
40°	1546
45°	680
50°	384
55°	430
60°	493
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P1191906
 CATALOG NUMBER: LDA4A35935D010TE LAR15SP 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1324.0	42.9
10°-20°	1348.8	43.7
20°-30°	386.9	12.5
30°-40°	22.0	0.7
40°-50°	3.3	0.1
50°-60°	1.8	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3059.8	99.1
0°-40°	3081.7	99.8
0°-60°	3086.9	100.0
0°-90°	3087.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3087.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20095	
5°	16700	###
15°	4676	1349
25°	489	387
35°	27	22
45°	4	3
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1191906
CATALOG NUMBER: LDA4A35935D010TE LAR15SP 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	20094.6
2.5°	19262.9
5°	16700.4
7.5°	12511.2
10°	8975.8
12.5°	6473.2
15°	4676.5
17.5°	3384.6
20°	2591.6
22.5°	1634.3
25°	489.3
27.5°	187.6
30°	96.7
32.5°	50.3
35°	27.1
37.5°	15.5
40°	9.6
42.5°	5.9
45°	3.9
47.5°	2.0
50°	2.0
52.5°	2.0
55°	2.0
57.5°	2.0
60°	2.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)