

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1191930

Luminaire Tested: **LDA4A35940D010TE LAR25NF 4LA1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1191930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25629)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA4A35940D010TE LAR25NF 4LA1
Description: PORTFOLIO 4" Adjustable Reflector, Self-flange Trim Ring, 25° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3597.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.45
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1191930

CATALOG NUMBER: LDA4A35940D010TE LAR25NF 4LA1

Luminous Intensity Polar Plot





TEST NUMBER: P1191930

CATALOG NUMBER: LDA4A35940D010TE LAR25NF 4LA1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97		
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	94		
3	108	104	100	97	106	102	99	97	100	97	95	98	96	94	96	94	92	91		
4	105	100	96	93	103	99	95	93	97	94	92	95	93	91	93	91	90	88		
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86		
6	99	93	89	86	98	93	89	86	91	88	85	90	87	85	89	86	84	83		
7	97	90	86	83	95	90	86	83	89	85	83	88	85	83	87	84	82	81		
8	94	88	84	81	93	87	83	81	86	83	81	85	82	80	85	82	80	79		
9	92	85	81	79	91	85	81	79	84	81	78	83	80	78	83	80	78	77		
10	89	83	79	76	89	83	79	76	82	79	76	81	78	76	81	78	76	75		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2004280
5°	1756911
10°	1310437
15°	833592
20°	442076
25°	99759
30°	23956
35°	6881
40°	2335
45°	733
50°	403
55°	452
60°	518
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P1191930
CATALOG NUMBER: LDA4A35940D010TE LAR25NF 4LA1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1241.3	34.5
10°-20°	1783.4	49.6
20°-30°	527.4	14.7
30°-40°	37.4	1.0
40°-50°	4.3	0.1
50°-60°	1.9	0.1
60°-70°	1.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3552.1	98.8
0°-40°	3589.5	99.8
0°-60°	3595.7	100.0
0°-90°	3597.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3597.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16249	
5°	14190	###
15°	6528	1783
25°	733	527
35°	46	37
45°	4	4
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1191930

CATALOG NUMBER: LDA4A35940D010TE LAR25NF 4LA1

CANDELA DISTRIBUTION (FULL):

	0°
0°	16249.3
2.5°	15396.0
5°	14189.6
7.5°	12622.0
10°	10462.7
12.5°	8431.9
15°	6527.9
17.5°	4756.8
20°	3367.9
22.5°	2132.3
25°	733.0
27.5°	319.8
30°	168.2
32.5°	85.1
35°	45.7
37.5°	27.0
40°	14.5
42.5°	8.3
45°	4.2
47.5°	2.1
50°	2.1
52.5°	2.1
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	0.0
67.5°	2.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)